

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035654

Luminaire Tested: S125DIW-B850D770UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035654
REPORT IS A COMBINATION OF REPORTS P1004339 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D770UB30-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6560.0 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035654

CATALOG NUMBER: S125DIW-B850D770UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035654

CATALOG NUMBER: S125DIW-B850D770UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49
2	89	82	76	71	82	76	71	66	65	61	57	55	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30
5	68	57	49	43	63	53	46	40	46	40	35	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	18
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8456	8456	8456
5°	8456	8259	8275
10°	8386	8070	8045
15°	8276	7843	7774
20°	8127	7581	7462
25°	7968	7295	7128
30°	7774	6996	6777
35°	7569	6683	6384
40°	7356	6353	6034
45°	7126	6030	5662
50°	6872	5665	5229
55°	6621	5262	4831
60°	6322	4837	4367
65°	5964	4345	3888
70°	5601	3780	3334
75°	4988	3112	2696
80°	4253	2325	1983
85°	3282	1376	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7126 cd/sqm

TEST NUMBER: P1035654

CATALOG NUMBER: S125DIW-B850D770UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	1.9
10°-20°	351.8	5.4
20°-30°	519.3	7.9
30°-40°	605.9	9.2
40°-50°	608.5	9.3
50°-60°	534.2	8.1
60°-70°	397.9	6.1
70°-80°	227.2	3.5
80°-90°	67.1	1.0
90°-100°	34.5	0.5
100°-110°	229.5	3.5
110°-120°	413.3	6.3
120°-130°	530.4	8.1
130°-140°	570.5	8.7
140°-150°	535.5	8.2
150°-160°	433.1	6.6
160°-170°	280.1	4.3
170°-180°	96.6	1.5
0°-30°	995.6	15.2
0°-40°	1601.5	24.4
0°-60°	2744.3	41.8
0°-90°	3436.5	52.4
90°-120°	677.3	10.3
90°-150°	2313.7	35.3
90°-180°	3124.0	47.6
0°-180°	6560.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1320	1320	1320	1320	1320	
5°	1318	1316	1305	1314	1314	125
15°	1256	1253	1241	1247	1247	354
25°	1140	1135	1121	1124	1120	525
35°	985	980	966	961	952	616
45°	806	802	789	777	774	621
55°	614	611	596	587	580	548
65°	414	412	401	392	387	411
75°	220	218	213	210	206	235
85°	57	58	58	57	55	63
90°	1	7	12	16	18	6
95°	43	41	12	16	16	53
105°	222	225	225	225	224	235
115°	416	420	421	418	413	412
125°	592	597	597	594	592	529
135°	738	742	741	739	735	569
145°	856	857	857	858	853	535
155°	942	938	939	942	935	434
165°	994	990	990	995	989	281
175°	1017	1012	1013	1019	1012	97
180°	1017	1017	1017	1017	1017	

TEST NUMBER: P1035654

CATALOG NUMBER: S125DIW-B850D770UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.8	1319.8	1319.8	1319.8	1319.8
2.5°	1323.9	1320.8	1310.4	1320.8	1319.8
5°	1317.7	1315.6	1305.1	1314.5	1313.5
7.5°	1308.3	1306.2	1294.7	1304.1	1303.1
10°	1294.7	1292.6	1281.1	1289.5	1288.4
12.5°	1278.0	1273.8	1263.4	1269.6	1269.6
15°	1256.1	1252.9	1241.4	1246.7	1246.7
17.5°	1233.1	1227.9	1216.4	1222.7	1217.4
20°	1202.8	1200.7	1187.2	1194.5	1189.2
22.5°	1172.5	1168.4	1155.8	1160.0	1156.9
25°	1140.2	1134.9	1121.4	1123.5	1120.3
27.5°	1102.6	1099.4	1085.9	1086.9	1083.8
30°	1066.0	1062.9	1047.2	1045.2	1042.0
32.5°	1026.4	1021.1	1007.6	1003.4	997.1
35°	984.6	980.4	965.8	960.6	952.2
37.5°	941.8	936.6	923.0	915.7	910.5
40°	897.9	892.7	878.1	868.7	865.6
42.5°	851.0	846.8	832.2	823.8	818.6
45°	806.1	801.9	789.3	776.8	773.7
47.5°	757.0	758.0	742.4	729.8	722.5
50°	710.0	706.9	694.3	680.8	673.5
52.5°	662.0	659.9	646.3	634.8	626.5
55°	613.9	610.8	596.2	586.8	579.5
57.5°	562.8	561.7	549.2	536.7	533.5
60°	514.7	510.6	499.1	488.6	481.3
62.5°	464.6	461.5	452.1	440.6	435.4
65°	414.5	412.4	400.9	391.5	387.4
67.5°	365.4	361.3	352.9	344.6	342.5
70°	319.5	314.3	304.9	298.6	294.4
72.5°	269.4	266.2	261.0	253.7	249.5
75°	220.3	218.2	213.0	209.9	205.7
77.5°	174.4	173.3	170.2	168.1	165.0
80°	131.6	131.6	129.5	128.4	126.3
82.5°	94.0	91.9	91.9	89.8	89.8
85°	57.4	58.5	58.5	57.4	55.3
87.5°	28.2	28.2	27.1	27.1	25.1
90°	0.8	6.8	12.1	15.8	18.1
92.5°	14.3	7.5	12.1	15.8	16.6
95°	43.0	40.7	12.1	15.8	15.8
97.5°	80.7	85.2	13.6	15.1	15.8
100°	125.9	128.1	131.2	18.8	15.8
102.5°	171.9	174.9	176.4	177.9	114.6
105°	221.6	224.6	224.6	224.6	223.9
107.5°	272.9	272.9	274.4	275.1	272.1
110°	322.6	322.6	324.1	321.9	322.6



TEST NUMBER: P1035654

CATALOG NUMBER: S125DIW-B850D770UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	369.3	371.6	372.4	369.3	367.8
115°	416.1	419.8	420.6	417.6	413.1
117.5°	465.1	465.1	468.1	463.6	462.1
120°	510.3	509.5	511.8	510.3	506.5
122.5°	550.2	554.0	554.8	553.3	548.7
125°	591.7	597.0	597.0	594.0	591.7
127.5°	631.7	635.4	634.7	633.2	627.1
130°	667.8	671.6	672.4	670.1	666.3
132.5°	704.0	708.5	706.3	706.3	702.5
135°	737.9	742.5	741.0	739.4	734.9
137.5°	769.6	774.1	772.6	772.6	768.8
140°	800.5	802.0	801.3	802.8	798.2
142.5°	828.4	829.1	830.7	830.7	826.1
145°	855.5	857.0	857.0	857.8	853.3
147.5°	879.6	879.6	880.4	881.2	875.9
150°	902.3	900.8	902.3	903.8	897.7
152.5°	924.1	920.3	921.9	923.4	918.1
155°	942.2	937.7	939.2	941.5	935.4
157.5°	956.5	954.3	954.3	956.5	950.5
160°	971.6	967.1	967.8	970.9	964.8
162.5°	983.7	979.1	979.9	984.4	977.6
165°	994.2	989.7	990.4	995.0	988.9
167.5°	1002.5	998.0	998.7	1004.0	997.2
170°	1009.3	1004.0	1004.8	1010.8	1004.0
172.5°	1013.8	1008.5	1010.0	1015.3	1008.5
175°	1016.8	1012.3	1013.1	1019.1	1012.3
177.5°	1019.1	1014.6	1015.3	1020.6	1014.6
180°	1016.8	1016.8	1016.8	1016.8	1016.8

(END OF REPORT)