

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035091

Luminaire Tested: S125DIW-B1270D1050UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035091
REPORT IS A COMBINATION OF REPORTS P1003056 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1050UB27-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8752.0 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035091

CATALOG NUMBER: S125DIW-B1270D1050UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035091

CATALOG NUMBER: S125DIW-B1270D1050UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	60	54	50	51	47	44	44	41	38
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33
5	69	58	49	43	65	54	47	41	47	41	37	41	36	33	35	32	29
6	64	52	43	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	29	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12544	12544	12544
5°	12545	12253	12277
10°	12442	11972	11935
15°	12278	11637	11532
20°	12057	11247	11070
25°	11820	10822	10576
30°	11534	10379	10055
35°	11228	9915	9471
40°	10913	9424	8952
45°	10571	8946	8400
50°	10195	8404	7757
55°	9823	7806	7166
60°	9380	7176	6479
65°	8848	6446	5768
70°	8309	5607	4947
75°	7400	4617	4000
80°	6308	3449	2942
85°	4871	2039	1622

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10571 cd/sqm

TEST NUMBER: P1035091

CATALOG NUMBER: S125DIW-B1270D1050UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.1
10°-20°	521.9	6.0
20°-30°	770.4	8.8
30°-40°	898.9	10.3
40°-50°	902.8	10.3
50°-60°	792.5	9.1
60°-70°	590.3	6.7
70°-80°	337.1	3.9
80°-90°	99.4	1.1
90°-100°	87.1	1.0
100°-110°	258.6	3.0
110°-120°	438.6	5.0
120°-130°	577.5	6.6
130°-140°	647.1	7.4
140°-150°	634.3	7.2
150°-160°	532.8	6.1
160°-170°	354.1	4.0
170°-180°	123.9	1.4
0°-30°	1477.1	16.9
0°-40°	2376.0	27.1
0°-60°	4071.3	46.5
0°-90°	5098.0	58.2
90°-120°	784.3	9.0
90°-150°	2643.2	30.2
90°-180°	3654.0	41.8
0°-180°	8752.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1958	1958	1958	1958	1958	
5°	1955	1952	1936	1950	1949	186
15°	1863	1859	1842	1850	1850	525
25°	1692	1684	1664	1667	1662	778
35°	1461	1454	1433	1425	1413	914
45°	1196	1190	1171	1152	1148	921
55°	911	906	884	870	860	813
65°	615	612	595	581	575	610
75°	327	324	316	311	305	348
85°	85	87	87	85	82	93
90°	1	9	16	21	24	10
95°	66	68	78	86	88	69
105°	232	237	244	250	253	248
115°	439	443	445	444	443	434
125°	641	647	648	646	645	574
135°	833	840	841	841	836	642
145°	1010	1014	1017	1017	1014	631
155°	1155	1155	1156	1160	1155	532
165°	1256	1254	1255	1259	1253	354
175°	1306	1302	1302	1308	1301	124
180°	1309	1309	1309	1309	1309	

TEST NUMBER: P1035091

CATALOG NUMBER: S125DIW-B1270D1050UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1957.9	1957.9	1957.9	1957.9	1957.9
2.5°	1964.1	1959.5	1944.0	1959.5	1957.9
5°	1954.8	1951.7	1936.2	1950.2	1948.6
7.5°	1940.9	1937.8	1920.8	1934.7	1933.1
10°	1920.8	1917.7	1900.6	1913.0	1911.5
12.5°	1896.0	1889.8	1874.3	1883.6	1883.6
15°	1863.4	1858.8	1841.8	1849.5	1849.5
17.5°	1829.4	1821.6	1804.6	1813.9	1806.1
20°	1784.4	1781.3	1761.2	1772.0	1764.3
22.5°	1739.5	1733.3	1714.7	1720.9	1716.3
25°	1691.5	1683.8	1663.6	1666.7	1662.1
27.5°	1635.7	1631.1	1611.0	1612.5	1607.9
30°	1581.5	1576.9	1553.6	1550.5	1545.9
32.5°	1522.7	1514.9	1494.8	1488.6	1479.3
35°	1460.7	1454.5	1432.8	1425.1	1412.7
37.5°	1397.2	1389.4	1369.3	1358.5	1350.7
40°	1332.1	1324.4	1302.7	1288.8	1284.1
42.5°	1262.4	1256.2	1234.5	1222.2	1214.4
45°	1195.8	1189.6	1171.0	1152.5	1147.8
47.5°	1123.0	1124.6	1101.3	1082.7	1071.9
50°	1053.3	1048.7	1030.1	1009.9	999.1
52.5°	982.1	979.0	958.8	941.8	929.4
55°	910.8	906.2	884.5	870.5	859.7
57.5°	834.9	833.4	814.8	796.2	791.5
60°	763.7	757.5	740.4	724.9	714.1
62.5°	689.3	684.7	670.7	653.7	645.9
65°	614.9	611.9	594.8	580.9	574.7
67.5°	542.1	536.0	523.6	511.2	508.1
70°	474.0	466.2	452.3	443.0	436.8
72.5°	399.6	395.0	387.2	376.4	370.2
75°	326.8	323.7	316.0	311.3	305.2
77.5°	258.7	257.1	252.5	249.4	244.7
80°	195.2	195.2	192.1	190.5	187.4
82.5°	139.4	136.3	136.3	133.2	133.2
85°	85.2	86.7	86.7	85.2	82.1
87.5°	41.8	41.8	40.3	40.3	37.2
90°	1.0	9.2	16.3	21.4	24.5
92.5°	30.6	35.7	44.8	52.0	54.0
95°	66.2	68.3	78.5	85.6	87.6
97.5°	101.9	102.9	117.2	123.3	124.3
100°	142.6	142.6	155.9	165.1	167.1
102.5°	186.5	191.5	196.6	206.8	209.9
105°	232.3	237.4	243.5	249.6	252.7
107.5°	282.2	287.3	292.4	295.5	295.5
110°	334.2	339.3	342.3	345.4	344.4



TEST NUMBER: P1035091

CATALOG NUMBER: S125DIW-B1270D1050UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	387.2	389.2	393.3	394.3	392.3
115°	439.1	443.2	445.2	444.2	443.2
117.5°	492.1	493.1	495.2	496.2	492.1
120°	541.0	546.1	547.1	547.1	543.1
122.5°	594.0	595.0	598.1	597.1	594.0
125°	640.9	647.0	648.0	646.0	644.9
127.5°	692.8	695.9	696.9	695.9	693.8
130°	738.7	743.8	745.8	744.8	742.7
132.5°	784.5	793.7	792.7	791.7	788.6
135°	833.4	839.5	840.6	840.6	836.5
137.5°	879.3	885.4	887.4	888.4	883.3
140°	923.1	928.2	931.2	933.3	928.2
142.5°	966.9	971.0	975.0	976.1	971.0
145°	1009.7	1013.8	1016.8	1016.8	1013.8
147.5°	1049.4	1052.5	1054.5	1057.6	1049.4
150°	1089.2	1088.1	1092.2	1092.2	1090.2
152.5°	1121.8	1123.8	1124.8	1127.9	1123.8
155°	1155.4	1155.4	1156.4	1160.5	1155.4
157.5°	1186.0	1183.9	1184.9	1189.0	1181.9
160°	1212.4	1209.4	1210.4	1214.5	1209.4
162.5°	1235.9	1233.8	1233.8	1238.9	1232.8
165°	1256.3	1254.2	1255.2	1259.3	1253.2
167.5°	1274.6	1270.5	1270.5	1276.6	1270.5
170°	1288.9	1284.8	1284.8	1290.9	1283.8
172.5°	1299.0	1295.0	1295.0	1301.1	1295.0
175°	1306.2	1302.1	1302.1	1308.2	1301.1
177.5°	1311.3	1307.2	1306.2	1312.3	1305.2
180°	1309.2	1309.2	1309.2	1309.2	1309.2

(END OF REPORT)