

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035099

Luminaire Tested: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035099
REPORT IS A COMBINATION OF REPORTS P1003089 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8920.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	55
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46
3	83	74	67	61	78	69	63	58	61	56	51	52	49	45	45	42	40
4	76	66	58	52	71	62	54	49	54	48	44	47	43	39	40	37	34
5	70	59	50	44	65	55	48	42	48	43	38	42	38	34	36	33	30
6	65	53	44	39	60	49	42	37	44	38	33	38	33	30	33	29	26
7	60	48	40	34	56	45	38	32	40	34	29	35	30	26	30	26	24
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21
9	52	39	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11845	11845	11845	11845
5°	11854	13437	11865	10195
10°	11782	15316	11762	8751
15°	11695	16607	11623	7907
20°	11548	18198	11442	7218
25°	11417	20852	11209	6810
30°	11228	21998	11034	6441
35°	10930	17634	10701	6144
40°	10465	12188	10311	5831
45°	9878	9073	9767	5571
50°	9206	7470	9054	5361
55°	8481	6371	8413	5181
60°	7769	5454	7633	5041
65°	7000	4710	6888	4835
70°	6190	3910	6107	4479
75°	5330	3024	5260	3888
80°	4211	2046	4059	2859
85°	2693	1023	2601	1458

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 18093 cd/sqm

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.9	2.0
10°-20°	530.0	5.9
20°-30°	860.9	9.7
30°-40°	1052.2	11.8
40°-50°	954.4	10.7
50°-60°	760.2	8.5
60°-70°	529.4	5.9
70°-80°	282.1	3.2
80°-90°	72.0	0.8
90°-100°	88.2	1.0
100°-110°	262.0	2.9
110°-120°	444.3	5.0
120°-130°	584.9	6.6
130°-140°	655.4	7.3
140°-150°	642.4	7.2
150°-160°	539.6	6.0
160°-170°	358.7	4.0
170°-180°	125.5	1.4
0°-30°	1568.8	17.6
0°-40°	2621.0	29.4
0°-60°	4335.5	48.6
0°-90°	5219.1	58.5
90°-120°	794.4	8.9
90°-150°	2677.1	30.0
90°-180°	3701.0	41.5
0°-180°	8920.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1849	1849	1849	1849	1849	
5°	1847	2133	1849	1618	1847	175
15°	1775	2663	1764	1268	1775	501
25°	1634	3277	1604	1070	1634	752
35°	1422	2630	1392	916	1422	888
45°	1117	1240	1105	761	1117	861
55°	786	764	780	622	786	703
65°	486	469	479	482	486	483
75°	235	231	232	297	235	250
85°	47	52	46	74	47	56
90°	1	25	1	25	1	8
95°	67	89	67	89	67	70
105°	235	256	235	256	235	251
115°	445	449	445	449	445	440
125°	649	653	649	653	649	582
135°	844	847	844	847	844	651
145°	1023	1027	1023	1027	1023	639
155°	1170	1170	1170	1170	1170	539
165°	1272	1269	1272	1269	1272	359
175°	1323	1318	1323	1318	1323	126
180°	1326	1326	1326	1326	1326	

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1851.9	1862.9	1875.5	1884.9	1900.6	1905.3	1913.1	1917.8	1922.5	1927.3	1930.4
5°	1847.2	1873.9	1897.4	1914.7	1944.5	1955.5	1969.6	1986.9	2007.3	2024.6	2035.5
7.5°	1834.7	1877.0	1908.4	1942.9	1983.8	2010.4	2024.6	2060.7	2093.6	2118.7	2151.7
10°	1819.0	1869.2	1917.8	1969.6	2027.7	2057.5	2085.8	2136.0	2181.5	2222.3	2255.3
12.5°	1801.7	1862.9	1921.0	1988.5	2066.9	2103.0	2121.9	2208.2	2264.7	2286.7	2351.0
15°	1775.0	1847.2	1930.4	2013.6	2079.5	2121.9	2173.7	2242.7	2299.2	2347.9	2399.7
17.5°	1749.9	1828.4	1913.1	2005.7	2101.5	2156.4	2195.6	2256.8	2318.0	2380.8	2429.5
20°	1709.1	1811.1	1897.4	1996.3	2109.3	2148.5	2189.3	2261.5	2327.5	2394.9	2456.2
22.5°	1676.1	1773.5	1891.2	1985.3	2081.1	2120.3	2170.5	2245.8	2324.3	2401.2	2490.7
25°	1633.8	1742.1	1844.1	1944.5	2043.4	2085.8	2131.3	2228.6	2310.2	2409.1	2507.9
27.5°	1588.3	1699.7	1801.7	1892.7	1985.3	2043.4	2092.0	2194.1	2302.3	2410.6	2539.3
30°	1539.6	1644.8	1742.1	1831.5	1933.5	1993.2	2041.8	2161.1	2281.9	2420.1	2573.9
32.5°	1487.8	1586.7	1669.9	1760.9	1869.2	1924.1	1990.0	2120.3	2263.1	2427.9	2620.9
35°	1421.9	1516.1	1589.8	1682.4	1790.7	1861.3	1930.4	2076.4	2242.7	2426.3	2647.6
37.5°	1356.0	1429.7	1500.4	1599.2	1724.8	1789.1	1861.3	2021.4	2211.3	2421.6	2658.6
40°	1277.5	1349.7	1410.9	1511.4	1643.2	1717.0	1792.3	1960.2	2175.2	2404.4	2619.4
42.5°	1199.0	1260.2	1327.7	1432.9	1560.0	1638.5	1718.5	1905.3	2128.1	2354.1	2511.1
45°	1117.4	1164.5	1238.3	1334.0	1469.0	1544.3	1635.3	1837.8	2062.2	2263.1	2341.6
47.5°	1032.7	1079.8	1148.8	1241.4	1374.8	1464.3	1550.6	1753.0	1979.0	2134.4	2134.4
50°	951.1	988.7	1056.2	1148.8	1283.8	1365.4	1453.3	1668.3	1850.4	1964.9	1862.9
52.5°	863.2	905.6	962.1	1059.4	1192.8	1266.5	1362.3	1545.9	1718.5	1765.6	1608.7
55°	786.3	820.8	874.2	966.8	1090.8	1167.7	1249.3	1425.0	1571.0	1567.9	1399.9
57.5°	706.2	734.5	791.0	875.7	990.3	1059.4	1141.0	1293.2	1412.5	1370.1	1211.6
60°	632.5	652.9	707.8	776.9	886.7	951.1	1029.5	1153.5	1244.6	1184.9	1024.8
62.5°	555.6	579.1	623.1	690.5	787.9	839.6	897.7	1023.3	1081.3	1028.0	864.8
65°	486.5	505.4	544.6	601.1	689.0	736.1	786.3	889.9	944.8	867.9	732.9
67.5°	417.5	439.4	467.7	517.9	587.0	630.9	674.9	764.3	789.4	720.4	607.4
70°	353.1	372.0	398.6	434.7	492.8	532.0	565.0	638.8	656.0	591.7	502.2
72.5°	290.3	302.9	324.9	354.7	408.1	430.0	464.6	514.8	536.7	478.7	414.3
75°	235.4	244.8	259.0	280.9	317.0	340.6	368.8	415.9	414.3	373.5	328.0
77.5°	182.1	183.6	199.3	219.7	241.7	262.1	276.2	309.2	312.3	287.2	249.5
80°	130.3	135.0	141.2	156.9	175.8	183.6	200.9	221.3	224.4	205.6	180.5
82.5°	83.2	86.3	91.0	100.4	113.0	122.4	131.8	139.7	147.5	136.5	116.1
85°	47.1	48.7	53.4	56.5	62.8	67.5	75.3	83.2	81.6	73.8	67.5
87.5°	23.5	23.5	23.5	26.7	29.8	29.8	33.0	34.5	36.1	33.0	29.8
90°	1.0	2.8	4.7	6.5	8.4	9.3	10.1	11.7	13.3	14.9	16.5
92.5°	31.0	32.1	33.3	34.4	35.5	36.1	37.1	39.2	41.3	43.3	45.4
95°	67.1	67.5	68.0	68.4	68.9	69.1	70.3	72.6	74.9	77.2	79.5
97.5°	103.2	103.4	103.6	103.9	104.1	104.2	105.8	109.0	112.3	115.5	118.7
100°	144.5	144.5	144.5	144.5	144.5	144.5	146.0	149.0	151.9	154.9	157.9
102.5°	188.8	190.0	191.1	192.3	193.4	194.0	194.6	195.7	196.9	198.0	199.2
105°	235.3	236.4	237.6	238.7	239.8	240.4	241.1	242.5	243.8	245.2	246.6
107.5°	285.9	287.0	288.2	289.3	290.4	291.0	291.6	292.7	293.9	295.0	296.2
110°	338.5	339.6	340.8	341.9	343.0	343.6	343.9	344.6	345.3	346.0	346.7

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	392.1	392.6	393.0	393.5	394.0	394.2	394.7	395.6	396.5	397.4	398.3
115°	444.8	445.7	446.6	447.5	448.4	448.9	449.1	449.6	450.1	450.5	451.0
117.5°	498.4	498.6	498.9	499.1	499.4	499.5	499.7	500.2	500.6	501.1	501.5
120°	548.0	549.1	550.3	551.4	552.5	553.1	553.2	553.5	553.7	554.0	554.2
122.5°	601.6	601.8	602.1	602.3	602.6	602.7	603.0	603.7	604.4	605.1	605.8
125°	649.1	650.5	651.9	653.2	654.6	655.3	655.4	655.6	655.9	656.1	656.3
127.5°	701.7	702.4	703.1	703.8	704.5	704.8	704.9	705.2	705.4	705.7	705.9
130°	748.2	749.3	750.5	751.6	752.7	753.3	753.5	754.0	754.5	754.9	755.4
132.5°	794.6	796.7	798.7	800.8	802.9	803.9	803.8	803.6	803.3	803.1	802.9
135°	844.1	845.5	846.9	848.2	849.6	850.3	850.4	850.7	850.9	851.2	851.4
137.5°	890.6	892.0	893.4	894.7	896.1	896.8	897.0	897.5	897.9	898.4	898.8
140°	935.0	936.1	937.3	938.4	939.5	940.1	940.4	941.1	941.8	942.5	943.2
142.5°	979.3	980.2	981.2	982.1	983.0	983.5	984.0	984.9	985.8	986.7	987.6
145°	1022.7	1023.6	1024.5	1025.4	1026.3	1026.8	1027.1	1027.8	1028.5	1029.2	1029.9
147.5°	1062.9	1063.6	1064.3	1065.0	1065.7	1066.0	1066.2	1066.7	1067.2	1067.6	1068.1
150°	1103.2	1103.0	1102.7	1102.5	1102.2	1102.1	1102.6	1103.5	1104.4	1105.4	1106.3
152.5°	1136.2	1136.6	1137.1	1137.5	1138.0	1138.2	1138.3	1138.6	1138.8	1139.1	1139.3
155°	1170.2	1170.2	1170.2	1170.2	1170.2	1170.2	1170.3	1170.6	1170.8	1171.1	1171.3
157.5°	1201.2	1200.7	1200.3	1199.8	1199.3	1199.1	1199.2	1199.5	1199.7	1200.0	1200.2
160°	1228.0	1227.3	1226.6	1225.9	1225.2	1224.9	1225.0	1225.3	1225.5	1225.8	1226.0
162.5°	1251.8	1251.3	1250.9	1250.4	1249.9	1249.7	1249.7	1249.7	1249.7	1249.7	1249.7
165°	1272.4	1271.9	1271.5	1271.0	1270.5	1270.3	1270.4	1270.7	1270.9	1271.2	1271.4
167.5°	1291.0	1290.1	1289.1	1288.2	1287.3	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8
170°	1305.4	1304.5	1303.6	1302.7	1301.8	1301.3	1301.3	1301.3	1301.3	1301.3	1301.3
172.5°	1315.7	1314.8	1313.9	1313.0	1312.1	1311.6	1311.6	1311.6	1311.6	1311.6	1311.6
175°	1323.0	1322.1	1321.1	1320.2	1319.3	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8
177.5°	1328.1	1327.2	1326.3	1325.4	1324.5	1324.0	1323.9	1323.7	1323.4	1323.2	1323.0
180°	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1933.5	1944.5	1953.9	1961.8	1968.1	1977.5	1971.2	1972.8	1975.9	1982.2	1982.2
5°	2059.1	2076.4	2085.8	2117.2	2125.0	2123.4	2118.7	2143.8	2142.3	2132.8	2131.3
7.5°	2181.5	2211.3	2238.0	2263.1	2271.0	2291.4	2296.1	2307.1	2303.9	2319.6	2311.8
10°	2292.9	2340.0	2365.1	2402.8	2412.2	2421.6	2434.2	2440.5	2454.6	2453.0	2453.0
12.5°	2379.2	2435.7	2468.7	2478.1	2514.2	2525.2	2536.2	2556.6	2551.9	2553.5	2562.9
15°	2446.7	2501.7	2529.9	2573.9	2599.0	2611.5	2630.4	2652.3	2649.2	2663.3	2660.2
17.5°	2497.0	2548.7	2600.5	2666.5	2668.0	2701.0	2744.9	2754.3	2774.7	2760.6	2760.6
20°	2537.8	2606.8	2680.6	2765.3	2774.7	2795.1	2848.5	2884.6	2908.1	2900.3	2905.0
22.5°	2581.7	2680.6	2766.9	2851.6	2897.2	2933.3	2985.0	3041.5	3061.9	3074.5	3071.4
25°	2638.2	2741.8	2868.9	2986.6	3033.7	3102.8	3171.8	3226.7	3242.4	3277.0	3245.6
27.5°	2696.3	2842.2	3000.7	3138.9	3198.5	3255.0	3338.2	3379.0	3399.4	3415.1	3404.1
30°	2744.9	2945.8	3118.4	3245.6	3287.9	3320.9	3368.0	3377.4	3369.6	3382.1	3397.8
32.5°	2820.3	3016.4	3162.4	3223.6	3218.9	3217.3	3181.2	3131.0	3120.0	3090.2	3131.0
35°	2861.1	3018.0	3074.5	2992.9	2959.9	2900.3	2785.7	2710.4	2644.5	2630.4	2633.5
37.5°	2837.5	2898.7	2831.2	2616.2	2562.9	2471.8	2319.6	2212.9	2164.2	2126.6	2175.2
40°	2710.4	2642.9	2457.7	2195.6	2118.7	2032.4	1889.6	1831.5	1762.5	1748.3	1812.7
42.5°	2500.1	2294.5	2032.4	1830.0	1749.9	1701.3	1582.0	1527.1	1478.4	1456.4	1492.5
45°	2214.5	1964.9	1701.3	1534.9	1467.4	1409.3	1338.7	1280.7	1249.3	1239.8	1269.7
47.5°	1919.4	1655.7	1445.4	1321.5	1250.8	1206.9	1141.0	1108.0	1082.9	1086.0	1090.8
50°	1636.9	1396.8	1235.1	1111.2	1076.6	1042.1	998.2	969.9	957.3	962.1	958.9
52.5°	1393.7	1199.0	1062.5	966.8	951.1	918.1	882.0	858.5	853.8	855.3	860.0
55°	1180.2	1028.0	919.7	850.6	833.4	809.8	787.9	772.2	759.6	764.3	762.7
57.5°	1018.6	885.2	802.0	745.5	732.9	718.8	698.4	690.5	685.8	676.4	684.3
60°	875.7	767.4	695.3	660.7	649.7	640.3	618.4	608.9	605.8	601.1	613.6
62.5°	740.8	663.9	608.9	577.5	566.6	557.1	546.2	538.3	539.9	533.6	539.9
65°	634.0	571.3	532.0	503.8	489.7	483.4	481.8	469.3	467.7	469.3	470.8
67.5°	535.2	481.8	452.0	434.7	423.7	417.5	412.8	404.9	411.2	406.5	409.6
70°	445.7	409.6	378.2	361.0	356.3	357.8	350.0	346.8	348.4	345.3	348.4
72.5°	359.4	329.6	317.0	304.5	298.2	296.6	291.9	287.2	291.9	290.3	290.3
75°	287.2	265.2	251.1	243.3	243.3	240.1	232.3	232.3	232.3	230.7	232.3
77.5°	221.3	202.5	196.2	188.3	188.3	183.6	182.1	182.1	178.9	183.6	180.5
80°	164.8	150.7	141.2	136.5	136.5	135.0	131.8	130.3	131.8	130.3	130.3
82.5°	106.7	100.4	95.7	91.0	89.5	91.0	89.5	86.3	87.9	86.3	89.5
85°	61.2	54.9	54.9	51.8	53.4	50.2	51.8	48.7	47.1	51.8	48.7
87.5°	26.7	25.1	25.1	22.0	22.0	22.0	20.4	22.0	20.4	18.8	20.4
90°	17.7	18.8	20.0	21.1	21.7	22.0	22.7	23.4	24.1	24.8	24.1
92.5°	47.0	48.6	50.2	51.8	52.6	52.8	53.3	53.8	54.2	54.7	54.2
95°	81.1	82.7	84.3	85.9	86.7	86.9	87.4	87.8	88.3	88.7	88.3
97.5°	120.1	121.5	122.8	124.2	124.9	125.0	125.2	125.5	125.7	125.9	125.7
100°	160.0	162.0	164.1	166.2	167.2	167.4	167.9	168.3	168.8	169.2	168.8
102.5°	201.5	203.8	206.1	208.4	209.5	209.8	210.5	211.2	211.9	212.6	211.9
105°	248.0	249.4	250.7	252.1	252.8	253.1	253.8	254.5	255.2	255.9	255.2
107.5°	296.9	297.6	298.3	299.0	299.3	299.3	299.3	299.3	299.3	299.3	299.3
110°	347.4	348.1	348.8	349.5	349.8	349.7	349.5	349.2	349.0	348.8	349.0

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	398.5	398.8	399.0	399.3	399.4	399.2	398.7	398.2	397.8	397.3	397.8
115°	450.8	450.5	450.3	450.0	449.9	449.8	449.6	449.3	449.1	448.9	449.1
117.5°	501.7	502.0	502.2	502.5	502.6	502.1	501.2	500.3	499.3	498.4	499.3
120°	554.2	554.2	554.2	554.2	554.2	553.7	552.8	551.9	550.9	550.0	550.9
122.5°	605.6	605.3	605.1	604.8	604.7	604.4	603.7	603.0	602.3	601.6	602.3
125°	655.9	655.4	655.0	654.5	654.3	654.2	653.9	653.7	653.4	653.2	653.4
127.5°	705.7	705.4	705.2	704.9	704.8	704.6	704.1	703.7	703.2	702.8	703.2
130°	755.2	755.0	754.7	754.5	754.4	754.2	753.7	753.2	752.8	752.3	752.8
132.5°	802.7	802.4	802.2	801.9	801.8	801.5	800.8	800.1	799.4	798.7	799.4
135°	851.4	851.4	851.4	851.4	851.4	850.9	850.0	849.1	848.1	847.2	848.1
137.5°	899.0	899.3	899.5	899.8	899.9	899.3	898.2	897.0	895.9	894.7	895.9
140°	943.7	944.1	944.6	945.1	945.3	944.7	943.6	942.4	941.3	940.1	941.3
142.5°	987.8	988.0	988.3	988.5	988.6	988.0	986.9	985.8	984.6	983.5	984.6
145°	1029.9	1029.9	1029.9	1029.9	1029.9	1029.6	1028.9	1028.2	1027.5	1026.8	1027.5
147.5°	1068.8	1069.5	1070.2	1070.9	1071.2	1070.3	1068.4	1066.6	1064.7	1062.9	1064.7
150°	1106.3	1106.3	1106.3	1106.3	1106.3	1106.1	1105.6	1105.1	1104.7	1104.2	1104.7
152.5°	1140.0	1140.7	1141.4	1142.1	1142.4	1141.9	1141.0	1140.1	1139.1	1138.2	1139.1
155°	1172.2	1173.1	1174.0	1174.9	1175.4	1174.8	1173.7	1172.5	1171.4	1170.2	1171.4
157.5°	1201.1	1202.0	1202.9	1203.8	1204.3	1203.5	1201.9	1200.3	1198.7	1197.1	1198.7
160°	1226.9	1227.8	1228.7	1229.6	1230.1	1229.5	1228.4	1227.2	1226.1	1224.9	1226.1
162.5°	1250.9	1252.0	1253.2	1254.3	1254.9	1254.2	1252.8	1251.5	1250.1	1248.7	1250.1
165°	1272.3	1273.2	1274.1	1275.0	1275.5	1274.8	1273.4	1272.1	1270.7	1269.3	1270.7
167.5°	1288.2	1289.6	1290.9	1292.3	1293.0	1292.3	1290.9	1289.6	1288.2	1286.8	1288.2
170°	1302.7	1304.1	1305.4	1306.8	1307.5	1306.7	1305.1	1303.5	1301.9	1300.3	1301.9
172.5°	1313.0	1314.4	1315.7	1317.1	1317.8	1317.1	1315.7	1314.4	1313.0	1311.6	1313.0
175°	1320.2	1321.6	1322.9	1324.3	1325.0	1324.2	1322.6	1321.0	1319.4	1317.8	1319.4
177.5°	1324.4	1325.8	1327.1	1328.5	1329.2	1328.4	1326.8	1325.1	1323.5	1321.9	1323.5
180°	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1979.0	1968.1	1971.2	1968.1	1960.2	1955.5	1942.9	1927.3	1921.0	1913.1	1908.4
5°	2137.6	2129.7	2128.1	2115.6	2112.4	2093.6	2062.2	2046.5	2027.7	2008.9	1990.0
7.5°	2310.2	2300.8	2269.4	2264.7	2267.8	2244.3	2203.5	2172.1	2132.8	2106.2	2070.1
10°	2453.0	2434.2	2407.5	2409.1	2398.1	2366.7	2325.9	2292.9	2236.4	2201.9	2150.1
12.5°	2539.3	2523.6	2520.5	2504.8	2495.4	2454.6	2405.9	2363.6	2321.2	2274.1	2234.9
15°	2644.5	2624.1	2610.0	2588.0	2581.7	2539.3	2486.0	2437.3	2388.7	2344.7	2261.5
17.5°	2760.6	2738.6	2685.3	2680.6	2642.9	2602.1	2550.3	2478.1	2426.3	2363.6	2302.3
20°	2892.5	2861.1	2792.0	2774.7	2744.9	2677.4	2606.8	2526.8	2443.6	2379.2	2307.1
22.5°	3040.0	2985.0	2934.8	2879.9	2857.9	2774.7	2677.4	2580.1	2479.7	2391.8	2305.5
25°	3231.4	3159.3	3088.6	3033.7	2996.0	2887.7	2757.5	2628.8	2512.7	2398.1	2285.1
27.5°	3382.1	3319.3	3242.4	3170.2	3121.6	2992.9	2843.8	2677.4	2533.1	2393.4	2272.5
30°	3393.1	3374.3	3327.2	3287.9	3234.6	3096.5	2931.7	2743.4	2564.4	2394.9	2247.4
32.5°	3187.5	3225.2	3245.6	3251.9	3240.9	3160.8	3010.2	2803.0	2592.7	2380.8	2225.4
35°	2744.9	2845.4	2969.4	3016.4	3061.9	3104.3	3025.9	2845.4	2602.1	2377.7	2190.9
37.5°	2260.0	2351.0	2556.6	2650.8	2704.1	2872.0	2936.4	2839.1	2620.9	2380.8	2158.0
40°	1823.7	1968.1	2115.6	2242.7	2325.9	2514.2	2713.5	2735.5	2594.3	2351.0	2115.6
42.5°	1534.9	1619.6	1731.1	1848.8	1922.5	2145.4	2415.3	2573.9	2511.1	2302.3	2063.8
45°	1307.3	1370.1	1475.3	1514.5	1608.7	1822.1	2107.7	2336.9	2368.3	2225.4	2004.2
47.5°	1122.1	1175.5	1243.0	1291.6	1367.0	1527.1	1768.7	2021.4	2172.1	2120.3	1921.0
50°	988.7	1032.7	1089.2	1117.4	1166.1	1310.5	1492.5	1743.6	1946.1	1963.4	1812.7
52.5°	877.3	902.4	946.4	977.8	1017.0	1104.9	1269.7	1476.8	1704.4	1798.6	1679.3
55°	780.0	800.4	839.6	860.0	880.4	955.8	1084.5	1272.8	1486.2	1610.2	1542.7
57.5°	692.1	709.4	742.3	761.2	772.2	844.4	943.2	1090.8	1282.2	1432.9	1395.2
60°	619.9	635.6	654.5	668.6	681.1	740.8	809.8	929.1	1100.2	1246.1	1236.7
62.5°	543.0	557.1	577.5	591.7	602.7	640.3	698.4	789.4	935.4	1070.3	1097.0
65°	475.5	486.5	500.6	506.9	521.0	549.3	596.4	678.0	797.3	918.1	936.9
67.5°	414.3	417.5	426.9	441.0	444.1	469.3	511.6	572.8	665.4	764.3	794.1
70°	348.4	353.1	361.0	372.0	378.2	393.9	430.0	470.8	550.9	637.2	659.2
72.5°	290.3	296.6	299.8	306.0	309.2	334.3	350.0	390.8	445.7	517.9	541.5
75°	235.4	241.7	243.3	246.4	249.5	260.5	282.5	307.6	353.1	400.2	431.6
77.5°	186.8	185.2	188.3	193.0	191.5	200.9	215.0	237.0	266.8	306.0	326.4
80°	131.8	131.8	136.5	141.2	139.7	149.1	153.8	169.5	194.6	219.7	227.6
82.5°	87.9	87.9	92.6	92.6	95.7	97.3	103.6	111.4	131.8	144.4	149.1
85°	50.2	50.2	51.8	51.8	51.8	54.9	59.6	62.8	69.1	76.9	80.0
87.5°	20.4	22.0	22.0	22.0	22.0	25.1	25.1	28.2	29.8	33.0	33.0
90°	23.4	22.7	22.0	21.7	21.1	20.0	18.8	17.7	16.5	14.9	13.3
92.5°	53.8	53.3	52.8	52.6	51.8	50.2	48.6	47.0	45.4	43.3	41.3
95°	87.8	87.4	86.9	86.7	85.9	84.3	82.7	81.1	79.5	77.2	74.9
97.5°	125.5	125.2	125.0	124.9	124.2	122.8	121.5	120.1	118.7	115.5	112.3
100°	168.3	167.9	167.4	167.2	166.2	164.1	162.0	160.0	157.9	154.9	151.9
102.5°	211.2	210.5	209.8	209.5	208.4	206.1	203.8	201.5	199.2	198.0	196.9
105°	254.5	253.8	253.1	252.8	252.1	250.7	249.4	248.0	246.6	245.2	243.8
107.5°	299.3	299.3	299.3	299.3	299.0	298.3	297.6	296.9	296.2	295.0	293.9
110°	349.2	349.5	349.7	349.8	349.5	348.8	348.1	347.4	346.7	346.0	345.3

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	398.2	398.7	399.2	399.4	399.3	399.0	398.8	398.5	398.3	397.4	396.5
115°	449.3	449.6	449.8	449.9	450.0	450.3	450.5	450.8	451.0	450.5	450.1
117.5°	500.3	501.2	502.1	502.6	502.5	502.2	502.0	501.7	501.5	501.1	500.6
120°	551.9	552.8	553.7	554.2	554.2	554.2	554.2	554.2	554.2	554.0	553.7
122.5°	603.0	603.7	604.4	604.7	604.8	605.1	605.3	605.6	605.8	605.1	604.4
125°	653.7	653.9	654.2	654.3	654.5	655.0	655.4	655.9	656.3	656.1	655.9
127.5°	703.7	704.1	704.6	704.8	704.9	705.2	705.4	705.7	705.9	705.7	705.4
130°	753.2	753.7	754.2	754.4	754.5	754.7	755.0	755.2	755.4	754.9	754.5
132.5°	800.1	800.8	801.5	801.8	801.9	802.2	802.4	802.7	802.9	803.1	803.3
135°	849.1	850.0	850.9	851.4	851.4	851.4	851.4	851.4	851.4	851.2	850.9
137.5°	897.0	898.2	899.3	899.9	899.8	899.5	899.3	899.0	898.8	898.4	897.9
140°	942.4	943.6	944.7	945.3	945.1	944.6	944.1	943.7	943.2	942.5	941.8
142.5°	985.8	986.9	988.0	988.6	988.5	988.3	988.0	987.8	987.6	986.7	985.8
145°	1028.2	1028.9	1029.6	1029.9	1029.9	1029.9	1029.9	1029.9	1029.9	1029.2	1028.5
147.5°	1066.6	1068.4	1070.3	1071.2	1070.9	1070.2	1069.5	1068.8	1068.1	1067.6	1067.2
150°	1105.1	1105.6	1106.1	1106.3	1106.3	1106.3	1106.3	1106.3	1106.3	1105.4	1104.4
152.5°	1140.1	1141.0	1141.9	1142.4	1142.1	1141.4	1140.7	1140.0	1139.3	1139.1	1138.8
155°	1172.5	1173.7	1174.8	1175.4	1174.9	1174.0	1173.1	1172.2	1171.3	1171.1	1170.8
157.5°	1200.3	1201.9	1203.5	1204.3	1203.8	1202.9	1202.0	1201.1	1200.2	1200.0	1199.7
160°	1227.2	1228.4	1229.5	1230.1	1229.6	1228.7	1227.8	1226.9	1226.0	1225.8	1225.5
162.5°	1251.5	1252.8	1254.2	1254.9	1254.3	1253.2	1252.0	1250.9	1249.7	1249.7	1249.7
165°	1272.1	1273.4	1274.8	1275.5	1275.0	1274.1	1273.2	1272.3	1271.4	1271.2	1270.9
167.5°	1289.6	1290.9	1292.3	1293.0	1292.3	1290.9	1289.6	1288.2	1286.8	1286.8	1286.8
170°	1303.5	1305.1	1306.7	1307.5	1306.8	1305.4	1304.1	1302.7	1301.3	1301.3	1301.3
172.5°	1314.4	1315.7	1317.1	1317.8	1317.1	1315.7	1314.4	1313.0	1311.6	1311.6	1311.6
175°	1321.0	1322.6	1324.2	1325.0	1324.3	1322.9	1321.6	1320.2	1318.8	1318.8	1318.8
177.5°	1325.1	1326.8	1328.4	1329.2	1328.5	1327.1	1325.8	1324.4	1323.0	1323.2	1323.4
180°	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1902.1	1894.3	1884.9	1884.9	1873.9	1869.2	1859.8	1856.6	1848.8	1836.2	1826.8
5°	1969.6	1949.2	1936.7	1925.7	1902.1	1884.9	1867.6	1848.8	1830.0	1808.0	1782.9
7.5°	2035.5	1997.9	1980.6	1961.8	1927.3	1891.2	1856.6	1831.5	1806.4	1771.9	1740.5
10°	2104.6	2057.5	2026.1	2001.0	1947.7	1902.1	1851.9	1815.8	1776.6	1732.6	1691.8
12.5°	2162.7	2101.5	2074.8	2027.7	1966.5	1911.6	1848.8	1793.9	1742.1	1690.3	1640.1
15°	2211.3	2153.3	2087.3	2068.5	1983.8	1905.3	1834.7	1764.0	1699.7	1647.9	1589.8
17.5°	2227.0	2153.3	2120.3	2074.8	1974.3	1892.7	1803.3	1726.4	1665.2	1588.3	1542.7
20°	2231.7	2161.1	2115.6	2073.2	1983.8	1875.5	1787.6	1693.4	1619.6	1542.7	1470.6
22.5°	2219.2	2136.0	2092.0	2051.2	1950.8	1858.2	1756.2	1652.6	1566.3	1495.7	1423.5
25°	2195.6	2098.3	2055.9	2012.0	1916.3	1814.3	1702.8	1604.0	1523.9	1439.2	1368.5
27.5°	2164.2	2052.8	2004.2	1958.6	1864.5	1768.7	1663.6	1561.6	1472.1	1382.7	1316.7
30°	2125.0	1996.3	1952.4	1892.7	1801.7	1710.7	1614.9	1512.9	1412.5	1327.7	1255.5
32.5°	2074.8	1939.8	1881.7	1825.2	1726.4	1643.2	1552.2	1456.4	1359.1	1275.9	1200.6
35°	2029.3	1875.5	1811.1	1754.6	1644.8	1556.9	1481.5	1392.1	1305.8	1219.4	1152.0
37.5°	1968.1	1811.1	1734.2	1676.1	1564.7	1475.3	1404.6	1335.6	1244.6	1161.4	1098.6
40°	1903.7	1731.1	1658.9	1600.8	1484.7	1387.4	1319.9	1258.7	1184.9	1108.0	1042.1
42.5°	1845.6	1654.2	1577.3	1506.6	1388.9	1302.6	1233.6	1186.5	1119.0	1049.9	990.3
45°	1771.9	1572.6	1489.4	1415.6	1302.6	1208.5	1142.5	1104.9	1054.7	987.2	935.4
47.5°	1696.5	1484.7	1398.4	1326.2	1203.7	1120.6	1056.2	1020.1	985.6	932.2	880.4
50°	1597.7	1392.1	1313.6	1230.4	1109.6	1024.8	971.5	935.4	908.7	871.0	827.1
52.5°	1489.4	1296.3	1211.6	1139.4	1020.1	943.2	882.0	861.6	834.9	806.7	769.0
55°	1374.8	1192.8	1111.2	1040.5	930.7	852.2	802.0	780.0	759.6	737.6	712.5
57.5°	1260.2	1084.5	1007.6	944.8	842.8	767.4	726.6	696.8	682.7	670.1	649.7
60°	1117.4	968.3	908.7	852.2	751.8	682.7	643.5	621.5	608.9	602.7	593.2
62.5°	991.9	869.5	803.5	748.6	668.6	607.4	569.7	552.4	541.5	538.3	527.3
65°	858.5	753.3	701.5	654.5	585.4	530.5	499.1	478.7	470.8	469.3	469.3
67.5°	732.9	648.2	596.4	563.4	503.8	455.1	425.3	417.5	412.8	406.5	404.9
70°	615.2	547.7	502.2	474.0	420.6	384.5	361.0	348.4	348.4	343.7	340.6
72.5°	511.6	444.1	414.3	390.8	346.8	315.5	298.2	295.1	284.1	282.5	282.5
75°	400.2	350.0	329.6	309.2	276.2	254.2	240.1	232.3	226.0	226.0	227.6
77.5°	301.3	266.8	248.0	232.3	208.7	194.6	183.6	180.5	174.2	174.2	174.2
80°	213.4	194.6	180.5	167.9	150.7	138.1	131.8	125.6	125.6	124.0	125.6
82.5°	138.1	122.4	114.6	113.0	97.3	92.6	84.7	86.3	81.6	80.0	83.2
85°	80.0	72.2	62.8	59.6	53.4	47.1	43.9	45.5	43.9	42.4	43.9
87.5°	31.4	26.7	25.1	25.1	20.4	18.8	17.3	18.8	15.7	15.7	17.3
90°	11.7	10.1	9.3	8.4	6.5	4.7	2.8	1.0	2.8	4.7	6.5
92.5°	39.2	37.1	36.1	35.5	34.4	33.3	32.1	31.0	32.1	33.3	34.4
95°	72.6	70.3	69.1	68.9	68.4	68.0	67.5	67.1	67.5	68.0	68.4
97.5°	109.0	105.8	104.2	104.1	103.9	103.6	103.4	103.2	103.4	103.6	103.9
100°	149.0	146.0	144.5	144.5	144.5	144.5	144.5	144.5	144.5	144.5	144.5
102.5°	195.7	194.6	194.0	193.4	192.3	191.1	190.0	188.8	190.0	191.1	192.3
105°	242.5	241.1	240.4	239.8	238.7	237.6	236.4	235.3	236.4	237.6	238.7
107.5°	292.7	291.6	291.0	290.4	289.3	288.2	287.0	285.9	287.0	288.2	289.3
110°	344.6	343.9	343.6	343.0	341.9	340.8	339.6	338.5	339.6	340.8	341.9

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	395.6	394.7	394.2	394.0	393.5	393.0	392.6	392.1	392.6	393.0	393.5
115°	449.6	449.1	448.9	448.4	447.5	446.6	445.7	444.8	445.7	446.6	447.5
117.5°	500.2	499.7	499.5	499.4	499.1	498.9	498.6	498.4	498.6	498.9	499.1
120°	553.5	553.2	553.1	552.5	551.4	550.3	549.1	548.0	549.1	550.3	551.4
122.5°	603.7	603.0	602.7	602.6	602.3	602.1	601.8	601.6	601.8	602.1	602.3
125°	655.6	655.4	655.3	654.6	653.2	651.9	650.5	649.1	650.5	651.9	653.2
127.5°	705.2	704.9	704.8	704.5	703.8	703.1	702.4	701.7	702.4	703.1	703.8
130°	754.0	753.5	753.3	752.7	751.6	750.5	749.3	748.2	749.3	750.5	751.6
132.5°	803.6	803.8	803.9	802.9	800.8	798.7	796.7	794.6	796.7	798.7	800.8
135°	850.7	850.4	850.3	849.6	848.2	846.9	845.5	844.1	845.5	846.9	848.2
137.5°	897.5	897.0	896.8	896.1	894.7	893.4	892.0	890.6	892.0	893.4	894.7
140°	941.1	940.4	940.1	939.5	938.4	937.3	936.1	935.0	936.1	937.3	938.4
142.5°	984.9	984.0	983.5	983.0	982.1	981.2	980.2	979.3	980.2	981.2	982.1
145°	1027.8	1027.1	1026.8	1026.3	1025.4	1024.5	1023.6	1022.7	1023.6	1024.5	1025.4
147.5°	1066.7	1066.2	1066.0	1065.7	1065.0	1064.3	1063.6	1062.9	1063.6	1064.3	1065.0
150°	1103.5	1102.6	1102.1	1102.2	1102.5	1102.7	1103.0	1103.2	1103.0	1102.7	1102.5
152.5°	1138.6	1138.3	1138.2	1138.0	1137.5	1137.1	1136.6	1136.2	1136.6	1137.1	1137.5
155°	1170.6	1170.3	1170.2	1170.2	1170.2	1170.2	1170.2	1170.2	1170.2	1170.2	1170.2
157.5°	1199.5	1199.2	1199.1	1199.3	1199.8	1200.3	1200.7	1201.2	1200.7	1200.3	1199.8
160°	1225.3	1225.0	1224.9	1225.2	1225.9	1226.6	1227.3	1228.0	1227.3	1226.6	1225.9
162.5°	1249.7	1249.7	1249.7	1249.9	1250.4	1250.9	1251.3	1251.8	1251.3	1250.9	1250.4
165°	1270.7	1270.4	1270.3	1270.5	1271.0	1271.5	1271.9	1272.4	1271.9	1271.5	1271.0
167.5°	1286.8	1286.8	1286.8	1287.3	1288.2	1289.1	1290.1	1291.0	1290.1	1289.1	1288.2
170°	1301.3	1301.3	1301.3	1301.8	1302.7	1303.6	1304.5	1305.4	1304.5	1303.6	1302.7
172.5°	1311.6	1311.6	1311.6	1312.1	1313.0	1313.9	1314.8	1315.7	1314.8	1313.9	1313.0
175°	1318.8	1318.8	1318.8	1319.3	1320.2	1321.1	1322.1	1323.0	1322.1	1321.1	1320.2
177.5°	1323.7	1323.9	1324.0	1324.5	1325.4	1326.3	1327.2	1328.1	1327.2	1326.3	1325.4
180°	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1823.7	1820.5	1812.7	1808.0	1792.3	1773.5	1767.2	1751.5	1757.8	1746.8	1746.8
5°	1775.0	1760.9	1751.5	1737.4	1707.5	1687.1	1665.2	1654.2	1647.9	1640.1	1633.8
7.5°	1712.2	1701.3	1691.8	1665.2	1632.2	1604.0	1577.3	1566.3	1545.9	1531.8	1525.5
10°	1657.3	1641.6	1619.6	1588.3	1553.7	1517.6	1494.1	1470.6	1454.9	1447.0	1429.7
12.5°	1600.8	1582.0	1558.4	1512.9	1475.3	1453.3	1410.9	1388.9	1381.1	1374.8	1354.4
15°	1542.7	1522.3	1494.1	1451.7	1418.8	1367.0	1341.9	1324.6	1305.8	1304.2	1288.5
17.5°	1491.0	1465.8	1442.3	1390.5	1349.7	1304.2	1290.1	1271.2	1254.0	1235.1	1227.3
20°	1425.0	1401.5	1384.2	1327.7	1282.2	1254.0	1230.4	1214.7	1203.7	1184.9	1181.8
22.5°	1365.4	1340.3	1316.7	1274.4	1235.1	1199.0	1170.8	1153.5	1148.8	1141.0	1126.8
25°	1307.3	1282.2	1254.0	1214.7	1173.9	1148.8	1123.7	1112.7	1103.3	1090.8	1079.8
27.5°	1258.7	1235.1	1208.5	1159.8	1125.3	1106.4	1079.8	1067.2	1054.7	1048.4	1043.7
30°	1200.6	1173.9	1153.5	1115.9	1078.2	1053.1	1034.3	1023.3	1012.3	1006.0	1002.9
32.5°	1144.1	1119.0	1104.9	1064.1	1034.3	1004.4	990.3	982.5	976.2	969.9	963.6
35°	1098.6	1073.5	1051.5	1013.8	984.0	963.6	952.6	940.1	935.4	929.1	929.1
37.5°	1042.1	1023.3	1001.3	965.2	938.5	922.8	913.4	897.7	896.1	893.0	888.3
40°	993.4	974.6	954.2	922.8	899.3	880.4	867.9	860.0	855.3	852.2	849.1
42.5°	941.7	921.3	911.8	875.7	855.3	836.5	830.2	822.4	820.8	814.5	806.7
45°	891.4	874.2	855.3	828.7	811.4	795.7	786.3	780.0	772.2	770.6	765.9
47.5°	847.5	827.1	809.8	784.7	765.9	753.3	745.5	737.6	731.4	726.6	721.9
50°	791.0	775.3	761.2	734.5	718.8	706.2	695.3	689.0	682.7	682.7	682.7
52.5°	736.1	721.9	709.4	690.5	671.7	660.7	648.2	643.5	640.3	635.6	640.3
55°	682.7	668.6	656.0	641.9	619.9	610.5	598.0	593.2	594.8	594.8	599.5
57.5°	626.2	615.2	607.4	590.1	569.7	560.3	552.4	547.7	547.7	554.0	555.6
60°	571.3	560.3	546.2	530.5	517.9	506.9	502.2	503.8	503.8	506.9	514.8
62.5°	510.1	503.8	495.9	474.0	466.1	458.3	452.0	456.7	455.1	463.0	474.0
65°	453.6	447.3	436.3	425.3	415.9	408.1	406.5	408.1	411.2	419.0	431.6
67.5°	390.8	390.8	381.4	372.0	364.1	356.3	357.8	359.4	362.5	372.0	390.8
70°	339.0	332.7	323.3	317.0	310.7	307.6	304.5	310.7	320.2	326.4	340.6
72.5°	282.5	277.8	269.9	263.7	262.1	259.0	257.4	260.5	269.9	280.9	296.6
75°	222.9	224.4	219.7	215.0	215.0	210.3	213.4	213.4	222.9	233.8	246.4
77.5°	172.6	171.1	169.5	166.4	164.8	164.8	164.8	167.9	177.3	183.6	196.2
80°	122.4	124.0	119.3	120.8	119.3	120.8	120.8	127.1	131.8	139.7	149.1
82.5°	81.6	81.6	78.5	80.0	80.0	80.0	81.6	84.7	91.0	97.3	103.6
85°	45.5	47.1	43.9	47.1	47.1	47.1	48.7	50.2	54.9	56.5	62.8
87.5°	17.3	20.4	20.4	17.3	18.8	20.4	22.0	20.4	23.5	26.7	28.2
90°	8.4	9.3	10.1	11.7	13.3	14.9	16.5	17.7	18.8	20.0	21.1
92.5°	35.5	36.1	37.1	39.2	41.3	43.3	45.4	47.0	48.6	50.2	51.8
95°	68.9	69.1	70.3	72.6	74.9	77.2	79.5	81.1	82.7	84.3	85.9
97.5°	104.1	104.2	105.8	109.0	112.3	115.5	118.7	120.1	121.5	122.8	124.2
100°	144.5	144.5	146.0	149.0	151.9	154.9	157.9	160.0	162.0	164.1	166.2
102.5°	193.4	194.0	194.6	195.7	196.9	198.0	199.2	201.5	203.8	206.1	208.4
105°	239.8	240.4	241.1	242.5	243.8	245.2	246.6	248.0	249.4	250.7	252.1
107.5°	290.4	291.0	291.6	292.7	293.9	295.0	296.2	296.9	297.6	298.3	299.0
110°	343.0	343.6	343.9	344.6	345.3	346.0	346.7	347.4	348.1	348.8	349.5

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	394.0	394.2	394.7	395.6	396.5	397.4	398.3	398.5	398.8	399.0	399.3
115°	448.4	448.9	449.1	449.6	450.1	450.5	451.0	450.8	450.5	450.3	450.0
117.5°	499.4	499.5	499.7	500.2	500.6	501.1	501.5	501.7	502.0	502.2	502.5
120°	552.5	553.1	553.2	553.5	553.7	554.0	554.2	554.2	554.2	554.2	554.2
122.5°	602.6	602.7	603.0	603.7	604.4	605.1	605.8	605.6	605.3	605.1	604.8
125°	654.6	655.3	655.4	655.6	655.9	656.1	656.3	655.9	655.4	655.0	654.5
127.5°	704.5	704.8	704.9	705.2	705.4	705.7	705.9	705.7	705.4	705.2	704.9
130°	752.7	753.3	753.5	754.0	754.5	754.9	755.4	755.2	755.0	754.7	754.5
132.5°	802.9	803.9	803.8	803.6	803.3	803.1	802.9	802.7	802.4	802.2	801.9
135°	849.6	850.3	850.4	850.7	850.9	851.2	851.4	851.4	851.4	851.4	851.4
137.5°	896.1	896.8	897.0	897.5	897.9	898.4	898.8	899.0	899.3	899.5	899.8
140°	939.5	940.1	940.4	941.1	941.8	942.5	943.2	943.7	944.1	944.6	945.1
142.5°	983.0	983.5	984.0	984.9	985.8	986.7	987.6	987.8	988.0	988.3	988.5
145°	1026.3	1026.8	1027.1	1027.8	1028.5	1029.2	1029.9	1029.9	1029.9	1029.9	1029.9
147.5°	1065.7	1066.0	1066.2	1066.7	1067.2	1067.6	1068.1	1068.8	1069.5	1070.2	1070.9
150°	1102.2	1102.1	1102.6	1103.5	1104.4	1105.4	1106.3	1106.3	1106.3	1106.3	1106.3
152.5°	1138.0	1138.2	1138.3	1138.6	1138.8	1139.1	1139.3	1140.0	1140.7	1141.4	1142.1
155°	1170.2	1170.2	1170.3	1170.6	1170.8	1171.1	1171.3	1172.2	1173.1	1174.0	1174.9
157.5°	1199.3	1199.1	1199.2	1199.5	1199.7	1200.0	1200.2	1201.1	1202.0	1202.9	1203.8
160°	1225.2	1224.9	1225.0	1225.3	1225.5	1225.8	1226.0	1226.9	1227.8	1228.7	1229.6
162.5°	1249.9	1249.7	1249.7	1249.7	1249.7	1249.7	1249.7	1250.9	1252.0	1253.2	1254.3
165°	1270.5	1270.3	1270.4	1270.7	1270.9	1271.2	1271.4	1272.3	1273.2	1274.1	1275.0
167.5°	1287.3	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1288.2	1289.6	1290.9	1292.3
170°	1301.8	1301.3	1301.3	1301.3	1301.3	1301.3	1301.3	1302.7	1304.1	1305.4	1306.8
172.5°	1312.1	1311.6	1311.6	1311.6	1311.6	1311.6	1311.6	1313.0	1314.4	1315.7	1317.1
175°	1319.3	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1320.2	1321.6	1322.9	1324.3
177.5°	1324.5	1324.0	1323.9	1323.7	1323.4	1323.2	1323.0	1324.4	1325.8	1327.1	1328.5
180°	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1753.0	1742.1	1740.5	1743.6	1737.4	1746.8	1743.6	1746.8	1738.9	1746.8	1742.1
5°	1632.2	1629.1	1622.8	1614.9	1616.5	1618.1	1625.9	1618.1	1624.4	1625.9	1633.8
7.5°	1519.2	1512.9	1517.6	1514.5	1500.4	1497.2	1500.4	1505.1	1514.5	1520.8	1525.5
10°	1428.2	1425.0	1418.8	1414.1	1406.2	1401.5	1407.8	1401.5	1414.1	1425.0	1425.0
12.5°	1359.1	1346.6	1338.7	1337.2	1319.9	1323.0	1329.3	1334.0	1348.1	1354.4	1354.4
15°	1286.9	1277.5	1274.4	1268.1	1261.8	1268.1	1265.0	1269.7	1275.9	1282.2	1285.4
17.5°	1224.2	1222.6	1224.2	1208.5	1213.2	1205.3	1206.9	1214.7	1210.0	1214.7	1224.2
20°	1167.7	1170.8	1166.1	1159.8	1159.8	1150.4	1161.4	1158.2	1159.8	1169.2	1183.3
22.5°	1125.3	1123.7	1119.0	1114.3	1108.0	1109.6	1111.2	1108.0	1120.6	1128.4	1130.0
25°	1079.8	1076.6	1075.1	1070.3	1064.1	1070.3	1068.8	1070.3	1073.5	1086.0	1076.6
27.5°	1037.4	1031.1	1034.3	1029.5	1028.0	1029.5	1029.5	1031.1	1034.3	1035.8	1037.4
30°	1001.3	995.0	993.4	990.3	988.7	990.3	993.4	990.3	1002.9	1001.3	1001.3
32.5°	962.1	957.3	954.2	954.2	952.6	951.1	952.6	954.2	963.6	957.3	963.6
35°	924.4	921.3	921.3	918.1	916.5	916.5	916.5	922.8	919.7	924.4	924.4
37.5°	888.3	888.3	886.7	883.6	882.0	883.6	882.0	885.2	883.6	885.2	886.7
40°	850.6	847.5	845.9	845.9	841.2	836.5	841.2	841.2	842.8	847.5	849.1
42.5°	805.1	806.7	806.7	800.4	800.4	800.4	802.0	803.5	803.5	806.7	806.7
45°	765.9	762.7	762.7	762.7	759.6	761.2	764.3	764.3	764.3	764.3	761.2
47.5°	721.9	721.9	723.5	723.5	728.2	726.6	726.6	725.1	721.9	721.9	723.5
50°	681.1	685.8	687.4	687.4	689.0	690.5	690.5	687.4	685.8	681.1	681.1
52.5°	641.9	645.0	648.2	652.9	656.0	654.5	654.5	651.3	645.0	643.5	641.9
55°	599.5	604.2	610.5	615.2	619.9	621.5	621.5	615.2	608.9	601.1	601.1
57.5°	560.3	565.0	576.0	580.7	587.0	587.0	583.8	579.1	569.7	563.4	558.7
60°	521.0	528.9	536.7	546.2	554.0	555.6	550.9	544.6	533.6	525.8	519.5
62.5°	478.7	486.5	502.2	511.6	517.9	517.9	517.9	510.1	495.9	485.0	475.5
65°	437.9	445.7	459.8	472.4	477.1	481.8	477.1	469.3	458.3	445.7	436.3
67.5°	395.5	404.9	419.0	428.5	434.7	439.4	436.3	430.0	415.9	398.6	392.4
70°	348.4	353.1	373.5	382.9	392.4	395.5	392.4	382.9	368.8	350.0	343.7
72.5°	304.5	309.2	328.0	335.9	343.7	346.8	342.1	335.9	323.3	306.0	298.2
75°	254.2	262.1	271.5	284.1	293.5	296.6	291.9	287.2	271.5	260.5	254.2
77.5°	200.9	208.7	221.3	232.3	241.7	240.1	233.8	235.4	218.2	205.6	200.9
80°	152.2	158.5	167.9	177.3	182.1	182.1	180.5	174.2	167.9	158.5	150.7
82.5°	105.2	113.0	120.8	127.1	127.1	128.7	125.6	124.0	117.7	109.9	108.3
85°	62.8	64.3	70.6	70.6	76.9	73.8	72.2	76.9	70.6	65.9	64.3
87.5°	28.2	26.7	28.2	28.2	26.7	29.8	29.8	28.2	29.8	28.2	28.2
90°	21.7	22.0	22.7	23.4	24.1	24.8	24.1	23.4	22.7	22.0	21.7
92.5°	52.6	52.8	53.3	53.8	54.2	54.7	54.2	53.8	53.3	52.8	52.6
95°	86.7	86.9	87.4	87.8	88.3	88.7	88.3	87.8	87.4	86.9	86.7
97.5°	124.9	125.0	125.2	125.5	125.7	125.9	125.7	125.5	125.2	125.0	124.9
100°	167.2	167.4	167.9	168.3	168.8	169.2	168.8	168.3	167.9	167.4	167.2
102.5°	209.5	209.8	210.5	211.2	211.9	212.6	211.9	211.2	210.5	209.8	209.5
105°	252.8	253.1	253.8	254.5	255.2	255.9	255.2	254.5	253.8	253.1	252.8
107.5°	299.3	299.3	299.3	299.3	299.3	299.3	299.3	299.3	299.3	299.3	299.3
110°	349.8	349.7	349.5	349.2	349.0	348.8	349.0	349.2	349.5	349.7	349.8



TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	399.4	399.2	398.7	398.2	397.8	397.3	397.8	398.2	398.7	399.2	399.4
115°	449.9	449.8	449.6	449.3	449.1	448.9	449.1	449.3	449.6	449.8	449.9
117.5°	502.6	502.1	501.2	500.3	499.3	498.4	499.3	500.3	501.2	502.1	502.6
120°	554.2	553.7	552.8	551.9	550.9	550.0	550.9	551.9	552.8	553.7	554.2
122.5°	604.7	604.4	603.7	603.0	602.3	601.6	602.3	603.0	603.7	604.4	604.7
125°	654.3	654.2	653.9	653.7	653.4	653.2	653.4	653.7	653.9	654.2	654.3
127.5°	704.8	704.6	704.1	703.7	703.2	702.8	703.2	703.7	704.1	704.6	704.8
130°	754.4	754.2	753.7	753.2	752.8	752.3	752.8	753.2	753.7	754.2	754.4
132.5°	801.8	801.5	800.8	800.1	799.4	798.7	799.4	800.1	800.8	801.5	801.8
135°	851.4	850.9	850.0	849.1	848.1	847.2	848.1	849.1	850.0	850.9	851.4
137.5°	899.9	899.3	898.2	897.0	895.9	894.7	895.9	897.0	898.2	899.3	899.9
140°	945.3	944.7	943.6	942.4	941.3	940.1	941.3	942.4	943.6	944.7	945.3
142.5°	988.6	988.0	986.9	985.8	984.6	983.5	984.6	985.8	986.9	988.0	988.6
145°	1029.9	1029.6	1028.9	1028.2	1027.5	1026.8	1027.5	1028.2	1028.9	1029.6	1029.9
147.5°	1071.2	1070.3	1068.4	1066.6	1064.7	1062.9	1064.7	1066.6	1068.4	1070.3	1071.2
150°	1106.3	1106.1	1105.6	1105.1	1104.7	1104.2	1104.7	1105.1	1105.6	1106.1	1106.3
152.5°	1142.4	1141.9	1141.0	1140.1	1139.1	1138.2	1139.1	1140.1	1141.0	1141.9	1142.4
155°	1175.4	1174.8	1173.7	1172.5	1171.4	1170.2	1171.4	1172.5	1173.7	1174.8	1175.4
157.5°	1204.3	1203.5	1201.9	1200.3	1198.7	1197.1	1198.7	1200.3	1201.9	1203.5	1204.3
160°	1230.1	1229.5	1228.4	1227.2	1226.1	1224.9	1226.1	1227.2	1228.4	1229.5	1230.1
162.5°	1254.9	1254.2	1252.8	1251.5	1250.1	1248.7	1250.1	1251.5	1252.8	1254.2	1254.9
165°	1275.5	1274.8	1273.4	1272.1	1270.7	1269.3	1270.7	1272.1	1273.4	1274.8	1275.5
167.5°	1293.0	1292.3	1290.9	1289.6	1288.2	1286.8	1288.2	1289.6	1290.9	1292.3	1293.0
170°	1307.5	1306.7	1305.1	1303.5	1301.9	1300.3	1301.9	1303.5	1305.1	1306.7	1307.5
172.5°	1317.8	1317.1	1315.7	1314.4	1313.0	1311.6	1313.0	1314.4	1315.7	1317.1	1317.8
175°	1325.0	1324.2	1322.6	1321.0	1319.4	1317.8	1319.4	1321.0	1322.6	1324.2	1325.0
177.5°	1329.2	1328.4	1326.8	1325.1	1323.5	1321.9	1323.5	1325.1	1326.8	1328.4	1329.2
180°	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1756.2	1746.8	1757.8	1743.6	1746.8	1764.0	1762.5	1778.2	1787.6	1786.0	1793.9
5°	1640.1	1640.1	1644.8	1643.2	1658.9	1673.0	1691.8	1707.5	1724.8	1734.2	1745.2
7.5°	1525.5	1541.2	1544.3	1552.2	1571.0	1594.5	1613.4	1636.9	1662.0	1679.3	1691.8
10°	1431.3	1443.9	1456.4	1462.7	1483.1	1514.5	1541.2	1578.8	1610.2	1629.1	1646.3
12.5°	1348.1	1362.3	1368.5	1396.8	1410.9	1431.3	1469.0	1509.8	1544.3	1564.7	1578.8
15°	1288.5	1296.3	1310.5	1327.7	1341.9	1367.0	1398.4	1443.9	1476.8	1494.1	1542.7
17.5°	1238.3	1247.7	1255.5	1263.4	1285.4	1312.0	1341.9	1381.1	1423.5	1453.3	1478.4
20°	1186.5	1191.2	1200.6	1213.2	1228.9	1254.0	1280.7	1321.5	1359.1	1382.7	1415.6
22.5°	1125.3	1139.4	1148.8	1158.2	1175.5	1203.7	1228.9	1258.7	1305.8	1332.4	1367.0
25°	1089.2	1095.5	1101.7	1112.7	1125.3	1150.4	1178.6	1210.0	1247.7	1275.9	1305.8
27.5°	1042.1	1051.5	1059.4	1073.5	1081.3	1101.7	1128.4	1159.8	1205.3	1228.9	1254.0
30°	1002.9	1012.3	1018.6	1024.8	1035.8	1057.8	1082.9	1108.0	1150.4	1180.2	1205.3
32.5°	963.6	973.0	980.9	985.6	996.6	1010.7	1031.1	1062.5	1098.6	1119.0	1152.0
35°	929.1	929.1	938.5	944.8	954.2	966.8	985.6	1009.1	1046.8	1073.5	1103.3
37.5°	889.9	891.4	899.3	904.0	913.4	926.0	944.8	966.8	998.2	1018.6	1048.4
40°	849.1	853.8	856.9	864.8	875.7	880.4	899.3	924.4	955.8	974.6	999.7
42.5°	808.3	811.4	819.2	825.5	834.9	842.8	855.3	878.9	902.4	930.7	951.1
45°	762.7	770.6	775.3	786.3	791.0	798.8	811.4	830.2	858.5	875.7	899.3
47.5°	723.5	726.6	729.8	743.9	753.3	758.0	770.6	781.6	811.4	827.1	849.1
50°	681.1	681.1	685.8	692.1	703.1	712.5	723.5	736.1	759.6	775.3	797.3
52.5°	641.9	637.2	640.3	643.5	654.5	663.9	674.9	692.1	714.1	723.5	742.3
55°	599.5	591.7	596.4	601.1	604.2	616.8	629.3	640.3	657.6	671.7	689.0
57.5°	554.0	552.4	549.3	550.9	558.7	566.6	576.0	590.1	610.5	621.5	630.9
60°	513.2	503.8	500.6	503.8	508.5	513.2	525.8	538.3	555.6	566.6	577.5
62.5°	470.8	461.4	455.1	450.4	455.1	466.1	474.0	483.4	497.5	510.1	519.5
65°	430.0	415.9	409.6	406.5	404.9	412.8	419.0	431.6	444.1	448.9	459.8
67.5°	384.5	372.0	364.1	359.4	359.4	359.4	365.7	378.2	390.8	392.4	403.3
70°	339.0	324.9	317.0	310.7	307.6	310.7	318.6	320.2	331.1	334.3	340.6
72.5°	290.3	277.8	268.4	260.5	262.1	265.2	265.2	268.4	274.6	282.5	282.5
75°	244.8	227.6	222.9	216.6	213.4	213.4	213.4	219.7	224.4	230.7	229.1
77.5°	193.0	183.6	174.2	171.1	166.4	164.8	167.9	167.9	171.1	175.8	177.3
80°	149.1	138.1	131.8	128.7	122.4	120.8	122.4	122.4	127.1	125.6	127.1
82.5°	103.6	95.7	91.0	86.3	83.2	84.7	83.2	83.2	84.7	83.2	83.2
85°	59.6	58.1	54.9	53.4	51.8	48.7	51.8	50.2	48.7	47.1	50.2
87.5°	28.2	26.7	26.7	23.5	23.5	22.0	23.5	23.5	22.0	22.0	22.0
90°	21.1	20.0	18.8	17.7	16.5	14.9	13.3	11.7	10.1	9.3	8.4
92.5°	51.8	50.2	48.6	47.0	45.4	43.3	41.3	39.2	37.1	36.1	35.5
95°	85.9	84.3	82.7	81.1	79.5	77.2	74.9	72.6	70.3	69.1	68.9
97.5°	124.2	122.8	121.5	120.1	118.7	115.5	112.3	109.0	105.8	104.2	104.1
100°	166.2	164.1	162.0	160.0	157.9	154.9	151.9	149.0	146.0	144.5	144.5
102.5°	208.4	206.1	203.8	201.5	199.2	198.0	196.9	195.7	194.6	194.0	193.4
105°	252.1	250.7	249.4	248.0	246.6	245.2	243.8	242.5	241.1	240.4	239.8
107.5°	299.0	298.3	297.6	296.9	296.2	295.0	293.9	292.7	291.6	291.0	290.4
110°	349.5	348.8	348.1	347.4	346.7	346.0	345.3	344.6	343.9	343.6	343.0

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	399.3	399.0	398.8	398.5	398.3	397.4	396.5	395.6	394.7	394.2	394.0
115°	450.0	450.3	450.5	450.8	451.0	450.5	450.1	449.6	449.1	448.9	448.4
117.5°	502.5	502.2	502.0	501.7	501.5	501.1	500.6	500.2	499.7	499.5	499.4
120°	554.2	554.2	554.2	554.2	554.2	554.0	553.7	553.5	553.2	553.1	552.5
122.5°	604.8	605.1	605.3	605.6	605.8	605.1	604.4	603.7	603.0	602.7	602.6
125°	654.5	655.0	655.4	655.9	656.3	656.1	655.9	655.6	655.4	655.3	654.6
127.5°	704.9	705.2	705.4	705.7	705.9	705.7	705.4	705.2	704.9	704.8	704.5
130°	754.5	754.7	755.0	755.2	755.4	754.9	754.5	754.0	753.5	753.3	752.7
132.5°	801.9	802.2	802.4	802.7	802.9	803.1	803.3	803.6	803.8	803.9	802.9
135°	851.4	851.4	851.4	851.4	851.4	851.2	850.9	850.7	850.4	850.3	849.6
137.5°	899.8	899.5	899.3	899.0	898.8	898.4	897.9	897.5	897.0	896.8	896.1
140°	945.1	944.6	944.1	943.7	943.2	942.5	941.8	941.1	940.4	940.1	939.5
142.5°	988.5	988.3	988.0	987.8	987.6	986.7	985.8	984.9	984.0	983.5	983.0
145°	1029.9	1029.9	1029.9	1029.9	1029.9	1029.2	1028.5	1027.8	1027.1	1026.8	1026.3
147.5°	1070.9	1070.2	1069.5	1068.8	1068.1	1067.6	1067.2	1066.7	1066.2	1066.0	1065.7
150°	1106.3	1106.3	1106.3	1106.3	1106.3	1105.4	1104.4	1103.5	1102.6	1102.1	1102.2
152.5°	1142.1	1141.4	1140.7	1140.0	1139.3	1139.1	1138.8	1138.6	1138.3	1138.2	1138.0
155°	1174.9	1174.0	1173.1	1172.2	1171.3	1171.1	1170.8	1170.6	1170.3	1170.2	1170.2
157.5°	1203.8	1202.9	1202.0	1201.1	1200.2	1200.0	1199.7	1199.5	1199.2	1199.1	1199.3
160°	1229.6	1228.7	1227.8	1226.9	1226.0	1225.8	1225.5	1225.3	1225.0	1224.9	1225.2
162.5°	1254.3	1253.2	1252.0	1250.9	1249.7	1249.7	1249.7	1249.7	1249.7	1249.7	1249.9
165°	1275.0	1274.1	1273.2	1272.3	1271.4	1271.2	1270.9	1270.7	1270.4	1270.3	1270.5
167.5°	1292.3	1290.9	1289.6	1288.2	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1287.3
170°	1306.8	1305.4	1304.1	1302.7	1301.3	1301.3	1301.3	1301.3	1301.3	1301.3	1301.8
172.5°	1317.1	1315.7	1314.4	1313.0	1311.6	1311.6	1311.6	1311.6	1311.6	1311.6	1312.1
175°	1324.3	1322.9	1321.6	1320.2	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1319.3
177.5°	1328.5	1327.1	1325.8	1324.4	1323.0	1323.2	1323.4	1323.7	1323.9	1324.0	1324.5
180°	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1	1326.1

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1848.8	1848.8	1848.8	1848.8
2.5°	1804.8	1820.5	1831.5	1851.9
5°	1764.0	1792.3	1819.0	1847.2
7.5°	1723.2	1756.2	1798.6	1834.7
10°	1677.7	1720.1	1770.3	1819.0
12.5°	1632.2	1682.4	1737.4	1801.7
15°	1577.3	1641.6	1706.0	1775.0
17.5°	1528.6	1594.5	1663.6	1749.9
20°	1473.7	1545.9	1621.2	1709.1
22.5°	1425.0	1505.1	1583.6	1676.1
25°	1370.1	1448.6	1534.9	1633.8
27.5°	1324.6	1396.8	1481.5	1588.3
30°	1269.7	1348.1	1432.9	1539.6
32.5°	1217.9	1293.2	1382.7	1487.8
35°	1164.5	1241.4	1321.5	1421.9
37.5°	1114.3	1180.2	1260.2	1356.0
40°	1057.8	1130.0	1202.2	1277.5
42.5°	1006.0	1071.9	1139.4	1199.0
45°	947.9	1004.4	1068.8	1117.4
47.5°	894.6	944.8	995.0	1032.7
50°	841.2	880.4	918.1	951.1
52.5°	778.4	822.4	842.8	863.2
55°	721.9	747.0	765.9	786.3
57.5°	667.0	678.0	687.4	706.2
60°	594.8	607.4	618.4	632.5
62.5°	532.0	538.3	541.5	555.6
65°	472.4	470.8	478.7	486.5
67.5°	408.1	406.5	414.3	417.5
70°	345.3	343.7	345.3	353.1
72.5°	285.6	285.6	287.2	290.3
75°	230.7	230.7	232.3	235.4
77.5°	174.2	177.3	175.8	182.1
80°	127.1	124.0	127.1	130.3
82.5°	83.2	86.3	86.3	83.2
85°	47.1	47.1	47.1	47.1
87.5°	20.4	20.4	22.0	23.5
90°	6.5	4.7	2.8	1.0
92.5°	34.4	33.3	32.1	31.0
95°	68.4	68.0	67.5	67.1
97.5°	103.9	103.6	103.4	103.2
100°	144.5	144.5	144.5	144.5
102.5°	192.3	191.1	190.0	188.8
105°	238.7	237.6	236.4	235.3
107.5°	289.3	288.2	287.0	285.9
110°	341.9	340.8	339.6	338.5

TEST NUMBER: P1035099

CATALOG NUMBER: S125DIW-B1270D1050UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	393.5	393.0	392.6	392.1
115°	447.5	446.6	445.7	444.8
117.5°	499.1	498.9	498.6	498.4
120°	551.4	550.3	549.1	548.0
122.5°	602.3	602.1	601.8	601.6
125°	653.2	651.9	650.5	649.1
127.5°	703.8	703.1	702.4	701.7
130°	751.6	750.5	749.3	748.2
132.5°	800.8	798.7	796.7	794.6
135°	848.2	846.9	845.5	844.1
137.5°	894.7	893.4	892.0	890.6
140°	938.4	937.3	936.1	935.0
142.5°	982.1	981.2	980.2	979.3
145°	1025.4	1024.5	1023.6	1022.7
147.5°	1065.0	1064.3	1063.6	1062.9
150°	1102.5	1102.7	1103.0	1103.2
152.5°	1137.5	1137.1	1136.6	1136.2
155°	1170.2	1170.2	1170.2	1170.2
157.5°	1199.8	1200.3	1200.7	1201.2
160°	1225.9	1226.6	1227.3	1228.0
162.5°	1250.4	1250.9	1251.3	1251.8
165°	1271.0	1271.5	1271.9	1272.4
167.5°	1288.2	1289.1	1290.1	1291.0
170°	1302.7	1303.6	1304.5	1305.4
172.5°	1313.0	1313.9	1314.8	1315.7
175°	1320.2	1321.1	1322.1	1323.0
177.5°	1325.4	1326.3	1327.2	1328.1
180°	1326.1	1326.1	1326.1	1326.1

(END OF REPORT)