

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035681

Luminaire Tested: S125RDIW-B1090D1050UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035681
REPORT IS A COMBINATION OF REPORTS P1005943 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1050UB30-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7886.0 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035681

CATALOG NUMBER: S125RDIW-B1090D1050UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035681

CATALOG NUMBER: S125RDIW-B1090D1050UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	53	51	50	50	50	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	43	43	43	38
3	82	73	66	60	76	68	62	56	58	54	50	50	46	43	41	39	37	37	37	37	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	32	32	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	28	28	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	25	25	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22	22	22	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	20	20	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	18	18	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11384	11384	11384
5°	11385	11100	11118
10°	11275	10821	10726
15°	11115	10429	10209
20°	10918	9958	9667
25°	10691	9498	9086
30°	10414	8992	8476
35°	10131	8479	7827
40°	9862	7951	7194
45°	9538	7382	6531
50°	9210	6778	5856
55°	8829	6182	5157
60°	8439	5502	4432
65°	7976	4741	3650
70°	7434	3859	2872
75°	6684	2902	2093
80°	5639	1880	1411
85°	4220	1009	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9538 cd/sqm

TEST NUMBER: P1035681

CATALOG NUMBER: S125RDIW-B1090D1050UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.2	2.1
10°-20°	467.3	5.9
20°-30°	677.6	8.6
30°-40°	772.0	9.8
40°-50°	752.5	9.5
50°-60°	633.3	8.0
60°-70°	443.8	5.6
70°-80°	227.5	2.9
80°-90°	58.8	0.7
90°-100°	87.8	1.1
100°-110°	260.9	3.3
110°-120°	442.5	5.6
120°-130°	582.5	7.4
130°-140°	652.7	8.3
140°-150°	639.8	8.1
150°-160°	537.4	6.8
160°-170°	357.2	4.5
170°-180°	125.0	1.6
0°-30°	1312.2	16.6
0°-40°	2084.2	26.4
0°-60°	3470.0	44.0
0°-90°	4200.1	53.3
90°-120°	791.2	10.0
90°-150°	2666.2	33.8
90°-180°	3686.0	46.7
0°-180°	7886.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1774	1769	1754	1767	1765	168
15°	1687	1679	1651	1649	1637	476
25°	1530	1510	1460	1443	1428	704
35°	1318	1286	1225	1186	1168	825
45°	1079	1040	966	913	892	832
55°	819	776	700	640	619	732
65°	554	509	438	384	364	549
75°	295	255	199	169	160	312
85°	74	50	43	42	40	81
90°	1	9	16	22	25	9
95°	67	69	79	86	88	70
105°	234	240	246	252	255	250
115°	443	447	449	448	447	438
125°	646	653	654	652	651	579
135°	841	847	848	848	844	648
145°	1018	1023	1026	1026	1023	637
155°	1166	1166	1166	1171	1166	537
165°	1267	1265	1266	1270	1264	358
175°	1318	1314	1314	1320	1312	125
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1035681

CATALOG NUMBER: S125RDIW-B1090D1050UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1776.8	1776.8	1776.8	1776.8	1776.8
2.5°	1780.8	1776.8	1763.4	1776.8	1775.5
5°	1774.1	1768.8	1754.0	1767.4	1764.7
7.5°	1760.7	1755.4	1737.9	1748.6	1746.0
10°	1740.6	1736.6	1717.8	1721.8	1717.8
12.5°	1717.8	1712.4	1685.6	1688.3	1681.5
15°	1686.9	1678.9	1650.7	1649.3	1637.3
17.5°	1654.7	1642.6	1609.1	1602.4	1593.0
20°	1615.8	1602.4	1559.4	1552.7	1540.6
22.5°	1572.8	1559.4	1513.8	1499.0	1489.6
25°	1529.9	1509.8	1460.1	1442.7	1427.9
27.5°	1481.6	1457.4	1405.1	1382.3	1367.5
30°	1427.9	1402.4	1346.0	1315.2	1303.1
32.5°	1375.6	1344.7	1287.0	1252.1	1236.0
35°	1317.9	1285.6	1225.3	1186.3	1167.5
37.5°	1262.8	1223.9	1162.2	1116.6	1097.8
40°	1203.8	1163.5	1099.1	1048.1	1032.0
42.5°	1142.1	1100.4	1033.3	985.0	959.5
45°	1079.0	1040.1	966.2	912.6	892.4
47.5°	1013.2	973.0	899.1	844.1	821.3
50°	951.5	907.2	830.7	774.3	754.2
52.5°	884.4	838.8	767.6	705.9	685.8
55°	818.6	775.7	700.5	640.1	618.7
57.5°	751.5	705.9	633.4	574.4	555.6
60°	687.1	640.1	567.7	508.6	488.5
62.5°	618.7	574.4	500.6	446.9	426.8
65°	554.3	508.6	437.5	383.8	363.7
67.5°	489.8	444.2	375.8	324.8	308.7
70°	424.1	378.4	311.3	269.7	253.6
72.5°	359.7	315.4	253.6	216.1	206.7
75°	295.2	255.0	198.6	169.1	159.7
77.5°	229.5	197.3	150.3	127.5	119.4
80°	174.5	142.3	104.7	92.6	89.9
82.5°	120.8	92.6	69.8	65.8	64.4
85°	73.8	49.7	42.9	41.6	40.3
87.5°	30.9	21.5	20.1	20.1	18.8
90°	1.0	9.2	16.4	21.6	24.7
92.5°	30.8	36.0	45.2	52.4	54.5
95°	66.8	68.9	79.1	86.3	88.4
97.5°	102.8	103.8	118.2	124.4	125.4
100°	143.9	143.9	157.2	166.5	168.6
102.5°	188.1	193.2	198.4	208.6	211.7
105°	234.3	239.5	245.6	251.8	254.9
107.5°	284.7	289.8	295.0	298.1	298.1
110°	337.1	342.2	345.3	348.4	347.4

TEST NUMBER: P1035681

CATALOG NUMBER: S125RDIW-B1090D1050UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	390.6	392.6	396.7	397.7	395.7
115°	443.0	447.1	449.1	448.1	447.1
117.5°	496.4	497.4	499.5	500.5	496.4
120°	545.7	550.9	551.9	551.9	547.8
122.5°	599.2	600.2	603.3	602.3	599.2
125°	646.5	652.6	653.7	651.6	650.6
127.5°	698.9	702.0	703.0	702.0	699.9
130°	745.1	750.3	752.3	751.3	749.2
132.5°	791.4	800.6	799.6	798.6	795.5
135°	840.7	846.9	847.9	847.9	843.8
137.5°	887.0	893.1	895.2	896.2	891.1
140°	931.2	936.3	939.4	941.4	936.3
142.5°	975.4	979.5	983.6	984.6	979.5
145°	1018.5	1022.6	1025.7	1025.7	1022.6
147.5°	1058.6	1061.7	1063.7	1066.8	1058.6
150°	1098.7	1097.7	1101.8	1101.8	1099.7
152.5°	1131.6	1133.6	1134.7	1137.7	1133.6
155°	1165.5	1165.5	1166.5	1170.6	1165.5
157.5°	1196.3	1194.3	1195.3	1199.4	1192.2
160°	1223.1	1220.0	1221.0	1225.1	1220.0
162.5°	1246.7	1244.6	1244.6	1249.8	1243.6
165°	1267.2	1265.2	1266.2	1270.3	1264.2
167.5°	1285.7	1281.6	1281.6	1287.8	1281.6
170°	1300.1	1296.0	1296.0	1302.2	1295.0
172.5°	1310.4	1306.3	1306.3	1312.5	1306.3
175°	1317.6	1313.5	1313.5	1319.7	1312.5
177.5°	1322.7	1318.6	1317.6	1323.8	1316.6
180°	1320.7	1320.7	1320.7	1320.7	1320.7

(END OF REPORT)