

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035121

Luminaire Tested: S125DIW-B1270D1340UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035121
REPORT IS A COMBINATION OF REPORTS P1003122 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1340UB27-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9713.0 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035121

CATALOG NUMBER: S125DIW-B1270D1340UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035121

CATALOG NUMBER: S125DIW-B1270D1340UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	52	50	49
2	89	82	76	71	83	76	71	66	65	61	57	55	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	35	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12544	12544	12544
5°	12545	12253	12277
10°	12442	11972	11935
15°	12278	11637	11532
20°	12057	11247	11070
25°	11820	10822	10576
30°	11534	10379	10055
35°	11228	9915	9471
40°	10913	9424	8952
45°	10571	8946	8400
50°	10195	8404	7757
55°	9823	7806	7166
60°	9380	7176	6479
65°	8848	6446	5768
70°	8309	5607	4947
75°	7400	4617	4000
80°	6308	3449	2942
85°	4871	2039	1622

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10571 cd/sqm

TEST NUMBER: P1035121

CATALOG NUMBER: S125DIW-B1270D1340UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	1.9
10°-20°	521.9	5.4
20°-30°	770.4	7.9
30°-40°	898.9	9.3
40°-50°	902.8	9.3
50°-60°	792.5	8.2
60°-70°	590.3	6.1
70°-80°	337.1	3.5
80°-90°	99.9	1.0
90°-100°	110.0	1.1
100°-110°	326.6	3.4
110°-120°	553.9	5.7
120°-130°	729.2	7.5
130°-140°	817.2	8.4
140°-150°	801.0	8.2
150°-160°	672.8	6.9
160°-170°	447.2	4.6
170°-180°	156.5	1.6
0°-30°	1477.1	15.2
0°-40°	2376.0	24.5
0°-60°	4071.3	41.9
0°-90°	5098.6	52.5
90°-120°	990.5	10.2
90°-150°	3337.9	34.4
90°-180°	4614.0	47.5
0°-180°	9713.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1958	1958	1958	1958	1958	
5°	1955	1952	1936	1950	1949	186
15°	1863	1859	1842	1850	1850	525
25°	1692	1684	1664	1667	1662	778
35°	1461	1454	1433	1425	1413	914
45°	1196	1190	1171	1152	1148	921
55°	911	906	884	870	860	813
65°	615	612	595	581	575	610
75°	327	324	316	311	305	348
85°	85	87	87	85	82	93
90°	1	12	21	27	31	11
95°	84	86	99	108	111	87
105°	293	300	308	315	319	313
115°	555	560	562	561	560	549
125°	809	817	818	816	814	725
135°	1052	1060	1062	1062	1056	811
145°	1275	1280	1284	1284	1280	797
155°	1459	1459	1460	1466	1459	672
165°	1586	1584	1585	1590	1583	448
175°	1650	1644	1644	1652	1643	157
180°	1653	1653	1653	1653	1653	

TEST NUMBER: P1035121

CATALOG NUMBER: S125DIW-B1270D1340UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1957.9	1957.9	1957.9	1957.9	1957.9
2.5°	1964.1	1959.5	1944.0	1959.5	1957.9
5°	1954.8	1951.7	1936.2	1950.2	1948.6
7.5°	1940.9	1937.8	1920.8	1934.7	1933.1
10°	1920.8	1917.7	1900.6	1913.0	1911.5
12.5°	1896.0	1889.8	1874.3	1883.6	1883.6
15°	1863.4	1858.8	1841.8	1849.5	1849.5
17.5°	1829.4	1821.6	1804.6	1813.9	1806.1
20°	1784.4	1781.3	1761.2	1772.0	1764.3
22.5°	1739.5	1733.3	1714.7	1720.9	1716.3
25°	1691.5	1683.8	1663.6	1666.7	1662.1
27.5°	1635.7	1631.1	1611.0	1612.5	1607.9
30°	1581.5	1576.9	1553.6	1550.5	1545.9
32.5°	1522.7	1514.9	1494.8	1488.6	1479.3
35°	1460.7	1454.5	1432.8	1425.1	1412.7
37.5°	1397.2	1389.4	1369.3	1358.5	1350.7
40°	1332.1	1324.4	1302.7	1288.8	1284.1
42.5°	1262.4	1256.2	1234.5	1222.2	1214.4
45°	1195.8	1189.6	1171.0	1152.5	1147.8
47.5°	1123.0	1124.6	1101.3	1082.7	1071.9
50°	1053.3	1048.7	1030.1	1009.9	999.1
52.5°	982.1	979.0	958.8	941.8	929.4
55°	910.8	906.2	884.5	870.5	859.7
57.5°	834.9	833.4	814.8	796.2	791.5
60°	763.7	757.5	740.4	724.9	714.1
62.5°	689.3	684.7	670.7	653.7	645.9
65°	614.9	611.9	594.8	580.9	574.7
67.5°	542.1	536.0	523.6	511.2	508.1
70°	474.0	466.2	452.3	443.0	436.8
72.5°	399.6	395.0	387.2	376.4	370.2
75°	326.8	323.7	316.0	311.3	305.2
77.5°	258.7	257.1	252.5	249.4	244.7
80°	195.2	195.2	192.1	190.5	187.4
82.5°	139.4	136.3	136.3	133.2	133.2
85°	85.2	86.7	86.7	85.2	82.1
87.5°	41.8	41.8	40.3	40.3	37.2
90°	1.3	11.6	20.6	27.0	30.9
92.5°	38.6	45.0	56.6	65.6	68.2
95°	83.6	86.2	99.1	108.1	110.7
97.5°	128.7	130.0	148.0	155.7	157.0
100°	180.1	180.1	196.9	208.4	211.0
102.5°	235.5	241.9	248.3	261.2	265.1
105°	293.4	299.8	307.5	315.2	319.1
107.5°	356.4	362.8	369.3	373.1	373.1
110°	422.0	428.5	432.3	436.2	434.9

TEST NUMBER: P1035121

CATALOG NUMBER: S125DIW-B1270D1340UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	488.9	491.5	496.7	497.9	495.4
115°	554.6	559.7	562.3	561.0	559.7
117.5°	621.5	622.7	625.3	626.6	621.5
120°	683.2	689.7	690.9	690.9	685.8
122.5°	750.1	751.4	755.3	754.0	750.1
125°	809.3	817.0	818.3	815.7	814.5
127.5°	874.9	878.8	880.1	878.8	876.2
130°	932.8	939.3	941.8	940.6	938.0
132.5°	990.7	1002.3	1001.0	999.7	995.9
135°	1052.5	1060.2	1061.5	1061.5	1056.4
137.5°	1110.4	1118.1	1120.7	1122.0	1115.5
140°	1165.7	1172.2	1176.0	1178.6	1172.2
142.5°	1221.1	1226.2	1231.3	1232.6	1226.2
145°	1275.1	1280.2	1284.1	1284.1	1280.2
147.5°	1325.3	1329.1	1331.7	1335.6	1325.3
150°	1375.5	1374.2	1379.3	1379.3	1376.7
152.5°	1416.6	1419.2	1420.5	1424.3	1419.2
155°	1459.1	1459.1	1460.4	1465.5	1459.1
157.5°	1497.7	1495.1	1496.4	1501.5	1492.5
160°	1531.1	1527.3	1528.6	1533.7	1527.3
162.5°	1560.7	1558.2	1558.2	1564.6	1556.9
165°	1586.5	1583.9	1585.2	1590.3	1582.6
167.5°	1609.6	1604.5	1604.5	1612.2	1604.5
170°	1627.6	1622.5	1622.5	1630.2	1621.2
172.5°	1640.5	1635.4	1635.4	1643.1	1635.4
175°	1649.5	1644.4	1644.4	1652.1	1643.1
177.5°	1655.9	1650.8	1649.5	1657.2	1648.2
180°	1653.4	1653.4	1653.4	1653.4	1653.4

(END OF REPORT)