

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035132

Luminaire Tested: S125DIW-B1270D1340UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035132
REPORT IS A COMBINATION OF REPORTS P1003160 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1340UB35-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10556.0 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035132

CATALOG NUMBER: S125DIW-B1270D1340UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035132

CATALOG NUMBER: S125DIW-B1270D1340UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	48	46			41
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39			34
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33			29
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29			25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25			22
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22			19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19			17
8	54	41	34	28	49	38	32	27	33	28	24	28	24	20	23	20	17			15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16			14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12710	12710	12710
5°	12710	12415	12439
10°	12605	12130	12092
15°	12439	11790	11684
20°	12216	11395	11216
25°	11975	10964	10715
30°	11686	10516	10187
35°	11376	10046	9595
40°	11056	9548	9069
45°	10710	9064	8511
50°	10330	8515	7859
55°	9953	7909	7261
60°	9503	7270	6564
65°	8964	6530	5843
70°	8417	5681	5012
75°	7497	4677	4053
80°	6389	3494	2981
85°	4934	2067	1644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10710 cd/sqm

TEST NUMBER: P1035132

CATALOG NUMBER: S125DIW-B1270D1340UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	1.8
10°-20°	528.7	5.0
20°-30°	780.6	7.4
30°-40°	910.7	8.6
40°-50°	914.7	8.7
50°-60°	802.9	7.6
60°-70°	598.0	5.7
70°-80°	341.6	3.2
80°-90°	101.2	1.0
90°-100°	59.5	0.6
100°-110°	396.0	3.8
110°-120°	713.2	6.8
120°-130°	915.4	8.7
130°-140°	984.6	9.3
140°-150°	924.1	8.8
150°-160°	747.5	7.1
160°-170°	483.4	4.6
170°-180°	166.7	1.6
0°-30°	1496.5	14.2
0°-40°	2407.2	22.8
0°-60°	4124.8	39.1
0°-90°	5165.6	48.9
90°-120°	1168.8	11.1
90°-150°	3992.8	37.8
90°-180°	5390.0	51.1
0°-180°	10556.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1980	1977	1962	1976	1974	188
15°	1888	1883	1866	1874	1874	532
25°	1714	1706	1686	1689	1684	789
35°	1480	1474	1452	1444	1431	926
45°	1212	1205	1186	1168	1163	933
55°	923	918	896	882	871	824
65°	623	620	603	588	582	618
75°	331	328	320	315	309	353
85°	86	88	88	86	83	95
90°	1	12	21	27	31	10
95°	74	70	21	27	27	91
105°	382	388	388	388	386	405
115°	718	725	726	721	713	712
125°	1021	1030	1030	1025	1021	912
135°	1274	1281	1279	1276	1268	982
145°	1476	1479	1479	1480	1472	923
155°	1626	1618	1621	1625	1614	749
165°	1716	1708	1709	1717	1707	485
175°	1755	1747	1748	1759	1747	167
180°	1755	1755	1755	1755	1755	

TEST NUMBER: P1035132

CATALOG NUMBER: S125DIW-B1270D1340UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.7	1983.7	1983.7	1983.7	1983.7
2.5°	1989.9	1985.2	1969.5	1985.2	1983.7
5°	1980.5	1977.4	1961.7	1975.8	1974.3
7.5°	1966.4	1963.3	1946.0	1960.1	1958.6
10°	1946.0	1942.9	1925.6	1938.2	1936.6
12.5°	1920.9	1914.6	1898.9	1908.3	1908.3
15°	1887.9	1883.2	1866.0	1873.8	1873.8
17.5°	1853.4	1845.6	1828.3	1837.7	1829.9
20°	1807.9	1804.8	1784.4	1795.3	1787.5
22.5°	1762.4	1756.1	1737.3	1743.6	1738.8
25°	1713.7	1705.9	1685.5	1688.6	1683.9
27.5°	1657.2	1652.5	1632.1	1633.7	1629.0
30°	1602.3	1597.6	1574.1	1570.9	1566.2
32.5°	1542.7	1534.8	1514.4	1508.2	1498.7
35°	1479.9	1473.6	1451.7	1443.8	1431.3
37.5°	1415.6	1407.7	1387.3	1376.3	1368.5
40°	1349.6	1341.8	1319.8	1305.7	1301.0
42.5°	1279.0	1272.7	1250.8	1238.2	1230.4
45°	1211.5	1205.3	1186.4	1167.6	1162.9
47.5°	1137.8	1139.4	1115.8	1097.0	1086.0
50°	1067.2	1062.5	1043.6	1023.2	1012.2
52.5°	995.0	991.8	971.4	954.2	941.6
55°	922.8	918.1	896.1	882.0	871.0
57.5°	845.9	844.3	825.5	806.6	801.9
60°	773.7	767.4	750.2	734.5	723.5
62.5°	698.4	693.7	679.5	662.3	654.4
65°	623.0	619.9	602.6	588.5	582.2
67.5°	549.3	543.0	530.4	517.9	514.7
70°	480.2	472.4	458.3	448.8	442.6
72.5°	404.9	400.2	392.3	381.4	375.1
75°	331.1	328.0	320.1	315.4	309.2
77.5°	262.1	260.5	255.8	252.7	248.0
80°	197.7	197.7	194.6	193.0	189.9
82.5°	141.2	138.1	138.1	135.0	135.0
85°	86.3	87.9	87.9	86.3	83.2
87.5°	42.4	42.4	40.8	40.8	37.7
90°	1.3	11.7	20.8	27.3	31.2
92.5°	24.7	13.0	20.8	27.3	28.6
95°	74.1	70.2	20.8	27.3	27.3
97.5°	139.2	147.0	23.4	26.0	27.3
100°	217.2	221.1	226.3	32.5	27.3
102.5°	296.6	301.8	304.4	307.0	197.7
105°	382.4	387.6	387.6	387.6	386.3
107.5°	470.9	470.9	473.5	474.8	469.6
110°	556.8	556.8	559.4	555.5	556.8



TEST NUMBER: P1035132

CATALOG NUMBER: S125DIW-B1270D1340UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	637.4	641.3	642.6	637.4	634.8
115°	718.1	724.6	725.9	720.7	712.8
117.5°	802.6	802.6	807.8	800.0	797.4
120°	880.7	879.4	883.3	880.7	874.2
122.5°	949.6	956.1	957.4	954.8	947.0
125°	1021.1	1030.3	1030.3	1025.0	1021.1
127.5°	1090.1	1096.6	1095.3	1092.7	1082.3
130°	1152.5	1159.0	1160.3	1156.4	1149.9
132.5°	1215.0	1222.8	1218.9	1218.9	1212.4
135°	1273.5	1281.3	1278.7	1276.1	1268.3
137.5°	1328.1	1335.9	1333.3	1333.3	1326.8
140°	1381.5	1384.1	1382.8	1385.4	1377.6
142.5°	1429.6	1430.9	1433.5	1433.5	1425.7
145°	1476.4	1479.0	1479.0	1480.3	1472.5
147.5°	1518.1	1518.1	1519.4	1520.7	1511.6
150°	1557.1	1554.5	1557.1	1559.7	1549.3
152.5°	1594.8	1588.3	1590.9	1593.5	1584.4
155°	1626.0	1618.2	1620.8	1624.7	1614.3
157.5°	1650.7	1646.8	1646.8	1650.7	1640.3
160°	1676.8	1669.0	1670.3	1675.5	1665.1
162.5°	1697.6	1689.8	1691.1	1698.9	1687.2
165°	1715.8	1708.0	1709.3	1717.1	1706.7
167.5°	1730.1	1722.3	1723.6	1732.7	1721.0
170°	1741.8	1732.7	1734.0	1744.4	1732.7
172.5°	1749.6	1740.5	1743.1	1752.2	1740.5
175°	1754.8	1747.0	1748.3	1758.7	1747.0
177.5°	1758.7	1750.9	1752.2	1761.3	1750.9
180°	1754.8	1754.8	1754.8	1754.8	1754.8

(END OF REPORT)