

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035154

Luminaire Tested: S125DIW-B1270D1560UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035154
REPORT IS A COMBINATION OF REPORTS P1003218 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1560UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10632.0 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035154

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035154

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	34	31	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	30	30	27	25
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12655	12655	12655
5°	12656	12362	12385
10°	12551	12078	12040
15°	12387	11739	11634
20°	12164	11346	11168
25°	11924	10918	10669
30°	11636	10471	10143
35°	11328	10003	9554
40°	11009	9508	9031
45°	10665	9026	8474
50°	10285	8479	7826
55°	9911	7875	7230
60°	9462	7239	6536
65°	8927	6503	5819
70°	8382	5657	4991
75°	7465	4658	4035
80°	6363	3480	2969
85°	4911	2057	1636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10665 cd/sqm

TEST NUMBER: P1035154

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	1.8
10°-20°	526.5	5.0
20°-30°	777.2	7.3
30°-40°	906.8	8.5
40°-50°	910.8	8.6
50°-60°	799.5	7.5
60°-70°	595.5	5.6
70°-80°	340.1	3.2
80°-90°	101.2	1.0
90°-100°	130.8	1.2
100°-110°	388.4	3.7
110°-120°	658.8	6.2
120°-130°	867.3	8.2
130°-140°	971.8	9.1
140°-150°	952.6	9.0
150°-160°	800.2	7.5
160°-170°	531.9	5.0
170°-180°	186.1	1.8
0°-30°	1490.1	14.0
0°-40°	2396.9	22.5
0°-60°	4107.2	38.6
0°-90°	5144.1	48.4
90°-120°	1178.0	11.1
90°-150°	3969.7	37.3
90°-180°	5488.0	51.6
0°-180°	10632.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	1969	1953	1967	1966	187
15°	1880	1875	1858	1866	1866	530
25°	1706	1699	1678	1681	1677	785
35°	1474	1467	1446	1438	1425	922
45°	1206	1200	1181	1163	1158	929
55°	919	914	892	878	867	820
65°	620	617	600	586	580	615
75°	330	327	319	314	308	351
85°	86	88	88	86	83	94
90°	2	14	24	32	37	12
95°	100	102	118	128	132	104
105°	349	356	366	375	380	372
115°	660	666	669	667	666	652
125°	962	972	973	970	969	862
135°	1252	1261	1262	1262	1256	965
145°	1516	1523	1527	1527	1523	948
155°	1735	1735	1737	1743	1735	799
165°	1887	1884	1885	1891	1882	532
175°	1962	1956	1956	1965	1954	186
180°	1966	1966	1966	1966	1966	

TEST NUMBER: P1035154

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1981.5	1976.8	1961.2	1976.8	1975.2
5°	1972.1	1969.0	1953.3	1967.4	1965.8
7.5°	1958.0	1954.9	1937.7	1951.8	1950.2
10°	1937.7	1934.6	1917.4	1929.9	1928.3
12.5°	1912.7	1906.5	1890.8	1900.2	1900.2
15°	1879.9	1875.2	1858.0	1865.8	1865.8
17.5°	1845.5	1837.7	1820.5	1829.9	1822.1
20°	1800.2	1797.1	1776.8	1787.7	1779.9
22.5°	1754.9	1748.6	1729.9	1736.1	1731.4
25°	1706.4	1698.6	1678.3	1681.4	1676.7
27.5°	1650.2	1645.5	1625.2	1626.7	1622.1
30°	1595.5	1590.8	1567.4	1564.2	1559.5
32.5°	1536.1	1528.3	1508.0	1501.7	1492.4
35°	1473.6	1467.3	1445.5	1437.7	1425.2
37.5°	1409.5	1401.7	1381.4	1370.5	1362.6
40°	1343.9	1336.1	1314.2	1300.1	1295.5
42.5°	1273.6	1267.3	1245.4	1232.9	1225.1
45°	1206.4	1200.1	1181.4	1162.6	1157.9
47.5°	1132.9	1134.5	1111.1	1092.3	1081.4
50°	1062.6	1057.9	1039.2	1018.9	1007.9
52.5°	990.7	987.6	967.3	950.1	937.6
55°	918.9	914.2	892.3	878.2	867.3
57.5°	842.3	840.7	822.0	803.2	798.5
60°	770.4	764.1	747.0	731.3	720.4
62.5°	695.4	690.7	676.6	659.4	651.6
65°	620.4	617.3	600.1	586.0	579.8
67.5°	546.9	540.7	528.2	515.7	512.6
70°	478.2	470.4	456.3	446.9	440.7
72.5°	403.2	398.5	390.7	379.7	373.5
75°	329.7	326.6	318.8	314.1	307.8
77.5°	261.0	259.4	254.7	251.6	246.9
80°	196.9	196.9	193.8	192.2	189.1
82.5°	140.6	137.5	137.5	134.4	134.4
85°	85.9	87.5	87.5	85.9	82.8
87.5°	42.2	42.2	40.6	40.6	37.5
90°	1.5	13.8	24.5	32.1	36.7
92.5°	45.9	53.6	67.3	78.0	81.1
95°	99.5	102.5	117.8	128.5	131.6
97.5°	153.0	154.6	176.0	185.2	186.7
100°	214.2	214.2	234.1	247.9	251.0
102.5°	280.0	287.7	295.3	310.6	315.2
105°	348.9	356.5	365.7	374.9	379.5
107.5°	423.9	431.5	439.2	443.8	443.8
110°	501.9	509.6	514.2	518.8	517.2

TEST NUMBER: P1035154

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	581.5	584.6	590.7	592.2	589.1
115°	659.5	665.7	668.7	667.2	665.7
117.5°	739.1	740.6	743.7	745.2	739.1
120°	812.6	820.2	821.7	821.7	815.6
122.5°	892.1	893.7	898.2	896.7	892.1
125°	962.5	971.7	973.2	970.2	968.6
127.5°	1040.6	1045.2	1046.7	1045.2	1042.1
130°	1109.4	1117.1	1120.1	1118.6	1115.5
132.5°	1178.3	1192.1	1190.5	1189.0	1184.4
135°	1251.7	1260.9	1262.4	1262.4	1256.3
137.5°	1320.6	1329.8	1332.8	1334.4	1326.7
140°	1386.4	1394.0	1398.6	1401.7	1394.0
142.5°	1452.2	1458.3	1464.4	1466.0	1458.3
145°	1516.5	1522.6	1527.2	1527.2	1522.6
147.5°	1576.1	1580.7	1583.8	1588.4	1576.1
150°	1635.8	1634.3	1640.4	1640.4	1637.4
152.5°	1684.8	1687.9	1689.4	1694.0	1687.9
155°	1735.3	1735.3	1736.8	1742.9	1735.3
157.5°	1781.2	1778.1	1779.7	1785.8	1775.1
160°	1821.0	1816.4	1817.9	1824.0	1816.4
162.5°	1856.2	1853.1	1853.1	1860.8	1851.6
165°	1886.8	1883.7	1885.3	1891.4	1882.2
167.5°	1914.3	1908.2	1908.2	1917.4	1908.2
170°	1935.8	1929.6	1929.6	1938.8	1928.1
172.5°	1951.1	1944.9	1944.9	1954.1	1944.9
175°	1961.8	1955.6	1955.6	1964.8	1954.1
177.5°	1969.4	1963.3	1961.8	1970.9	1960.2
180°	1966.4	1966.4	1966.4	1966.4	1966.4

(END OF REPORT)