

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035724

Luminaire Tested: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035724
REPORT IS A COMBINATION OF REPORTS P1006039 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10506.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	37	36	34
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	33	31	30
4	73	63	55	50	67	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	48	42	61	51	45	40	43	38	34	35	31	28	27	25	23
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10412	10412	10412	10412
5°	10403	11734	10403	9019
10°	10344	13186	10309	7797
15°	10232	13951	10162	6788
20°	10096	15060	10006	6136
25°	9919	17046	9808	5569
30°	9740	18119	9594	5163
35°	9507	14901	9374	4785
40°	9093	10119	9017	4445
45°	8551	7274	8539	4111
50°	7993	5594	8032	3801
55°	7367	4549	7352	3504
60°	6784	3728	6752	3111
65°	6105	3106	6143	2504
70°	5543	2493	5520	2085
75°	4682	1889	4682	1713
80°	3794	1152	3752	1152
85°	2670	606	2596	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14820 cd/sqm

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	1.5
10°-20°	456.8	4.3
20°-30°	724.4	6.9
30°-40°	875.3	8.3
40°-50°	779.3	7.4
50°-60°	597.6	5.7
60°-70°	388.1	3.7
70°-80°	188.4	1.8
80°-90°	47.3	0.5
90°-100°	69.5	0.7
100°-110°	462.4	4.4
110°-120°	832.6	7.9
120°-130°	1068.7	10.2
130°-140°	1149.4	10.9
140°-150°	1078.8	10.3
150°-160°	872.6	8.3
160°-170°	564.3	5.4
170°-180°	194.6	1.9
0°-30°	1337.0	12.7
0°-40°	2212.3	21.1
0°-60°	3589.2	34.2
0°-90°	4213.0	40.1
90°-120°	1364.5	13.0
90°-150°	4661.4	44.4
90°-180°	6293.0	59.9
0°-180°	10506.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1625	1625	1625	1625	1625	
5°	1621	1862	1621	1432	1621	154
15°	1553	2237	1542	1089	1553	438
25°	1420	2679	1404	875	1420	654
35°	1237	2223	1219	714	1237	770
45°	967	994	966	562	967	746
55°	683	546	682	420	683	612
65°	424	310	427	250	424	424
75°	207	144	207	131	207	222
85°	47	31	45	35	47	53
90°	2	36	2	36	2	7
95°	87	32	87	32	87	106
105°	446	451	446	451	446	473
115°	838	832	838	832	838	831
125°	1192	1192	1192	1192	1192	1065
135°	1487	1481	1487	1481	1487	1146
145°	1724	1719	1724	1719	1724	1078
155°	1898	1885	1898	1885	1898	875
165°	2003	1992	2003	1992	2003	566
175°	2049	2040	2049	2040	2049	195
180°	2049	2049	2049	2049	2049	

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1626.3	1639.7	1643.7	1654.3	1666.3	1669.0	1675.7	1685.0	1690.4	1689.0	1689.0
5°	1621.0	1643.7	1659.7	1678.4	1701.0	1710.4	1718.4	1738.4	1754.4	1763.7	1779.7
7.5°	1611.6	1645.0	1671.7	1699.7	1734.4	1750.4	1767.7	1795.8	1825.1	1843.8	1861.1
10°	1597.0	1639.7	1677.0	1718.4	1765.1	1789.1	1810.4	1853.1	1889.1	1913.2	1953.2
12.5°	1575.6	1629.0	1681.0	1735.7	1794.4	1819.8	1849.1	1895.8	1946.5	1981.2	2014.6
15°	1552.9	1617.0	1673.0	1738.4	1809.1	1847.8	1885.1	1934.5	1979.9	2018.6	2057.2
17.5°	1526.3	1594.3	1663.7	1738.4	1818.4	1857.1	1889.1	1947.8	1995.9	2034.6	2069.3
20°	1494.2	1570.3	1649.0	1731.7	1813.1	1849.1	1879.8	1943.8	1986.5	2027.9	2077.3
22.5°	1459.6	1542.3	1626.3	1707.7	1787.7	1826.4	1862.5	1918.5	1965.2	2021.2	2085.3
25°	1419.5	1510.2	1595.6	1677.0	1753.1	1789.1	1821.1	1882.5	1947.8	2018.6	2090.6
27.5°	1379.5	1467.6	1550.3	1625.0	1707.7	1741.1	1773.1	1850.5	1927.8	2002.5	2101.3
30°	1335.5	1424.9	1496.9	1566.3	1646.3	1681.0	1721.0	1809.1	1897.1	1998.5	2118.6
32.5°	1286.1	1367.5	1434.2	1506.2	1578.3	1621.0	1671.7	1767.7	1869.1	1990.5	2144.0
35°	1236.7	1302.1	1363.5	1431.5	1518.3	1563.6	1613.0	1714.4	1841.1	1986.5	2165.3
37.5°	1174.0	1236.7	1284.8	1354.2	1443.5	1496.9	1546.3	1663.7	1807.8	1977.2	2164.0
40°	1110.0	1163.4	1208.7	1280.8	1378.2	1427.5	1480.9	1609.0	1773.1	1950.5	2132.0
42.5°	1040.6	1086.0	1135.4	1204.7	1299.5	1347.5	1408.9	1558.3	1725.0	1913.2	2049.2
45°	967.3	1011.3	1052.6	1124.7	1219.4	1271.4	1338.1	1491.6	1666.3	1834.4	1915.8
47.5°	895.2	933.9	977.9	1040.6	1136.7	1194.1	1262.1	1426.2	1587.6	1729.0	1735.7
50°	825.8	856.5	893.9	957.9	1058.0	1112.7	1183.4	1336.8	1494.2	1591.6	1526.3
52.5°	753.8	781.8	820.5	876.5	969.9	1034.0	1095.3	1248.8	1380.8	1446.2	1326.1
55°	683.1	707.1	747.1	809.8	891.2	940.6	1003.3	1146.0	1262.1	1263.4	1132.7
57.5°	613.7	635.1	668.4	724.4	800.5	857.9	915.2	1039.3	1118.0	1095.3	949.9
60°	552.3	565.7	596.4	651.1	721.8	763.1	824.5	928.6	980.6	939.2	783.1
62.5°	488.3	501.6	525.7	569.7	636.4	680.4	719.1	804.5	840.5	777.8	649.7
65°	424.3	440.3	457.6	492.3	555.0	584.4	619.0	681.7	716.4	643.1	532.3
67.5°	368.2	376.2	393.6	429.6	473.6	500.3	524.3	567.0	573.7	515.0	424.3
70°	316.2	318.9	334.9	356.2	389.6	405.6	425.6	450.9	450.9	402.9	330.9
72.5°	257.5	261.5	273.5	296.2	316.2	324.2	330.9	346.9	344.2	300.2	250.8
75°	206.8	209.5	218.8	229.5	237.5	252.2	257.5	254.8	253.5	216.1	188.1
77.5°	160.1	161.4	168.1	177.4	178.8	184.1	180.1	180.1	168.1	146.8	132.1
80°	117.4	118.7	121.4	124.1	124.1	124.1	124.1	117.4	109.4	96.1	92.1
82.5°	78.7	78.7	80.0	82.7	81.4	78.7	76.0	69.4	64.0	60.0	57.4
85°	46.7	46.7	48.0	46.7	41.4	40.0	37.4	36.0	34.7	33.4	33.4
87.5°	22.7	21.3	18.7	16.0	16.0	16.0	16.0	16.0	16.0	14.7	14.7
90°	1.5	4.2	6.9	9.6	12.3	13.7	14.9	17.2	19.6	21.9	24.3
92.5°	28.9	25.9	22.8	19.8	16.7	15.2	16.2	18.2	20.3	22.3	24.3
95°	86.6	85.6	84.6	83.5	82.5	82.0	75.6	62.8	49.9	37.1	24.3
97.5°	162.5	164.5	166.5	168.6	170.6	171.6	155.6	123.5	91.4	59.4	27.3
100°	253.6	254.6	255.6	256.7	257.7	258.2	258.9	260.2	261.5	262.9	264.2
102.5°	346.2	347.6	348.9	350.3	351.6	352.3	352.6	353.3	354.0	354.7	355.4
105°	446.5	447.9	449.2	450.6	451.9	452.6	452.6	452.6	452.6	452.6	452.6
107.5°	549.7	549.7	549.7	549.7	549.7	549.7	550.0	550.7	551.4	552.1	552.8
110°	650.0	650.0	650.0	650.0	650.0	650.0	650.3	651.0	651.7	652.3	653.0



TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	744.1	745.1	746.1	747.2	748.2	748.7	748.9	749.2	749.5	749.9	750.2
115°	838.3	840.0	841.7	843.4	845.1	845.9	846.1	846.4	846.7	847.1	847.4
117.5°	937.0	937.0	937.0	937.0	937.0	937.0	937.7	939.0	940.4	941.7	943.1
120°	1028.1	1027.8	1027.4	1027.1	1026.8	1026.6	1027.1	1028.1	1029.1	1030.1	1031.1
122.5°	1108.6	1110.3	1112.0	1113.7	1115.4	1116.2	1116.4	1116.7	1117.0	1117.4	1117.7
125°	1192.1	1194.5	1196.9	1199.2	1201.6	1202.8	1202.8	1202.8	1202.8	1202.8	1202.8
127.5°	1272.6	1274.3	1276.0	1277.7	1279.4	1280.2	1280.0	1279.7	1279.4	1279.0	1278.7
130°	1345.5	1347.2	1348.9	1350.6	1352.3	1353.1	1353.3	1353.6	1353.9	1354.3	1354.6
132.5°	1418.4	1420.4	1422.4	1424.5	1426.5	1427.5	1427.0	1426.0	1425.0	1424.0	1423.0
135°	1486.7	1488.7	1490.7	1492.8	1494.8	1495.8	1495.5	1494.8	1494.1	1493.5	1492.8
137.5°	1550.5	1552.5	1554.5	1556.6	1558.6	1559.6	1559.3	1558.6	1557.9	1557.3	1556.6
140°	1612.8	1613.5	1614.1	1614.8	1615.5	1615.8	1615.6	1615.3	1615.0	1614.6	1614.3
142.5°	1669.0	1669.3	1669.7	1670.0	1670.3	1670.5	1670.8	1671.5	1672.2	1672.8	1673.5
145°	1723.6	1724.3	1725.0	1725.7	1726.4	1726.7	1726.7	1726.7	1726.7	1726.7	1726.7
147.5°	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2	1772.4	1772.7	1773.1	1773.4	1773.8
150°	1817.8	1817.1	1816.5	1815.8	1815.1	1814.8	1815.1	1815.8	1816.5	1817.1	1817.8
152.5°	1861.8	1860.1	1858.4	1856.7	1855.0	1854.2	1854.5	1855.2	1855.9	1856.6	1857.3
155°	1898.3	1896.3	1894.3	1892.2	1890.2	1889.2	1889.5	1890.2	1890.9	1891.5	1892.2
157.5°	1927.1	1926.1	1925.1	1924.1	1923.1	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6
160°	1957.5	1955.5	1953.5	1951.4	1949.4	1948.4	1948.6	1948.9	1949.2	1949.6	1949.9
162.5°	1981.8	1979.8	1977.8	1975.7	1973.7	1972.7	1972.9	1973.2	1973.5	1973.9	1974.2
165°	2003.1	2001.1	1999.1	1997.0	1995.0	1994.0	1994.2	1994.5	1994.8	1995.2	1995.5
167.5°	2019.8	2017.8	2015.8	2013.7	2011.7	2010.7	2010.9	2011.2	2011.5	2011.9	2012.2
170°	2033.4	2031.0	2028.7	2026.3	2024.0	2022.8	2023.0	2023.3	2023.6	2024.0	2024.3
172.5°	2042.6	2040.2	2037.8	2035.5	2033.1	2031.9	2032.2	2032.9	2033.6	2034.3	2035.0
175°	2048.6	2046.6	2044.6	2042.5	2040.5	2039.5	2039.7	2040.0	2040.3	2040.7	2041.0
177.5°	2053.2	2051.2	2049.2	2047.1	2045.1	2044.1	2044.3	2044.6	2044.9	2045.3	2045.6
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1695.7	1705.0	1713.0	1709.0	1725.0	1723.7	1726.4	1731.7	1733.0	1730.4	1725.0
5°	1787.7	1801.1	1823.8	1835.8	1833.1	1843.8	1849.1	1857.1	1865.1	1862.5	1862.5
7.5°	1890.5	1909.2	1931.8	1962.5	1966.5	1975.9	1991.9	1991.9	2001.2	1997.2	1995.9
10°	1979.9	2002.5	2038.6	2062.6	2073.3	2078.6	2094.6	2099.9	2110.6	2111.9	2111.9
12.5°	2053.2	2093.3	2117.3	2141.3	2146.6	2154.6	2166.6	2174.7	2178.7	2178.7	2174.7
15°	2091.9	2124.0	2152.0	2177.3	2192.0	2198.7	2210.7	2220.0	2225.3	2237.4	2240.0
17.5°	2107.9	2146.6	2192.0	2228.0	2253.4	2260.0	2284.1	2292.1	2302.7	2308.1	2314.7
20°	2130.6	2186.7	2241.4	2285.4	2309.4	2326.7	2352.1	2389.4	2400.1	2400.1	2396.1
22.5°	2150.6	2222.7	2297.4	2368.1	2388.1	2422.8	2469.5	2509.5	2525.5	2532.2	2526.9
25°	2174.7	2273.4	2370.8	2458.8	2513.5	2538.9	2601.6	2649.6	2668.3	2679.0	2681.6
27.5°	2216.0	2340.1	2464.2	2576.2	2632.3	2661.6	2727.0	2768.3	2791.0	2800.4	2793.7
30°	2262.7	2414.8	2558.9	2658.9	2696.3	2732.3	2775.0	2791.0	2785.7	2785.7	2805.7
32.5°	2310.7	2468.2	2596.2	2661.6	2675.0	2669.6	2652.3	2604.2	2576.2	2576.2	2593.6
35°	2337.4	2473.5	2538.9	2517.5	2465.5	2434.8	2340.1	2286.7	2226.7	2222.7	2242.7
37.5°	2322.7	2381.4	2354.8	2214.7	2144.0	2085.3	1937.2	1878.5	1834.4	1773.1	1867.8
40°	2220.0	2200.0	2061.2	1859.8	1781.1	1698.4	1581.0	1522.3	1460.9	1451.5	1474.2
42.5°	2046.6	1927.8	1725.0	1530.3	1450.2	1391.5	1302.1	1244.8	1206.1	1190.1	1216.7
45°	1830.4	1643.7	1440.9	1286.1	1198.1	1167.4	1086.0	1035.3	1005.9	993.9	1012.6
47.5°	1566.3	1378.2	1186.1	1055.3	1003.3	972.6	917.9	873.9	848.5	840.5	848.5
50°	1330.1	1136.7	975.3	891.2	844.5	819.2	773.8	745.8	725.8	720.4	733.8
52.5°	1126.0	949.9	827.2	752.5	721.8	700.4	668.4	644.4	632.4	627.0	636.4
55°	943.2	800.5	701.8	637.7	615.0	601.7	573.7	560.3	547.0	545.7	555.0
57.5°	781.8	683.1	592.4	547.0	540.3	520.3	496.3	484.3	477.6	476.3	480.3
60°	651.1	563.0	508.3	468.3	458.9	442.9	429.6	421.6	413.6	410.9	413.6
62.5°	541.7	472.3	428.3	401.6	388.2	384.2	369.6	360.2	358.9	358.9	361.6
65°	446.9	388.2	360.2	338.9	329.5	325.5	314.9	308.2	309.5	309.5	310.9
67.5°	364.2	321.5	296.2	285.5	277.5	276.2	265.5	262.8	260.2	260.2	262.8
70°	289.5	262.8	244.1	238.8	237.5	228.1	224.1	222.8	218.8	220.1	220.1
72.5°	226.8	209.5	198.8	190.8	192.1	186.8	181.4	181.4	178.8	182.8	182.8
75°	168.1	160.1	152.1	149.4	152.1	149.4	145.4	144.1	145.4	144.1	144.1
77.5°	124.1	120.1	117.4	116.1	116.1	110.7	108.1	110.7	105.4	108.1	108.1
80°	86.7	81.4	80.0	77.4	78.7	74.7	76.0	73.4	73.4	73.4	73.4
82.5°	54.7	53.4	53.4	53.4	52.0	52.0	52.0	52.0	52.0	52.0	50.7
85°	33.4	32.0	32.0	32.0	30.7	30.7	30.7	30.7	30.7	30.7	30.7
87.5°	13.3	14.7	14.7	16.0	14.7	13.3	13.3	13.3	14.7	14.7	13.3
90°	26.0	27.7	29.4	31.1	31.9	32.4	33.4	34.4	35.4	36.4	35.4
92.5°	26.0	27.7	29.4	31.1	31.9	32.1	32.4	32.7	33.1	33.4	33.1
95°	26.0	27.7	29.4	31.1	31.9	31.9	31.9	31.9	31.9	31.9	31.9
97.5°	28.0	28.7	29.4	30.1	30.4	30.6	30.9	31.2	31.6	31.9	31.6
100°	213.9	163.7	113.4	63.1	38.0	37.3	36.0	34.6	33.3	31.9	33.3
102.5°	356.1	356.7	357.4	358.1	358.4	344.2	315.9	287.5	259.2	230.8	259.2
105°	452.6	452.6	452.6	452.6	452.6	452.4	452.1	451.7	451.4	451.0	451.4
107.5°	553.1	553.5	553.8	554.1	554.3	553.6	552.3	550.9	549.6	548.2	549.6
110°	652.0	651.0	650.0	649.0	648.5	648.7	649.0	649.3	649.7	650.0	649.7

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	748.8	747.5	746.1	744.8	744.1	743.8	743.1	742.4	741.8	741.1	741.8
115°	846.0	844.7	843.3	842.0	841.3	840.3	838.3	836.2	834.2	832.2	834.2
117.5°	941.1	939.1	937.0	935.0	934.0	933.7	933.0	932.3	931.6	930.9	931.6
120°	1030.4	1029.8	1029.1	1028.4	1028.1	1027.3	1025.6	1023.9	1022.2	1020.5	1022.2
122.5°	1117.0	1116.4	1115.7	1115.0	1114.7	1113.7	1111.7	1109.6	1107.6	1105.6	1107.6
125°	1201.4	1200.1	1198.7	1197.4	1196.7	1196.2	1195.2	1194.1	1193.1	1192.1	1193.1
127.5°	1278.0	1277.3	1276.6	1275.9	1275.6	1274.3	1271.6	1268.9	1266.2	1263.5	1266.2
130°	1353.6	1352.6	1351.6	1350.6	1350.1	1349.3	1347.6	1345.9	1344.2	1342.5	1344.2
132.5°	1423.0	1423.0	1423.0	1423.0	1423.0	1422.2	1420.5	1418.8	1417.1	1415.4	1417.1
135°	1492.1	1491.5	1490.8	1490.1	1489.8	1488.8	1486.8	1484.7	1482.7	1480.7	1482.7
137.5°	1556.6	1556.6	1556.6	1556.6	1556.6	1555.8	1554.1	1552.4	1550.7	1549.0	1550.7
140°	1615.0	1615.6	1616.3	1617.0	1617.3	1616.3	1614.3	1612.2	1610.2	1608.2	1610.2
142.5°	1673.5	1673.5	1673.5	1673.5	1673.5	1672.5	1670.5	1668.4	1666.4	1664.4	1666.4
145°	1727.0	1727.4	1727.7	1728.0	1728.2	1727.2	1725.2	1723.1	1721.1	1719.1	1721.1
147.5°	1774.1	1774.5	1774.8	1775.1	1775.3	1774.1	1771.7	1769.4	1767.0	1764.6	1767.0
150°	1818.5	1819.1	1819.8	1820.5	1820.8	1819.5	1816.8	1814.1	1811.4	1808.7	1811.4
152.5°	1858.0	1858.6	1859.3	1860.0	1860.3	1859.1	1856.8	1854.4	1852.1	1849.7	1852.1
155°	1893.2	1894.2	1895.3	1896.3	1896.8	1895.4	1892.7	1890.0	1887.3	1884.6	1887.3
157.5°	1923.6	1924.6	1925.6	1926.6	1927.1	1925.8	1923.1	1920.4	1917.7	1915.0	1917.7
160°	1951.3	1952.6	1954.0	1955.3	1956.0	1954.6	1951.9	1949.2	1946.5	1943.8	1946.5
162.5°	1976.2	1978.2	1980.3	1982.3	1983.3	1981.8	1978.8	1975.7	1972.7	1969.7	1972.7
165°	1997.5	1999.5	2001.6	2003.6	2004.6	2003.2	2000.5	1997.8	1995.1	1992.4	1995.1
167.5°	2014.6	2016.9	2019.3	2021.6	2022.8	2021.3	2018.2	2015.2	2012.1	2009.1	2012.1
170°	2027.0	2029.7	2032.4	2035.1	2036.5	2035.0	2031.9	2028.9	2025.8	2022.8	2025.8
172.5°	2037.4	2039.7	2042.1	2044.4	2045.6	2044.1	2041.0	2038.0	2034.9	2031.9	2034.9
175°	2043.7	2046.4	2049.1	2051.8	2053.2	2051.7	2048.6	2045.6	2042.5	2039.5	2042.5
177.5°	2048.0	2050.3	2052.7	2055.0	2056.2	2054.9	2052.2	2049.5	2046.8	2044.1	2046.8
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1731.7	1722.4	1726.4	1722.4	1718.4	1714.4	1705.0	1691.7	1681.0	1673.0	1671.7
5°	1865.1	1853.1	1845.1	1841.1	1833.1	1822.4	1805.1	1785.1	1761.1	1751.7	1733.0
7.5°	1987.9	1983.9	1965.2	1962.5	1957.2	1937.2	1907.8	1881.1	1850.5	1825.1	1801.1
10°	2103.9	2094.6	2081.3	2062.6	2059.9	2034.6	2006.5	1969.2	1929.2	1905.2	1862.5
12.5°	2176.0	2165.3	2150.6	2138.6	2132.0	2115.9	2077.3	2039.9	2003.9	1959.9	1922.5
15°	2228.0	2214.7	2188.0	2178.7	2170.6	2149.3	2121.3	2082.6	2034.6	2003.9	1950.5
17.5°	2298.7	2282.7	2256.0	2238.7	2224.0	2190.7	2150.6	2098.6	2053.2	2018.6	1970.5
20°	2380.1	2356.1	2321.4	2298.7	2277.4	2238.7	2182.7	2121.3	2055.9	2013.2	1963.9
22.5°	2514.9	2469.5	2414.8	2382.8	2353.4	2286.7	2220.0	2144.0	2070.6	2006.5	1946.5
25°	2645.6	2600.2	2532.2	2488.2	2442.8	2365.4	2277.4	2172.0	2078.6	2003.9	1925.2
27.5°	2767.0	2720.3	2657.6	2604.2	2560.2	2444.1	2328.1	2209.3	2090.6	1987.9	1907.8
30°	2795.0	2775.0	2727.0	2680.3	2640.3	2533.5	2398.8	2248.0	2105.3	1973.2	1883.8
32.5°	2625.6	2675.0	2687.0	2680.3	2654.9	2578.9	2454.8	2296.1	2126.6	1966.5	1843.8
35°	2273.4	2362.8	2454.8	2504.2	2528.2	2538.9	2465.5	2320.1	2141.3	1955.9	1817.1
37.5°	1885.1	1971.9	2117.3	2190.7	2272.0	2378.8	2408.1	2314.7	2134.6	1947.8	1774.4
40°	1548.9	1659.7	1779.7	1846.5	1917.2	2109.3	2254.7	2244.0	2113.3	1918.5	1741.1
42.5°	1260.8	1330.1	1435.5	1508.9	1595.6	1810.4	2005.2	2101.3	2049.2	1882.5	1698.4
45°	1051.3	1104.7	1179.4	1254.1	1307.5	1502.2	1733.0	1890.5	1939.8	1818.4	1633.0
47.5°	885.9	925.9	991.3	1038.0	1095.3	1248.8	1448.9	1670.3	1774.4	1727.7	1563.6
50°	759.1	791.1	843.2	872.5	923.2	1055.3	1207.4	1439.5	1597.0	1602.3	1471.6
52.5°	648.4	680.4	724.4	749.8	780.5	869.9	1023.3	1219.4	1400.8	1467.6	1366.2
55°	564.3	583.0	619.0	639.1	667.1	753.8	851.2	1017.9	1207.4	1316.8	1252.8
57.5°	487.0	507.0	529.7	545.7	565.7	635.1	723.1	848.5	1036.6	1155.4	1134.0
60°	424.3	436.3	457.6	469.6	488.3	533.7	595.0	720.4	869.9	981.9	993.9
62.5°	365.6	376.2	390.9	401.6	413.6	449.6	495.0	584.4	715.1	836.5	852.5
65°	314.9	324.2	332.2	341.5	350.9	373.6	412.2	481.6	583.0	696.4	731.1
67.5°	269.5	272.2	284.2	285.5	290.8	308.2	336.2	392.2	465.6	556.3	601.7
70°	225.5	230.8	233.5	237.5	242.8	254.8	277.5	306.9	361.6	434.9	477.6
72.5°	182.8	184.1	188.1	190.8	196.1	205.5	216.1	238.8	273.5	326.9	365.6
75°	145.4	146.8	149.4	150.8	154.8	157.4	162.8	178.8	202.8	234.8	262.8
77.5°	109.4	112.1	114.7	114.7	116.1	118.7	121.4	126.7	138.8	160.1	184.1
80°	74.7	76.0	76.0	77.4	76.0	80.0	84.1	90.7	96.1	102.7	114.7
82.5°	52.0	52.0	52.0	53.4	53.4	54.7	54.7	56.0	57.4	61.4	66.7
85°	32.0	32.0	33.4	30.7	32.0	33.4	33.4	32.0	33.4	34.7	36.0
87.5°	13.3	13.3	14.7	14.7	14.7	14.7	13.3	14.7	13.3	14.7	14.7
90°	34.4	33.4	32.4	31.9	31.1	29.4	27.7	26.0	24.3	21.9	19.6
92.5°	32.7	32.4	32.1	31.9	31.1	29.4	27.7	26.0	24.3	22.3	20.3
95°	31.9	31.9	31.9	31.9	31.1	29.4	27.7	26.0	24.3	37.1	49.9
97.5°	31.2	30.9	30.6	30.4	30.1	29.4	28.7	28.0	27.3	59.4	91.4
100°	34.6	36.0	37.3	38.0	63.1	113.4	163.7	213.9	264.2	262.9	261.5
102.5°	287.5	315.9	344.2	358.4	358.1	357.4	356.7	356.1	355.4	354.7	354.0
105°	451.7	452.1	452.4	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
107.5°	550.9	552.3	553.6	554.3	554.1	553.8	553.5	553.1	552.8	552.1	551.4
110°	649.3	649.0	648.7	648.5	649.0	650.0	651.0	652.0	653.0	652.3	651.7

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	742.4	743.1	743.8	744.1	744.8	746.1	747.5	748.8	750.2	749.9	749.5
115°	836.2	838.3	840.3	841.3	842.0	843.3	844.7	846.0	847.4	847.1	846.7
117.5°	932.3	933.0	933.7	934.0	935.0	937.0	939.1	941.1	943.1	941.7	940.4
120°	1023.9	1025.6	1027.3	1028.1	1028.4	1029.1	1029.8	1030.4	1031.1	1030.1	1029.1
122.5°	1109.6	1111.7	1113.7	1114.7	1115.0	1115.7	1116.4	1117.0	1117.7	1117.4	1117.0
125°	1194.1	1195.2	1196.2	1196.7	1197.4	1198.7	1200.1	1201.4	1202.8	1202.8	1202.8
127.5°	1268.9	1271.6	1274.3	1275.6	1275.9	1276.6	1277.3	1278.0	1278.7	1279.0	1279.4
130°	1345.9	1347.6	1349.3	1350.1	1350.6	1351.6	1352.6	1353.6	1354.6	1354.3	1353.9
132.5°	1418.8	1420.5	1422.2	1423.0	1423.0	1423.0	1423.0	1423.0	1423.0	1424.0	1425.0
135°	1484.7	1486.8	1488.8	1489.8	1490.1	1490.8	1491.5	1492.1	1492.8	1493.5	1494.1
137.5°	1552.4	1554.1	1555.8	1556.6	1556.6	1556.6	1556.6	1556.6	1556.6	1557.3	1557.9
140°	1612.2	1614.3	1616.3	1617.3	1617.0	1616.3	1615.6	1615.0	1614.3	1614.6	1615.0
142.5°	1668.4	1670.5	1672.5	1673.5	1673.5	1673.5	1673.5	1673.5	1673.5	1672.8	1672.2
145°	1723.1	1725.2	1727.2	1728.2	1728.0	1727.7	1727.4	1727.0	1726.7	1726.7	1726.7
147.5°	1769.4	1771.7	1774.1	1775.3	1775.1	1774.8	1774.5	1774.1	1773.8	1773.4	1773.1
150°	1814.1	1816.8	1819.5	1820.8	1820.5	1819.8	1819.1	1818.5	1817.8	1817.1	1816.5
152.5°	1854.4	1856.8	1859.1	1860.3	1860.0	1859.3	1858.6	1858.0	1857.3	1856.6	1855.9
155°	1890.0	1892.7	1895.4	1896.8	1896.3	1895.3	1894.2	1893.2	1892.2	1891.5	1890.9
157.5°	1920.4	1923.1	1925.8	1927.1	1926.6	1925.6	1924.6	1923.6	1922.6	1922.6	1922.6
160°	1949.2	1951.9	1954.6	1956.0	1955.3	1954.0	1952.6	1951.3	1949.9	1949.6	1949.2
162.5°	1975.7	1978.8	1981.8	1983.3	1982.3	1980.3	1978.2	1976.2	1974.2	1973.9	1973.5
165°	1997.8	2000.5	2003.2	2004.6	2003.6	2001.6	1999.5	1997.5	1995.5	1995.2	1994.8
167.5°	2015.2	2018.2	2021.3	2022.8	2021.6	2019.3	2016.9	2014.6	2012.2	2011.9	2011.5
170°	2028.9	2031.9	2035.0	2036.5	2035.1	2032.4	2029.7	2027.0	2024.3	2024.0	2023.6
172.5°	2038.0	2041.0	2044.1	2045.6	2044.4	2042.1	2039.7	2037.4	2035.0	2034.3	2033.6
175°	2045.6	2048.6	2051.7	2053.2	2051.8	2049.1	2046.4	2043.7	2041.0	2040.7	2040.3
177.5°	2049.5	2052.2	2054.9	2056.2	2055.0	2052.7	2050.3	2048.0	2045.6	2045.3	2044.9
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1667.7	1659.7	1654.3	1653.0	1645.0	1638.3	1630.3	1629.0	1625.0	1614.3	1607.6
5°	1719.7	1701.0	1697.0	1685.0	1665.0	1650.3	1631.7	1621.0	1609.0	1589.0	1573.0
7.5°	1773.1	1747.7	1729.0	1711.7	1683.7	1657.0	1630.3	1609.0	1587.6	1558.3	1534.3
10°	1825.1	1786.4	1763.7	1738.4	1699.7	1659.7	1622.3	1591.6	1556.9	1522.3	1487.6
12.5°	1873.1	1823.8	1790.4	1754.4	1706.4	1657.0	1609.0	1566.3	1530.3	1483.6	1444.9
15°	1902.5	1847.8	1814.4	1779.7	1707.7	1653.0	1597.0	1542.3	1494.2	1444.9	1408.9
17.5°	1919.8	1858.5	1821.1	1789.1	1715.7	1641.0	1569.0	1510.2	1458.2	1399.5	1351.5
20°	1911.8	1851.8	1817.1	1786.4	1701.0	1626.3	1548.9	1480.9	1415.5	1355.5	1304.8
22.5°	1894.5	1831.8	1793.1	1765.1	1689.0	1601.0	1515.6	1442.2	1374.2	1314.1	1256.8
25°	1857.1	1795.8	1762.4	1727.7	1653.0	1569.0	1482.2	1403.5	1331.5	1267.4	1203.4
27.5°	1823.8	1749.1	1714.4	1683.7	1605.0	1530.3	1444.9	1358.2	1284.8	1218.1	1154.0
30°	1785.1	1701.0	1663.7	1622.3	1551.6	1480.9	1395.5	1315.5	1239.4	1168.7	1107.3
32.5°	1743.7	1646.3	1603.6	1556.9	1484.9	1418.2	1346.1	1267.4	1191.4	1122.0	1058.0
35°	1690.4	1586.3	1536.9	1492.9	1418.2	1351.5	1284.8	1219.4	1143.4	1070.0	1008.6
37.5°	1639.7	1524.9	1472.9	1422.2	1343.5	1279.4	1224.7	1163.4	1090.0	1019.3	960.6
40°	1582.3	1450.2	1396.8	1350.2	1268.8	1198.1	1148.7	1100.7	1036.6	968.6	904.5
42.5°	1530.3	1380.8	1324.8	1276.8	1191.4	1124.7	1078.0	1038.0	981.9	919.2	853.9
45°	1458.2	1306.1	1248.8	1198.1	1111.3	1048.6	1000.6	965.9	921.9	863.2	804.5
47.5°	1391.5	1234.1	1171.4	1110.0	1031.3	967.3	923.2	896.5	867.2	815.2	755.1
50°	1310.1	1151.4	1087.3	1036.6	947.2	892.5	848.5	829.8	803.2	753.8	705.8
52.5°	1222.1	1071.3	1011.3	949.9	867.2	813.8	775.1	753.8	732.4	696.4	651.1
55°	1119.3	981.9	925.9	871.2	788.5	739.1	704.4	681.7	669.7	636.4	603.0
57.5°	1020.6	891.2	839.2	788.5	716.4	660.4	637.7	617.7	600.4	576.3	548.3
60°	920.6	803.2	747.1	701.8	639.1	588.4	569.7	549.7	536.3	517.6	497.6
62.5°	805.8	705.8	663.1	620.4	567.0	527.0	505.6	489.6	472.3	460.3	442.9
65°	684.4	613.7	572.3	540.3	489.6	453.6	437.6	426.9	412.2	400.2	386.9
67.5°	571.0	515.0	497.6	462.9	424.3	392.2	380.2	366.9	354.9	348.2	336.2
70°	461.6	421.6	404.2	394.9	352.2	330.9	320.2	314.9	300.2	293.5	285.5
72.5°	357.5	342.9	330.9	318.9	290.8	277.5	265.5	260.2	249.5	244.1	241.5
75°	264.2	254.8	248.2	246.8	234.8	221.5	209.5	206.8	198.8	193.5	190.8
77.5°	185.4	182.8	181.4	182.8	174.8	166.8	164.1	161.4	152.1	150.8	150.8
80°	121.4	128.1	128.1	126.7	124.1	122.7	118.7	116.1	110.7	109.4	110.7
82.5°	74.7	78.7	80.0	82.7	81.4	80.0	77.4	76.0	77.4	74.7	76.0
85°	37.4	40.0	45.4	45.4	46.7	46.7	46.7	45.4	42.7	44.0	42.7
87.5°	14.7	16.0	16.0	16.0	14.7	18.7	20.0	20.0	20.0	17.3	17.3
90°	17.2	14.9	13.7	12.3	9.6	6.9	4.2	1.5	4.2	6.9	9.6
92.5°	18.2	16.2	15.2	16.7	19.8	22.8	25.9	28.9	25.9	22.8	19.8
95°	62.8	75.6	82.0	82.5	83.5	84.6	85.6	86.6	85.6	84.6	83.5
97.5°	123.5	155.6	171.6	170.6	168.6	166.5	164.5	162.5	164.5	166.5	168.6
100°	260.2	258.9	258.2	257.7	256.7	255.6	254.6	253.6	254.6	255.6	256.7
102.5°	353.3	352.6	352.3	351.6	350.3	348.9	347.6	346.2	347.6	348.9	350.3
105°	452.6	452.6	452.6	451.9	450.6	449.2	447.9	446.5	447.9	449.2	450.6
107.5°	550.7	550.0	549.7	549.7	549.7	549.7	549.7	549.7	549.7	549.7	549.7
110°	651.0	650.3	650.0	650.0	650.0	650.0	650.0	650.0	650.0	650.0	650.0

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	749.2	748.9	748.7	748.2	747.2	746.1	745.1	744.1	745.1	746.1	747.2
115°	846.4	846.1	845.9	845.1	843.4	841.7	840.0	838.3	840.0	841.7	843.4
117.5°	939.0	937.7	937.0	937.0	937.0	937.0	937.0	937.0	937.0	937.0	937.0
120°	1028.1	1027.1	1026.6	1026.8	1027.1	1027.4	1027.8	1028.1	1027.8	1027.4	1027.1
122.5°	1116.7	1116.4	1116.2	1115.4	1113.7	1112.0	1110.3	1108.6	1110.3	1112.0	1113.7
125°	1202.8	1202.8	1202.8	1201.6	1199.2	1196.9	1194.5	1192.1	1194.5	1196.9	1199.2
127.5°	1279.7	1280.0	1280.2	1279.4	1277.7	1276.0	1274.3	1272.6	1274.3	1276.0	1277.7
130°	1353.6	1353.3	1353.1	1352.3	1350.6	1348.9	1347.2	1345.5	1347.2	1348.9	1350.6
132.5°	1426.0	1427.0	1427.5	1426.5	1424.5	1422.4	1420.4	1418.4	1420.4	1422.4	1424.5
135°	1494.8	1495.5	1495.8	1494.8	1492.8	1490.7	1488.7	1486.7	1488.7	1490.7	1492.8
137.5°	1558.6	1559.3	1559.6	1558.6	1556.6	1554.5	1552.5	1550.5	1552.5	1554.5	1556.6
140°	1615.3	1615.6	1615.8	1615.5	1614.8	1614.1	1613.5	1612.8	1613.5	1614.1	1614.8
142.5°	1671.5	1670.8	1670.5	1670.3	1670.0	1669.7	1669.3	1669.0	1669.3	1669.7	1670.0
145°	1726.7	1726.7	1726.7	1726.4	1725.7	1725.0	1724.3	1723.6	1724.3	1725.0	1725.7
147.5°	1772.7	1772.4	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2
150°	1815.8	1815.1	1814.8	1815.1	1815.8	1816.5	1817.1	1817.8	1817.1	1816.5	1815.8
152.5°	1855.2	1854.5	1854.2	1855.0	1856.7	1858.4	1860.1	1861.8	1860.1	1858.4	1856.7
155°	1890.2	1889.5	1889.2	1890.2	1892.2	1894.3	1896.3	1898.3	1896.3	1894.3	1892.2
157.5°	1922.6	1922.6	1922.6	1923.1	1924.1	1925.1	1926.1	1927.1	1926.1	1925.1	1924.1
160°	1948.9	1948.6	1948.4	1949.4	1951.4	1953.5	1955.5	1957.5	1955.5	1953.5	1951.4
162.5°	1973.2	1972.9	1972.7	1973.7	1975.7	1977.8	1979.8	1981.8	1979.8	1977.8	1975.7
165°	1994.5	1994.2	1994.0	1995.0	1997.0	1999.1	2001.1	2003.1	2001.1	1999.1	1997.0
167.5°	2011.2	2010.9	2010.7	2011.7	2013.7	2015.8	2017.8	2019.8	2017.8	2015.8	2013.7
170°	2023.3	2023.0	2022.8	2024.0	2026.3	2028.7	2031.0	2033.4	2031.0	2028.7	2026.3
172.5°	2032.9	2032.2	2031.9	2033.1	2035.5	2037.8	2040.2	2042.6	2040.2	2037.8	2035.5
175°	2040.0	2039.7	2039.5	2040.5	2042.5	2044.6	2046.6	2048.6	2046.6	2044.6	2042.5
177.5°	2044.6	2044.3	2044.1	2045.1	2047.1	2049.2	2051.2	2053.2	2051.2	2049.2	2047.1
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1603.6	1598.3	1594.3	1590.3	1573.0	1554.3	1551.6	1547.6	1539.6	1548.9	1544.9
5°	1562.3	1550.3	1543.6	1526.3	1504.9	1488.9	1475.6	1459.6	1452.9	1447.5	1446.2
7.5°	1511.6	1500.9	1488.9	1471.6	1444.9	1418.2	1398.2	1382.2	1368.8	1362.2	1362.2
10°	1462.2	1448.9	1432.9	1403.5	1378.2	1344.8	1323.5	1307.5	1288.8	1278.1	1268.8
12.5°	1411.5	1396.8	1382.2	1344.8	1315.5	1280.8	1250.1	1230.1	1220.7	1208.7	1192.7
15°	1360.8	1338.1	1323.5	1286.1	1248.8	1214.1	1194.1	1172.7	1151.4	1139.4	1134.0
17.5°	1307.5	1291.4	1267.4	1227.4	1186.1	1155.4	1126.0	1106.0	1080.7	1068.6	1056.6
20°	1259.4	1235.4	1211.4	1171.4	1131.4	1090.0	1060.6	1036.6	1020.6	1011.3	1000.6
22.5°	1202.1	1179.4	1159.4	1116.7	1072.6	1034.0	1001.9	987.3	971.3	956.6	945.9
25°	1152.7	1130.0	1110.0	1063.3	1015.3	979.3	955.2	936.6	919.2	912.6	901.9
27.5°	1100.7	1079.3	1052.6	1005.9	963.3	932.6	907.2	889.9	876.5	863.2	855.2
30°	1051.3	1027.3	1003.3	952.6	917.9	887.2	863.2	841.8	831.2	824.5	811.2
32.5°	1003.3	972.6	952.6	905.9	872.5	843.2	823.2	804.5	791.1	779.1	768.5
35°	951.2	917.9	897.9	859.2	824.5	795.1	777.8	764.5	748.5	737.8	732.4
37.5°	901.9	873.9	853.9	813.8	779.1	755.1	736.4	719.1	712.4	697.8	695.1
40°	848.5	824.5	805.8	767.1	735.1	716.4	696.4	680.4	668.4	661.7	652.4
42.5°	800.5	780.5	760.5	724.4	693.8	671.1	656.4	641.7	631.0	620.4	613.7
45°	756.5	735.1	716.4	681.7	651.1	631.0	616.4	599.0	596.4	581.7	575.0
47.5°	709.8	691.1	675.1	639.1	611.0	591.0	573.7	561.7	549.7	544.3	535.0
50°	664.4	645.7	627.0	595.0	569.7	549.7	532.3	519.0	512.3	504.3	496.3
52.5°	615.0	600.4	585.7	552.3	527.0	509.6	495.0	477.6	471.0	464.3	458.9
55°	573.7	552.3	536.3	508.3	485.6	466.9	450.9	437.6	430.9	425.6	418.9
57.5°	517.6	504.3	491.0	465.6	444.3	425.6	409.6	398.9	390.9	386.9	388.2
60°	469.6	454.9	446.9	420.3	398.9	384.2	369.6	358.9	350.9	346.9	345.5
62.5°	418.9	408.2	393.6	374.9	353.5	340.2	329.5	321.5	308.2	306.9	302.9
65°	369.6	361.6	348.2	330.9	313.5	301.5	289.5	278.8	273.5	266.8	262.8
67.5°	321.5	313.5	301.5	286.8	274.8	262.8	252.2	241.5	232.1	226.8	224.1
70°	274.8	268.2	260.2	242.8	228.1	218.8	210.8	204.1	194.8	192.1	190.8
72.5°	229.5	222.8	218.8	204.1	190.8	182.8	174.8	168.1	164.1	162.8	158.8
75°	188.1	181.4	176.1	162.8	154.8	149.4	141.4	138.8	134.7	133.4	132.1
77.5°	146.8	140.1	138.8	129.4	120.1	117.4	114.7	109.4	109.4	109.4	106.7
80°	105.4	104.1	102.7	93.4	89.4	86.7	85.4	81.4	78.7	76.0	74.7
82.5°	70.7	69.4	68.0	64.0	60.0	58.7	57.4	54.7	54.7	56.0	53.4
85°	42.7	40.0	38.7	37.4	34.7	34.7	36.0	34.7	34.7	34.7	33.4
87.5°	16.0	16.0	16.0	16.0	17.3	14.7	16.0	16.0	14.7	14.7	13.3
90°	12.3	13.7	14.9	17.2	19.6	21.9	24.3	26.0	27.7	29.4	31.1
92.5°	16.7	15.2	16.2	18.2	20.3	22.3	24.3	26.0	27.7	29.4	31.1
95°	82.5	82.0	75.6	62.8	49.9	37.1	24.3	26.0	27.7	29.4	31.1
97.5°	170.6	171.6	155.6	123.5	91.4	59.4	27.3	28.0	28.7	29.4	30.1
100°	257.7	258.2	258.9	260.2	261.5	262.9	264.2	213.9	163.7	113.4	63.1
102.5°	351.6	352.3	352.6	353.3	354.0	354.7	355.4	356.1	356.7	357.4	358.1
105°	451.9	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
107.5°	549.7	549.7	550.0	550.7	551.4	552.1	552.8	553.1	553.5	553.8	554.1
110°	650.0	650.0	650.3	651.0	651.7	652.3	653.0	652.0	651.0	650.0	649.0

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	748.2	748.7	748.9	749.2	749.5	749.9	750.2	748.8	747.5	746.1	744.8
115°	845.1	845.9	846.1	846.4	846.7	847.1	847.4	846.0	844.7	843.3	842.0
117.5°	937.0	937.0	937.7	939.0	940.4	941.7	943.1	941.1	939.1	937.0	935.0
120°	1026.8	1026.6	1027.1	1028.1	1029.1	1030.1	1031.1	1030.4	1029.8	1029.1	1028.4
122.5°	1115.4	1116.2	1116.4	1116.7	1117.0	1117.4	1117.7	1117.0	1116.4	1115.7	1115.0
125°	1201.6	1202.8	1202.8	1202.8	1202.8	1202.8	1202.8	1201.4	1200.1	1198.7	1197.4
127.5°	1279.4	1280.2	1280.0	1279.7	1279.4	1279.0	1278.7	1278.0	1277.3	1276.6	1275.9
130°	1352.3	1353.1	1353.3	1353.6	1353.9	1354.3	1354.6	1353.6	1352.6	1351.6	1350.6
132.5°	1426.5	1427.5	1427.0	1426.0	1425.0	1424.0	1423.0	1423.0	1423.0	1423.0	1423.0
135°	1494.8	1495.8	1495.5	1494.8	1494.1	1493.5	1492.8	1492.1	1491.5	1490.8	1490.1
137.5°	1558.6	1559.6	1559.3	1558.6	1557.9	1557.3	1556.6	1556.6	1556.6	1556.6	1556.6
140°	1615.5	1615.8	1615.6	1615.3	1615.0	1614.6	1614.3	1615.0	1615.6	1616.3	1617.0
142.5°	1670.3	1670.5	1670.8	1671.5	1672.2	1672.8	1673.5	1673.5	1673.5	1673.5	1673.5
145°	1726.4	1726.7	1726.7	1726.7	1726.7	1726.7	1726.7	1727.0	1727.4	1727.7	1728.0
147.5°	1772.2	1772.2	1772.4	1772.7	1773.1	1773.4	1773.8	1774.1	1774.5	1774.8	1775.1
150°	1815.1	1814.8	1815.1	1815.8	1816.5	1817.1	1817.8	1818.5	1819.1	1819.8	1820.5
152.5°	1855.0	1854.2	1854.5	1855.2	1855.9	1856.6	1857.3	1858.0	1858.6	1859.3	1860.0
155°	1890.2	1889.2	1889.5	1890.2	1890.9	1891.5	1892.2	1893.2	1894.2	1895.3	1896.3
157.5°	1923.1	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1923.6	1924.6	1925.6	1926.6
160°	1949.4	1948.4	1948.6	1948.9	1949.2	1949.6	1949.9	1951.3	1952.6	1954.0	1955.3
162.5°	1973.7	1972.7	1972.9	1973.2	1973.5	1973.9	1974.2	1976.2	1978.2	1980.3	1982.3
165°	1995.0	1994.0	1994.2	1994.5	1994.8	1995.2	1995.5	1997.5	1999.5	2001.6	2003.6
167.5°	2011.7	2010.7	2010.9	2011.2	2011.5	2011.9	2012.2	2014.6	2016.9	2019.3	2021.6
170°	2024.0	2022.8	2023.0	2023.3	2023.6	2024.0	2024.3	2027.0	2029.7	2032.4	2035.1
172.5°	2033.1	2031.9	2032.2	2032.9	2033.6	2034.3	2035.0	2037.4	2039.7	2042.1	2044.4
175°	2040.5	2039.5	2039.7	2040.0	2040.3	2040.7	2041.0	2043.7	2046.4	2049.1	2051.8
177.5°	2045.1	2044.1	2044.3	2044.6	2044.9	2045.3	2045.6	2048.0	2050.3	2052.7	2055.0
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1538.3	1540.9	1534.3	1531.6	1526.3	1532.9	1534.3	1532.9	1544.9	1539.6	1542.3
5°	1448.9	1443.5	1439.5	1430.2	1430.2	1431.5	1435.5	1428.9	1432.9	1442.2	1440.9
7.5°	1350.2	1347.5	1348.8	1338.1	1330.1	1332.8	1330.1	1342.1	1348.8	1346.1	1351.5
10°	1260.8	1266.1	1254.1	1248.8	1243.4	1248.8	1247.4	1250.1	1258.1	1263.4	1272.8
12.5°	1188.7	1187.4	1180.7	1175.4	1166.0	1168.7	1176.7	1174.0	1175.4	1187.4	1186.1
15°	1120.7	1112.7	1107.3	1095.3	1098.0	1088.7	1096.7	1106.0	1110.0	1120.7	1127.3
17.5°	1052.6	1051.3	1044.6	1043.3	1028.6	1024.6	1032.6	1035.3	1039.3	1044.6	1054.0
20°	995.3	993.9	984.6	981.9	969.9	977.9	975.3	980.6	983.3	993.9	997.9
22.5°	943.2	936.6	933.9	929.9	925.9	924.6	929.9	928.6	937.9	941.9	943.2
25°	895.2	889.9	888.5	881.9	879.2	875.2	879.2	883.2	893.9	897.9	903.2
27.5°	851.2	847.2	844.5	839.2	835.2	835.2	837.8	843.2	847.2	849.8	852.5
30°	811.2	808.5	800.5	797.8	793.8	793.8	793.8	796.5	803.2	811.2	815.2
32.5°	769.8	764.5	759.1	759.1	755.1	755.1	756.5	759.1	765.8	767.1	773.8
35°	729.8	724.4	720.4	717.8	719.1	713.8	716.4	720.4	728.4	731.1	735.1
37.5°	691.1	689.8	681.7	677.7	680.4	680.4	679.1	681.7	687.1	692.4	695.1
40°	648.4	645.7	645.7	641.7	643.1	637.7	641.7	644.4	647.1	652.4	656.4
42.5°	611.0	608.4	603.0	604.4	600.4	600.4	603.0	604.4	608.4	615.0	617.7
45°	571.0	571.0	568.3	564.3	565.7	561.7	564.3	565.7	571.0	577.7	575.0
47.5°	532.3	531.0	531.0	525.7	528.3	524.3	528.3	529.7	532.3	536.3	535.0
50°	495.0	491.0	492.3	491.0	489.6	489.6	492.3	492.3	495.0	495.0	499.0
52.5°	456.3	456.3	453.6	454.9	457.6	454.9	458.9	454.9	457.6	458.9	461.6
55°	421.6	418.9	420.3	418.9	424.3	420.3	424.3	421.6	424.3	422.9	425.6
57.5°	384.2	380.2	381.6	380.2	384.2	382.9	386.9	382.9	384.2	385.6	389.6
60°	341.5	341.5	341.5	338.9	342.9	342.9	341.5	341.5	346.9	349.5	348.2
62.5°	301.5	300.2	296.2	294.8	296.2	293.5	298.8	297.5	300.2	302.9	305.5
65°	257.5	254.8	253.5	250.8	250.8	249.5	250.8	256.2	257.5	258.8	265.5
67.5°	221.5	220.1	218.8	214.8	214.8	217.5	217.5	217.5	225.5	221.5	226.8
70°	189.4	186.8	184.1	182.8	182.8	184.1	185.4	186.8	185.4	190.8	192.1
72.5°	158.8	160.1	157.4	157.4	157.4	156.1	156.1	158.8	160.1	158.8	160.1
75°	132.1	132.1	130.7	132.1	132.1	130.7	130.7	133.4	133.4	132.1	136.1
77.5°	106.7	105.4	102.7	100.1	101.4	100.1	101.4	100.1	104.1	108.1	105.4
80°	74.7	73.4	73.4	73.4	74.7	73.4	76.0	73.4	74.7	74.7	76.0
82.5°	53.4	54.7	54.7	53.4	54.7	53.4	54.7	54.7	54.7	53.4	54.7
85°	34.7	34.7	34.7	34.7	33.4	34.7	34.7	34.7	36.0	34.7	36.0
87.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	16.0	14.7	16.0
90°	31.9	32.4	33.4	34.4	35.4	36.4	35.4	34.4	33.4	32.4	31.9
92.5°	31.9	32.1	32.4	32.7	33.1	33.4	33.1	32.7	32.4	32.1	31.9
95°	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9
97.5°	30.4	30.6	30.9	31.2	31.6	31.9	31.6	31.2	30.9	30.6	30.4
100°	38.0	37.3	36.0	34.6	33.3	31.9	33.3	34.6	36.0	37.3	38.0
102.5°	358.4	344.2	315.9	287.5	259.2	230.8	259.2	287.5	315.9	344.2	358.4
105°	452.6	452.4	452.1	451.7	451.4	451.0	451.4	451.7	452.1	452.4	452.6
107.5°	554.3	553.6	552.3	550.9	549.6	548.2	549.6	550.9	552.3	553.6	554.3
110°	648.5	648.7	649.0	649.3	649.7	650.0	649.7	649.3	649.0	648.7	648.5

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	744.1	743.8	743.1	742.4	741.8	741.1	741.8	742.4	743.1	743.8	744.1
115°	841.3	840.3	838.3	836.2	834.2	832.2	834.2	836.2	838.3	840.3	841.3
117.5°	934.0	933.7	933.0	932.3	931.6	930.9	931.6	932.3	933.0	933.7	934.0
120°	1028.1	1027.3	1025.6	1023.9	1022.2	1020.5	1022.2	1023.9	1025.6	1027.3	1028.1
122.5°	1114.7	1113.7	1111.7	1109.6	1107.6	1105.6	1107.6	1109.6	1111.7	1113.7	1114.7
125°	1196.7	1196.2	1195.2	1194.1	1193.1	1192.1	1193.1	1194.1	1195.2	1196.2	1196.7
127.5°	1275.6	1274.3	1271.6	1268.9	1266.2	1263.5	1266.2	1268.9	1271.6	1274.3	1275.6
130°	1350.1	1349.3	1347.6	1345.9	1344.2	1342.5	1344.2	1345.9	1347.6	1349.3	1350.1
132.5°	1423.0	1422.2	1420.5	1418.8	1417.1	1415.4	1417.1	1418.8	1420.5	1422.2	1423.0
135°	1489.8	1488.8	1486.8	1484.7	1482.7	1480.7	1482.7	1484.7	1486.8	1488.8	1489.8
137.5°	1556.6	1555.8	1554.1	1552.4	1550.7	1549.0	1550.7	1552.4	1554.1	1555.8	1556.6
140°	1617.3	1616.3	1614.3	1612.2	1610.2	1608.2	1610.2	1612.2	1614.3	1616.3	1617.3
142.5°	1673.5	1672.5	1670.5	1668.4	1666.4	1664.4	1666.4	1668.4	1670.5	1672.5	1673.5
145°	1728.2	1727.2	1725.2	1723.1	1721.1	1719.1	1721.1	1723.1	1725.2	1727.2	1728.2
147.5°	1775.3	1774.1	1771.7	1769.4	1767.0	1764.6	1767.0	1769.4	1771.7	1774.1	1775.3
150°	1820.8	1819.5	1816.8	1814.1	1811.4	1808.7	1811.4	1814.1	1816.8	1819.5	1820.8
152.5°	1860.3	1859.1	1856.8	1854.4	1852.1	1849.7	1852.1	1854.4	1856.8	1859.1	1860.3
155°	1896.8	1895.4	1892.7	1890.0	1887.3	1884.6	1887.3	1890.0	1892.7	1895.4	1896.8
157.5°	1927.1	1925.8	1923.1	1920.4	1917.7	1915.0	1917.7	1920.4	1923.1	1925.8	1927.1
160°	1956.0	1954.6	1951.9	1949.2	1946.5	1943.8	1946.5	1949.2	1951.9	1954.6	1956.0
162.5°	1983.3	1981.8	1978.8	1975.7	1972.7	1969.7	1972.7	1975.7	1978.8	1981.8	1983.3
165°	2004.6	2003.2	2000.5	1997.8	1995.1	1992.4	1995.1	1997.8	2000.5	2003.2	2004.6
167.5°	2022.8	2021.3	2018.2	2015.2	2012.1	2009.1	2012.1	2015.2	2018.2	2021.3	2022.8
170°	2036.5	2035.0	2031.9	2028.9	2025.8	2022.8	2025.8	2028.9	2031.9	2035.0	2036.5
172.5°	2045.6	2044.1	2041.0	2038.0	2034.9	2031.9	2034.9	2038.0	2041.0	2044.1	2045.6
175°	2053.2	2051.7	2048.6	2045.6	2042.5	2039.5	2042.5	2045.6	2048.6	2051.7	2053.2
177.5°	2056.2	2054.9	2052.2	2049.5	2046.8	2044.1	2046.8	2049.5	2052.2	2054.9	2056.2
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1536.9	1543.6	1538.3	1534.3	1544.9	1550.3	1550.3	1559.6	1569.0	1577.0	1578.3
5°	1442.2	1452.9	1455.5	1454.2	1470.2	1478.2	1495.6	1504.9	1518.3	1527.6	1538.3
7.5°	1355.5	1370.2	1371.5	1374.2	1398.2	1411.5	1426.2	1450.2	1468.9	1482.2	1494.2
10°	1268.8	1278.1	1287.4	1299.5	1323.5	1346.1	1367.5	1392.8	1416.9	1430.2	1447.5
12.5°	1203.4	1210.1	1220.7	1228.7	1254.1	1274.1	1302.1	1336.8	1371.5	1382.2	1403.5
15°	1135.4	1139.4	1160.7	1168.7	1190.1	1223.4	1240.8	1274.1	1311.5	1331.5	1355.5
17.5°	1056.6	1080.7	1094.0	1103.3	1130.0	1156.7	1184.7	1219.4	1267.4	1286.1	1303.5
20°	1000.6	1017.9	1032.6	1044.6	1068.6	1108.7	1134.0	1162.0	1207.4	1228.7	1254.1
22.5°	951.2	965.9	979.3	992.6	1008.6	1044.6	1074.0	1112.7	1158.0	1178.0	1207.4
25°	904.5	919.2	927.2	943.2	964.6	989.9	1024.6	1059.3	1104.7	1127.3	1155.4
27.5°	859.2	873.9	888.5	901.9	916.6	940.6	964.6	1008.6	1055.3	1082.0	1106.0
30°	820.5	827.2	840.5	855.2	869.9	892.5	920.6	951.2	1004.6	1028.6	1058.0
32.5°	777.8	789.8	799.2	809.8	828.5	847.2	872.5	911.2	953.9	976.6	1008.6
35°	737.8	748.5	755.1	773.8	785.8	805.8	831.2	865.9	901.9	927.2	955.2
37.5°	699.1	709.8	717.8	728.4	744.5	761.8	788.5	813.8	856.5	877.9	909.9
40°	659.1	668.4	677.7	689.8	704.4	725.8	741.8	773.8	808.5	832.5	856.5
42.5°	620.4	625.7	636.4	649.7	664.4	683.1	705.8	731.1	765.8	787.1	808.5
45°	579.0	588.4	600.4	609.7	623.0	641.7	661.7	684.4	719.1	740.4	763.1
47.5°	540.3	547.0	555.0	569.7	587.0	600.4	621.7	643.1	675.1	695.1	716.4
50°	500.3	507.0	519.0	528.3	541.7	559.0	579.0	601.7	632.4	645.7	667.1
52.5°	462.9	465.6	477.6	487.0	500.3	520.3	536.3	556.3	585.7	600.4	621.7
55°	425.6	428.3	434.9	444.3	458.9	475.0	492.3	515.0	540.3	553.7	573.7
57.5°	386.9	389.6	396.2	402.9	417.6	432.3	452.3	471.0	496.3	508.3	527.0
60°	348.2	348.2	354.9	364.2	374.9	388.2	405.6	428.3	446.9	461.6	475.0
62.5°	306.9	310.9	314.9	321.5	333.5	349.5	364.2	380.2	402.9	413.6	425.6
65°	265.5	269.5	277.5	284.2	293.5	304.2	322.9	336.2	353.5	365.6	376.2
67.5°	229.5	233.5	238.8	246.8	253.5	265.5	278.8	292.2	310.9	318.9	326.9
70°	192.1	196.1	200.1	210.8	217.5	226.8	236.1	249.5	265.5	270.8	277.5
72.5°	162.8	164.1	169.4	172.1	181.4	189.4	200.1	208.1	220.1	226.8	232.1
75°	137.4	137.4	138.8	141.4	146.8	152.1	160.1	168.1	178.8	182.8	189.4
77.5°	108.1	112.1	110.7	113.4	116.1	118.7	125.4	130.7	141.4	144.1	146.8
80°	77.4	78.7	82.7	86.7	86.7	90.7	94.7	96.1	102.7	106.7	106.7
82.5°	56.0	57.4	56.0	57.4	58.7	60.0	64.0	69.4	69.4	70.7	73.4
85°	34.7	34.7	36.0	37.4	37.4	36.0	38.7	37.4	38.7	41.4	41.4
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	16.0	17.3	17.3	17.3
90°	31.1	29.4	27.7	26.0	24.3	21.9	19.6	17.2	14.9	13.7	12.3
92.5°	31.1	29.4	27.7	26.0	24.3	22.3	20.3	18.2	16.2	15.2	16.7
95°	31.1	29.4	27.7	26.0	24.3	37.1	49.9	62.8	75.6	82.0	82.5
97.5°	30.1	29.4	28.7	28.0	27.3	59.4	91.4	123.5	155.6	171.6	170.6
100°	63.1	113.4	163.7	213.9	264.2	262.9	261.5	260.2	258.9	258.2	257.7
102.5°	358.1	357.4	356.7	356.1	355.4	354.7	354.0	353.3	352.6	352.3	351.6
105°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	451.9
107.5°	554.1	553.8	553.5	553.1	552.8	552.1	551.4	550.7	550.0	549.7	549.7
110°	649.0	650.0	651.0	652.0	653.0	652.3	651.7	651.0	650.3	650.0	650.0

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	744.8	746.1	747.5	748.8	750.2	749.9	749.5	749.2	748.9	748.7	748.2
115°	842.0	843.3	844.7	846.0	847.4	847.1	846.7	846.4	846.1	845.9	845.1
117.5°	935.0	937.0	939.1	941.1	943.1	941.7	940.4	939.0	937.7	937.0	937.0
120°	1028.4	1029.1	1029.8	1030.4	1031.1	1030.1	1029.1	1028.1	1027.1	1026.6	1026.8
122.5°	1115.0	1115.7	1116.4	1117.0	1117.7	1117.4	1117.0	1116.7	1116.4	1116.2	1115.4
125°	1197.4	1198.7	1200.1	1201.4	1202.8	1202.8	1202.8	1202.8	1202.8	1202.8	1201.6
127.5°	1275.9	1276.6	1277.3	1278.0	1278.7	1279.0	1279.4	1279.7	1280.0	1280.2	1279.4
130°	1350.6	1351.6	1352.6	1353.6	1354.6	1354.3	1353.9	1353.6	1353.3	1353.1	1352.3
132.5°	1423.0	1423.0	1423.0	1423.0	1423.0	1424.0	1425.0	1426.0	1427.0	1427.5	1426.5
135°	1490.1	1490.8	1491.5	1492.1	1492.8	1493.5	1494.1	1494.8	1495.5	1495.8	1494.8
137.5°	1556.6	1556.6	1556.6	1556.6	1556.6	1557.3	1557.9	1558.6	1559.3	1559.6	1558.6
140°	1617.0	1616.3	1615.6	1615.0	1614.3	1614.6	1615.0	1615.3	1615.6	1615.8	1615.5
142.5°	1673.5	1673.5	1673.5	1673.5	1673.5	1672.8	1672.2	1671.5	1670.8	1670.5	1670.3
145°	1728.0	1727.7	1727.4	1727.0	1726.7	1726.7	1726.7	1726.7	1726.7	1726.7	1726.4
147.5°	1775.1	1774.8	1774.5	1774.1	1773.8	1773.4	1773.1	1772.7	1772.4	1772.2	1772.2
150°	1820.5	1819.8	1819.1	1818.5	1817.8	1817.1	1816.5	1815.8	1815.1	1814.8	1815.1
152.5°	1860.0	1859.3	1858.6	1858.0	1857.3	1856.6	1855.9	1855.2	1854.5	1854.2	1855.0
155°	1896.3	1895.3	1894.2	1893.2	1892.2	1891.5	1890.9	1890.2	1889.5	1889.2	1890.2
157.5°	1926.6	1925.6	1924.6	1923.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1923.1
160°	1955.3	1954.0	1952.6	1951.3	1949.9	1949.6	1949.2	1948.9	1948.6	1948.4	1949.4
162.5°	1982.3	1980.3	1978.2	1976.2	1974.2	1973.9	1973.5	1973.2	1972.9	1972.7	1973.7
165°	2003.6	2001.6	1999.5	1997.5	1995.5	1995.2	1994.8	1994.5	1994.2	1994.0	1995.0
167.5°	2021.6	2019.3	2016.9	2014.6	2012.2	2011.9	2011.5	2011.2	2010.9	2010.7	2011.7
170°	2035.1	2032.4	2029.7	2027.0	2024.3	2024.0	2023.6	2023.3	2023.0	2022.8	2024.0
172.5°	2044.4	2042.1	2039.7	2037.4	2035.0	2034.3	2033.6	2032.9	2032.2	2031.9	2033.1
175°	2051.8	2049.1	2046.4	2043.7	2041.0	2040.7	2040.3	2040.0	2039.7	2039.5	2040.5
177.5°	2055.0	2052.7	2050.3	2048.0	2045.6	2045.3	2044.9	2044.6	2044.3	2044.1	2045.1
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1625.0	1625.0	1625.0	1625.0
2.5°	1587.6	1599.6	1611.6	1626.3
5°	1555.6	1577.0	1599.6	1621.0
7.5°	1520.9	1551.6	1581.0	1611.6
10°	1482.2	1520.9	1554.3	1597.0
12.5°	1439.5	1480.9	1527.6	1575.6
15°	1396.8	1448.9	1498.2	1552.9
17.5°	1356.8	1406.2	1460.9	1526.3
20°	1308.8	1363.5	1424.9	1494.2
22.5°	1258.1	1318.1	1384.8	1459.6
25°	1215.4	1276.8	1340.8	1419.5
27.5°	1168.7	1232.7	1295.5	1379.5
30°	1115.3	1184.7	1248.8	1335.5
32.5°	1064.6	1134.0	1204.7	1286.1
35°	1015.3	1083.3	1154.0	1236.7
37.5°	968.6	1030.0	1099.3	1174.0
40°	924.6	980.6	1042.0	1110.0
42.5°	868.5	933.9	991.3	1040.6
45°	820.5	873.9	927.2	967.3
47.5°	764.5	817.8	863.2	895.2
50°	717.8	760.5	797.8	825.8
52.5°	661.7	701.8	732.4	753.8
55°	607.0	641.7	668.4	683.1
57.5°	557.7	580.4	600.4	613.7
60°	503.0	520.3	537.7	552.3
62.5°	444.3	462.9	472.3	488.3
65°	392.2	404.2	418.9	424.3
67.5°	341.5	348.2	357.5	368.2
70°	288.2	292.2	301.5	316.2
72.5°	241.5	245.5	252.2	257.5
75°	192.1	196.1	201.5	206.8
77.5°	150.8	152.1	154.8	160.1
80°	109.4	113.4	116.1	117.4
82.5°	76.0	77.4	77.4	78.7
85°	48.0	45.4	45.4	46.7
87.5°	17.3	20.0	20.0	22.7
90°	9.6	6.9	4.2	1.5
92.5°	19.8	22.8	25.9	28.9
95°	83.5	84.6	85.6	86.6
97.5°	168.6	166.5	164.5	162.5
100°	256.7	255.6	254.6	253.6
102.5°	350.3	348.9	347.6	346.2
105°	450.6	449.2	447.9	446.5
107.5°	549.7	549.7	549.7	549.7
110°	650.0	650.0	650.0	650.0

TEST NUMBER: P1035724

CATALOG NUMBER: S125RDIW-B1090D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	747.2	746.1	745.1	744.1
115°	843.4	841.7	840.0	838.3
117.5°	937.0	937.0	937.0	937.0
120°	1027.1	1027.4	1027.8	1028.1
122.5°	1113.7	1112.0	1110.3	1108.6
125°	1199.2	1196.9	1194.5	1192.1
127.5°	1277.7	1276.0	1274.3	1272.6
130°	1350.6	1348.9	1347.2	1345.5
132.5°	1424.5	1422.4	1420.4	1418.4
135°	1492.8	1490.7	1488.7	1486.7
137.5°	1556.6	1554.5	1552.5	1550.5
140°	1614.8	1614.1	1613.5	1612.8
142.5°	1670.0	1669.7	1669.3	1669.0
145°	1725.7	1725.0	1724.3	1723.6
147.5°	1772.2	1772.2	1772.2	1772.2
150°	1815.8	1816.5	1817.1	1817.8
152.5°	1856.7	1858.4	1860.1	1861.8
155°	1892.2	1894.3	1896.3	1898.3
157.5°	1924.1	1925.1	1926.1	1927.1
160°	1951.4	1953.5	1955.5	1957.5
162.5°	1975.7	1977.8	1979.8	1981.8
165°	1997.0	1999.1	2001.1	2003.1
167.5°	2013.7	2015.8	2017.8	2019.8
170°	2026.3	2028.7	2031.0	2033.4
172.5°	2035.5	2037.8	2040.2	2042.6
175°	2042.5	2044.6	2046.6	2048.6
177.5°	2047.1	2049.2	2051.2	2053.2
180°	2048.6	2048.6	2048.6	2048.6

(END OF REPORT)