

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035166

Luminaire Tested: S125DIW-B1270D1560UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035166
REPORT IS A COMBINATION OF REPORTS P1003236 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1560UB40-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10571.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035166

CATALOG NUMBER: S125DIW-B1270D1560UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035166

CATALOG NUMBER: S125DIW-B1270D1560UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	34	31	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	30	30	27	25
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12582	12582	12582
5°	12582	12289	12313
10°	12478	12008	11970
15°	12314	11671	11566
20°	12093	11280	11103
25°	11855	10854	10607
30°	11568	10410	10084
35°	11262	9944	9498
40°	10945	9452	8978
45°	10602	8973	8425
50°	10225	8429	7780
55°	9852	7829	7187
60°	9407	7197	6498
65°	8875	6465	5785
70°	8333	5623	4961
75°	7422	4630	4011
80°	6324	3458	2951
85°	4883	2046	1626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10602 cd/sqm

TEST NUMBER: P1035166

CATALOG NUMBER: S125DIW-B1270D1560UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.3	1.8
10°-20°	523.4	5.0
20°-30°	772.7	7.3
30°-40°	901.5	8.5
40°-50°	905.5	8.6
50°-60°	794.8	7.5
60°-70°	592.0	5.6
70°-80°	338.1	3.2
80°-90°	100.6	1.0
90°-100°	130.0	1.2
100°-110°	386.3	3.7
110°-120°	655.1	6.2
120°-130°	862.4	8.2
130°-140°	966.4	9.1
140°-150°	947.2	9.0
150°-160°	795.6	7.5
160°-170°	528.9	5.0
170°-180°	185.1	1.8
0°-30°	1481.4	14.0
0°-40°	2383.0	22.5
0°-60°	4083.2	38.6
0°-90°	5114.0	48.4
90°-120°	1171.4	11.1
90°-150°	3947.4	37.3
90°-180°	5457.0	51.6
0°-180°	10571.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1961	1958	1942	1956	1954	186
15°	1869	1864	1847	1855	1855	527
25°	1696	1689	1668	1672	1667	781
35°	1465	1459	1437	1429	1417	916
45°	1199	1193	1174	1156	1151	924
55°	914	909	887	873	862	815
65°	617	614	597	583	576	612
75°	328	325	317	312	306	349
85°	85	87	87	85	82	94
90°	2	14	24	32	36	12
95°	99	102	117	128	131	103
105°	347	354	364	373	377	370
115°	656	662	665	663	662	649
125°	957	966	968	965	963	858
135°	1245	1254	1255	1255	1249	959
145°	1508	1514	1519	1519	1514	943
155°	1726	1726	1727	1733	1726	795
165°	1876	1873	1875	1881	1872	529
175°	1951	1945	1945	1954	1943	185
180°	1955	1955	1955	1955	1955	

TEST NUMBER: P1035166

CATALOG NUMBER: S125DIW-B1270D1560UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1963.7	1963.7	1963.7	1963.7	1963.7
2.5°	1969.9	1965.2	1949.7	1965.2	1963.7
5°	1960.6	1957.5	1941.9	1955.9	1954.4
7.5°	1946.6	1943.5	1926.4	1940.4	1938.8
10°	1926.4	1923.3	1906.2	1918.6	1917.1
12.5°	1901.5	1895.3	1879.8	1889.1	1889.1
15°	1868.9	1864.3	1847.2	1854.9	1854.9
17.5°	1834.7	1827.0	1809.9	1819.2	1811.4
20°	1789.7	1786.6	1766.4	1777.3	1769.5
22.5°	1744.6	1738.4	1719.8	1726.0	1721.3
25°	1696.5	1688.7	1668.5	1671.6	1667.0
27.5°	1640.6	1635.9	1615.7	1617.2	1612.6
30°	1586.2	1581.5	1558.2	1555.1	1550.4
32.5°	1527.1	1519.4	1499.2	1493.0	1483.6
35°	1465.0	1458.8	1437.0	1429.3	1416.8
37.5°	1401.3	1393.5	1373.3	1362.5	1354.7
40°	1336.1	1328.3	1306.5	1292.6	1287.9
42.5°	1266.1	1259.9	1238.2	1225.8	1218.0
45°	1199.3	1193.1	1174.5	1155.8	1151.2
47.5°	1126.3	1127.9	1104.6	1085.9	1075.1
50°	1056.4	1051.8	1033.1	1012.9	1002.0
52.5°	985.0	981.8	961.6	944.6	932.1
55°	913.5	908.8	887.1	873.1	862.2
57.5°	837.4	835.8	817.2	798.5	793.9
60°	765.9	759.7	742.6	727.1	716.2
62.5°	691.3	686.7	672.7	655.6	647.8
65°	616.8	613.7	596.6	582.6	576.4
67.5°	543.7	537.5	525.1	512.7	509.6
70°	475.4	467.6	453.6	444.3	438.1
72.5°	400.8	396.2	388.4	377.5	371.3
75°	327.8	324.7	316.9	312.3	306.0
77.5°	259.4	257.9	253.2	250.1	245.5
80°	195.7	195.7	192.6	191.1	188.0
82.5°	139.8	136.7	136.7	133.6	133.6
85°	85.4	87.0	87.0	85.4	82.3
87.5°	41.9	41.9	40.4	40.4	37.3
90°	1.5	13.7	24.3	32.0	36.5
92.5°	45.6	53.3	67.0	77.6	80.6
95°	98.9	101.9	117.2	127.8	130.9
97.5°	152.2	153.7	175.0	184.1	185.6
100°	213.0	213.0	232.8	246.5	249.5
102.5°	278.5	286.1	293.7	308.9	313.4
105°	346.9	354.5	363.7	372.8	377.4
107.5°	421.5	429.1	436.7	441.3	441.3
110°	499.1	506.7	511.3	515.8	514.3

TEST NUMBER: P1035166

CATALOG NUMBER: S125DIW-B1270D1560UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.2	581.3	587.3	588.9	585.8
115°	655.8	661.9	664.9	663.4	661.9
117.5°	734.9	736.5	739.5	741.0	734.9
120°	808.0	815.6	817.1	817.1	811.0
122.5°	887.1	888.6	893.2	891.7	887.1
125°	957.1	966.2	967.7	964.7	963.2
127.5°	1034.7	1039.3	1040.8	1039.3	1036.2
130°	1103.2	1110.8	1113.8	1112.3	1109.2
132.5°	1171.6	1185.3	1183.8	1182.3	1177.7
135°	1244.7	1253.8	1255.3	1255.3	1249.2
137.5°	1313.1	1322.3	1325.3	1326.8	1319.2
140°	1378.6	1386.2	1390.7	1393.8	1386.2
142.5°	1444.0	1450.1	1456.2	1457.7	1450.1
145°	1507.9	1514.0	1518.6	1518.6	1514.0
147.5°	1567.2	1571.8	1574.9	1579.4	1567.2
150°	1626.6	1625.1	1631.2	1631.2	1628.1
152.5°	1675.3	1678.3	1679.8	1684.4	1678.3
155°	1725.5	1725.5	1727.0	1733.1	1725.5
157.5°	1771.1	1768.1	1769.6	1775.7	1765.1
160°	1810.7	1806.1	1807.7	1813.7	1806.1
162.5°	1845.7	1842.7	1842.7	1850.3	1841.1
165°	1876.1	1873.1	1874.6	1880.7	1871.6
167.5°	1903.5	1897.4	1897.4	1906.6	1897.4
170°	1924.8	1918.7	1918.7	1927.9	1917.2
172.5°	1940.0	1934.0	1934.0	1943.1	1934.0
175°	1950.7	1944.6	1944.6	1953.7	1943.1
177.5°	1958.3	1952.2	1950.7	1959.8	1949.2
180°	1955.3	1955.3	1955.3	1955.3	1955.3

(END OF REPORT)