

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035743

Luminaire Tested: S125RDIW-B1090D470UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035743
REPORT IS A COMBINATION OF REPORTS P1006081 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D470UB35-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5867.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035743

CATALOG NUMBER: S125RDIW-B1090D470UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035743

CATALOG NUMBER: S125RDIW-B1090D470UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	99	95	91	98	94	90	87	84	82	79	76	74	72	68	66	65
2	94	87	80	75	89	82	77	72	74	70	66	67	64	61	60	58	55
3	86	76	69	63	81	73	66	61	66	60	56	59	55	52	54	50	47
4	79	68	60	54	75	65	57	52	59	53	48	53	48	45	48	44	41
5	73	61	52	46	69	58	50	45	53	47	42	48	43	39	43	39	36
6	67	55	46	40	63	52	45	39	48	41	37	44	38	34	40	35	32
7	62	50	41	36	59	48	40	35	43	37	33	40	34	30	36	32	28
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	26
9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11433	11433	11433
5°	11434	11148	11166
10°	11323	10867	10771
15°	11162	10474	10253
20°	10964	10001	9708
25°	10737	9539	9125
30°	10458	9031	8512
35°	10174	8515	7861
40°	9903	7985	7225
45°	9579	7414	6560
50°	9250	6807	5881
55°	8867	6209	5179
60°	8476	5525	4451
65°	8009	4762	3665
70°	7466	3876	2884
75°	6714	2915	2102
80°	5662	1887	1418
85°	4237	1013	798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9579 cd/sqm

TEST NUMBER: P1035743

CATALOG NUMBER: S125RDIW-B1090D470UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.9	2.9
10°-20°	469.3	8.0
20°-30°	680.5	11.6
30°-40°	775.3	13.2
40°-50°	755.7	12.9
50°-60°	636.0	10.8
60°-70°	445.7	7.6
70°-80°	228.5	3.9
80°-90°	57.9	1.0
90°-100°	39.3	0.7
100°-110°	116.8	2.0
110°-120°	198.1	3.4
120°-130°	260.8	4.4
130°-140°	292.2	5.0
140°-150°	286.4	4.9
150°-160°	240.6	4.1
160°-170°	159.9	2.7
170°-180°	56.0	1.0
0°-30°	1317.8	22.5
0°-40°	2093.2	35.7
0°-60°	3484.9	59.4
0°-90°	4216.9	71.9
90°-120°	354.2	6.0
90°-150°	1193.6	20.3
90°-180°	1650.0	28.1
0°-180°	5867.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1784	1784	1784	1784	1784	
5°	1782	1776	1762	1775	1772	169
15°	1694	1686	1658	1656	1644	478
25°	1536	1516	1466	1449	1434	707
35°	1324	1291	1230	1191	1173	829
45°	1084	1044	970	916	896	836
55°	822	779	704	643	621	735
65°	557	511	439	386	365	551
75°	296	256	200	170	160	313
85°	74	50	43	42	40	81
90°	0	4	7	10	11	6
95°	30	31	35	39	40	31
105°	105	107	110	113	114	112
115°	198	200	201	201	200	196
125°	289	292	293	292	291	259
135°	376	379	380	380	378	290
145°	456	458	459	459	458	285
155°	522	522	522	524	522	240
165°	567	566	567	569	566	160
175°	590	588	588	591	588	56
180°	591	591	591	591	591	

TEST NUMBER: P1035743

CATALOG NUMBER: S125RDIW-B1090D470UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.4	1784.4	1784.4	1784.4	1784.4
2.5°	1788.5	1784.4	1771.0	1784.4	1783.1
5°	1781.7	1776.4	1761.5	1775.0	1772.3
7.5°	1768.3	1762.9	1745.4	1756.1	1753.4
10°	1748.1	1744.0	1725.1	1729.2	1725.1
12.5°	1725.1	1719.7	1692.8	1695.5	1688.8
15°	1694.1	1686.1	1657.8	1656.4	1644.3
17.5°	1661.8	1649.7	1616.0	1609.2	1599.8
20°	1622.7	1609.2	1566.1	1559.4	1547.2
22.5°	1579.6	1566.1	1520.3	1505.5	1496.0
25°	1536.5	1516.2	1466.4	1448.8	1434.0
27.5°	1487.9	1463.7	1411.1	1388.2	1373.4
30°	1434.0	1408.4	1351.8	1320.8	1308.7
32.5°	1381.5	1350.5	1292.5	1257.5	1241.3
35°	1323.5	1291.2	1230.5	1191.4	1172.6
37.5°	1268.2	1229.2	1167.2	1121.3	1102.5
40°	1208.9	1168.5	1103.8	1052.6	1036.4
42.5°	1146.9	1105.2	1037.8	989.3	963.7
45°	1083.6	1044.5	970.4	916.5	896.3
47.5°	1017.6	977.1	903.0	847.7	824.8
50°	955.6	911.1	834.3	777.7	757.4
52.5°	888.2	842.4	770.9	708.9	688.7
55°	822.1	779.0	703.5	642.9	621.3
57.5°	754.7	708.9	636.1	576.8	558.0
60°	690.1	642.9	570.1	510.8	490.6
62.5°	621.3	576.8	502.7	448.8	428.6
65°	556.6	510.8	439.4	385.5	365.2
67.5°	491.9	446.1	377.4	326.2	310.0
70°	425.9	380.1	312.7	270.9	254.7
72.5°	361.2	316.7	254.7	217.0	207.6
75°	296.5	256.1	199.5	169.8	160.4
77.5°	230.5	198.1	150.9	128.0	120.0
80°	175.2	142.9	105.1	93.0	90.3
82.5°	121.3	93.0	70.1	66.0	64.7
85°	74.1	49.9	43.1	41.8	40.4
87.5°	31.0	21.6	20.2	20.2	18.9
90°	0.5	4.1	7.4	9.7	11.0
92.5°	13.8	16.1	20.2	23.5	24.4
95°	29.9	30.8	35.4	38.6	39.6
97.5°	46.0	46.5	52.9	55.7	56.1
100°	64.4	64.4	70.4	74.5	75.5
102.5°	84.2	86.5	88.8	93.4	94.8
105°	104.9	107.2	110.0	112.7	114.1
107.5°	127.4	129.7	132.0	133.4	133.4
110°	150.9	153.2	154.6	156.0	155.5

TEST NUMBER: P1035743

CATALOG NUMBER: S125RDIW-B1090D470UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	175.8	177.6	178.1	177.1
115°	198.3	200.1	201.1	200.6	200.1
117.5°	222.2	222.7	223.6	224.1	222.2
120°	244.3	246.6	247.1	247.1	245.2
122.5°	268.2	268.7	270.1	269.6	268.2
125°	289.4	292.2	292.6	291.7	291.2
127.5°	312.9	314.2	314.7	314.2	313.3
130°	333.6	335.9	336.8	336.3	335.4
132.5°	354.3	358.4	358.0	357.5	356.1
135°	376.4	379.1	379.6	379.6	377.7
137.5°	397.1	399.8	400.7	401.2	398.9
140°	416.9	419.2	420.5	421.5	419.2
142.5°	436.6	438.5	440.3	440.8	438.5
145°	456.0	457.8	459.2	459.2	457.8
147.5°	473.9	475.3	476.2	477.6	473.9
150°	491.8	491.4	493.2	493.2	492.3
152.5°	506.6	507.5	508.0	509.3	507.5
155°	521.8	521.8	522.2	524.1	521.8
157.5°	535.6	534.6	535.1	536.9	533.7
160°	547.5	546.1	546.6	548.4	546.1
162.5°	558.1	557.2	557.2	559.5	556.7
165°	567.3	566.4	566.8	568.7	565.9
167.5°	575.6	573.7	573.7	576.5	573.7
170°	582.0	580.2	580.2	582.9	579.7
172.5°	586.6	584.8	584.8	587.6	584.8
175°	589.9	588.0	588.0	590.8	587.6
177.5°	592.2	590.3	589.9	592.6	589.4
180°	591.2	591.2	591.2	591.2	591.2

(END OF REPORT)