

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035190

Luminaire Tested: S125DIW-B1270D470UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035190
REPORT IS A COMBINATION OF REPORTS P1003293 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D470UB35-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6814.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035190
CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot





TEST NUMBER: P1035190

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	76		
1	103	99	95	91	98	94	91	87	86	83	80	78	76	74	70	69	67	64		
2	94	86	80	74	89	82	77	72	75	70	66	68	65	61	62	59	57	53		
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	45		
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41	39		
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	34		
6	67	54	46	40	63	52	44	38	48	41	36	44	38	34	40	36	32	29		
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28	26		
8	58	45	37	31	55	43	35	30	40	33	29	37	31	27	34	29	25	23		
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	21		
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12710	12710	12710
5°	12710	12415	12439
10°	12605	12130	12092
15°	12439	11790	11684
20°	12216	11395	11216
25°	11975	10964	10715
30°	11686	10516	10187
35°	11376	10046	9595
40°	11056	9548	9069
45°	10710	9064	8511
50°	10330	8515	7859
55°	9953	7909	7261
60°	9503	7270	6564
65°	8964	6530	5843
70°	8417	5681	5012
75°	7497	4677	4053
80°	6389	3494	2981
85°	4934	2067	1644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10710 cd/sqm



TEST NUMBER: P1035190

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.7
10°-20°	528.7	7.8
20°-30°	780.6	11.5
30°-40°	910.7	13.4
40°-50°	914.7	13.4
50°-60°	802.9	11.8
60°-70°	598.0	8.8
70°-80°	341.6	5.0
80°-90°	99.5	1.5
90°-100°	39.3	0.6
100°-110°	116.8	1.7
110°-120°	198.1	2.9
120°-130°	260.8	3.8
130°-140°	292.2	4.3
140°-150°	286.4	4.2
150°-160°	240.6	3.5
160°-170°	159.9	2.3
170°-180°	56.0	0.8
0°-30°	1496.5	22.0
0°-40°	2407.2	35.3
0°-60°	4124.8	60.5
0°-90°	5163.9	75.8
90°-120°	354.2	5.2
90°-150°	1193.6	17.5
90°-180°	1650.0	24.2
0°-180°	6814.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1980	1977	1962	1976	1974	188
15°	1888	1883	1866	1874	1874	532
25°	1714	1706	1686	1689	1684	789
35°	1480	1474	1452	1444	1431	926
45°	1212	1205	1186	1168	1163	933
55°	923	918	896	882	871	824
65°	623	620	603	588	582	618
75°	331	328	320	315	309	353
85°	86	88	88	86	83	95
90°	0	4	7	10	11	8
95°	30	31	35	39	40	31
105°	105	107	110	113	114	112
115°	198	200	201	201	200	196
125°	289	292	293	292	291	259
135°	376	379	380	380	378	290
145°	456	458	459	459	458	285
155°	522	522	522	524	522	240
165°	567	566	567	569	566	160
175°	590	588	588	591	588	56
180°	591	591	591	591	591	



TEST NUMBER: P1035190

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.7	1983.7	1983.7	1983.7	1983.7
2.5°	1989.9	1985.2	1969.5	1985.2	1983.7
5°	1980.5	1977.4	1961.7	1975.8	1974.3
7.5°	1966.4	1963.3	1946.0	1960.1	1958.6
10°	1946.0	1942.9	1925.6	1938.2	1936.6
12.5°	1920.9	1914.6	1898.9	1908.3	1908.3
15°	1887.9	1883.2	1866.0	1873.8	1873.8
17.5°	1853.4	1845.6	1828.3	1837.7	1829.9
20°	1807.9	1804.8	1784.4	1795.3	1787.5
22.5°	1762.4	1756.1	1737.3	1743.6	1738.8
25°	1713.7	1705.9	1685.5	1688.6	1683.9
27.5°	1657.2	1652.5	1632.1	1633.7	1629.0
30°	1602.3	1597.6	1574.1	1570.9	1566.2
32.5°	1542.7	1534.8	1514.4	1508.2	1498.7
35°	1479.9	1473.6	1451.7	1443.8	1431.3
37.5°	1415.6	1407.7	1387.3	1376.3	1368.5
40°	1349.6	1341.8	1319.8	1305.7	1301.0
42.5°	1279.0	1272.7	1250.8	1238.2	1230.4
45°	1211.5	1205.3	1186.4	1167.6	1162.9
47.5°	1137.8	1139.4	1115.8	1097.0	1086.0
50°	1067.2	1062.5	1043.6	1023.2	1012.2
52.5°	995.0	991.8	971.4	954.2	941.6
55°	922.8	918.1	896.1	882.0	871.0
57.5°	845.9	844.3	825.5	806.6	801.9
60°	773.7	767.4	750.2	734.5	723.5
62.5°	698.4	693.7	679.5	662.3	654.4
65°	623.0	619.9	602.6	588.5	582.2
67.5°	549.3	543.0	530.4	517.9	514.7
70°	480.2	472.4	458.3	448.8	442.6
72.5°	404.9	400.2	392.3	381.4	375.1
75°	331.1	328.0	320.1	315.4	309.2
77.5°	262.1	260.5	255.8	252.7	248.0
80°	197.7	197.7	194.6	193.0	189.9
82.5°	141.2	138.1	138.1	135.0	135.0
85°	86.3	87.9	87.9	86.3	83.2
87.5°	42.4	42.4	40.8	40.8	37.7
90°	0.5	4.1	7.4	9.7	11.0
92.5°	13.8	16.1	20.2	23.5	24.4
95°	29.9	30.8	35.4	38.6	39.6
97.5°	46.0	46.5	52.9	55.7	56.1
100°	64.4	64.4	70.4	74.5	75.5
102.5°	84.2	86.5	88.8	93.4	94.8
105°	104.9	107.2	110.0	112.7	114.1
107.5°	127.4	129.7	132.0	133.4	133.4
110°	150.9	153.2	154.6	156.0	155.5



TEST NUMBER: P1035190
 CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	175.8	177.6	178.1	177.1
115°	198.3	200.1	201.1	200.6	200.1
117.5°	222.2	222.7	223.6	224.1	222.2
120°	244.3	246.6	247.1	247.1	245.2
122.5°	268.2	268.7	270.1	269.6	268.2
125°	289.4	292.2	292.6	291.7	291.2
127.5°	312.9	314.2	314.7	314.2	313.3
130°	333.6	335.9	336.8	336.3	335.4
132.5°	354.3	358.4	358.0	357.5	356.1
135°	376.4	379.1	379.6	379.6	377.7
137.5°	397.1	399.8	400.7	401.2	398.9
140°	416.9	419.2	420.5	421.5	419.2
142.5°	436.6	438.5	440.3	440.8	438.5
145°	456.0	457.8	459.2	459.2	457.8
147.5°	473.9	475.3	476.2	477.6	473.9
150°	491.8	491.4	493.2	493.2	492.3
152.5°	506.6	507.5	508.0	509.3	507.5
155°	521.8	521.8	522.2	524.1	521.8
157.5°	535.6	534.6	535.1	536.9	533.7
160°	547.5	546.1	546.6	548.4	546.1
162.5°	558.1	557.2	557.2	559.5	556.7
165°	567.3	566.4	566.8	568.7	565.9
167.5°	575.6	573.7	573.7	576.5	573.7
170°	582.0	580.2	580.2	582.9	579.7
172.5°	586.6	584.8	584.8	587.6	584.8
175°	589.9	588.0	588.0	590.8	587.6
177.5°	592.2	590.3	589.9	592.6	589.4
180°	591.2	591.2	591.2	591.2	591.2

(END OF REPORT)