

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035774

Luminaire Tested: S125RDIW-B1270D1050UB27-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035774
REPORT IS A COMBINATION OF REPORTS P1006142 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D1050UB27-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9062.0 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035774

CATALOG NUMBER: S125RDIW-B1270D1050UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035774

CATALOG NUMBER: S125RDIW-B1270D1050UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	56	59	54	50	50	46	43	42	39	37
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20
9	51	39	32	27	48	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13142	13142	13142
5°	13143	12814	12834
10°	13015	12491	12381
15°	12831	12039	11785
20°	12603	11495	11159
25°	12341	10964	10488
30°	12021	10380	9784
35°	11694	9788	9036
40°	11384	9179	8305
45°	11010	8521	7540
50°	10632	7823	6760
55°	10192	7137	5954
60°	9742	6351	5116
65°	9206	5473	4213
70°	8580	4455	3316
75°	7717	3350	2417
80°	6508	2169	1630
85°	4871	1166	919

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11010 cd/sqm

TEST NUMBER: P1035774

CATALOG NUMBER: S125RDIW-B1270D1050UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.0	2.1
10°-20°	539.5	6.0
20°-30°	782.2	8.6
30°-40°	891.2	9.8
40°-50°	868.6	9.6
50°-60°	731.0	8.1
60°-70°	512.3	5.7
70°-80°	262.6	2.9
80°-90°	67.5	0.7
90°-100°	46.6	0.5
100°-110°	309.6	3.4
110°-120°	557.5	6.2
120°-130°	715.6	7.9
130°-140°	769.7	8.5
140°-150°	722.4	8.0
150°-160°	584.3	6.4
160°-170°	377.9	4.2
170°-180°	130.3	1.4
0°-30°	1514.8	16.7
0°-40°	2405.9	26.5
0°-60°	4005.6	44.2
0°-90°	4848.0	53.5
90°-120°	913.7	10.1
90°-150°	3121.4	34.4
90°-180°	4214.0	46.5
0°-180°	9062.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2051	2051	2051	2051	2051	
5°	2048	2042	2025	2040	2037	194
15°	1947	1938	1906	1904	1890	549
25°	1766	1743	1686	1665	1648	813
35°	1521	1484	1414	1370	1348	953
45°	1246	1201	1115	1053	1030	961
55°	945	895	809	739	714	845
65°	640	587	505	443	420	634
75°	341	294	229	195	184	360
85°	85	57	50	48	46	93
90°	1	9	16	21	24	8
95°	58	55	16	21	21	71
105°	299	303	303	303	302	317
115°	561	566	567	563	557	556
125°	798	805	805	801	798	713
135°	996	1002	1000	998	992	768
145°	1154	1156	1156	1157	1151	722
155°	1271	1265	1267	1270	1262	586
165°	1341	1335	1336	1342	1334	379
175°	1372	1366	1367	1375	1366	131
180°	1372	1372	1372	1372	1372	

TEST NUMBER: P1035774

CATALOG NUMBER: S125RDIW-B1270D1050UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2051.1	2051.1	2051.1	2051.1	2051.1
2.5°	2055.7	2051.1	2035.6	2051.1	2049.5
5°	2048.0	2041.8	2024.8	2040.2	2037.1
7.5°	2032.5	2026.3	2006.2	2018.6	2015.5
10°	2009.3	2004.6	1982.9	1987.6	1982.9
12.5°	1982.9	1976.7	1945.7	1948.8	1941.1
15°	1947.3	1938.0	1905.5	1903.9	1890.0
17.5°	1910.1	1896.2	1857.4	1849.7	1838.9
20°	1865.2	1849.7	1800.1	1792.4	1778.4
22.5°	1815.6	1800.1	1747.5	1730.4	1719.6
25°	1766.0	1742.8	1685.5	1665.4	1648.3
27.5°	1710.3	1682.4	1622.0	1595.6	1578.6
30°	1648.3	1618.9	1553.8	1518.2	1504.2
32.5°	1587.9	1552.3	1485.6	1445.4	1426.8
35°	1521.3	1484.1	1414.4	1369.5	1347.8
37.5°	1457.8	1412.8	1341.6	1288.9	1267.2
40°	1389.6	1343.1	1268.8	1209.9	1191.3
42.5°	1318.3	1270.3	1192.9	1137.1	1107.7
45°	1245.5	1200.6	1115.4	1053.4	1030.2
47.5°	1169.6	1123.1	1037.9	974.4	948.1
50°	1098.4	1047.2	958.9	893.9	870.6
52.5°	1020.9	968.2	886.1	814.9	791.6
55°	945.0	895.4	808.7	739.0	714.2
57.5°	867.5	814.9	731.2	663.0	641.4
60°	793.2	739.0	655.3	587.1	563.9
62.5°	714.2	663.0	577.8	515.9	492.6
65°	639.8	587.1	505.0	443.1	419.8
67.5°	565.4	512.8	433.8	374.9	356.3
70°	489.5	436.9	359.4	311.4	292.8
72.5°	415.2	364.1	292.8	249.4	238.6
75°	340.8	294.3	229.3	195.2	184.4
77.5°	264.9	227.7	173.5	147.2	137.9
80°	201.4	164.2	120.8	106.9	103.8
82.5°	139.4	106.9	80.6	75.9	74.4
85°	85.2	57.3	49.6	48.0	46.5
87.5°	35.6	24.8	23.2	23.2	21.7
90°	1.0	9.2	16.3	21.4	24.4
92.5°	19.3	10.2	16.3	21.4	22.4
95°	58.0	54.9	16.3	21.4	21.4
97.5°	108.8	114.9	18.3	20.3	21.4
100°	169.8	172.9	176.9	25.4	21.4
102.5°	231.9	235.9	238.0	240.0	154.6
105°	299.0	303.0	303.0	303.0	302.0
107.5°	368.1	368.1	370.2	371.2	367.1
110°	435.2	435.2	437.3	434.2	435.2

TEST NUMBER: P1035774

CATALOG NUMBER: S125RDIW-B1270D1050UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	498.3	501.3	502.4	498.3	496.3
115°	561.3	566.4	567.4	563.4	557.3
117.5°	627.4	627.4	631.5	625.4	623.4
120°	688.5	687.4	690.5	688.5	683.4
122.5°	742.4	747.4	748.5	746.4	740.3
125°	798.3	805.4	805.4	801.3	798.3
127.5°	852.2	857.3	856.2	854.2	846.1
130°	901.0	906.1	907.1	904.0	899.0
132.5°	949.8	955.9	952.9	952.9	947.8
135°	995.6	1001.7	999.6	997.6	991.5
137.5°	1038.3	1044.4	1042.3	1042.3	1037.3
140°	1080.0	1082.0	1081.0	1083.0	1076.9
142.5°	1117.6	1118.6	1120.6	1120.6	1114.5
145°	1154.2	1156.2	1156.2	1157.3	1151.2
147.5°	1186.7	1186.7	1187.8	1188.8	1181.7
150°	1217.3	1215.2	1217.3	1219.3	1211.2
152.5°	1246.7	1241.7	1243.7	1245.7	1238.6
155°	1271.2	1265.1	1267.1	1270.1	1262.0
157.5°	1290.5	1287.4	1287.4	1290.5	1282.3
160°	1310.8	1304.7	1305.7	1309.8	1301.7
162.5°	1327.1	1321.0	1322.0	1328.1	1318.9
165°	1341.3	1335.2	1336.2	1342.3	1334.2
167.5°	1352.5	1346.4	1347.4	1354.5	1345.4
170°	1361.7	1354.5	1355.6	1363.7	1354.5
172.5°	1367.8	1360.6	1362.7	1369.8	1360.6
175°	1371.8	1365.7	1366.7	1374.9	1365.7
177.5°	1374.9	1368.8	1369.8	1376.9	1368.8
180°	1371.8	1371.8	1371.8	1371.8	1371.8

(END OF REPORT)