

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035214

Luminaire Tested: S125DIW-B1270D770UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035214
REPORT IS A COMBINATION OF REPORTS P1003350 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D770UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7851.0 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035214

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035214

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70
1	101	97	93	89	95	91	88	84	81	78	76	71	69	67	62	61	59
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	55	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	40	37
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12655	12655	12655
5°	12656	12362	12385
10°	12551	12078	12040
15°	12387	11739	11634
20°	12164	11346	11168
25°	11924	10918	10669
30°	11636	10471	10143
35°	11328	10003	9554
40°	11009	9508	9031
45°	10665	9026	8474
50°	10285	8479	7826
55°	9911	7875	7230
60°	9462	7239	6536
65°	8927	6503	5819
70°	8382	5657	4991
75°	7465	4658	4035
80°	6363	3480	2969
85°	4911	2057	1636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10665 cd/sqm

TEST NUMBER: P1035214

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.4
10°-20°	526.5	6.7
20°-30°	777.2	9.9
30°-40°	906.8	11.6
40°-50°	910.8	11.6
50°-60°	799.5	10.2
60°-70°	595.5	7.6
70°-80°	340.1	4.3
80°-90°	99.7	1.3
90°-100°	64.5	0.8
100°-110°	191.7	2.4
110°-120°	325.1	4.1
120°-130°	428.0	5.5
130°-140°	479.7	6.1
140°-150°	470.1	6.0
150°-160°	394.9	5.0
160°-170°	262.5	3.3
170°-180°	91.9	1.2
0°-30°	1490.1	19.0
0°-40°	2396.9	30.5
0°-60°	4107.2	52.3
0°-90°	5142.5	65.5
90°-120°	581.4	7.4
90°-150°	1959.2	25.0
90°-180°	2708.0	34.5
0°-180°	7851.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	1969	1953	1967	1966	187
15°	1880	1875	1858	1866	1866	530
25°	1706	1699	1678	1681	1677	785
35°	1474	1467	1446	1438	1425	922
45°	1206	1200	1181	1163	1158	929
55°	919	914	892	878	867	820
65°	620	617	600	586	580	615
75°	330	327	319	314	308	351
85°	86	88	88	86	83	94
90°	1	7	12	16	18	9
95°	49	51	58	63	65	51
105°	172	176	180	185	187	184
115°	326	328	330	329	328	322
125°	475	480	480	479	478	426
135°	618	622	623	623	620	476
145°	748	751	754	754	751	468
155°	856	856	857	860	856	394
165°	931	930	930	934	929	263
175°	968	965	965	970	964	92
180°	970	970	970	970	970	

TEST NUMBER: P1035214

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1981.5	1976.8	1961.2	1976.8	1975.2
5°	1972.1	1969.0	1953.3	1967.4	1965.8
7.5°	1958.0	1954.9	1937.7	1951.8	1950.2
10°	1937.7	1934.6	1917.4	1929.9	1928.3
12.5°	1912.7	1906.5	1890.8	1900.2	1900.2
15°	1879.9	1875.2	1858.0	1865.8	1865.8
17.5°	1845.5	1837.7	1820.5	1829.9	1822.1
20°	1800.2	1797.1	1776.8	1787.7	1779.9
22.5°	1754.9	1748.6	1729.9	1736.1	1731.4
25°	1706.4	1698.6	1678.3	1681.4	1676.7
27.5°	1650.2	1645.5	1625.2	1626.7	1622.1
30°	1595.5	1590.8	1567.4	1564.2	1559.5
32.5°	1536.1	1528.3	1508.0	1501.7	1492.4
35°	1473.6	1467.3	1445.5	1437.7	1425.2
37.5°	1409.5	1401.7	1381.4	1370.5	1362.6
40°	1343.9	1336.1	1314.2	1300.1	1295.5
42.5°	1273.6	1267.3	1245.4	1232.9	1225.1
45°	1206.4	1200.1	1181.4	1162.6	1157.9
47.5°	1132.9	1134.5	1111.1	1092.3	1081.4
50°	1062.6	1057.9	1039.2	1018.9	1007.9
52.5°	990.7	987.6	967.3	950.1	937.6
55°	918.9	914.2	892.3	878.2	867.3
57.5°	842.3	840.7	822.0	803.2	798.5
60°	770.4	764.1	747.0	731.3	720.4
62.5°	695.4	690.7	676.6	659.4	651.6
65°	620.4	617.3	600.1	586.0	579.8
67.5°	546.9	540.7	528.2	515.7	512.6
70°	478.2	470.4	456.3	446.9	440.7
72.5°	403.2	398.5	390.7	379.7	373.5
75°	329.7	326.6	318.8	314.1	307.8
77.5°	261.0	259.4	254.7	251.6	246.9
80°	196.9	196.9	193.8	192.2	189.1
82.5°	140.6	137.5	137.5	134.4	134.4
85°	85.9	87.5	87.5	85.9	82.8
87.5°	42.2	42.2	40.6	40.6	37.5
90°	0.8	6.8	12.1	15.9	18.1
92.5°	22.7	26.4	33.2	38.5	40.0
95°	49.1	50.6	58.2	63.4	64.9
97.5°	75.5	76.3	86.9	91.4	92.1
100°	105.7	105.7	115.5	122.3	123.9
102.5°	138.2	142.0	145.8	153.3	155.6
105°	172.2	176.0	180.5	185.0	187.3
107.5°	209.2	213.0	216.7	219.0	219.0
110°	247.7	251.5	253.8	256.0	255.3

TEST NUMBER: P1035214

CATALOG NUMBER: S125DIW-B1270D770UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.0	288.5	291.5	292.3	290.8
115°	325.5	328.5	330.0	329.3	328.5
117.5°	364.8	365.5	367.0	367.8	364.8
120°	401.0	404.8	405.6	405.6	402.5
122.5°	440.3	441.1	443.3	442.6	440.3
125°	475.0	479.6	480.3	478.8	478.1
127.5°	513.6	515.8	516.6	515.8	514.3
130°	547.5	551.3	552.8	552.1	550.6
132.5°	581.5	588.3	587.6	586.8	584.5
135°	617.8	622.3	623.1	623.1	620.0
137.5°	651.8	656.3	657.8	658.6	654.8
140°	684.2	688.0	690.3	691.8	688.0
142.5°	716.7	719.7	722.8	723.5	719.7
145°	748.4	751.4	753.7	753.7	751.4
147.5°	777.9	780.1	781.7	783.9	777.9
150°	807.3	806.6	809.6	809.6	808.1
152.5°	831.5	833.0	833.8	836.0	833.0
155°	856.4	856.4	857.2	860.2	856.4
157.5°	879.1	877.6	878.3	881.3	876.1
160°	898.7	896.5	897.2	900.2	896.5
162.5°	916.1	914.6	914.6	918.4	913.8
165°	931.2	929.7	930.4	933.5	928.9
167.5°	944.8	941.8	941.8	946.3	941.8
170°	955.4	952.3	952.3	956.9	951.6
172.5°	962.9	959.9	959.9	964.4	959.9
175°	968.2	965.2	965.2	969.7	964.4
177.5°	972.0	969.0	968.2	972.7	967.4
180°	970.5	970.5	970.5	970.5	970.5

(END OF REPORT)