

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035809

Luminaire Tested: S125RDIW-B1270D1340UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035809
REPORT IS A COMBINATION OF REPORTS P1006225 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D1340UB50-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9178.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035809

CATALOG NUMBER: S125RDIW-B1270D1340UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035809

CATALOG NUMBER: S125RDIW-B1270D1340UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41
3	82	73	65	60	75	67	61	56	58	53	49	49	45	42	40	38	36
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	29	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21
8	55	42	35	29	50	40	33	28	34	29	25	30	25	22	25	22	19
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12746	12746	12746
5°	12747	12428	12448
10°	12622	12115	12008
15°	12444	11677	11429
20°	12223	11149	10823
25°	11969	10634	10172
30°	11659	10068	9489
35°	11341	9493	8763
40°	11040	8902	8054
45°	10679	8265	7313
50°	10311	7588	6556
55°	9885	6922	5773
60°	9449	6160	4962
65°	8928	5308	4087
70°	8323	4322	3216
75°	7483	3249	2344
80°	6311	2104	1581
85°	4723	1131	891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10679 cd/sqm

TEST NUMBER: P1035809

CATALOG NUMBER: S125RDIW-B1270D1340UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.0
10°-20°	523.2	5.7
20°-30°	758.7	8.3
30°-40°	864.3	9.4
40°-50°	842.5	9.2
50°-60°	709.0	7.7
60°-70°	496.8	5.4
70°-80°	254.7	2.8
80°-90°	66.0	0.7
90°-100°	106.6	1.2
100°-110°	316.8	3.5
110°-120°	537.3	5.9
120°-130°	707.3	7.7
130°-140°	792.6	8.6
140°-150°	776.9	8.5
150°-160°	652.5	7.1
160°-170°	433.8	4.7
170°-180°	151.8	1.7
0°-30°	1469.1	16.0
0°-40°	2333.5	25.4
0°-60°	3884.9	42.3
0°-90°	4702.5	51.2
90°-120°	960.7	10.5
90°-150°	3237.4	35.3
90°-180°	4475.0	48.8
0°-180°	9178.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1989	1989	1989	1989	1989	
5°	1986	1980	1964	1979	1976	188
15°	1889	1880	1848	1847	1833	533
25°	1713	1690	1635	1615	1599	788
35°	1475	1439	1372	1328	1307	924
45°	1208	1164	1082	1022	999	932
55°	916	868	784	717	693	820
65°	620	569	490	430	407	614
75°	330	286	222	189	179	349
85°	83	56	48	47	45	90
90°	1	11	20	26	30	10
95°	81	84	96	105	107	85
105°	284	291	298	306	310	303
115°	538	543	545	544	543	532
125°	785	792	794	791	790	703
135°	1021	1028	1030	1030	1025	787
145°	1237	1242	1245	1245	1242	773
155°	1415	1415	1416	1421	1415	652
165°	1539	1536	1538	1542	1535	434
175°	1600	1595	1595	1602	1594	152
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P1035809

CATALOG NUMBER: S125RDIW-B1270D1340UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1989.3	1989.3	1989.3	1989.3	1989.3
2.5°	1993.8	1989.3	1974.3	1989.3	1987.8
5°	1986.3	1980.3	1963.8	1978.8	1975.8
7.5°	1971.3	1965.3	1945.7	1957.7	1954.7
10°	1948.7	1944.2	1923.2	1927.7	1923.2
12.5°	1923.2	1917.2	1887.1	1890.1	1882.6
15°	1888.6	1879.6	1848.1	1846.6	1833.0
17.5°	1852.6	1839.0	1801.5	1794.0	1783.5
20°	1809.0	1794.0	1745.9	1738.4	1724.9
22.5°	1760.9	1745.9	1694.8	1678.3	1667.8
25°	1712.8	1690.3	1634.7	1615.2	1598.6
27.5°	1658.7	1631.7	1573.1	1547.6	1531.0
30°	1598.6	1570.1	1507.0	1472.4	1458.9
32.5°	1540.1	1505.5	1440.9	1401.8	1383.8
35°	1475.4	1439.4	1371.8	1328.2	1307.2
37.5°	1413.8	1370.3	1301.2	1250.1	1229.0
40°	1347.7	1302.7	1230.5	1173.4	1155.4
42.5°	1278.6	1232.0	1156.9	1102.8	1074.3
45°	1208.0	1164.4	1081.8	1021.7	999.2
47.5°	1134.4	1089.3	1006.7	945.1	919.5
50°	1065.3	1015.7	930.0	866.9	844.4
52.5°	990.1	939.1	859.4	790.3	767.8
55°	916.5	868.4	784.3	716.7	692.6
57.5°	841.4	790.3	709.2	643.1	622.0
60°	769.3	716.7	635.6	569.4	546.9
62.5°	692.6	643.1	560.4	500.3	477.8
65°	620.5	569.4	489.8	429.7	407.2
67.5°	548.4	497.3	420.7	363.6	345.6
70°	474.8	423.7	348.6	302.0	284.0
72.5°	402.7	353.1	284.0	241.9	231.4
75°	330.5	285.5	222.4	189.3	178.8
77.5°	256.9	220.9	168.3	142.7	133.7
80°	195.3	159.3	117.2	103.7	100.7
82.5°	135.2	103.7	78.1	73.6	72.1
85°	82.6	55.6	48.1	46.6	45.1
87.5°	34.6	24.0	22.5	22.5	21.0
90°	1.2	11.2	20.0	26.2	30.0
92.5°	37.4	43.7	54.9	63.6	66.1
95°	81.1	83.6	96.1	104.8	107.3
97.5°	124.8	126.0	143.5	151.0	152.2
100°	174.7	174.7	190.9	202.2	204.7
102.5°	228.4	234.6	240.9	253.3	257.1
105°	284.5	290.8	298.3	305.7	309.5
107.5°	345.7	351.9	358.2	361.9	361.9
110°	409.3	415.6	419.3	423.0	421.8

TEST NUMBER: P1035809

CATALOG NUMBER: S125RDIW-B1270D1340UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	474.2	476.7	481.7	483.0	480.5
115°	537.9	542.9	545.3	544.1	542.9
117.5°	602.8	604.0	606.5	607.7	602.8
120°	662.7	668.9	670.1	670.1	665.1
122.5°	727.5	728.8	732.5	731.3	727.5
125°	785.0	792.4	793.7	791.2	789.9
127.5°	848.6	852.3	853.6	852.3	849.8
130°	904.8	911.0	913.5	912.2	909.7
132.5°	960.9	972.1	970.9	969.6	965.9
135°	1020.8	1028.3	1029.5	1029.5	1024.6
137.5°	1077.0	1084.5	1087.0	1088.2	1082.0
140°	1130.6	1136.9	1140.6	1143.1	1136.9
142.5°	1184.3	1189.3	1194.3	1195.5	1189.3
145°	1236.7	1241.7	1245.4	1245.4	1241.7
147.5°	1285.4	1289.1	1291.6	1295.4	1285.4
150°	1334.0	1332.8	1337.8	1337.8	1335.3
152.5°	1374.0	1376.5	1377.7	1381.5	1376.5
155°	1415.2	1415.2	1416.4	1421.4	1415.2
157.5°	1452.6	1450.1	1451.3	1456.3	1447.6
160°	1485.0	1481.3	1482.5	1487.5	1481.3
162.5°	1513.7	1511.2	1511.2	1517.5	1510.0
165°	1538.7	1536.2	1537.5	1542.4	1535.0
167.5°	1561.2	1556.2	1556.2	1563.7	1556.2
170°	1578.6	1573.6	1573.6	1581.1	1572.4
172.5°	1591.1	1586.1	1586.1	1593.6	1586.1
175°	1599.9	1594.9	1594.9	1602.3	1593.6
177.5°	1606.1	1601.1	1599.9	1607.3	1598.6
180°	1603.6	1603.6	1603.6	1603.6	1603.6

(END OF REPORT)