

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035816

Luminaire Tested: S125RDIW-B1270D1560UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035816
REPORT IS A COMBINATION OF REPORTS P1006250 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D1560UB30-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11220.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035816

CATALOG NUMBER: S125RDIW-B1270D1560UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035816

CATALOG NUMBER: S125RDIW-B1270D1560UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	24
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13256	13256	13256
5°	13257	12925	12946
10°	13128	12599	12488
15°	12942	12144	11887
20°	12712	11595	11256
25°	12448	11059	10579
30°	12125	10471	9869
35°	11796	9872	9114
40°	11482	9259	8377
45°	11106	8595	7605
50°	10724	7891	6819
55°	10281	7199	6005
60°	9826	6406	5161
65°	9285	5520	4250
70°	8656	4494	3344
75°	7785	3379	2437
80°	6563	2189	1644
85°	4911	1176	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11106 cd/sqm

TEST NUMBER: P1035816

CATALOG NUMBER: S125RDIW-B1270D1560UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.7	1.7
10°-20°	544.2	4.8
20°-30°	789.0	7.0
30°-40°	898.9	8.0
40°-50°	876.2	7.8
50°-60°	737.4	6.6
60°-70°	516.7	4.6
70°-80°	264.9	2.4
80°-90°	69.1	0.6
90°-100°	69.9	0.6
100°-110°	465.0	4.1
110°-120°	837.4	7.5
120°-130°	1074.8	9.6
130°-140°	1156.0	10.3
140°-150°	1084.9	9.7
150°-160°	877.6	7.8
160°-170°	567.6	5.1
170°-180°	195.7	1.7
0°-30°	1527.9	13.6
0°-40°	2426.8	21.6
0°-60°	4040.3	36.0
0°-90°	4891.0	43.6
90°-120°	1372.3	12.2
90°-150°	4688.0	41.8
90°-180°	6329.0	56.4
0°-180°	11220.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2066	2060	2042	2058	2055	196
15°	1964	1955	1922	1920	1906	554
25°	1781	1758	1700	1680	1663	820
35°	1534	1497	1427	1381	1360	961
45°	1256	1211	1125	1063	1039	969
55°	953	903	816	745	720	852
65°	645	592	509	447	424	639
75°	344	297	231	197	186	363
85°	86	58	50	48	47	94
90°	2	14	24	32	37	9
95°	87	82	24	32	32	107
105°	449	455	455	455	454	476
115°	843	851	852	846	837	836
125°	1199	1210	1210	1204	1199	1071
135°	1495	1504	1501	1498	1489	1153
145°	1734	1737	1737	1738	1729	1084
155°	1909	1900	1903	1908	1895	880
165°	2014	2005	2007	2016	2004	569
175°	2060	2051	2053	2065	2051	196
180°	2060	2060	2060	2060	2060	

TEST NUMBER: P1035816

CATALOG NUMBER: S125RDIW-B1270D1560UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.9	2068.9	2068.9	2068.9	2068.9
2.5°	2073.6	2068.9	2053.2	2068.9	2067.3
5°	2065.7	2059.5	2042.3	2057.9	2054.8
7.5°	2050.1	2043.9	2023.6	2036.1	2032.9
10°	2026.7	2022.0	2000.1	2004.8	2000.1
12.5°	2000.1	1993.9	1962.6	1965.7	1957.9
15°	1964.2	1954.8	1922.0	1920.4	1906.4
17.5°	1926.7	1912.6	1873.5	1865.7	1854.8
20°	1881.4	1865.7	1815.7	1807.9	1793.9
22.5°	1831.4	1815.7	1762.6	1745.4	1734.5
25°	1781.4	1757.9	1700.1	1679.8	1662.6
27.5°	1725.1	1697.0	1636.0	1609.5	1592.3
30°	1662.6	1632.9	1567.3	1531.3	1517.3
32.5°	1601.7	1565.7	1498.5	1457.9	1439.1
35°	1534.5	1497.0	1426.6	1381.3	1359.5
37.5°	1470.4	1425.1	1353.2	1300.1	1278.2
40°	1401.6	1354.8	1279.8	1220.4	1201.6
42.5°	1329.8	1281.3	1203.2	1146.9	1117.3
45°	1256.3	1211.0	1125.1	1062.6	1039.1
47.5°	1179.8	1132.9	1046.9	982.9	956.3
50°	1107.9	1056.3	967.2	901.6	878.2
52.5°	1029.7	976.6	893.8	821.9	798.5
55°	953.2	903.2	815.7	745.4	720.4
57.5°	875.1	821.9	737.5	668.8	646.9
60°	800.0	745.4	661.0	592.2	568.8
62.5°	720.4	668.8	582.8	520.3	496.9
65°	645.3	592.2	509.4	446.9	423.5
67.5°	570.3	517.2	437.5	378.1	359.4
70°	493.8	440.7	362.5	314.1	295.3
72.5°	418.8	367.2	295.3	251.6	240.6
75°	343.8	296.9	231.3	196.9	185.9
77.5°	267.2	229.7	175.0	148.4	139.1
80°	203.1	165.6	121.9	107.8	104.7
82.5°	140.6	107.8	81.3	76.6	75.0
85°	85.9	57.8	50.0	48.4	46.9
87.5°	35.9	25.0	23.4	23.4	21.9
90°	1.5	13.7	24.4	32.1	36.7
92.5°	29.0	15.3	24.4	32.1	33.6
95°	87.1	82.5	24.4	32.1	32.1
97.5°	163.4	172.6	27.5	30.5	32.1
100°	255.1	259.6	265.8	38.2	32.1
102.5°	348.2	354.3	357.4	360.4	232.2
105°	449.0	455.1	455.1	455.1	453.6
107.5°	552.9	552.9	555.9	557.5	551.4
110°	653.7	653.7	656.7	652.2	653.7

TEST NUMBER: P1035816

CATALOG NUMBER: S125RDIW-B1270D1560UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	748.4	753.0	754.5	748.4	745.3
115°	843.1	850.7	852.2	846.1	837.0
117.5°	942.4	942.4	948.5	939.3	936.2
120°	1034.0	1032.5	1037.0	1034.0	1026.4
122.5°	1114.9	1122.6	1124.1	1121.0	1111.9
125°	1198.9	1209.6	1209.6	1203.5	1198.9
127.5°	1279.9	1287.5	1286.0	1282.9	1270.7
130°	1353.2	1360.8	1362.4	1357.8	1350.1
132.5°	1426.5	1435.7	1431.1	1431.1	1423.5
135°	1495.2	1504.4	1501.3	1498.3	1489.1
137.5°	1559.4	1568.6	1565.5	1565.5	1557.9
140°	1622.0	1625.1	1623.5	1626.6	1617.4
142.5°	1678.5	1680.0	1683.1	1683.1	1673.9
145°	1733.5	1736.6	1736.6	1738.1	1728.9
147.5°	1782.4	1782.4	1783.9	1785.4	1774.7
150°	1828.2	1825.1	1828.2	1831.2	1819.0
152.5°	1872.5	1864.8	1867.9	1871.0	1860.3
155°	1909.1	1900.0	1903.0	1907.6	1895.4
157.5°	1938.2	1933.6	1933.6	1938.2	1925.9
160°	1968.7	1959.5	1961.1	1967.2	1955.0
162.5°	1993.1	1984.0	1985.5	1994.7	1980.9
165°	2014.5	2005.4	2006.9	2016.1	2003.8
167.5°	2031.3	2022.2	2023.7	2034.4	2020.6
170°	2045.1	2034.4	2035.9	2048.1	2034.4
172.5°	2054.2	2043.5	2046.6	2057.3	2043.5
175°	2060.3	2051.2	2052.7	2064.9	2051.2
177.5°	2064.9	2055.8	2057.3	2068.0	2055.8
180°	2060.3	2060.3	2060.3	2060.3	2060.3

(END OF REPORT)