

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035243

Luminaire Tested: S125DIW-B375D1050UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035243
REPORT IS A COMBINATION OF REPORTS P1003415 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D1050UB30-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5733.0 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035243

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035243

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	84	81	82	79	76	73	61	59	57	45	44	42	30	29	29
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	60	55	68	60	54	50	47	43	40	35	32	30	23	22	20
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	21	19	18
5	64	53	45	39	57	47	41	36	37	32	29	28	24	22	19	17	15
6	59	47	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	9
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3070 cd/sqm

TEST NUMBER: P1035243

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	0.9
10°-20°	151.6	2.6
20°-30°	223.8	3.9
30°-40°	261.1	4.6
40°-50°	262.2	4.6
50°-60°	230.2	4.0
60°-70°	171.4	3.0
70°-80°	97.9	1.7
80°-90°	30.3	0.5
90°-100°	47.0	0.8
100°-110°	312.3	5.4
110°-120°	562.4	9.8
120°-130°	721.9	12.6
130°-140°	776.4	13.5
140°-150°	728.7	12.7
150°-160°	589.5	10.3
160°-170°	381.2	6.6
170°-180°	131.5	2.3
0°-30°	429.0	7.5
0°-40°	690.0	12.0
0°-60°	1182.4	20.6
0°-90°	1482.0	25.9
90°-120°	921.7	16.1
90°-150°	3148.8	54.9
90°-180°	4251.0	74.1
0°-180°	5733.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	1	9	16	22	25	5
95°	58	55	16	22	22	72
105°	302	306	306	306	305	320
115°	566	571	572	568	562	561
125°	805	812	812	808	805	719
135°	1004	1010	1008	1006	1000	774
145°	1164	1166	1166	1167	1161	728
155°	1282	1276	1278	1281	1273	591
165°	1353	1347	1348	1354	1346	382
175°	1384	1378	1379	1387	1378	132
180°	1384	1384	1384	1384	1384	

TEST NUMBER: P1035243

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	1.0	9.2	16.4	21.5	24.6
92.5°	19.5	10.3	16.4	21.5	22.6
95°	58.5	55.4	16.4	21.5	21.5
97.5°	109.8	115.9	18.5	20.5	21.5
100°	171.3	174.4	178.5	25.6	21.5
102.5°	233.9	238.0	240.0	242.1	155.9
105°	301.6	305.7	305.7	305.7	304.7
107.5°	371.4	371.4	373.4	374.4	370.3
110°	439.1	439.1	441.1	438.0	439.1

TEST NUMBER: P1035243

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	502.7	505.7	506.8	502.7	500.6
115°	566.3	571.4	572.4	568.3	562.2
117.5°	632.9	632.9	637.1	630.9	628.8
120°	694.5	693.5	696.5	694.5	689.4
122.5°	748.9	754.0	755.0	753.0	746.8
125°	805.3	812.5	812.5	808.4	805.3
127.5°	859.7	864.8	863.8	861.7	853.5
130°	908.9	914.0	915.1	912.0	906.8
132.5°	958.1	964.3	961.2	961.2	956.1
135°	1004.3	1010.5	1008.4	1006.4	1000.2
137.5°	1047.4	1053.5	1051.5	1051.5	1046.4
140°	1089.4	1091.5	1090.5	1092.5	1086.4
142.5°	1127.4	1128.4	1130.5	1130.5	1124.3
145°	1164.3	1166.4	1166.4	1167.4	1161.3
147.5°	1197.2	1197.2	1198.2	1199.2	1192.0
150°	1227.9	1225.9	1227.9	1230.0	1221.8
152.5°	1257.7	1252.6	1254.6	1256.7	1249.5
155°	1282.3	1276.2	1278.2	1281.3	1273.1
157.5°	1301.8	1298.7	1298.7	1301.8	1293.6
160°	1322.3	1316.2	1317.2	1321.3	1313.1
162.5°	1338.7	1332.6	1333.6	1339.8	1330.5
165°	1353.1	1346.9	1348.0	1354.1	1345.9
167.5°	1364.4	1358.2	1359.2	1366.4	1357.2
170°	1373.6	1366.4	1367.5	1375.7	1366.4
172.5°	1379.8	1372.6	1374.6	1381.8	1372.6
175°	1383.9	1377.7	1378.7	1386.9	1377.7
177.5°	1386.9	1380.8	1381.8	1389.0	1380.8
180°	1383.9	1383.9	1383.9	1383.9	1383.9

(END OF REPORT)