

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035244

Luminaire Tested: S125DIW-B375D1050UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035244
REPORT IS A COMBINATION OF REPORTS P1003416 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D1050UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5168.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035244

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035244

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	37	37	29
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	31	31	24
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26	26	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	22	22	17
4	70	60	52	47	63	54	48	42	43	38	34	32	29	27	22	20	19	19	19	15
5	65	53	46	40	58	48	41	36	38	33	30	29	25	23	20	18	16	16	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	14	14	11
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13	13	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	11	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	10	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	12	13	11	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3070 cd/sqm

TEST NUMBER: P1035244

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.0
10°-20°	151.6	2.9
20°-30°	223.8	4.3
30°-40°	261.1	5.1
40°-50°	262.2	5.1
50°-60°	230.2	4.5
60°-70°	171.4	3.3
70°-80°	97.9	1.9
80°-90°	30.3	0.6
90°-100°	87.8	1.7
100°-110°	260.9	5.0
110°-120°	442.5	8.6
120°-130°	582.5	11.3
130°-140°	652.7	12.6
140°-150°	639.8	12.4
150°-160°	537.4	10.4
160°-170°	357.2	6.9
170°-180°	125.0	2.4
0°-30°	429.0	8.3
0°-40°	690.0	13.4
0°-60°	1182.4	22.9
0°-90°	1482.0	28.7
90°-120°	791.2	15.3
90°-150°	2666.2	51.6
90°-180°	3686.0	71.3
0°-180°	5168.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	1	9	16	22	25	6
95°	67	69	79	86	88	70
105°	234	240	246	252	255	250
115°	443	447	449	448	447	438
125°	646	653	654	652	651	579
135°	841	847	848	848	844	648
145°	1018	1023	1026	1026	1023	637
155°	1166	1166	1166	1171	1166	537
165°	1267	1265	1266	1270	1264	358
175°	1318	1314	1314	1320	1312	125
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1035244

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	1.0	9.2	16.4	21.6	24.7
92.5°	30.8	36.0	45.2	52.4	54.5
95°	66.8	68.9	79.1	86.3	88.4
97.5°	102.8	103.8	118.2	124.4	125.4
100°	143.9	143.9	157.2	166.5	168.6
102.5°	188.1	193.2	198.4	208.6	211.7
105°	234.3	239.5	245.6	251.8	254.9
107.5°	284.7	289.8	295.0	298.1	298.1
110°	337.1	342.2	345.3	348.4	347.4

TEST NUMBER: P1035244

CATALOG NUMBER: S125DIW-B375D1050UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	390.6	392.6	396.7	397.7	395.7
115°	443.0	447.1	449.1	448.1	447.1
117.5°	496.4	497.4	499.5	500.5	496.4
120°	545.7	550.9	551.9	551.9	547.8
122.5°	599.2	600.2	603.3	602.3	599.2
125°	646.5	652.6	653.7	651.6	650.6
127.5°	698.9	702.0	703.0	702.0	699.9
130°	745.1	750.3	752.3	751.3	749.2
132.5°	791.4	800.6	799.6	798.6	795.5
135°	840.7	846.9	847.9	847.9	843.8
137.5°	887.0	893.1	895.2	896.2	891.1
140°	931.2	936.3	939.4	941.4	936.3
142.5°	975.4	979.5	983.6	984.6	979.5
145°	1018.5	1022.6	1025.7	1025.7	1022.6
147.5°	1058.6	1061.7	1063.7	1066.8	1058.6
150°	1098.7	1097.7	1101.8	1101.8	1099.7
152.5°	1131.6	1133.6	1134.7	1137.7	1133.6
155°	1165.5	1165.5	1166.5	1170.6	1165.5
157.5°	1196.3	1194.3	1195.3	1199.4	1192.2
160°	1223.1	1220.0	1221.0	1225.1	1220.0
162.5°	1246.7	1244.6	1244.6	1249.8	1243.6
165°	1267.2	1265.2	1266.2	1270.3	1264.2
167.5°	1285.7	1281.6	1281.6	1287.8	1281.6
170°	1300.1	1296.0	1296.0	1302.2	1295.0
172.5°	1310.4	1306.3	1306.3	1312.5	1306.3
175°	1317.6	1313.5	1313.5	1319.7	1312.5
177.5°	1322.7	1318.6	1317.6	1323.8	1316.6
180°	1320.7	1320.7	1320.7	1320.7	1320.7

(END OF REPORT)