

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035853

Luminaire Tested: S125RDIW-B1270D770UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035853
REPORT IS A COMBINATION OF REPORTS P1006319 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D770UB27-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7532.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035853

CATALOG NUMBER: S125RDIW-B1270D770UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035853

CATALOG NUMBER: S125RDIW-B1270D770UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59
2	92	85	79	74	87	80	75	70	71	67	63	63	59	57	55	52	50
3	85	75	68	62	79	71	64	59	63	58	53	56	52	48	49	46	43
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37
5	71	60	51	45	67	56	49	43	50	44	40	45	40	36	39	36	33
6	66	54	45	40	62	51	43	38	45	39	35	41	36	32	36	32	29
7	61	49	40	35	57	46	39	34	41	35	31	37	32	28	33	29	26
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23
9	53	40	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21
10	50	37	30	25	47	36	29	24	32	26	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13142	13142	13142
5°	13143	12814	12834
10°	13015	12491	12381
15°	12831	12039	11785
20°	12603	11495	11159
25°	12341	10964	10488
30°	12021	10380	9784
35°	11694	9788	9036
40°	11384	9179	8305
45°	11010	8521	7540
50°	10632	7823	6760
55°	10192	7137	5954
60°	9742	6351	5116
65°	9206	5473	4213
70°	8580	4455	3316
75°	7717	3350	2417
80°	6508	2169	1630
85°	4871	1166	919

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11010 cd/sqm

TEST NUMBER: P1035853

CATALOG NUMBER: S125RDIW-B1270D770UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.0	2.6
10°-20°	539.5	7.2
20°-30°	782.2	10.4
30°-40°	891.2	11.8
40°-50°	868.6	11.5
50°-60°	731.0	9.7
60°-70°	512.3	6.8
70°-80°	262.6	3.5
80°-90°	67.0	0.9
90°-100°	64.0	0.8
100°-110°	190.0	2.5
110°-120°	322.3	4.3
120°-130°	424.2	5.6
130°-140°	475.4	6.3
140°-150°	466.0	6.2
150°-160°	391.4	5.2
160°-170°	260.2	3.5
170°-180°	91.1	1.2
0°-30°	1514.8	20.1
0°-40°	2405.9	31.9
0°-60°	4005.6	53.2
0°-90°	4847.5	64.4
90°-120°	576.3	7.7
90°-150°	1941.9	25.8
90°-180°	2685.0	35.6
0°-180°	7532.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2051	2051	2051	2051	2051	
5°	2048	2042	2025	2040	2037	194
15°	1947	1938	1906	1904	1890	549
25°	1766	1743	1686	1665	1648	813
35°	1521	1484	1414	1370	1348	953
45°	1246	1201	1115	1053	1030	961
55°	945	895	809	739	714	845
65°	640	587	505	443	420	634
75°	341	294	229	195	184	360
85°	85	57	50	48	46	93
90°	1	7	12	16	18	8
95°	49	50	58	63	64	51
105°	171	174	179	183	186	182
115°	323	326	327	326	326	319
125°	471	475	476	475	474	422
135°	612	617	618	618	614	472
145°	742	745	747	747	745	464
155°	849	849	850	853	849	391
165°	923	921	922	925	921	260
175°	960	957	957	961	956	91
180°	962	962	962	962	962	

TEST NUMBER: P1035853

CATALOG NUMBER: S125RDIW-B1270D770UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2051.1	2051.1	2051.1	2051.1	2051.1
2.5°	2055.7	2051.1	2035.6	2051.1	2049.5
5°	2048.0	2041.8	2024.8	2040.2	2037.1
7.5°	2032.5	2026.3	2006.2	2018.6	2015.5
10°	2009.3	2004.6	1982.9	1987.6	1982.9
12.5°	1982.9	1976.7	1945.7	1948.8	1941.1
15°	1947.3	1938.0	1905.5	1903.9	1890.0
17.5°	1910.1	1896.2	1857.4	1849.7	1838.9
20°	1865.2	1849.7	1800.1	1792.4	1778.4
22.5°	1815.6	1800.1	1747.5	1730.4	1719.6
25°	1766.0	1742.8	1685.5	1665.4	1648.3
27.5°	1710.3	1682.4	1622.0	1595.6	1578.6
30°	1648.3	1618.9	1553.8	1518.2	1504.2
32.5°	1587.9	1552.3	1485.6	1445.4	1426.8
35°	1521.3	1484.1	1414.4	1369.5	1347.8
37.5°	1457.8	1412.8	1341.6	1288.9	1267.2
40°	1389.6	1343.1	1268.8	1209.9	1191.3
42.5°	1318.3	1270.3	1192.9	1137.1	1107.7
45°	1245.5	1200.6	1115.4	1053.4	1030.2
47.5°	1169.6	1123.1	1037.9	974.4	948.1
50°	1098.4	1047.2	958.9	893.9	870.6
52.5°	1020.9	968.2	886.1	814.9	791.6
55°	945.0	895.4	808.7	739.0	714.2
57.5°	867.5	814.9	731.2	663.0	641.4
60°	793.2	739.0	655.3	587.1	563.9
62.5°	714.2	663.0	577.8	515.9	492.6
65°	639.8	587.1	505.0	443.1	419.8
67.5°	565.4	512.8	433.8	374.9	356.3
70°	489.5	436.9	359.4	311.4	292.8
72.5°	415.2	364.1	292.8	249.4	238.6
75°	340.8	294.3	229.3	195.2	184.4
77.5°	264.9	227.7	173.5	147.2	137.9
80°	201.4	164.2	120.8	106.9	103.8
82.5°	139.4	106.9	80.6	75.9	74.4
85°	85.2	57.3	49.6	48.0	46.5
87.5°	35.6	24.8	23.2	23.2	21.7
90°	0.7	6.7	12.0	15.7	18.0
92.5°	22.5	26.2	32.9	38.2	39.7
95°	48.7	50.2	57.6	62.9	64.4
97.5°	74.9	75.6	86.1	90.6	91.3
100°	104.8	104.8	114.5	121.3	122.8
102.5°	137.0	140.7	144.5	152.0	154.2
105°	170.7	174.4	178.9	183.4	185.6
107.5°	207.3	211.1	214.8	217.1	217.1
110°	245.5	249.3	251.5	253.8	253.0



TEST NUMBER: P1035853

CATALOG NUMBER: S125RDIW-B1270D770UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.4	285.9	288.9	289.7	288.2
115°	322.6	325.6	327.1	326.4	325.6
117.5°	361.5	362.3	363.8	364.5	361.5
120°	397.5	401.2	402.0	402.0	399.0
122.5°	436.4	437.1	439.4	438.6	436.4
125°	470.8	475.3	476.1	474.6	473.8
127.5°	509.0	511.3	512.0	511.3	509.8
130°	542.7	546.4	547.9	547.2	545.7
132.5°	576.4	583.1	582.4	581.6	579.4
135°	612.3	616.8	617.5	617.5	614.5
137.5°	646.0	650.5	652.0	652.7	649.0
140°	678.2	681.9	684.2	685.7	681.9
142.5°	710.4	713.4	716.4	717.1	713.4
145°	741.8	744.8	747.0	747.0	744.8
147.5°	771.0	773.2	774.7	777.0	771.0
150°	800.2	799.4	802.4	802.4	800.9
152.5°	824.1	825.6	826.4	828.6	825.6
155°	848.8	848.8	849.6	852.6	848.8
157.5°	871.3	869.8	870.5	873.5	868.3
160°	890.8	888.5	889.3	892.3	888.5
162.5°	908.0	906.5	906.5	910.2	905.7
165°	922.9	921.4	922.2	925.2	920.7
167.5°	936.4	933.4	933.4	937.9	933.4
170°	946.9	943.9	943.9	948.4	943.2
172.5°	954.4	951.4	951.4	955.9	951.4
175°	959.6	956.6	956.6	961.1	955.9
177.5°	963.4	960.4	959.6	964.1	958.9
180°	961.9	961.9	961.9	961.9	961.9

(END OF REPORT)