

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035313

Luminaire Tested: S125DIW-B375D1560UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035313
REPORT IS A COMBINATION OF REPORTS P1003566 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D1560UB40-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6932.0 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035313

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035313

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30
1	91	87	83	80	81	77	74	71	59	57	55	42	41	40	26	26	25
2	83	76	70	65	73	67	63	58	51	48	45	37	35	33	23	22	21
3	76	67	60	54	67	59	53	49	45	41	38	32	30	28	20	19	18
4	69	59	51	46	61	52	46	41	40	36	32	29	26	24	18	17	15
5	63	52	45	39	56	47	40	35	36	31	28	26	23	20	16	15	13
6	58	47	39	33	51	42	35	30	32	27	24	23	20	18	15	13	12
7	54	42	34	29	47	37	31	26	29	24	21	21	18	16	13	12	10
8	50	38	31	25	44	34	28	23	26	22	18	19	16	14	12	11	9
9	46	34	27	22	41	31	25	20	24	19	16	17	14	12	11	10	8
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3624	3624	3624
5°	3624	3540	3546
10°	3594	3458	3447
15°	3547	3361	3331
20°	3482	3249	3198
25°	3414	3126	3055
30°	3331	2998	2904
35°	3243	2864	2736
40°	3152	2722	2586
45°	3053	2585	2426
50°	2945	2427	2241
55°	2838	2255	2070
60°	2709	2073	1872
65°	2555	1862	1666
70°	2400	1620	1429
75°	2137	1334	1155
80°	1823	996	849
85°	1407	590	468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3053 cd/sqm

TEST NUMBER: P1035313

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	0.8
10°-20°	150.7	2.2
20°-30°	222.5	3.2
30°-40°	259.6	3.7
40°-50°	260.8	3.8
50°-60°	228.9	3.3
60°-70°	170.5	2.5
70°-80°	97.4	1.4
80°-90°	31.2	0.4
90°-100°	130.0	1.9
100°-110°	386.3	5.6
110°-120°	655.1	9.5
120°-130°	862.4	12.4
130°-140°	966.4	13.9
140°-150°	947.2	13.7
150°-160°	795.6	11.5
160°-170°	528.9	7.6
170°-180°	185.1	2.7
0°-30°	426.7	6.2
0°-40°	686.3	9.9
0°-60°	1176.0	17.0
0°-90°	1475.1	21.3
90°-120°	1171.4	16.9
90°-150°	3947.4	56.9
90°-180°	5457.0	78.7
0°-180°	6932.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	566	566	566	566	566	
5°	565	564	559	563	563	54
15°	538	537	532	534	534	152
25°	489	486	480	481	480	225
35°	422	420	414	412	408	264
45°	345	344	338	333	332	266
55°	263	262	256	252	248	235
65°	178	177	172	168	166	176
75°	94	94	91	90	88	100
85°	25	25	25	25	24	27
90°	2	14	24	32	36	8
95°	99	102	117	128	131	103
105°	347	354	364	373	377	370
115°	656	662	665	663	662	649
125°	957	966	968	965	963	858
135°	1245	1254	1255	1255	1249	959
145°	1508	1514	1519	1519	1514	943
155°	1726	1726	1727	1733	1726	795
165°	1876	1873	1875	1881	1872	529
175°	1951	1945	1945	1954	1943	185
180°	1955	1955	1955	1955	1955	

TEST NUMBER: P1035313

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	565.6	565.6	565.6	565.6	565.6
2.5°	567.3	566.0	561.5	566.0	565.6
5°	564.7	563.8	559.3	563.3	562.9
7.5°	560.6	559.7	554.8	558.8	558.4
10°	554.8	553.9	549.0	552.6	552.1
12.5°	547.7	545.9	541.4	544.1	544.1
15°	538.3	536.9	532.0	534.2	534.2
17.5°	528.4	526.2	521.3	523.9	521.7
20°	515.4	514.5	508.7	511.9	509.6
22.5°	502.5	500.7	495.3	497.1	495.8
25°	488.6	486.4	480.5	481.4	480.1
27.5°	472.5	471.1	465.3	465.8	464.4
30°	456.8	455.5	448.8	447.9	446.5
32.5°	439.8	437.6	431.8	430.0	427.3
35°	421.9	420.1	413.9	411.6	408.1
37.5°	403.6	401.3	395.5	392.4	390.2
40°	384.8	382.6	376.3	372.3	370.9
42.5°	364.7	362.9	356.6	353.0	350.8
45°	345.4	343.6	338.3	332.9	331.5
47.5°	324.4	324.8	318.1	312.8	309.6
50°	304.3	302.9	297.5	291.7	288.6
52.5°	283.7	282.8	277.0	272.0	268.5
55°	263.1	261.7	255.5	251.5	248.3
57.5°	241.2	240.7	235.3	230.0	228.6
60°	220.6	218.8	213.9	209.4	206.3
62.5°	199.1	197.8	193.7	188.8	186.6
65°	177.6	176.7	171.8	167.8	166.0
67.5°	156.6	154.8	151.2	147.7	146.8
70°	136.9	134.7	130.7	128.0	126.2
72.5°	115.4	114.1	111.9	108.7	106.9
75°	94.4	93.5	91.3	89.9	88.1
77.5°	74.7	74.3	72.9	72.0	70.7
80°	56.4	56.4	55.5	55.0	54.1
82.5°	40.3	39.4	39.4	38.5	38.5
85°	24.6	25.1	25.1	24.6	23.7
87.5°	12.1	12.1	11.6	11.6	10.7
90°	1.5	13.7	24.3	32.0	36.5
92.5°	45.6	53.3	67.0	77.6	80.6
95°	98.9	101.9	117.2	127.8	130.9
97.5°	152.2	153.7	175.0	184.1	185.6
100°	213.0	213.0	232.8	246.5	249.5
102.5°	278.5	286.1	293.7	308.9	313.4
105°	346.9	354.5	363.7	372.8	377.4
107.5°	421.5	429.1	436.7	441.3	441.3
110°	499.1	506.7	511.3	515.8	514.3

TEST NUMBER: P1035313

CATALOG NUMBER: S125DIW-B375D1560UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.2	581.3	587.3	588.9	585.8
115°	655.8	661.9	664.9	663.4	661.9
117.5°	734.9	736.5	739.5	741.0	734.9
120°	808.0	815.6	817.1	817.1	811.0
122.5°	887.1	888.6	893.2	891.7	887.1
125°	957.1	966.2	967.7	964.7	963.2
127.5°	1034.7	1039.3	1040.8	1039.3	1036.2
130°	1103.2	1110.8	1113.8	1112.3	1109.2
132.5°	1171.6	1185.3	1183.8	1182.3	1177.7
135°	1244.7	1253.8	1255.3	1255.3	1249.2
137.5°	1313.1	1322.3	1325.3	1326.8	1319.2
140°	1378.6	1386.2	1390.7	1393.8	1386.2
142.5°	1444.0	1450.1	1456.2	1457.7	1450.1
145°	1507.9	1514.0	1518.6	1518.6	1514.0
147.5°	1567.2	1571.8	1574.9	1579.4	1567.2
150°	1626.6	1625.1	1631.2	1631.2	1628.1
152.5°	1675.3	1678.3	1679.8	1684.4	1678.3
155°	1725.5	1725.5	1727.0	1733.1	1725.5
157.5°	1771.1	1768.1	1769.6	1775.7	1765.1
160°	1810.7	1806.1	1807.7	1813.7	1806.1
162.5°	1845.7	1842.7	1842.7	1850.3	1841.1
165°	1876.1	1873.1	1874.6	1880.7	1871.6
167.5°	1903.5	1897.4	1897.4	1906.6	1897.4
170°	1924.8	1918.7	1918.7	1927.9	1917.2
172.5°	1940.0	1934.0	1934.0	1943.1	1934.0
175°	1950.7	1944.6	1944.6	1953.7	1943.1
177.5°	1958.3	1952.2	1950.7	1959.8	1949.2
180°	1955.3	1955.3	1955.3	1955.3	1955.3

(END OF REPORT)