

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035897

Luminaire Tested: S125RDIW-B375D1340UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035897
REPORT IS A COMBINATION OF REPORTS P1006427 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D1340UB30-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6064.0 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035897

CATALOG NUMBER: S125RDIW-B375D1340UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035897

CATALOG NUMBER: S125RDIW-B375D1340UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27
2	84	77	71	66	74	68	63	59	53	49	47	38	36	34	25	24	23
3	76	67	61	55	68	60	54	50	46	42	39	34	31	29	22	21	19
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11
8	50	38	31	26	45	35	28	24	27	22	19	20	17	15	13	12	10
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	11	9
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3815	3815	3815
5°	3816	3721	3727
10°	3779	3627	3595
15°	3725	3495	3421
20°	3659	3338	3240
25°	3583	3184	3045
30°	3490	3014	2840
35°	3395	2842	2623
40°	3305	2665	2411
45°	3197	2474	2189
50°	3087	2271	1963
55°	2959	2072	1729
60°	2829	1844	1485
65°	2673	1589	1223
70°	2491	1294	963
75°	2242	973	701
80°	1890	630	473
85°	1412	339	267

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3197 cd/sqm

TEST NUMBER: P1035897

CATALOG NUMBER: S125RDIW-B375D1340UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.0	0.9
10°-20°	156.6	2.6
20°-30°	227.1	3.7
30°-40°	258.7	4.3
40°-50°	252.2	4.2
50°-60°	212.2	3.5
60°-70°	148.7	2.5
70°-80°	76.3	1.3
80°-90°	21.6	0.4
90°-100°	110.9	1.8
100°-110°	329.5	5.4
110°-120°	558.7	9.2
120°-130°	735.5	12.1
130°-140°	824.2	13.6
140°-150°	807.9	13.3
150°-160°	678.6	11.2
160°-170°	451.1	7.4
170°-180°	157.9	2.6
0°-30°	439.8	7.3
0°-40°	698.5	11.5
0°-60°	1163.0	19.2
0°-90°	1409.6	23.2
90°-120°	999.1	16.5
90°-150°	3366.8	55.5
90°-180°	4654.0	76.7
0°-180°	6064.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	595	593	588	592	592	56
15°	565	563	553	553	549	159
25°	513	506	489	484	479	236
35°	442	431	411	398	391	277
45°	362	349	324	306	299	279
55°	274	260	235	214	207	245
65°	186	170	147	129	122	184
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	1	12	21	27	31	7
95°	84	87	100	109	112	88
105°	296	302	310	318	322	316
115°	559	565	567	566	565	553
125°	816	824	825	823	822	731
135°	1062	1069	1071	1071	1066	818
145°	1286	1291	1295	1295	1291	804
155°	1472	1472	1473	1478	1472	678
165°	1600	1598	1599	1604	1596	452
175°	1664	1659	1659	1666	1657	158
180°	1668	1668	1668	1668	1668	

TEST NUMBER: P1035897

CATALOG NUMBER: S125RDIW-B375D1340UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	595.5	595.5	595.5	595.5	595.5
2.5°	596.9	595.5	591.0	595.5	595.1
5°	594.6	592.8	587.9	592.4	591.5
7.5°	590.1	588.3	582.5	586.1	585.2
10°	583.4	582.0	575.7	577.1	575.7
12.5°	575.7	573.9	564.9	565.8	563.6
15°	565.4	562.7	553.2	552.8	548.7
17.5°	554.6	550.5	539.3	537.0	533.9
20°	541.5	537.0	522.7	520.4	516.4
22.5°	527.2	522.7	507.4	502.4	499.3
25°	512.8	506.0	489.4	483.5	478.6
27.5°	496.6	488.5	470.9	463.3	458.3
30°	478.6	470.0	451.1	440.8	436.7
32.5°	461.0	450.7	431.3	419.7	414.3
35°	441.7	430.9	410.7	397.6	391.3
37.5°	423.3	410.2	389.5	374.2	367.9
40°	403.5	390.0	368.4	351.3	345.9
42.5°	382.8	368.8	346.3	330.1	321.6
45°	361.6	348.6	323.8	305.9	299.1
47.5°	339.6	326.1	301.4	282.9	275.3
50°	318.9	304.1	278.4	259.5	252.8
52.5°	296.4	281.1	257.3	236.6	229.8
55°	274.4	260.0	234.8	214.5	207.4
57.5°	251.9	236.6	212.3	192.5	186.2
60°	230.3	214.5	190.3	170.5	163.7
62.5°	207.4	192.5	167.8	149.8	143.0
65°	185.8	170.5	146.6	128.6	121.9
67.5°	164.2	148.9	125.9	108.8	103.5
70°	142.1	126.8	104.4	90.4	85.0
72.5°	120.5	105.7	85.0	72.4	69.3
75°	99.0	85.5	66.6	56.7	53.5
77.5°	76.9	66.1	50.4	42.7	40.0
80°	58.5	47.7	35.1	31.0	30.1
82.5°	40.5	31.0	23.4	22.0	21.6
85°	24.7	16.6	14.4	13.9	13.5
87.5°	10.3	7.2	6.7	6.7	6.3
90°	1.3	11.7	20.8	27.3	31.1
92.5°	38.9	45.4	57.1	66.2	68.8
95°	84.4	87.0	99.9	109.0	111.6
97.5°	129.8	131.1	149.2	157.0	158.3
100°	181.7	181.7	198.6	210.2	212.8
102.5°	237.5	244.0	250.5	263.5	267.4
105°	295.9	302.4	310.2	318.0	321.9
107.5°	359.5	366.0	372.5	376.4	376.4
110°	425.7	432.2	436.1	440.0	438.7

TEST NUMBER: P1035897

CATALOG NUMBER: S125RDIW-B375D1340UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	493.2	495.8	501.0	502.3	499.7
115°	559.4	564.6	567.1	565.8	564.6
117.5°	626.8	628.1	630.7	632.0	626.8
120°	689.1	695.6	696.9	696.9	691.7
122.5°	756.6	757.9	761.8	760.5	756.6
125°	816.3	824.1	825.4	822.8	821.5
127.5°	882.5	886.4	887.7	886.4	883.8
130°	940.9	947.4	950.0	948.7	946.1
132.5°	999.3	1011.0	1009.7	1008.4	1004.5
135°	1061.6	1069.4	1070.7	1070.7	1065.5
137.5°	1120.0	1127.8	1130.4	1131.7	1125.2
140°	1175.8	1182.3	1186.2	1188.8	1182.3
142.5°	1231.6	1236.8	1242.0	1243.3	1236.8
145°	1286.1	1291.3	1295.2	1295.2	1291.3
147.5°	1336.8	1340.6	1343.2	1347.1	1336.8
150°	1387.4	1386.1	1391.3	1391.3	1388.7
152.5°	1428.9	1431.5	1432.8	1436.7	1431.5
155°	1471.7	1471.7	1473.0	1478.2	1471.7
157.5°	1510.7	1508.1	1509.4	1514.6	1505.5
160°	1544.4	1540.5	1541.8	1547.0	1540.5
162.5°	1574.3	1571.7	1571.7	1578.1	1570.4
165°	1600.2	1597.6	1598.9	1604.1	1596.3
167.5°	1623.6	1618.4	1618.4	1626.2	1618.4
170°	1641.7	1636.5	1636.5	1644.3	1635.3
172.5°	1654.7	1649.5	1649.5	1657.3	1649.5
175°	1663.8	1658.6	1658.6	1666.4	1657.3
177.5°	1670.3	1665.1	1663.8	1671.6	1662.5
180°	1667.7	1667.7	1667.7	1667.7	1667.7

(END OF REPORT)