

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035379

Luminaire Tested: S125DIW-B375D770UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035379
REPORT IS A COMBINATION OF REPORTS P1003707 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D770UB50-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4027.9 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035379

CATALOG NUMBER: S125DIW-B375D770UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035379

CATALOG NUMBER: S125DIW-B375D770UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35		
1	94	90	86	83	85	82	78	76	66	64	62	51	50	48	38	37	36	30		
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	32	30	25		
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21		
4	72	61	53	47	64	56	49	44	45	40	36	35	32	29	26	24	22	18		
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	24	21	19	16		
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14		
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12		
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11		
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10		
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3503	3503	3503
5°	3503	3422	3428
10°	3474	3343	3333
15°	3428	3249	3221
20°	3367	3141	3091
25°	3300	3022	2953
30°	3221	2898	2808
35°	3136	2769	2645
40°	3047	2632	2500
45°	2952	2498	2346
50°	2847	2346	2166
55°	2743	2180	2001
60°	2619	2004	1809
65°	2471	1800	1611
70°	2321	1566	1382
75°	2067	1289	1117
80°	1761	962	821
85°	1361	569	452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2952 cd/sqm

TEST NUMBER: P1035379

CATALOG NUMBER: S125DIW-B375D770UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	1.3
10°-20°	145.7	3.6
20°-30°	215.1	5.3
30°-40°	251.0	6.2
40°-50°	252.1	6.3
50°-60°	221.3	5.5
60°-70°	164.8	4.1
70°-80°	94.1	2.3
80°-90°	28.6	0.7
90°-100°	62.0	1.5
100°-110°	184.3	4.6
110°-120°	312.5	7.8
120°-130°	411.4	10.2
130°-140°	461.1	11.4
140°-150°	451.9	11.2
150°-160°	379.6	9.4
160°-170°	252.3	6.3
170°-180°	88.3	2.2
0°-30°	412.5	10.2
0°-40°	663.5	16.5
0°-60°	1136.8	28.2
0°-90°	1424.4	35.4
90°-120°	558.8	13.9
90°-150°	1883.3	46.8
90°-180°	2603.0	64.6
0°-180°	4027.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	546	545	541	545	544	52
15°	520	519	514	516	516	147
25°	472	470	464	465	464	217
35°	408	406	400	398	394	255
45°	334	332	327	322	320	257
55°	254	253	247	243	240	227
65°	172	171	166	162	160	170
75°	91	90	88	87	85	97
85°	24	24	24	24	23	26
90°	1	6	12	15	17	5
95°	47	49	56	61	62	49
105°	166	169	174	178	180	176
115°	313	316	317	316	316	310
125°	457	461	462	460	460	409
135°	594	598	599	599	596	458
145°	719	722	724	724	722	450
155°	823	823	824	827	823	379
165°	895	894	894	897	893	253
175°	931	928	928	932	927	88
180°	933	933	933	933	933	

TEST NUMBER: P1035379

CATALOG NUMBER: S125DIW-B375D770UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	546.7	546.7	546.7	546.7	546.7
2.5°	548.5	547.2	542.8	547.2	546.7
5°	545.9	545.0	540.7	544.6	544.1
7.5°	542.0	541.1	536.3	540.2	539.8
10°	536.3	535.5	530.7	534.2	533.8
12.5°	529.4	527.7	523.4	526.0	526.0
15°	520.3	519.0	514.3	516.5	516.5
17.5°	510.8	508.7	503.9	506.5	504.3
20°	498.3	497.4	491.8	494.8	492.7
22.5°	485.7	484.0	478.8	480.6	479.3
25°	472.3	470.2	464.5	465.4	464.1
27.5°	456.8	455.5	449.8	450.3	449.0
30°	441.6	440.3	433.8	433.0	431.7
32.5°	425.2	423.0	417.4	415.7	413.1
35°	407.9	406.2	400.1	397.9	394.5
37.5°	390.1	388.0	382.4	379.3	377.2
40°	372.0	369.8	363.8	359.9	358.6
42.5°	352.5	350.8	344.7	341.3	339.1
45°	333.9	332.2	327.0	321.8	320.5
47.5°	313.6	314.0	307.5	302.3	299.3
50°	294.1	292.8	287.6	282.0	279.0
52.5°	274.2	273.4	267.7	263.0	259.5
55°	254.3	253.0	247.0	243.1	240.1
57.5°	233.1	232.7	227.5	222.3	221.0
60°	213.2	211.5	206.8	202.4	199.4
62.5°	192.5	191.2	187.3	182.5	180.4
65°	171.7	170.9	166.1	162.2	160.5
67.5°	151.4	149.7	146.2	142.7	141.9
70°	132.4	130.2	126.3	123.7	122.0
72.5°	111.6	110.3	108.1	105.1	103.4
75°	91.3	90.4	88.2	86.9	85.2
77.5°	72.2	71.8	70.5	69.6	68.3
80°	54.5	54.5	53.6	53.2	52.3
82.5°	38.9	38.1	38.1	37.2	37.2
85°	23.8	24.2	24.2	23.8	22.9
87.5°	11.7	11.7	11.2	11.2	10.4
90°	0.7	6.5	11.6	15.2	17.4
92.5°	21.8	25.4	31.9	37.0	38.5
95°	47.2	48.6	55.9	61.0	62.4
97.5°	72.6	73.3	83.5	87.8	88.6
100°	101.6	101.6	111.1	117.6	119.1
102.5°	132.9	136.5	140.1	147.4	149.5
105°	165.5	169.1	173.5	177.9	180.0
107.5°	201.1	204.7	208.4	210.5	210.5
110°	238.1	241.7	243.9	246.1	245.4

TEST NUMBER: P1035379

CATALOG NUMBER: S125DIW-B375D770UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	275.9	277.3	280.2	280.9	279.5
115°	312.9	315.8	317.2	316.5	315.8
117.5°	350.6	351.4	352.8	353.5	350.6
120°	385.5	389.1	389.8	389.8	386.9
122.5°	423.2	424.0	426.1	425.4	423.2
125°	456.6	461.0	461.7	460.3	459.5
127.5°	493.7	495.8	496.6	495.8	494.4
130°	526.3	530.0	531.4	530.7	529.2
132.5°	559.0	565.5	564.8	564.1	561.9
135°	593.8	598.2	598.9	598.9	596.0
137.5°	626.5	630.9	632.3	633.0	629.4
140°	657.7	661.4	663.5	665.0	661.4
142.5°	688.9	691.8	694.7	695.5	691.8
145°	719.4	722.3	724.5	724.5	722.3
147.5°	747.7	749.9	751.4	753.6	747.7
150°	776.1	775.3	778.2	778.2	776.8
152.5°	799.3	800.7	801.5	803.6	800.7
155°	823.2	823.2	824.0	826.9	823.2
157.5°	845.0	843.6	844.3	847.2	842.1
160°	863.9	861.7	862.4	865.3	861.7
162.5°	880.6	879.1	879.1	882.8	878.4
165°	895.1	893.7	894.4	897.3	892.9
167.5°	908.2	905.3	905.3	909.6	905.3
170°	918.3	915.4	915.4	919.8	914.7
172.5°	925.6	922.7	922.7	927.1	922.7
175°	930.7	927.8	927.8	932.1	927.1
177.5°	934.3	931.4	930.7	935.0	930.0
180°	932.9	932.9	932.9	932.9	932.9

(END OF REPORT)