

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035934

Luminaire Tested: S125RDIW-B375D470UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

**Test Information**


Test Method: LM-79-2019  
Report Number: P1035934  
REPORT IS A COMBINATION OF REPORTS P1006514 AND P1007351  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-B375D470UB30-4F0-XX-W2A-F  
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}  
{m-EER=0.647}  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3303.0 lumens  
Efficiency: N/A  
Efficacy: 126.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 26.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1035934  
CATALOG NUMBER: S125RDIW-B375D470UB30-4F0-XX-W2A-F

### Luminous Intensity Polar Plot





TEST NUMBER: P1035934

CATALOG NUMBER: S125RDIW-B375D470UB30-4F0-XX-W2A-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	49	49	49	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	44	43	42	36
2	88	81	75	70	80	74	69	64	61	58	54	50	47	45	39	37	36	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	32	31	35	32	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26	31	28	26	23
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	25	23	20	25	23	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	23	20	18	15
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	18	16	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	20	17	15	13
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3815	3815	3815
5°	3816	3721	3727
10°	3779	3627	3595
15°	3725	3495	3421
20°	3659	3338	3240
25°	3583	3184	3045
30°	3490	3014	2840
35°	3395	2842	2623
40°	3305	2665	2411
45°	3197	2474	2189
50°	3087	2271	1963
55°	2959	2072	1729
60°	2829	1844	1485
65°	2673	1589	1223
70°	2491	1294	963
75°	2242	973	701
80°	1890	630	473
85°	1412	339	267

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3197 cd/sqm



TEST NUMBER: P1035934

CATALOG NUMBER: S125RDIW-B375D470UB30-4F0-XX-W2A-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.0	1.7
10°-20°	156.6	4.7
20°-30°	227.1	6.9
30°-40°	258.7	7.8
40°-50°	252.2	7.6
50°-60°	212.2	6.4
60°-70°	148.7	4.5
70°-80°	76.3	2.3
80°-90°	19.9	0.6
90°-100°	20.9	0.6
100°-110°	139.2	4.2
110°-120°	250.7	7.6
120°-130°	321.8	9.7
130°-140°	346.1	10.5
140°-150°	324.9	9.8
150°-160°	262.8	8.0
160°-170°	170.0	5.1
170°-180°	58.6	1.8
0°-30°	439.8	13.3
0°-40°	698.5	21.1
0°-60°	1163.0	35.2
0°-90°	1407.9	42.6
90°-120°	410.9	12.4
90°-150°	1403.8	42.5
90°-180°	1895.0	57.4
0°-180°	3303.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	595	593	588	592	592	56
15°	565	563	553	553	549	159
25°	513	506	489	484	479	236
35°	442	431	411	398	391	277
45°	362	349	324	306	299	279
55°	274	260	235	214	207	245
65°	186	170	147	129	122	184
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	0	4	7	10	11	3
95°	26	25	7	10	10	32
105°	134	136	136	136	136	142
115°	252	255	255	253	251	250
125°	359	362	362	360	359	321
135°	448	450	450	449	446	345
145°	519	520	520	520	518	325
155°	572	569	570	571	568	263
165°	603	600	601	604	600	170
175°	617	614	615	618	614	59
180°	617	617	617	617	617	



TEST NUMBER: P1035934

CATALOG NUMBER: S125RDIW-B375D470UB30-4F0-XX-W2A-F

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	595.5	595.5	595.5	595.5	595.5
2.5°	596.9	595.5	591.0	595.5	595.1
5°	594.6	592.8	587.9	592.4	591.5
7.5°	590.1	588.3	582.5	586.1	585.2
10°	583.4	582.0	575.7	577.1	575.7
12.5°	575.7	573.9	564.9	565.8	563.6
15°	565.4	562.7	553.2	552.8	548.7
17.5°	554.6	550.5	539.3	537.0	533.9
20°	541.5	537.0	522.7	520.4	516.4
22.5°	527.2	522.7	507.4	502.4	499.3
25°	512.8	506.0	489.4	483.5	478.6
27.5°	496.6	488.5	470.9	463.3	458.3
30°	478.6	470.0	451.1	440.8	436.7
32.5°	461.0	450.7	431.3	419.7	414.3
35°	441.7	430.9	410.7	397.6	391.3
37.5°	423.3	410.2	389.5	374.2	367.9
40°	403.5	390.0	368.4	351.3	345.9
42.5°	382.8	368.8	346.3	330.1	321.6
45°	361.6	348.6	323.8	305.9	299.1
47.5°	339.6	326.1	301.4	282.9	275.3
50°	318.9	304.1	278.4	259.5	252.8
52.5°	296.4	281.1	257.3	236.6	229.8
55°	274.4	260.0	234.8	214.5	207.4
57.5°	251.9	236.6	212.3	192.5	186.2
60°	230.3	214.5	190.3	170.5	163.7
62.5°	207.4	192.5	167.8	149.8	143.0
65°	185.8	170.5	146.6	128.6	121.9
67.5°	164.2	148.9	125.9	108.8	103.5
70°	142.1	126.8	104.4	90.4	85.0
72.5°	120.5	105.7	85.0	72.4	69.3
75°	99.0	85.5	66.6	56.7	53.5
77.5°	76.9	66.1	50.4	42.7	40.0
80°	58.5	47.7	35.1	31.0	30.1
82.5°	40.5	31.0	23.4	22.0	21.6
85°	24.7	16.6	14.4	13.9	13.5
87.5°	10.3	7.2	6.7	6.7	6.3
90°	0.5	4.1	7.3	9.6	11.0
92.5°	8.7	4.6	7.3	9.6	10.1
95°	26.1	24.7	7.3	9.6	9.6
97.5°	48.9	51.7	8.2	9.1	9.6
100°	76.4	77.7	79.6	11.4	9.6
102.5°	104.3	106.1	107.0	107.9	69.5
105°	134.5	136.3	136.3	136.3	135.8
107.5°	165.6	165.6	166.5	166.9	165.1
110°	195.7	195.7	196.6	195.3	195.7



TEST NUMBER: P1035934

CATALOG NUMBER: S125RDIW-B375D470UB30-4F0-XX-W2A-F

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	224.1	225.5	225.9	224.1	223.2
115°	252.4	254.7	255.2	253.4	250.6
117.5°	282.2	282.2	284.0	281.3	280.3
120°	309.6	309.2	310.5	309.6	307.3
122.5°	333.8	336.1	336.6	335.7	332.9
125°	359.0	362.2	362.2	360.4	359.0
127.5°	383.2	385.5	385.1	384.2	380.5
130°	405.2	407.5	407.9	406.6	404.3
132.5°	427.1	429.9	428.5	428.5	426.2
135°	447.7	450.5	449.6	448.6	445.9
137.5°	466.9	469.7	468.8	468.8	466.5
140°	485.7	486.6	486.1	487.1	484.3
142.5°	502.6	503.1	504.0	504.0	501.2
145°	519.1	520.0	520.0	520.4	517.7
147.5°	533.7	533.7	534.2	534.6	531.4
150°	547.4	546.5	547.4	548.3	544.7
152.5°	560.7	558.4	559.3	560.2	557.0
155°	571.7	568.9	569.8	571.2	567.5
157.5°	580.3	579.0	579.0	580.3	576.7
160°	589.5	586.7	587.2	589.0	585.4
162.5°	596.8	594.1	594.5	597.3	593.2
165°	603.2	600.5	600.9	603.7	600.0
167.5°	608.2	605.5	606.0	609.2	605.0
170°	612.4	609.2	609.6	613.3	609.2
172.5°	615.1	611.9	612.8	616.0	611.9
175°	616.9	614.2	614.6	618.3	614.2
177.5°	618.3	615.6	616.0	619.2	615.6
180°	616.9	616.9	616.9	616.9	616.9

(END OF REPORT)