

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035946

Luminaire Tested: S125RDIW-B375D470UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035946
REPORT IS A COMBINATION OF REPORTS P1006532 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D470UB50-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3176.0 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035946

CATALOG NUMBER: S125RDIW-B375D470UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035946

CATALOG NUMBER: S125RDIW-B375D470UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	64	61	58	54	50	47	45	39	37	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	32	31
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	25	23	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	18	16
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3669	3669	3669
5°	3670	3578	3584
10°	3634	3487	3457
15°	3582	3361	3290
20°	3519	3210	3115
25°	3446	3061	2928
30°	3356	2898	2732
35°	3265	2733	2523
40°	3179	2562	2319
45°	3075	2379	2105
50°	2969	2184	1888
55°	2845	1993	1662
60°	2721	1774	1428
65°	2570	1528	1176
70°	2396	1243	925
75°	2156	935	675
80°	1816	605	455
85°	1361	324	257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3075 cd/sqm

TEST NUMBER: P1035946

CATALOG NUMBER: S125RDIW-B375D470UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.7
10°-20°	150.6	4.7
20°-30°	218.4	6.9
30°-40°	248.8	7.8
40°-50°	242.5	7.6
50°-60°	204.1	6.4
60°-70°	143.0	4.5
70°-80°	73.3	2.3
80°-90°	19.2	0.6
90°-100°	20.1	0.6
100°-110°	133.9	4.2
110°-120°	241.1	7.6
120°-130°	309.4	9.7
130°-140°	332.8	10.5
140°-150°	312.4	9.8
150°-160°	252.7	8.0
160°-170°	163.4	5.1
170°-180°	56.4	1.8
0°-30°	422.9	13.3
0°-40°	671.7	21.2
0°-60°	1118.4	35.2
0°-90°	1353.9	42.6
90°-120°	395.1	12.4
90°-150°	1349.7	42.5
90°-180°	1822.0	57.4
0°-180°	3176.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	573	573	573	573	573	
5°	572	570	565	570	569	54
15°	544	541	532	532	528	153
25°	493	487	471	465	460	227
35°	425	414	395	382	376	266
45°	348	335	311	294	288	268
55°	264	250	226	206	199	236
65°	179	164	141	124	117	177
75°	95	82	64	54	52	101
85°	24	16	14	13	13	26
90°	0	4	7	9	11	3
95°	25	24	7	9	9	31
105°	129	131	131	131	131	137
115°	243	245	245	244	241	241
125°	345	348	348	346	345	308
135°	430	433	432	431	429	332
145°	499	500	500	500	498	312
155°	550	547	548	549	546	253
165°	580	577	578	580	577	164
175°	593	590	591	594	590	56
180°	593	593	593	593	593	

TEST NUMBER: P1035946

CATALOG NUMBER: S125RDIW-B375D470UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	572.7	572.7	572.7	572.7	572.7
2.5°	574.0	572.7	568.3	572.7	572.2
5°	571.8	570.1	565.3	569.6	568.8
7.5°	567.5	565.7	560.1	563.6	562.7
10°	561.0	559.7	553.6	554.9	553.6
12.5°	553.6	551.9	543.3	544.1	542.0
15°	543.7	541.1	532.0	531.6	527.7
17.5°	533.3	529.4	518.6	516.4	513.4
20°	520.8	516.4	502.6	500.4	496.5
22.5°	506.9	502.6	487.9	483.1	480.1
25°	493.1	486.6	470.6	465.0	460.2
27.5°	477.5	469.7	452.9	445.5	440.7
30°	460.2	452.0	433.8	423.9	420.0
32.5°	443.3	433.4	414.8	403.5	398.4
35°	424.7	414.4	394.9	382.4	376.3
37.5°	407.0	394.5	374.6	359.9	353.8
40°	388.0	375.0	354.2	337.8	332.6
42.5°	368.1	354.7	333.0	317.5	309.3
45°	347.8	335.2	311.4	294.1	287.6
47.5°	326.6	313.6	289.8	272.1	264.7
50°	306.7	292.4	267.7	249.6	243.1
52.5°	285.0	270.3	247.4	227.5	221.0
55°	263.8	250.0	225.8	206.3	199.4
57.5°	242.2	227.5	204.2	185.1	179.1
60°	221.5	206.3	183.0	163.9	157.4
62.5°	199.4	185.1	161.3	144.0	137.5
65°	178.6	163.9	141.0	123.7	117.2
67.5°	157.9	143.2	121.1	104.7	99.5
70°	136.7	122.0	100.3	86.9	81.7
72.5°	115.9	101.6	81.7	69.6	66.6
75°	95.2	82.2	64.0	54.5	51.5
77.5°	74.0	63.6	48.4	41.1	38.5
80°	56.2	45.8	33.7	29.8	29.0
82.5°	38.9	29.8	22.5	21.2	20.8
85°	23.8	16.0	13.8	13.4	13.0
87.5°	9.9	6.9	6.5	6.5	6.1
90°	0.4	4.0	7.0	9.2	10.6
92.5°	8.4	4.4	7.0	9.2	9.7
95°	25.1	23.7	7.0	9.2	9.2
97.5°	47.0	49.7	7.9	8.8	9.2
100°	73.4	74.8	76.5	11.0	9.2
102.5°	100.3	102.0	102.9	103.8	66.8
105°	129.3	131.0	131.0	131.0	130.6
107.5°	159.2	159.2	160.1	160.5	158.7
110°	188.2	188.2	189.1	187.8	188.2

TEST NUMBER: P1035946

CATALOG NUMBER: S125RDIW-B375D470UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.5	216.8	217.2	215.5	214.6
115°	242.7	244.9	245.4	243.6	241.0
117.5°	271.3	271.3	273.1	270.4	269.5
120°	297.7	297.2	298.6	297.7	295.5
122.5°	321.0	323.2	323.6	322.8	320.1
125°	345.2	348.3	348.3	346.5	345.2
127.5°	368.5	370.7	370.2	369.4	365.8
130°	389.6	391.8	392.2	390.9	388.7
132.5°	410.7	413.3	412.0	412.0	409.8
135°	430.5	433.1	432.2	431.4	428.7
137.5°	449.0	451.6	450.7	450.7	448.5
140°	467.0	467.9	467.4	468.3	465.7
142.5°	483.2	483.7	484.6	484.6	481.9
145°	499.1	500.0	500.0	500.4	497.8
147.5°	513.2	513.2	513.6	514.0	511.0
150°	526.3	525.5	526.3	527.2	523.7
152.5°	539.1	536.9	537.8	538.7	535.6
155°	549.6	547.0	547.9	549.2	545.7
157.5°	558.0	556.7	556.7	558.0	554.5
160°	566.8	564.2	564.6	566.4	562.8
162.5°	573.8	571.2	571.6	574.3	570.3
165°	580.0	577.3	577.8	580.4	576.9
167.5°	584.8	582.2	582.6	585.7	581.7
170°	588.8	585.7	586.1	589.7	585.7
172.5°	591.4	588.3	589.2	592.3	588.3
175°	593.2	590.5	591.0	594.5	590.5
177.5°	594.5	591.9	592.3	595.4	591.9
180°	593.2	593.2	593.2	593.2	593.2

(END OF REPORT)