

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035958

Luminaire Tested: S125RDIW-B375D770UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035958
REPORT IS A COMBINATION OF REPORTS P1006564 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D770UB35-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4551.0 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035958

CATALOG NUMBER: S125RDIW-B375D770UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035958

CATALOG NUMBER: S125RDIW-B375D770UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	90	86	82	84	81	78	75	64	62	60	49	47	46	34	34	33
2	85	78	72	68	77	71	66	61	56	53	50	43	41	39	30	29	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21
5	65	54	46	41	59	49	42	37	39	34	31	30	27	24	22	20	18
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16
7	56	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3832	3832	3832
5°	3833	3736	3742
10°	3795	3642	3610
15°	3741	3510	3436
20°	3675	3352	3254
25°	3598	3197	3058
30°	3505	3027	2853
35°	3410	2854	2635
40°	3319	2676	2422
45°	3211	2484	2198
50°	3100	2281	1971
55°	2971	2081	1736
60°	2841	1852	1492
65°	2685	1596	1228
70°	2501	1299	967
75°	2251	977	705
80°	1897	632	476
85°	1418	341	269

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3211 cd/sqm

TEST NUMBER: P1035958

CATALOG NUMBER: S125RDIW-B375D770UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.2
10°-20°	157.3	3.5
20°-30°	228.1	5.0
30°-40°	259.9	5.7
40°-50°	253.3	5.6
50°-60°	213.2	4.7
60°-70°	149.4	3.3
70°-80°	76.6	1.7
80°-90°	20.6	0.5
90°-100°	34.7	0.8
100°-110°	230.4	5.1
110°-120°	415.0	9.1
120°-130°	532.7	11.7
130°-140°	572.9	12.6
140°-150°	537.7	11.8
150°-160°	434.9	9.6
160°-170°	281.3	6.2
170°-180°	97.0	2.1
0°-30°	441.7	9.7
0°-40°	701.5	15.4
0°-60°	1168.0	25.7
0°-90°	1414.5	31.1
90°-120°	680.1	14.9
90°-150°	2323.3	51.0
90°-180°	3136.0	68.9
0°-180°	4551.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	597	595	590	595	594	57
15°	568	565	556	555	551	160
25°	515	508	492	486	481	237
35°	444	433	412	399	393	278
45°	363	350	325	307	300	280
55°	276	261	236	216	208	246
65°	187	171	147	129	122	185
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	1	7	12	16	18	4
95°	43	41	12	16	16	53
105°	222	226	226	226	225	236
115°	418	422	422	419	415	414
125°	594	600	600	596	594	531
135°	741	746	744	742	738	571
145°	859	861	861	861	857	537
155°	946	942	943	945	939	436
165°	998	994	995	999	993	282
175°	1021	1016	1017	1023	1016	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1035958

CATALOG NUMBER: S125RDIW-B375D770UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	598.1	598.1	598.1	598.1	598.1
2.5°	599.4	598.1	593.5	598.1	597.6
5°	597.2	595.3	590.4	594.9	594.0
7.5°	592.6	590.8	585.0	588.6	587.7
10°	585.9	584.5	578.2	579.5	578.2
12.5°	578.2	576.4	567.3	568.2	566.0
15°	567.8	565.1	555.6	555.1	551.1
17.5°	557.0	552.9	541.6	539.3	536.2
20°	543.9	539.3	524.9	522.6	518.6
22.5°	529.4	524.9	509.5	504.6	501.4
25°	514.9	508.2	491.5	485.6	480.6
27.5°	498.7	490.6	472.9	465.3	460.3
30°	480.6	472.0	453.1	442.7	438.6
32.5°	463.0	452.6	433.2	421.4	416.0
35°	443.6	432.7	412.4	399.3	393.0
37.5°	425.1	412.0	391.2	375.8	369.5
40°	405.2	391.6	369.9	352.8	347.4
42.5°	384.4	370.4	347.8	331.6	323.0
45°	363.2	350.1	325.2	307.2	300.4
47.5°	341.0	327.5	302.6	284.1	276.4
50°	320.3	305.4	279.6	260.6	253.9
52.5°	297.7	282.3	258.4	237.6	230.8
55°	275.5	261.1	235.8	215.5	208.2
57.5°	253.0	237.6	213.2	193.3	187.0
60°	231.3	215.5	191.1	171.2	164.4
62.5°	208.2	193.3	168.5	150.4	143.6
65°	186.6	171.2	147.3	129.2	122.4
67.5°	164.9	149.5	126.5	109.3	103.9
70°	142.7	127.4	104.8	90.8	85.4
72.5°	121.1	106.2	85.4	72.7	69.6
75°	99.4	85.8	66.9	56.9	53.8
77.5°	77.2	66.4	50.6	42.9	40.2
80°	58.7	47.9	35.2	31.2	30.3
82.5°	40.7	31.2	23.5	22.1	21.7
85°	24.8	16.7	14.5	14.0	13.6
87.5°	10.4	7.2	6.8	6.8	6.3
90°	0.8	6.8	12.1	15.9	18.2
92.5°	14.4	7.6	12.1	15.9	16.7
95°	43.1	40.9	12.1	15.9	15.9
97.5°	81.0	85.5	13.6	15.1	15.9
100°	126.4	128.7	131.7	18.9	15.9
102.5°	172.6	175.6	177.1	178.6	115.0
105°	222.5	225.6	225.6	225.6	224.8
107.5°	274.0	274.0	275.5	276.3	273.2
110°	324.0	324.0	325.5	323.2	324.0

TEST NUMBER: P1035958

CATALOG NUMBER: S125RDIW-B375D770UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.9	373.2	373.9	370.9	369.4
115°	417.8	421.6	422.4	419.3	414.8
117.5°	467.0	467.0	470.0	465.5	464.0
120°	512.4	511.7	513.9	512.4	508.6
122.5°	552.5	556.3	557.1	555.6	551.0
125°	594.2	599.5	599.5	596.4	594.2
127.5°	634.3	638.1	637.3	635.8	629.7
130°	670.6	674.4	675.2	672.9	669.1
132.5°	706.9	711.5	709.2	709.2	705.4
135°	741.0	745.5	744.0	742.5	738.0
137.5°	772.8	777.3	775.8	775.8	772.0
140°	803.8	805.3	804.6	806.1	801.6
142.5°	831.8	832.6	834.1	834.1	829.6
145°	859.1	860.6	860.6	861.4	856.8
147.5°	883.3	883.3	884.1	884.8	879.5
150°	906.0	904.5	906.0	907.5	901.5
152.5°	928.0	924.2	925.7	927.2	921.9
155°	946.1	941.6	943.1	945.4	939.3
157.5°	960.5	958.2	958.2	960.5	954.5
160°	975.6	971.1	971.9	974.9	968.8
162.5°	987.8	983.2	984.0	988.5	981.7
165°	998.4	993.8	994.6	999.1	993.1
167.5°	1006.7	1002.1	1002.9	1008.2	1001.4
170°	1013.5	1008.2	1009.0	1015.0	1008.2
172.5°	1018.0	1012.7	1014.2	1019.5	1012.7
175°	1021.1	1016.5	1017.3	1023.3	1016.5
177.5°	1023.3	1018.8	1019.5	1024.8	1018.8
180°	1021.1	1021.1	1021.1	1021.1	1021.1

(END OF REPORT)