

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036036

Luminaire Tested: S125RDIW-B610D470UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036036
REPORT IS A COMBINATION OF REPORTS P1006740 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D470UB35-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4281.0 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036036

CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1036036

CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	55	53	52
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	39	35	33
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29
6	64	52	44	38	60	49	42	36	43	37	33	37	33	29	32	28	25
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23
8	55	43	35	30	51	40	33	29	36	30	26	31	26	23	27	23	20
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6446	6446	6446
5°	6447	6286	6295
10°	6384	6127	6073
15°	6294	5905	5780
20°	6182	5639	5473
25°	6054	5378	5144
30°	5896	5092	4799
35°	5736	4801	4432
40°	5584	4502	4073
45°	5400	4180	3698
50°	5215	3838	3316
55°	4999	3501	2920
60°	4779	3115	2510
65°	4515	2684	2066
70°	4209	2186	1626
75°	3786	1644	1185
80°	3193	1065	799
85°	2390	571	450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5400 cd/sqm

TEST NUMBER: P1036036

CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	2.2
10°-20°	264.6	6.2
20°-30°	383.7	9.0
30°-40°	437.1	10.2
40°-50°	426.1	10.0
50°-60°	358.6	8.4
60°-70°	251.3	5.9
70°-80°	128.8	3.0
80°-90°	33.0	0.8
90°-100°	21.0	0.5
100°-110°	139.8	3.3
110°-120°	251.8	5.9
120°-130°	323.2	7.5
130°-140°	347.6	8.1
140°-150°	326.2	7.6
150°-160°	263.9	6.2
160°-170°	170.7	4.0
170°-180°	58.9	1.4
0°-30°	743.0	17.4
0°-40°	1180.1	27.6
0°-60°	1964.8	45.9
0°-90°	2377.9	55.5
90°-120°	412.6	9.6
90°-150°	1409.7	32.9
90°-180°	1903.0	44.5
0°-180°	4281.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1005	1002	993	1001	999	95
15°	955	951	935	934	927	269
25°	866	855	827	817	808	399
35°	746	728	694	672	661	467
45°	611	589	547	517	505	471
55°	464	439	397	362	350	414
65°	314	288	248	217	206	311
75°	167	144	112	96	90	177
85°	42	28	24	24	23	46
90°	0	4	7	10	11	4
95°	26	25	7	10	10	32
105°	135	137	137	137	136	143
115°	254	256	256	254	252	251
125°	360	364	364	362	360	322
135°	450	452	451	450	448	347
145°	521	522	522	523	520	326
155°	574	571	572	574	570	265
165°	606	603	604	606	602	171
175°	620	617	617	621	617	59
180°	620	620	620	620	620	

TEST NUMBER: P1036036

CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1006.1	1006.1	1006.1	1006.1	1006.1
2.5°	1008.4	1006.1	998.5	1006.1	1005.3
5°	1004.6	1001.5	993.2	1000.8	999.2
7.5°	997.0	993.9	984.0	990.1	988.6
10°	985.6	983.3	972.6	974.9	972.6
12.5°	972.6	969.6	954.4	955.9	952.1
15°	955.2	950.6	934.6	933.9	927.0
17.5°	936.9	930.1	911.1	907.3	902.0
20°	914.9	907.3	883.0	879.2	872.3
22.5°	890.6	883.0	857.1	848.8	843.5
25°	866.3	854.9	826.7	816.9	808.5
27.5°	838.9	825.2	795.6	782.7	774.3
30°	808.5	794.1	762.2	744.7	737.8
32.5°	778.9	761.4	728.7	709.0	699.8
35°	746.2	728.0	693.8	671.7	661.1
37.5°	715.0	693.0	658.1	632.2	621.6
40°	681.6	658.8	622.3	593.5	584.3
42.5°	646.7	623.1	585.1	557.7	543.3
45°	610.9	588.9	547.1	516.7	505.3
47.5°	573.7	550.9	509.1	478.0	465.0
50°	538.8	513.7	470.4	438.4	427.1
52.5°	500.8	474.9	434.6	399.7	388.3
55°	463.5	439.2	396.7	362.5	350.3
57.5°	425.5	399.7	358.7	325.2	314.6
60°	389.1	362.5	321.4	288.0	276.6
62.5°	350.3	325.2	283.4	253.0	241.6
65°	313.8	288.0	247.7	217.3	205.9
67.5°	277.4	251.5	212.8	183.9	174.8
70°	240.1	214.3	176.3	152.7	143.6
72.5°	203.6	178.6	143.6	122.3	117.0
75°	167.2	144.4	112.5	95.7	90.4
77.5°	129.9	111.7	85.1	72.2	67.6
80°	98.8	80.5	59.3	52.4	50.9
82.5°	68.4	52.4	39.5	37.2	36.5
85°	41.8	28.1	24.3	23.6	22.8
87.5°	17.5	12.2	11.4	11.4	10.6
90°	0.5	4.1	7.3	9.6	11.0
92.5°	8.7	4.6	7.3	9.6	10.1
95°	26.2	24.8	7.3	9.6	9.6
97.5°	49.1	51.9	8.3	9.2	9.6
100°	76.7	78.1	79.9	11.5	9.6
102.5°	104.7	106.5	107.5	108.4	69.8
105°	135.0	136.9	136.9	136.9	136.4
107.5°	166.3	166.3	167.2	167.6	165.8
110°	196.6	196.6	197.5	196.1	196.6



TEST NUMBER: P1036036

CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.0	226.4	226.9	225.0	224.1
115°	253.5	255.8	256.3	254.4	251.7
117.5°	283.4	283.4	285.2	282.4	281.5
120°	310.9	310.5	311.8	310.9	308.6
122.5°	335.3	337.6	338.0	337.1	334.3
125°	360.5	363.7	363.7	361.9	360.5
127.5°	384.9	387.2	386.7	385.8	382.1
130°	406.9	409.2	409.7	408.3	406.0
132.5°	428.9	431.7	430.3	430.3	428.0
135°	449.6	452.4	451.4	450.5	447.8
137.5°	468.9	471.7	470.7	470.7	468.4
140°	487.7	488.6	488.2	489.1	486.4
142.5°	504.7	505.2	506.1	506.1	503.3
145°	521.3	522.2	522.2	522.6	519.9
147.5°	536.0	536.0	536.4	536.9	533.7
150°	549.7	548.8	549.7	550.6	547.0
152.5°	563.0	560.8	561.7	562.6	559.4
155°	574.1	571.3	572.2	573.6	569.9
157.5°	582.8	581.4	581.4	582.8	579.1
160°	592.0	589.2	589.7	591.5	587.8
162.5°	599.3	596.6	597.0	599.8	595.7
165°	605.8	603.0	603.5	606.2	602.5
167.5°	610.8	608.1	608.5	611.7	607.6
170°	614.9	611.7	612.2	615.9	611.7
172.5°	617.7	614.5	615.4	618.6	614.5
175°	619.5	616.8	617.2	620.9	616.8
177.5°	620.9	618.2	618.6	621.8	618.2
180°	619.5	619.5	619.5	619.5	619.5

(END OF REPORT)