

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036037

Luminaire Tested: S125RDIW-B610D470UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036037
REPORT IS A COMBINATION OF REPORTS P1006741 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D470UB35-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4028.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036037
CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot





TEST NUMBER: P1036037

CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																			
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50																			
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43																			
3	83	74	67	61	78	69	63	58	61	56	52	53	49	46	45	42	40	36																			
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31																			
5	70	59	51	45	65	55	48	42	49	43	38	42	38	34	37	33	30	27																			
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24																			
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	21																			
8	56	43	36	30	52	41	34	29	36	31	27	32	27	24	28	24	22	19																			
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	19	17																			
10	49	37	29	24	46	35	28	23	31	25	22	27	23	20	24	20	18	16																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6446	6446	6446
5°	6447	6286	6295
10°	6384	6127	6073
15°	6294	5905	5780
20°	6182	5639	5473
25°	6054	5378	5144
30°	5896	5092	4799
35°	5736	4801	4432
40°	5584	4502	4073
45°	5400	4180	3698
50°	5215	3838	3316
55°	4999	3501	2920
60°	4779	3115	2510
65°	4515	2684	2066
70°	4209	2186	1626
75°	3786	1644	1185
80°	3193	1065	799
85°	2390	571	450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5400 cd/sqm



TEST NUMBER: P1036037

CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	2.4
10°-20°	264.6	6.6
20°-30°	383.7	9.5
30°-40°	437.1	10.9
40°-50°	426.1	10.6
50°-60°	358.6	8.9
60°-70°	251.3	6.2
70°-80°	128.8	3.2
80°-90°	33.1	0.8
90°-100°	39.3	1.0
100°-110°	116.8	2.9
110°-120°	198.1	4.9
120°-130°	260.8	6.5
130°-140°	292.2	7.3
140°-150°	286.4	7.1
150°-160°	240.6	6.0
160°-170°	159.9	4.0
170°-180°	56.0	1.4
0°-30°	743.0	18.4
0°-40°	1180.1	29.3
0°-60°	1964.8	48.8
0°-90°	2377.9	59.0
90°-120°	354.2	8.8
90°-150°	1193.6	29.6
90°-180°	1650.0	41.0
0°-180°	4028.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1005	1002	993	1001	999	95
15°	955	951	935	934	927	269
25°	866	855	827	817	808	399
35°	746	728	694	672	661	467
45°	611	589	547	517	505	471
55°	464	439	397	362	350	414
65°	314	288	248	217	206	311
75°	167	144	112	96	90	177
85°	42	28	24	24	23	46
90°	0	4	7	10	11	4
95°	30	31	35	39	40	31
105°	105	107	110	113	114	112
115°	198	200	201	201	200	196
125°	289	292	293	292	291	259
135°	376	379	380	380	378	290
145°	456	458	459	459	458	285
155°	522	522	522	524	522	240
165°	567	566	567	569	566	160
175°	590	588	588	591	588	56
180°	591	591	591	591	591	



TEST NUMBER: P1036037

CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1006.1	1006.1	1006.1	1006.1	1006.1
2.5°	1008.4	1006.1	998.5	1006.1	1005.3
5°	1004.6	1001.5	993.2	1000.8	999.2
7.5°	997.0	993.9	984.0	990.1	988.6
10°	985.6	983.3	972.6	974.9	972.6
12.5°	972.6	969.6	954.4	955.9	952.1
15°	955.2	950.6	934.6	933.9	927.0
17.5°	936.9	930.1	911.1	907.3	902.0
20°	914.9	907.3	883.0	879.2	872.3
22.5°	890.6	883.0	857.1	848.8	843.5
25°	866.3	854.9	826.7	816.9	808.5
27.5°	838.9	825.2	795.6	782.7	774.3
30°	808.5	794.1	762.2	744.7	737.8
32.5°	778.9	761.4	728.7	709.0	699.8
35°	746.2	728.0	693.8	671.7	661.1
37.5°	715.0	693.0	658.1	632.2	621.6
40°	681.6	658.8	622.3	593.5	584.3
42.5°	646.7	623.1	585.1	557.7	543.3
45°	610.9	588.9	547.1	516.7	505.3
47.5°	573.7	550.9	509.1	478.0	465.0
50°	538.8	513.7	470.4	438.4	427.1
52.5°	500.8	474.9	434.6	399.7	388.3
55°	463.5	439.2	396.7	362.5	350.3
57.5°	425.5	399.7	358.7	325.2	314.6
60°	389.1	362.5	321.4	288.0	276.6
62.5°	350.3	325.2	283.4	253.0	241.6
65°	313.8	288.0	247.7	217.3	205.9
67.5°	277.4	251.5	212.8	183.9	174.8
70°	240.1	214.3	176.3	152.7	143.6
72.5°	203.6	178.6	143.6	122.3	117.0
75°	167.2	144.4	112.5	95.7	90.4
77.5°	129.9	111.7	85.1	72.2	67.6
80°	98.8	80.5	59.3	52.4	50.9
82.5°	68.4	52.4	39.5	37.2	36.5
85°	41.8	28.1	24.3	23.6	22.8
87.5°	17.5	12.2	11.4	11.4	10.6
90°	0.5	4.1	7.4	9.7	11.0
92.5°	13.8	16.1	20.2	23.5	24.4
95°	29.9	30.8	35.4	38.6	39.6
97.5°	46.0	46.5	52.9	55.7	56.1
100°	64.4	64.4	70.4	74.5	75.5
102.5°	84.2	86.5	88.8	93.4	94.8
105°	104.9	107.2	110.0	112.7	114.1
107.5°	127.4	129.7	132.0	133.4	133.4
110°	150.9	153.2	154.6	156.0	155.5



TEST NUMBER: P1036037

CATALOG NUMBER: S125RDIW-B610D470UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	175.8	177.6	178.1	177.1
115°	198.3	200.1	201.1	200.6	200.1
117.5°	222.2	222.7	223.6	224.1	222.2
120°	244.3	246.6	247.1	247.1	245.2
122.5°	268.2	268.7	270.1	269.6	268.2
125°	289.4	292.2	292.6	291.7	291.2
127.5°	312.9	314.2	314.7	314.2	313.3
130°	333.6	335.9	336.8	336.3	335.4
132.5°	354.3	358.4	358.0	357.5	356.1
135°	376.4	379.1	379.6	379.6	377.7
137.5°	397.1	399.8	400.7	401.2	398.9
140°	416.9	419.2	420.5	421.5	419.2
142.5°	436.6	438.5	440.3	440.8	438.5
145°	456.0	457.8	459.2	459.2	457.8
147.5°	473.9	475.3	476.2	477.6	473.9
150°	491.8	491.4	493.2	493.2	492.3
152.5°	506.6	507.5	508.0	509.3	507.5
155°	521.8	521.8	522.2	524.1	521.8
157.5°	535.6	534.6	535.1	536.9	533.7
160°	547.5	546.1	546.6	548.4	546.1
162.5°	558.1	557.2	557.2	559.5	556.7
165°	567.3	566.4	566.8	568.7	565.9
167.5°	575.6	573.7	573.7	576.5	573.7
170°	582.0	580.2	580.2	582.9	579.7
172.5°	586.6	584.8	584.8	587.6	584.8
175°	589.9	588.0	588.0	590.8	587.6
177.5°	592.2	590.3	589.9	592.6	589.4
180°	591.2	591.2	591.2	591.2	591.2

(END OF REPORT)