

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036048

Luminaire Tested: S125RDIW-B610D770UB27-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036048
REPORT IS A COMBINATION OF REPORTS P1006758 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D770UB27-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5445.0 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036048

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1036048

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	74	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	21
7	58	45	38	32	52	42	35	30	35	30	26	29	25	22	23	21	18
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	16
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6365	6365	6365
5°	6366	6206	6216
10°	6303	6050	5997
15°	6214	5831	5707
20°	6103	5567	5404
25°	5977	5310	5080
30°	5822	5027	4738
35°	5664	4740	4376
40°	5513	4446	4022
45°	5332	4127	3651
50°	5149	3789	3274
55°	4936	3456	2883
60°	4718	3076	2478
65°	4459	2651	2040
70°	4156	2158	1606
75°	3738	1622	1171
80°	3151	1050	790
85°	2361	564	444

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5332 cd/sqm

TEST NUMBER: P1036048

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.7
10°-20°	261.3	4.8
20°-30°	378.8	7.0
30°-40°	431.6	7.9
40°-50°	420.7	7.7
50°-60°	354.1	6.5
60°-70°	248.1	4.6
70°-80°	127.2	2.3
80°-90°	33.2	0.6
90°-100°	34.2	0.6
100°-110°	227.5	4.2
110°-120°	409.7	7.5
120°-130°	525.9	9.7
130°-140°	565.6	10.4
140°-150°	530.8	9.7
150°-160°	429.4	7.9
160°-170°	277.7	5.1
170°-180°	95.8	1.8
0°-30°	733.6	13.5
0°-40°	1165.2	21.4
0°-60°	1940.0	35.6
0°-90°	2348.5	43.1
90°-120°	671.4	12.3
90°-150°	2293.7	42.1
90°-180°	3097.0	56.9
0°-180°	5445.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	992	989	981	988	987	94
15°	943	939	923	922	915	266
25°	855	844	816	807	798	394
35°	737	719	685	663	653	461
45°	603	582	540	510	499	465
55°	458	434	392	358	346	409
65°	310	284	245	215	203	307
75°	165	143	111	94	89	174
85°	41	28	24	23	22	45
90°	1	7	12	16	18	5
95°	43	40	12	16	16	52
105°	220	223	223	223	222	233
115°	412	416	417	414	410	409
125°	587	592	592	589	587	524
135°	732	736	735	733	729	564
145°	848	850	850	850	846	530
155°	934	930	931	933	927	430
165°	986	981	982	986	980	278
175°	1008	1004	1004	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1036048

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	993.4	993.4	993.4	993.4	993.4
2.5°	995.6	993.4	985.9	993.4	992.6
5°	991.9	988.9	980.6	988.1	986.6
7.5°	984.4	981.4	971.6	977.6	976.1
10°	973.1	970.9	960.4	962.6	960.4
12.5°	960.4	957.4	942.4	943.9	940.1
15°	943.1	938.6	922.9	922.1	915.3
17.5°	925.1	918.3	899.6	895.8	890.6
20°	903.3	895.8	871.8	868.1	861.3
22.5°	879.3	871.8	846.3	838.1	832.8
25°	855.3	844.1	816.3	806.6	798.3
27.5°	828.3	814.8	785.5	772.8	764.5
30°	798.3	784.0	752.5	735.3	728.5
32.5°	769.0	751.8	719.5	700.0	691.0
35°	736.8	718.8	685.0	663.3	652.7
37.5°	706.0	684.3	649.7	624.2	613.7
40°	673.0	650.5	614.5	586.0	577.0
42.5°	638.5	615.2	577.7	550.7	536.5
45°	603.2	581.5	540.2	510.2	498.9
47.5°	566.5	544.0	502.7	471.9	459.2
50°	532.0	507.2	464.4	432.9	421.7
52.5°	494.4	468.9	429.2	394.7	383.4
55°	457.7	433.7	391.6	357.9	345.9
57.5°	420.2	394.7	354.1	321.1	310.6
60°	384.1	357.9	317.4	284.4	273.1
62.5°	345.9	321.1	279.9	249.8	238.6
65°	309.9	284.4	244.6	214.6	203.3
67.5°	273.9	248.3	210.1	181.6	172.6
70°	237.1	211.6	174.1	150.8	141.8
72.5°	201.1	176.3	141.8	120.8	115.5
75°	165.1	142.6	111.0	94.5	89.3
77.5°	128.3	110.3	84.0	71.3	66.8
80°	97.5	79.5	58.5	51.8	50.3
82.5°	67.5	51.8	39.0	36.8	36.0
85°	41.3	27.8	24.0	23.3	22.5
87.5°	17.3	12.0	11.3	11.3	10.5
90°	0.7	6.7	12.0	15.7	17.9
92.5°	14.2	7.5	12.0	15.7	16.4
95°	42.6	40.4	12.0	15.7	15.7
97.5°	80.0	84.4	13.5	14.9	15.7
100°	124.8	127.0	130.0	18.7	15.7
102.5°	170.4	173.4	174.9	176.4	113.6
105°	219.7	222.7	222.7	222.7	221.9
107.5°	270.5	270.5	272.0	272.7	269.8
110°	319.8	319.8	321.3	319.1	319.8

TEST NUMBER: P1036048

CATALOG NUMBER: S125RDIW-B610D770UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	366.2	368.4	369.1	366.2	364.7
115°	412.5	416.2	417.0	414.0	409.5
117.5°	461.1	461.1	464.0	459.6	458.1
120°	505.9	505.1	507.4	505.9	502.2
122.5°	545.5	549.2	550.0	548.5	544.0
125°	586.6	591.8	591.8	588.8	586.6
127.5°	626.2	629.9	629.2	627.7	621.7
130°	662.1	665.8	666.6	664.3	660.6
132.5°	697.9	702.4	700.2	700.2	696.4
135°	731.6	736.0	734.6	733.1	728.6
137.5°	762.9	767.4	765.9	765.9	762.2
140°	793.6	795.1	794.3	795.8	791.3
142.5°	821.2	822.0	823.5	823.5	819.0
145°	848.1	849.6	849.6	850.4	845.9
147.5°	872.0	872.0	872.8	873.5	868.3
150°	894.5	893.0	894.5	896.0	890.0
152.5°	916.1	912.4	913.9	915.4	910.2
155°	934.1	929.6	931.1	933.3	927.3
157.5°	948.3	946.0	946.0	948.3	942.3
160°	963.2	958.7	959.5	962.5	956.5
162.5°	975.2	970.7	971.4	975.9	969.2
165°	985.6	981.1	981.9	986.4	980.4
167.5°	993.8	989.4	990.1	995.3	988.6
170°	1000.6	995.3	996.1	1002.1	995.3
172.5°	1005.1	999.8	1001.3	1006.6	999.8
175°	1008.0	1003.6	1004.3	1010.3	1003.6
177.5°	1010.3	1005.8	1006.6	1011.8	1005.8
180°	1008.0	1008.0	1008.0	1008.0	1008.0

(END OF REPORT)