

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036102

Luminaire Tested: S125RDIW-B850D1340UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036102
REPORT IS A COMBINATION OF REPORTS P1006884 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B850D1340UB50-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8304.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036102

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1036102

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38		
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32		
2	87	80	74	69	79	73	67	63	59	56	52	47	44	42	35	34	32	27		
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23		
4	73	62	54	49	66	57	50	45	46	42	38	37	34	31	28	26	24	20		
5	67	55	47	42	60	51	44	39	42	36	33	33	30	27	25	23	21	18		
6	61	50	42	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15		
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	19	17	14		
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12		
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11		
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8515	8515	8515
5°	8516	8303	8316
10°	8433	8094	8023
15°	8314	7801	7636
20°	8166	7448	7231
25°	7996	7104	6796
30°	7789	6726	6340
35°	7577	6342	5855
40°	7376	5948	5381
45°	7134	5521	4885
50°	6889	5069	4380
55°	6604	4625	3857
60°	6312	4115	3315
65°	5966	3546	2730
70°	5560	2887	2148
75°	4999	2171	1566
80°	4217	1406	1057
85°	3156	755	595

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7134 cd/sqm

TEST NUMBER: P1036102

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.5
10°-20°	349.6	4.2
20°-30°	506.9	6.1
30°-40°	577.5	7.0
40°-50°	562.8	6.8
50°-60°	473.7	5.7
60°-70°	331.9	4.0
70°-80°	170.2	2.0
80°-90°	44.9	0.5
90°-100°	57.0	0.7
100°-110°	379.2	4.6
110°-120°	682.9	8.2
120°-130°	876.6	10.6
130°-140°	942.8	11.4
140°-150°	884.8	10.7
150°-160°	715.7	8.6
160°-170°	462.9	5.6
170°-180°	159.6	1.9
0°-30°	981.5	11.8
0°-40°	1559.0	18.8
0°-60°	2595.5	31.3
0°-90°	3142.5	37.8
90°-120°	1119.2	13.5
90°-150°	3823.3	46.0
90°-180°	5162.0	62.2
0°-180°	8304.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1327	1323	1312	1322	1320	126
15°	1262	1256	1235	1234	1225	356
25°	1144	1129	1092	1079	1068	527
35°	986	962	916	887	873	617
45°	807	778	723	683	668	622
55°	612	580	524	479	463	548
65°	415	380	327	287	272	411
75°	221	191	149	126	120	233
85°	55	37	32	31	30	60
90°	1	11	20	26	30	7
95°	71	67	20	26	26	87
105°	366	371	371	371	370	388
115°	688	694	695	690	683	682
125°	978	986	986	982	978	873
135°	1219	1227	1224	1222	1214	940
145°	1414	1416	1416	1418	1410	884
155°	1557	1550	1552	1556	1546	717
165°	1643	1636	1637	1644	1634	464
175°	1680	1673	1674	1684	1673	160
180°	1680	1680	1680	1680	1680	

TEST NUMBER: P1036102

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1329.0	1329.0	1329.0	1329.0	1329.0
2.5°	1332.0	1329.0	1319.0	1329.0	1328.0
5°	1327.0	1323.0	1312.0	1322.0	1320.0
7.5°	1317.0	1313.0	1299.9	1307.9	1305.9
10°	1301.9	1298.9	1284.9	1287.9	1284.9
12.5°	1284.9	1280.8	1260.8	1262.8	1257.8
15°	1261.8	1255.7	1234.7	1233.7	1224.6
17.5°	1237.7	1228.6	1203.5	1198.5	1191.5
20°	1208.6	1198.5	1166.4	1161.4	1152.4
22.5°	1176.4	1166.4	1132.3	1121.2	1114.2
25°	1144.3	1129.3	1092.1	1079.1	1068.0
27.5°	1108.2	1090.1	1051.0	1033.9	1022.9
30°	1068.0	1049.0	1006.8	983.7	974.7
32.5°	1028.9	1005.8	962.6	936.5	924.5
35°	985.7	961.6	916.5	887.4	873.3
37.5°	944.6	915.5	869.3	835.2	821.1
40°	900.4	870.3	822.1	784.0	771.9
42.5°	854.2	823.1	772.9	736.8	717.7
45°	807.0	777.9	722.7	682.6	667.5
47.5°	757.9	727.7	672.5	631.4	614.3
50°	711.7	678.6	621.3	579.2	564.1
52.5°	661.5	627.4	574.2	528.0	512.9
55°	612.3	580.2	524.0	478.8	462.7
57.5°	562.1	528.0	473.8	429.6	415.6
60°	513.9	478.8	424.6	380.4	365.4
62.5°	462.7	429.6	374.4	334.3	319.2
65°	414.6	380.4	327.2	287.1	272.0
67.5°	366.4	332.3	281.1	242.9	230.9
70°	317.2	283.1	232.9	201.8	189.7
72.5°	269.0	235.9	189.7	161.6	154.6
75°	220.8	190.7	148.6	126.5	119.5
77.5°	171.6	147.6	112.4	95.4	89.3
80°	130.5	106.4	78.3	69.3	67.3
82.5°	90.3	69.3	52.2	49.2	48.2
85°	55.2	37.1	32.1	31.1	30.1
87.5°	23.1	16.1	15.1	15.1	14.1
90°	1.2	11.2	19.9	26.2	29.9
92.5°	23.7	12.5	19.9	26.2	27.4
95°	71.0	67.3	19.9	26.2	26.2
97.5°	133.3	140.8	22.4	24.9	26.2
100°	208.0	211.7	216.7	31.1	26.2
102.5°	284.0	289.0	291.5	294.0	189.3
105°	366.2	371.2	371.2	371.2	369.9
107.5°	450.9	450.9	453.4	454.6	449.7
110°	533.1	533.1	535.6	531.9	533.1

TEST NUMBER: P1036102

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	610.3	614.1	615.3	610.3	607.8
115°	687.6	693.8	695.0	690.1	682.6
117.5°	768.5	768.5	773.5	766.0	763.5
120°	843.3	842.0	845.8	843.3	837.0
122.5°	909.3	915.5	916.8	914.3	906.8
125°	977.8	986.5	986.5	981.5	977.8
127.5°	1043.8	1050.0	1048.8	1046.3	1036.3
130°	1103.6	1109.8	1111.1	1107.3	1101.1
132.5°	1163.4	1170.8	1167.1	1167.1	1160.9
135°	1219.4	1226.9	1224.4	1221.9	1214.4
137.5°	1271.7	1279.2	1276.7	1276.7	1270.5
140°	1322.8	1325.3	1324.1	1326.5	1319.1
142.5°	1368.9	1370.1	1372.6	1372.6	1365.2
145°	1413.7	1416.2	1416.2	1417.5	1410.0
147.5°	1453.6	1453.6	1454.8	1456.1	1447.4
150°	1491.0	1488.5	1491.0	1493.5	1483.5
152.5°	1527.1	1520.9	1523.4	1525.8	1517.1
155°	1557.0	1549.5	1552.0	1555.7	1545.8
157.5°	1580.6	1576.9	1576.9	1580.6	1570.7
160°	1605.6	1598.1	1599.3	1604.3	1594.3
162.5°	1625.5	1618.0	1619.3	1626.7	1615.5
165°	1642.9	1635.5	1636.7	1644.2	1634.2
167.5°	1656.6	1649.2	1650.4	1659.1	1647.9
170°	1667.8	1659.1	1660.4	1670.3	1659.1
172.5°	1675.3	1666.6	1669.1	1677.8	1666.6
175°	1680.3	1672.8	1674.1	1684.0	1672.8
177.5°	1684.0	1676.6	1677.8	1686.5	1676.6
180°	1680.3	1680.3	1680.3	1680.3	1680.3

(END OF REPORT)