

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035538

Luminaire Tested: S125DIW-B850D1050UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035538
REPORT IS A COMBINATION OF REPORTS P1004076 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D1050UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7123.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035538

CATALOG NUMBER: S125DIW-B850D1050UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035538

CATALOG NUMBER: S125DIW-B850D1050UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	97	93	89	86	89	86	82	79	72	70	67	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	39
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	25
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8456	8456	8456
5°	8456	8259	8275
10°	8386	8070	8045
15°	8276	7843	7774
20°	8127	7581	7462
25°	7968	7295	7128
30°	7774	6996	6777
35°	7569	6683	6384
40°	7356	6353	6034
45°	7126	6030	5662
50°	6872	5665	5229
55°	6621	5262	4831
60°	6322	4837	4367
65°	5964	4345	3888
70°	5601	3780	3334
75°	4988	3112	2696
80°	4253	2325	1983
85°	3282	1376	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7126 cd/sqm

TEST NUMBER: P1035538

CATALOG NUMBER: S125DIW-B850D1050UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	1.7
10°-20°	351.8	4.9
20°-30°	519.3	7.3
30°-40°	605.9	8.5
40°-50°	608.5	8.5
50°-60°	534.2	7.5
60°-70°	397.9	5.6
70°-80°	227.2	3.2
80°-90°	67.7	0.9
90°-100°	87.8	1.2
100°-110°	260.9	3.7
110°-120°	442.5	6.2
120°-130°	582.5	8.2
130°-140°	652.7	9.2
140°-150°	639.8	9.0
150°-160°	537.4	7.5
160°-170°	357.2	5.0
170°-180°	125.0	1.8
0°-30°	995.6	14.0
0°-40°	1601.5	22.5
0°-60°	2744.3	38.5
0°-90°	3437.1	48.3
90°-120°	791.2	11.1
90°-150°	2666.2	37.4
90°-180°	3686.0	51.7
0°-180°	7123.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1320	1320	1320	1320	1320	
5°	1318	1316	1305	1314	1314	125
15°	1256	1253	1241	1247	1247	354
25°	1140	1135	1121	1124	1120	525
35°	985	980	966	961	952	616
45°	806	802	789	777	774	621
55°	614	611	596	587	580	548
65°	414	412	401	392	387	411
75°	220	218	213	210	206	235
85°	57	58	58	57	55	63
90°	1	9	16	22	25	8
95°	67	69	79	86	88	70
105°	234	240	246	252	255	250
115°	443	447	449	448	447	438
125°	646	653	654	652	651	579
135°	841	847	848	848	844	648
145°	1018	1023	1026	1026	1023	637
155°	1166	1166	1166	1171	1166	537
165°	1267	1265	1266	1270	1264	358
175°	1318	1314	1314	1320	1312	125
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1035538

CATALOG NUMBER: S125DIW-B850D1050UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.8	1319.8	1319.8	1319.8	1319.8
2.5°	1323.9	1320.8	1310.4	1320.8	1319.8
5°	1317.7	1315.6	1305.1	1314.5	1313.5
7.5°	1308.3	1306.2	1294.7	1304.1	1303.1
10°	1294.7	1292.6	1281.1	1289.5	1288.4
12.5°	1278.0	1273.8	1263.4	1269.6	1269.6
15°	1256.1	1252.9	1241.4	1246.7	1246.7
17.5°	1233.1	1227.9	1216.4	1222.7	1217.4
20°	1202.8	1200.7	1187.2	1194.5	1189.2
22.5°	1172.5	1168.4	1155.8	1160.0	1156.9
25°	1140.2	1134.9	1121.4	1123.5	1120.3
27.5°	1102.6	1099.4	1085.9	1086.9	1083.8
30°	1066.0	1062.9	1047.2	1045.2	1042.0
32.5°	1026.4	1021.1	1007.6	1003.4	997.1
35°	984.6	980.4	965.8	960.6	952.2
37.5°	941.8	936.6	923.0	915.7	910.5
40°	897.9	892.7	878.1	868.7	865.6
42.5°	851.0	846.8	832.2	823.8	818.6
45°	806.1	801.9	789.3	776.8	773.7
47.5°	757.0	758.0	742.4	729.8	722.5
50°	710.0	706.9	694.3	680.8	673.5
52.5°	662.0	659.9	646.3	634.8	626.5
55°	613.9	610.8	596.2	586.8	579.5
57.5°	562.8	561.7	549.2	536.7	533.5
60°	514.7	510.6	499.1	488.6	481.3
62.5°	464.6	461.5	452.1	440.6	435.4
65°	414.5	412.4	400.9	391.5	387.4
67.5°	365.4	361.3	352.9	344.6	342.5
70°	319.5	314.3	304.9	298.6	294.4
72.5°	269.4	266.2	261.0	253.7	249.5
75°	220.3	218.2	213.0	209.9	205.7
77.5°	174.4	173.3	170.2	168.1	165.0
80°	131.6	131.6	129.5	128.4	126.3
82.5°	94.0	91.9	91.9	89.8	89.8
85°	57.4	58.5	58.5	57.4	55.3
87.5°	28.2	28.2	27.1	27.1	25.1
90°	1.0	9.2	16.4	21.6	24.7
92.5°	30.8	36.0	45.2	52.4	54.5
95°	66.8	68.9	79.1	86.3	88.4
97.5°	102.8	103.8	118.2	124.4	125.4
100°	143.9	143.9	157.2	166.5	168.6
102.5°	188.1	193.2	198.4	208.6	211.7
105°	234.3	239.5	245.6	251.8	254.9
107.5°	284.7	289.8	295.0	298.1	298.1
110°	337.1	342.2	345.3	348.4	347.4



TEST NUMBER: P1035538

CATALOG NUMBER: S125DIW-B850D1050UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	390.6	392.6	396.7	397.7	395.7
115°	443.0	447.1	449.1	448.1	447.1
117.5°	496.4	497.4	499.5	500.5	496.4
120°	545.7	550.9	551.9	551.9	547.8
122.5°	599.2	600.2	603.3	602.3	599.2
125°	646.5	652.6	653.7	651.6	650.6
127.5°	698.9	702.0	703.0	702.0	699.9
130°	745.1	750.3	752.3	751.3	749.2
132.5°	791.4	800.6	799.6	798.6	795.5
135°	840.7	846.9	847.9	847.9	843.8
137.5°	887.0	893.1	895.2	896.2	891.1
140°	931.2	936.3	939.4	941.4	936.3
142.5°	975.4	979.5	983.6	984.6	979.5
145°	1018.5	1022.6	1025.7	1025.7	1022.6
147.5°	1058.6	1061.7	1063.7	1066.8	1058.6
150°	1098.7	1097.7	1101.8	1101.8	1099.7
152.5°	1131.6	1133.6	1134.7	1137.7	1133.6
155°	1165.5	1165.5	1166.5	1170.6	1165.5
157.5°	1196.3	1194.3	1195.3	1199.4	1192.2
160°	1223.1	1220.0	1221.0	1225.1	1220.0
162.5°	1246.7	1244.6	1244.6	1249.8	1243.6
165°	1267.2	1265.2	1266.2	1270.3	1264.2
167.5°	1285.7	1281.6	1281.6	1287.8	1281.6
170°	1300.1	1296.0	1296.0	1302.2	1295.0
172.5°	1310.4	1306.3	1306.3	1312.5	1306.3
175°	1317.6	1313.5	1313.5	1319.7	1312.5
177.5°	1322.7	1318.6	1317.6	1323.8	1316.6
180°	1320.7	1320.7	1320.7	1320.7	1320.7

(END OF REPORT)