

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036151

Luminaire Tested: S125RDIW-B850D770UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036151
REPORT IS A COMBINATION OF REPORTS P1006999 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B850D770UB30-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5976.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036151

CATALOG NUMBER: S125RDIW-B850D770UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1036151

CATALOG NUMBER: S125RDIW-B850D770UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32
5	70	58	50	44	64	54	47	42	47	41	37	41	36	33	34	31	28
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	22
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8857	8857	8857
5°	8858	8636	8650
10°	8772	8418	8344
15°	8647	8114	7943
20°	8494	7747	7521
25°	8317	7389	7069
30°	8102	6996	6594
35°	7882	6596	6089
40°	7672	6186	5597
45°	7420	5743	5081
50°	7165	5273	4556
55°	6869	4810	4012
60°	6566	4280	3448
65°	6205	3689	2839
70°	5783	3002	2234
75°	5201	2257	1628
80°	4385	1461	1099
85°	3282	785	618

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7420 cd/sqm

TEST NUMBER: P1036151

CATALOG NUMBER: S125RDIW-B850D770UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	2.2
10°-20°	363.6	6.1
20°-30°	527.2	8.8
30°-40°	600.6	10.1
40°-50°	585.4	9.8
50°-60°	492.7	8.2
60°-70°	345.2	5.8
70°-80°	177.0	3.0
80°-90°	45.7	0.8
90°-100°	64.5	1.1
100°-110°	191.7	3.2
110°-120°	325.1	5.4
120°-130°	428.0	7.2
130°-140°	479.7	8.0
140°-150°	470.1	7.9
150°-160°	394.9	6.6
160°-170°	262.5	4.4
170°-180°	91.9	1.5
0°-30°	1020.9	17.1
0°-40°	1621.5	27.1
0°-60°	2699.6	45.2
0°-90°	3267.5	54.7
90°-120°	581.4	9.7
90°-150°	1959.2	32.8
90°-180°	2708.0	45.3
0°-180°	5976.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1382	1382	1382	1382	1382	
5°	1380	1376	1365	1375	1373	131
15°	1312	1306	1284	1283	1274	370
25°	1190	1175	1136	1122	1111	548
35°	1025	1000	953	923	908	642
45°	839	809	752	710	694	647
55°	637	604	545	498	481	570
65°	431	396	340	299	283	427
75°	230	198	154	132	124	243
85°	57	39	33	32	31	63
90°	1	7	12	16	18	7
95°	49	51	58	63	65	51
105°	172	176	180	185	187	184
115°	326	328	330	329	328	322
125°	475	480	480	479	478	426
135°	618	622	623	623	620	476
145°	748	751	754	754	751	468
155°	856	856	857	860	856	394
165°	931	930	930	934	929	263
175°	968	965	965	970	964	92
180°	970	970	970	970	970	

TEST NUMBER: P1036151

CATALOG NUMBER: S125RDIW-B850D770UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1382.3	1382.3	1382.3	1382.3	1382.3
2.5°	1385.5	1382.3	1371.9	1382.3	1381.3
5°	1380.3	1376.1	1364.6	1375.0	1373.0
7.5°	1369.8	1365.6	1352.1	1360.4	1358.3
10°	1354.2	1351.0	1336.4	1339.5	1336.4
12.5°	1336.4	1332.2	1311.4	1313.4	1308.2
15°	1312.4	1306.1	1284.2	1283.2	1273.8
17.5°	1287.3	1277.9	1251.8	1246.6	1239.3
20°	1257.1	1246.6	1213.2	1208.0	1198.6
22.5°	1223.7	1213.2	1177.7	1166.2	1158.9
25°	1190.2	1174.6	1135.9	1122.4	1110.9
27.5°	1152.7	1133.9	1093.1	1075.4	1063.9
30°	1110.9	1091.1	1047.2	1023.2	1013.8
32.5°	1070.2	1046.2	1001.3	974.1	961.6
35°	1025.3	1000.2	953.2	923.0	908.3
37.5°	982.5	952.2	904.2	868.7	854.0
40°	936.5	905.2	855.1	815.4	802.9
42.5°	888.5	856.1	803.9	766.3	746.5
45°	839.4	809.2	751.7	710.0	694.3
47.5°	788.3	757.0	699.5	656.7	639.0
50°	740.2	705.8	646.3	602.4	586.8
52.5°	688.0	652.5	597.2	549.2	533.5
55°	636.9	603.5	545.0	498.0	481.3
57.5°	584.7	549.2	492.8	446.9	432.2
60°	534.6	498.0	441.6	395.7	380.0
62.5°	481.3	446.9	389.4	347.7	332.0
65°	431.2	395.7	340.4	298.6	282.9
67.5°	381.1	345.6	292.3	252.7	240.1
70°	329.9	294.4	242.2	209.9	197.3
72.5°	279.8	245.4	197.3	168.1	160.8
75°	229.7	198.4	154.5	131.6	124.2
77.5°	178.5	153.5	116.9	99.2	92.9
80°	135.7	110.7	81.4	72.0	70.0
82.5°	94.0	72.0	54.3	51.2	50.1
85°	57.4	38.6	33.4	32.4	31.3
87.5°	24.0	16.7	15.7	15.7	14.6
90°	0.8	6.8	12.1	15.9	18.1
92.5°	22.7	26.4	33.2	38.5	40.0
95°	49.1	50.6	58.2	63.4	64.9
97.5°	75.5	76.3	86.9	91.4	92.1
100°	105.7	105.7	115.5	122.3	123.9
102.5°	138.2	142.0	145.8	153.3	155.6
105°	172.2	176.0	180.5	185.0	187.3
107.5°	209.2	213.0	216.7	219.0	219.0
110°	247.7	251.5	253.8	256.0	255.3

TEST NUMBER: P1036151

CATALOG NUMBER: S125RDIW-B850D770UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.0	288.5	291.5	292.3	290.8
115°	325.5	328.5	330.0	329.3	328.5
117.5°	364.8	365.5	367.0	367.8	364.8
120°	401.0	404.8	405.6	405.6	402.5
122.5°	440.3	441.1	443.3	442.6	440.3
125°	475.0	479.6	480.3	478.8	478.1
127.5°	513.6	515.8	516.6	515.8	514.3
130°	547.5	551.3	552.8	552.1	550.6
132.5°	581.5	588.3	587.6	586.8	584.5
135°	617.8	622.3	623.1	623.1	620.0
137.5°	651.8	656.3	657.8	658.6	654.8
140°	684.2	688.0	690.3	691.8	688.0
142.5°	716.7	719.7	722.8	723.5	719.7
145°	748.4	751.4	753.7	753.7	751.4
147.5°	777.9	780.1	781.7	783.9	777.9
150°	807.3	806.6	809.6	809.6	808.1
152.5°	831.5	833.0	833.8	836.0	833.0
155°	856.4	856.4	857.2	860.2	856.4
157.5°	879.1	877.6	878.3	881.3	876.1
160°	898.7	896.5	897.2	900.2	896.5
162.5°	916.1	914.6	914.6	918.4	913.8
165°	931.2	929.7	930.4	933.5	928.9
167.5°	944.8	941.8	941.8	946.3	941.8
170°	955.4	952.3	952.3	956.9	951.6
172.5°	962.9	959.9	959.9	964.4	959.9
175°	968.2	965.2	965.2	969.7	964.4
177.5°	972.0	969.0	968.2	972.7	967.4
180°	970.5	970.5	970.5	970.5	970.5

(END OF REPORT)