

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036157

Luminaire Tested: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036157
REPORT IS A COMBINATION OF REPORTS P1007008 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B850D770UB40-4F0-XX-W2A-A1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5970.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52
2	91	84	78	73	84	78	73	68	67	63	60	57	55	52	48	46	45
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	38
4	76	66	58	52	71	61	54	49	53	48	44	46	42	39	39	36	33
5	70	59	51	45	65	55	48	42	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	49	42	37	43	38	33	37	33	30	32	29	26
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	29	26	23
8	56	43	36	30	52	41	34	29	36	30	26	31	27	23	27	23	21
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8102	8102	8102	8102
5°	8095	9131	8095	7018
10°	8049	10261	8022	6067
15°	7962	10856	7907	5282
20°	7856	11718	7787	4775
25°	7719	13264	7632	4333
30°	7579	14099	7465	4018
35°	7398	11595	7294	3723
40°	7075	7874	7016	3459
45°	6654	5660	6644	3199
50°	6220	4353	6250	2958
55°	5732	3539	5722	2726
60°	5279	2901	5253	2421
65°	4750	2418	4780	1948
70°	4312	1940	4295	1623
75°	3643	1469	3643	1333
80°	2954	896	2918	896
85°	2075	472	2018	533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 11532 cd/sqm

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	2.0
10°-20°	355.5	6.0
20°-30°	563.7	9.4
30°-40°	681.1	11.4
40°-50°	606.4	10.2
50°-60°	465.0	7.8
60°-70°	302.0	5.1
70°-80°	146.6	2.5
80°-90°	36.0	0.6
90°-100°	64.1	1.1
100°-110°	190.6	3.2
110°-120°	323.2	5.4
120°-130°	425.5	7.1
130°-140°	476.8	8.0
140°-150°	467.4	7.8
150°-160°	392.6	6.6
160°-170°	261.0	4.4
170°-180°	91.3	1.5
0°-30°	1040.4	17.4
0°-40°	1721.5	28.8
0°-60°	2793.0	46.8
0°-90°	3277.5	54.9
90°-120°	578.0	9.7
90°-150°	1947.6	32.6
90°-180°	2692.0	45.1
0°-180°	5970.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1264	1264	1264	1264	1264	
5°	1261	1449	1261	1114	1261	120
15°	1208	1741	1200	847	1208	341
25°	1105	2085	1092	681	1105	509
35°	962	1730	949	555	962	599
45°	753	773	752	437	753	581
55°	532	425	530	327	532	476
65°	330	241	332	194	330	330
75°	161	112	161	102	161	173
85°	36	24	35	27	36	41
90°	1	18	1	18	1	6
95°	49	65	49	65	49	51
105°	171	186	171	186	171	183
115°	324	327	324	327	324	320
125°	472	475	472	475	472	423
135°	614	616	614	616	614	473
145°	744	747	744	747	744	465
155°	851	851	851	851	851	392
165°	926	923	926	923	926	261
175°	962	959	962	959	962	91
180°	965	965	965	965	965	

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1265.5	1275.9	1279.0	1287.3	1296.7	1298.7	1303.9	1311.2	1315.3	1314.3	1314.3
5°	1261.4	1279.0	1291.5	1306.0	1323.7	1330.9	1337.1	1352.7	1365.2	1372.4	1384.9
7.5°	1254.1	1280.0	1300.8	1322.6	1349.6	1362.1	1375.6	1397.4	1420.2	1434.7	1448.2
10°	1242.7	1275.9	1305.0	1337.1	1373.5	1392.2	1408.8	1442.0	1470.0	1488.7	1519.9
12.5°	1226.1	1267.6	1308.1	1350.6	1396.3	1416.0	1438.9	1475.2	1514.7	1541.7	1567.6
15°	1208.4	1258.2	1301.9	1352.7	1407.7	1437.8	1466.9	1505.3	1540.6	1570.7	1600.8
17.5°	1187.7	1240.6	1294.6	1352.7	1415.0	1445.1	1470.0	1515.7	1553.1	1583.2	1610.2
20°	1162.7	1221.9	1283.2	1347.5	1410.9	1438.9	1462.8	1512.6	1545.8	1578.0	1616.4
22.5°	1135.7	1200.1	1265.5	1328.8	1391.1	1421.2	1449.3	1492.9	1529.2	1572.8	1622.6
25°	1104.6	1175.2	1241.6	1305.0	1364.1	1392.2	1417.1	1464.8	1515.7	1570.7	1626.8
27.5°	1073.5	1142.0	1206.3	1264.5	1328.8	1354.8	1379.7	1439.9	1500.1	1558.3	1635.1
30°	1039.2	1108.8	1164.8	1218.8	1281.1	1308.1	1339.2	1407.7	1476.3	1555.2	1648.6
32.5°	1000.8	1064.1	1116.0	1172.1	1228.1	1261.4	1300.8	1375.6	1454.5	1548.9	1668.3
35°	962.4	1013.2	1061.0	1113.9	1181.4	1216.7	1255.1	1334.0	1432.7	1545.8	1684.9
37.5°	913.6	962.4	999.7	1053.7	1123.3	1164.8	1203.2	1294.6	1406.7	1538.6	1683.9
40°	863.7	905.3	940.6	996.6	1072.4	1110.8	1152.4	1252.0	1379.7	1517.8	1659.0
42.5°	809.8	845.1	883.5	937.5	1011.2	1048.5	1096.3	1212.6	1342.3	1488.7	1594.6
45°	752.7	786.9	819.1	875.2	948.9	989.4	1041.3	1160.7	1296.7	1427.5	1490.8
47.5°	696.6	726.7	761.0	809.8	884.5	929.2	982.1	1109.8	1235.4	1345.5	1350.6
50°	642.6	666.5	695.6	745.4	823.3	865.8	920.8	1040.2	1162.7	1238.5	1187.7
52.5°	586.6	608.4	638.5	682.1	754.7	804.6	852.3	971.7	1074.5	1125.4	1031.9
55°	531.5	550.2	581.4	630.2	693.5	731.9	780.7	891.8	982.1	983.1	881.4
57.5°	477.6	494.2	520.1	563.7	622.9	667.5	712.2	808.7	870.0	852.3	739.2
60°	429.8	440.2	464.1	506.6	561.6	593.8	641.6	722.6	763.0	730.9	609.4
62.5°	380.0	390.3	409.0	443.3	495.2	529.5	559.6	626.0	654.0	605.2	505.6
65°	330.1	342.6	356.1	383.1	431.9	454.7	481.7	530.5	557.5	500.4	414.2
67.5°	286.5	292.8	306.3	334.3	368.5	389.3	408.0	441.2	446.4	400.7	330.1
70°	246.0	248.1	260.6	277.2	303.1	315.6	331.2	350.9	350.9	313.5	257.5
72.5°	200.4	203.5	212.8	230.5	246.0	252.3	257.5	269.9	267.8	233.6	195.2
75°	160.9	163.0	170.3	178.6	184.8	196.2	200.4	198.3	197.3	168.2	146.4
77.5°	124.6	125.6	130.8	138.1	139.1	143.3	140.2	140.2	130.8	114.2	102.8
80°	91.4	92.4	94.5	96.5	96.5	96.5	96.5	91.4	85.1	74.7	71.6
82.5°	61.3	61.3	62.3	64.4	63.3	61.3	59.2	54.0	49.8	46.7	44.6
85°	36.3	36.3	37.4	36.3	32.2	31.1	29.1	28.0	27.0	26.0	26.0
87.5°	17.6	16.6	14.5	12.5	12.5	12.5	12.5	12.5	12.5	11.4	11.4
90°	0.8	2.1	3.5	4.8	6.1	6.8	7.4	8.5	9.7	10.8	12.0
92.5°	22.5	23.3	24.2	25.0	25.9	26.3	27.0	28.5	30.0	31.5	33.0
95°	48.8	49.1	49.5	49.8	50.1	50.3	51.1	52.8	54.5	56.1	57.8
97.5°	75.1	75.3	75.4	75.6	75.7	75.8	77.0	79.3	81.6	84.0	86.3
100°	105.1	105.1	105.1	105.1	105.1	105.1	106.2	108.4	110.5	112.7	114.9
102.5°	137.4	138.2	139.0	139.9	140.7	141.1	141.5	142.4	143.2	144.1	144.9
105°	171.2	172.0	172.8	173.7	174.5	174.9	175.4	176.4	177.4	178.4	179.4
107.5°	208.0	208.8	209.6	210.5	211.3	211.7	212.1	213.0	213.8	214.7	215.5
110°	246.3	247.1	247.9	248.8	249.6	250.0	250.3	250.8	251.3	251.8	252.3

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	285.3	285.6	286.0	286.3	286.6	286.8	287.1	287.8	288.5	289.1	289.8
115°	323.6	324.3	324.9	325.6	326.3	326.6	326.8	327.1	327.4	327.8	328.1
117.5°	362.6	362.8	363.0	363.1	363.3	363.4	363.6	363.9	364.2	364.6	364.9
120°	398.7	399.5	400.3	401.2	402.0	402.4	402.5	402.7	402.8	403.0	403.2
122.5°	437.7	437.9	438.0	438.2	438.3	438.4	438.7	439.2	439.7	440.2	440.7
125°	472.2	473.2	474.2	475.2	476.2	476.7	476.8	477.0	477.1	477.3	477.5
127.5°	510.5	511.0	511.5	512.0	512.5	512.8	512.9	513.0	513.2	513.3	513.5
130°	544.3	545.1	546.0	546.8	547.7	548.1	548.3	548.6	548.9	549.3	549.6
132.5°	578.1	579.6	581.1	582.6	584.1	584.8	584.7	584.6	584.4	584.3	584.1
135°	614.1	615.1	616.1	617.1	618.1	618.6	618.7	618.9	619.0	619.2	619.4
137.5°	647.9	648.9	649.9	650.9	651.9	652.4	652.6	652.9	653.2	653.6	653.9
140°	680.2	681.0	681.8	682.7	683.5	683.9	684.2	684.7	685.2	685.7	686.2
142.5°	712.5	713.2	713.8	714.5	715.2	715.5	715.8	716.5	717.2	717.8	718.5
145°	744.0	744.7	745.3	746.0	746.7	747.0	747.3	747.8	748.3	748.8	749.3
147.5°	773.3	773.8	774.3	774.8	775.3	775.5	775.7	776.0	776.3	776.7	777.0
150°	802.6	802.4	802.2	802.1	801.9	801.8	802.1	802.8	803.5	804.1	804.8
152.5°	826.6	826.9	827.3	827.6	827.9	828.1	828.2	828.3	828.5	828.6	828.8
155°	851.4	851.4	851.4	851.4	851.4	851.4	851.5	851.6	851.8	851.9	852.1
157.5°	873.9	873.6	873.2	872.9	872.6	872.4	872.5	872.6	872.8	872.9	873.1
160°	893.4	892.9	892.4	891.9	891.4	891.2	891.3	891.4	891.6	891.7	891.9
162.5°	910.7	910.4	910.0	909.7	909.4	909.2	909.2	909.2	909.2	909.2	909.2
165°	925.7	925.4	925.0	924.7	924.4	924.2	924.3	924.4	924.6	924.7	924.9
167.5°	939.2	938.5	937.9	937.2	936.5	936.2	936.2	936.2	936.2	936.2	936.2
170°	949.7	949.0	948.4	947.7	947.0	946.7	946.7	946.7	946.7	946.7	946.7
172.5°	957.2	956.5	955.9	955.2	954.5	954.2	954.2	954.2	954.2	954.2	954.2
175°	962.5	961.8	961.2	960.5	959.8	959.5	959.5	959.5	959.5	959.5	959.5
177.5°	966.2	965.5	964.9	964.2	963.5	963.2	963.1	963.0	962.8	962.7	962.5
180°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1319.5	1326.8	1333.0	1329.9	1342.3	1341.3	1343.4	1347.5	1348.6	1346.5	1342.3
5°	1391.1	1401.5	1419.2	1428.5	1426.4	1434.7	1438.9	1445.1	1451.3	1449.3	1449.3
7.5°	1471.1	1485.6	1503.3	1527.1	1530.2	1537.5	1550.0	1550.0	1557.2	1554.1	1553.1
10°	1540.6	1558.3	1586.3	1605.0	1613.3	1617.5	1629.9	1634.1	1642.4	1643.4	1643.4
12.5°	1597.7	1628.9	1647.6	1666.2	1670.4	1676.6	1686.0	1692.2	1695.3	1695.3	1692.2
15°	1627.8	1652.7	1674.5	1694.3	1705.7	1710.9	1720.2	1727.5	1731.6	1741.0	1743.1
17.5°	1640.3	1670.4	1705.7	1733.7	1753.4	1758.6	1777.3	1783.6	1791.9	1796.0	1801.2
20°	1657.9	1701.5	1744.1	1778.4	1797.1	1810.5	1830.3	1859.3	1867.6	1867.6	1864.5
22.5°	1673.5	1729.6	1787.7	1842.7	1858.3	1885.3	1921.6	1952.8	1965.2	1970.4	1966.3
25°	1692.2	1769.0	1844.8	1913.3	1955.9	1975.6	2024.4	2061.8	2076.3	2084.6	2086.7
27.5°	1724.4	1820.9	1917.5	2004.7	2048.3	2071.1	2122.0	2154.2	2171.8	2179.1	2173.9
30°	1760.7	1879.1	1991.2	2069.1	2098.1	2126.1	2159.4	2171.8	2167.7	2167.7	2183.2
32.5°	1798.1	1920.6	2020.3	2071.1	2081.5	2077.4	2063.9	2026.5	2004.7	2004.7	2018.2
35°	1818.9	1924.7	1975.6	1959.0	1918.5	1894.6	1820.9	1779.4	1732.7	1729.6	1745.1
37.5°	1807.4	1853.1	1832.3	1723.3	1668.3	1622.6	1507.4	1461.7	1427.5	1379.7	1453.4
40°	1727.5	1711.9	1604.0	1447.2	1385.9	1321.6	1230.2	1184.5	1136.8	1129.5	1147.2
42.5°	1592.5	1500.1	1342.3	1190.8	1128.5	1082.8	1013.2	968.6	938.5	926.0	946.8
45°	1424.4	1279.0	1121.2	1000.8	932.3	908.4	845.1	805.6	782.8	773.4	788.0
47.5°	1218.8	1072.4	922.9	821.2	780.7	756.8	714.3	680.0	660.3	654.0	660.3
50°	1035.0	884.5	758.9	693.5	657.2	637.4	602.1	580.3	564.8	560.6	571.0
52.5°	876.2	739.2	643.7	585.5	561.6	545.0	520.1	501.4	492.1	487.9	495.2
55°	734.0	622.9	546.1	496.2	478.6	468.2	446.4	436.0	425.6	424.6	431.9
57.5°	608.4	531.5	460.9	425.6	420.5	404.9	386.2	376.9	371.7	370.6	373.7
60°	506.6	438.1	395.5	364.4	357.1	344.7	334.3	328.1	321.8	319.8	321.8
62.5°	421.5	367.5	333.2	312.5	302.1	299.0	287.6	280.3	279.3	279.3	281.3
65°	347.8	302.1	280.3	263.7	256.4	253.3	245.0	239.8	240.9	240.9	241.9
67.5°	283.4	250.2	230.5	222.2	215.9	214.9	206.6	204.5	202.4	202.4	204.5
70°	225.3	204.5	190.0	185.8	184.8	177.5	174.4	173.4	170.3	171.3	171.3
72.5°	176.5	163.0	154.7	148.5	149.5	145.3	141.2	141.2	139.1	142.2	142.2
75°	130.8	124.6	118.4	116.3	118.4	116.3	113.2	112.1	113.2	112.1	112.1
77.5°	96.5	93.4	91.4	90.3	90.3	86.2	84.1	86.2	82.0	84.1	84.1
80°	67.5	63.3	62.3	60.2	61.3	58.1	59.2	57.1	57.1	57.1	57.1
82.5°	42.6	41.5	41.5	41.5	40.5	40.5	40.5	40.5	40.5	40.5	39.5
85°	26.0	24.9	24.9	24.9	23.9	23.9	23.9	23.9	23.9	23.9	23.9
87.5°	10.4	11.4	11.4	12.5	11.4	10.4	10.4	10.4	11.4	11.4	10.4
90°	12.8	13.7	14.5	15.4	15.8	16.0	16.5	17.0	17.5	18.0	17.5
92.5°	34.2	35.4	36.5	37.7	38.3	38.5	38.8	39.1	39.5	39.8	39.5
95°	59.0	60.2	61.3	62.5	63.1	63.3	63.6	63.9	64.3	64.6	64.3
97.5°	87.3	88.3	89.3	90.3	90.8	90.9	91.1	91.2	91.4	91.6	91.4
100°	116.4	117.9	119.4	120.9	121.6	121.8	122.1	122.4	122.8	123.1	122.8
102.5°	146.6	148.2	149.9	151.6	152.4	152.7	153.2	153.7	154.2	154.7	154.2
105°	180.4	181.4	182.4	183.4	183.9	184.2	184.7	185.2	185.7	186.2	185.7
107.5°	216.0	216.5	217.0	217.5	217.7	217.7	217.7	217.7	217.7	217.7	217.7
110°	252.8	253.3	253.8	254.3	254.5	254.4	254.3	254.1	254.0	253.8	254.0

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	290.0	290.1	290.3	290.4	290.5	290.3	290.0	289.7	289.3	289.0	289.3
115°	327.9	327.7	327.6	327.4	327.3	327.2	327.1	326.9	326.8	326.6	326.8
117.5°	365.1	365.2	365.4	365.5	365.6	365.3	364.6	363.9	363.3	362.6	363.3
120°	403.2	403.2	403.2	403.2	403.2	402.9	402.2	401.5	400.9	400.2	400.9
122.5°	440.5	440.3	440.2	440.0	439.9	439.7	439.2	438.7	438.2	437.7	438.2
125°	477.2	476.8	476.5	476.2	476.0	475.9	475.7	475.6	475.4	475.2	475.4
127.5°	513.3	513.2	513.0	512.9	512.8	512.6	512.3	512.0	511.6	511.3	511.6
130°	549.4	549.2	549.1	548.9	548.8	548.6	548.3	548.0	547.6	547.3	547.6
132.5°	583.9	583.7	583.6	583.4	583.3	583.1	582.6	582.1	581.6	581.1	581.6
135°	619.4	619.4	619.4	619.4	619.4	619.1	618.4	617.7	617.1	616.4	617.1
137.5°	654.1	654.3	654.4	654.6	654.7	654.3	653.4	652.6	651.7	650.9	651.7
140°	686.5	686.9	687.2	687.5	687.7	687.3	686.4	685.6	684.7	683.9	684.7
142.5°	718.7	718.8	719.0	719.1	719.2	718.8	718.0	717.1	716.3	715.5	716.3
145°	749.3	749.3	749.3	749.3	749.3	749.0	748.5	748.0	747.5	747.0	747.5
147.5°	777.5	778.0	778.5	779.0	779.3	778.6	777.3	776.0	774.6	773.3	774.6
150°	804.8	804.8	804.8	804.8	804.8	804.6	804.3	804.0	803.6	803.3	803.6
152.5°	829.3	829.8	830.3	830.8	831.1	830.8	830.1	829.4	828.8	828.1	828.8
155°	852.8	853.4	854.1	854.8	855.1	854.7	853.9	853.0	852.2	851.4	852.2
157.5°	873.8	874.4	875.1	875.8	876.1	875.5	874.4	873.2	872.1	870.9	872.1
160°	892.6	893.2	893.9	894.6	894.9	894.5	893.7	892.8	892.0	891.2	892.0
162.5°	910.0	910.8	911.7	912.5	912.9	912.4	911.4	910.4	909.4	908.4	909.4
165°	925.6	926.2	926.9	927.6	927.9	927.4	926.4	925.4	924.4	923.4	924.4
167.5°	937.2	938.2	939.2	940.2	940.7	940.2	939.2	938.2	937.2	936.2	937.2
170°	947.7	948.7	949.7	950.7	951.2	950.6	949.5	948.3	947.2	946.0	947.2
172.5°	955.2	956.2	957.2	958.2	958.7	958.2	957.2	956.2	955.2	954.2	955.2
175°	960.5	961.5	962.5	963.5	964.0	963.4	962.2	961.1	959.9	958.7	959.9
177.5°	963.5	964.5	965.5	966.5	967.0	966.4	965.2	964.1	962.9	961.7	962.9
180°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1347.5	1340.3	1343.4	1340.3	1337.1	1334.0	1326.8	1316.4	1308.1	1301.9	1300.8
5°	1451.3	1442.0	1435.8	1432.7	1426.4	1418.1	1404.6	1389.1	1370.4	1363.1	1348.6
7.5°	1546.9	1543.7	1529.2	1527.1	1523.0	1507.4	1484.6	1463.8	1439.9	1420.2	1401.5
10°	1637.2	1629.9	1619.5	1605.0	1602.9	1583.2	1561.4	1532.3	1501.2	1482.5	1449.3
12.5°	1693.2	1684.9	1673.5	1664.2	1659.0	1646.5	1616.4	1587.3	1559.3	1525.1	1496.0
15°	1733.7	1723.3	1702.6	1695.3	1689.1	1672.5	1650.7	1620.6	1583.2	1559.3	1517.8
17.5°	1788.7	1776.3	1755.5	1742.0	1730.6	1704.7	1673.5	1633.0	1597.7	1570.7	1533.4
20°	1852.1	1833.4	1806.4	1788.7	1772.1	1742.0	1698.4	1650.7	1599.8	1566.6	1528.2
22.5°	1956.9	1921.6	1879.1	1854.2	1831.3	1779.4	1727.5	1668.3	1611.2	1561.4	1514.7
25°	2058.7	2023.4	1970.4	1936.2	1900.9	1840.7	1772.1	1690.1	1617.5	1559.3	1498.1
27.5°	2153.1	2116.8	2068.0	2026.5	1992.2	1901.9	1811.6	1719.2	1626.8	1546.9	1484.6
30°	2174.9	2159.4	2122.0	2085.7	2054.5	1971.5	1866.6	1749.3	1638.2	1535.4	1465.9
32.5°	2043.1	2081.5	2090.9	2085.7	2065.9	2006.8	1910.2	1786.7	1654.8	1530.2	1434.7
35°	1769.0	1838.6	1910.2	1948.6	1967.3	1975.6	1918.5	1805.4	1666.2	1521.9	1414.0
37.5°	1466.9	1534.4	1647.6	1704.7	1768.0	1851.0	1873.9	1801.2	1661.1	1515.7	1380.8
40°	1205.3	1291.5	1384.9	1436.8	1491.8	1641.3	1754.5	1746.2	1644.4	1492.9	1354.8
42.5°	981.1	1035.0	1117.1	1174.2	1241.6	1408.8	1560.4	1635.1	1594.6	1464.8	1321.6
45°	818.1	859.6	917.7	975.9	1017.4	1169.0	1348.6	1471.1	1509.5	1415.0	1270.7
47.5°	689.3	720.5	771.4	807.7	852.3	971.7	1127.4	1299.8	1380.8	1344.4	1216.7
50°	590.7	615.6	656.1	679.0	718.4	821.2	939.5	1120.2	1242.7	1246.8	1145.1
52.5°	504.5	529.5	563.7	583.4	607.3	676.9	796.3	948.9	1090.1	1142.0	1063.1
55°	439.1	453.7	481.7	497.3	519.1	586.6	662.3	792.1	939.5	1024.7	974.8
57.5°	378.9	394.5	412.1	424.6	440.2	494.2	562.7	660.3	806.6	899.0	882.4
60°	330.1	339.5	356.1	365.4	380.0	415.3	463.0	560.6	676.9	764.1	773.4
62.5°	284.5	292.8	304.2	312.5	321.8	349.9	385.2	454.7	556.5	650.9	663.4
65°	245.0	252.3	258.5	265.8	273.0	290.7	320.8	374.8	453.7	541.9	568.9
67.5°	209.7	211.8	221.1	222.2	226.3	239.8	261.6	305.2	362.3	432.9	468.2
70°	175.4	179.6	181.7	184.8	188.9	198.3	215.9	238.8	281.3	338.4	371.7
72.5°	142.2	143.3	146.4	148.5	152.6	159.9	168.2	185.8	212.8	254.3	284.5
75°	113.2	114.2	116.3	117.3	120.4	122.5	126.7	139.1	157.8	182.7	204.5
77.5°	85.1	87.2	89.3	89.3	90.3	92.4	94.5	98.6	108.0	124.6	143.3
80°	58.1	59.2	59.2	60.2	59.2	62.3	65.4	70.6	74.7	79.9	89.3
82.5°	40.5	40.5	40.5	41.5	41.5	42.6	42.6	43.6	44.6	47.8	51.9
85°	24.9	24.9	26.0	23.9	24.9	26.0	26.0	24.9	26.0	27.0	28.0
87.5°	10.4	10.4	11.4	11.4	11.4	11.4	10.4	11.4	10.4	11.4	11.4
90°	17.0	16.5	16.0	15.8	15.4	14.5	13.7	12.8	12.0	10.8	9.7
92.5°	39.1	38.8	38.5	38.3	37.7	36.5	35.4	34.2	33.0	31.5	30.0
95°	63.9	63.6	63.3	63.1	62.5	61.3	60.2	59.0	57.8	56.1	54.5
97.5°	91.2	91.1	90.9	90.8	90.3	89.3	88.3	87.3	86.3	84.0	81.6
100°	122.4	122.1	121.8	121.6	120.9	119.4	117.9	116.4	114.9	112.7	110.5
102.5°	153.7	153.2	152.7	152.4	151.6	149.9	148.2	146.6	144.9	144.1	143.2
105°	185.2	184.7	184.2	183.9	183.4	182.4	181.4	180.4	179.4	178.4	177.4
107.5°	217.7	217.7	217.7	217.7	217.5	217.0	216.5	216.0	215.5	214.7	213.8
110°	254.1	254.3	254.4	254.5	254.3	253.8	253.3	252.8	252.3	251.8	251.3

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	289.7	290.0	290.3	290.5	290.4	290.3	290.1	290.0	289.8	289.1	288.5
115°	326.9	327.1	327.2	327.3	327.4	327.6	327.7	327.9	328.1	327.8	327.4
117.5°	363.9	364.6	365.3	365.6	365.5	365.4	365.2	365.1	364.9	364.6	364.2
120°	401.5	402.2	402.9	403.2	403.2	403.2	403.2	403.2	403.2	403.0	402.8
122.5°	438.7	439.2	439.7	439.9	440.0	440.2	440.3	440.5	440.7	440.2	439.7
125°	475.6	475.7	475.9	476.0	476.2	476.5	476.8	477.2	477.5	477.3	477.1
127.5°	512.0	512.3	512.6	512.8	512.9	513.0	513.2	513.3	513.5	513.3	513.2
130°	548.0	548.3	548.6	548.8	548.9	549.1	549.2	549.4	549.6	549.3	548.9
132.5°	582.1	582.6	583.1	583.3	583.4	583.6	583.7	583.9	584.1	584.3	584.4
135°	617.7	618.4	619.1	619.4	619.4	619.4	619.4	619.4	619.4	619.2	619.0
137.5°	652.6	653.4	654.3	654.7	654.6	654.4	654.3	654.1	653.9	653.6	653.2
140°	685.6	686.4	687.3	687.7	687.5	687.2	686.9	686.5	686.2	685.7	685.2
142.5°	717.1	718.0	718.8	719.2	719.1	719.0	718.8	718.7	718.5	717.8	717.2
145°	748.0	748.5	749.0	749.3	749.3	749.3	749.3	749.3	749.3	748.8	748.3
147.5°	776.0	777.3	778.6	779.3	779.0	778.5	778.0	777.5	777.0	776.7	776.3
150°	804.0	804.3	804.6	804.8	804.8	804.8	804.8	804.8	804.8	804.1	803.5
152.5°	829.4	830.1	830.8	831.1	830.8	830.3	829.8	829.3	828.8	828.6	828.5
155°	853.0	853.9	854.7	855.1	854.8	854.1	853.4	852.8	852.1	851.9	851.8
157.5°	873.2	874.4	875.5	876.1	875.8	875.1	874.4	873.8	873.1	872.9	872.8
160°	892.8	893.7	894.5	894.9	894.6	893.9	893.2	892.6	891.9	891.7	891.6
162.5°	910.4	911.4	912.4	912.9	912.5	911.7	910.8	910.0	909.2	909.2	909.2
165°	925.4	926.4	927.4	927.9	927.6	926.9	926.2	925.6	924.9	924.7	924.6
167.5°	938.2	939.2	940.2	940.7	940.2	939.2	938.2	937.2	936.2	936.2	936.2
170°	948.3	949.5	950.6	951.2	950.7	949.7	948.7	947.7	946.7	946.7	946.7
172.5°	956.2	957.2	958.2	958.7	958.2	957.2	956.2	955.2	954.2	954.2	954.2
175°	961.1	962.2	963.4	964.0	963.5	962.5	961.5	960.5	959.5	959.5	959.5
177.5°	964.1	965.2	966.4	967.0	966.5	965.5	964.5	963.5	962.5	962.7	962.8
180°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1297.7	1291.5	1287.3	1286.3	1280.0	1274.9	1268.6	1267.6	1264.5	1256.2	1251.0
5°	1338.2	1323.7	1320.5	1311.2	1295.6	1284.2	1269.7	1261.4	1252.0	1236.4	1224.0
7.5°	1379.7	1360.0	1345.5	1332.0	1310.2	1289.4	1268.6	1252.0	1235.4	1212.6	1193.9
10°	1420.2	1390.1	1372.4	1352.7	1322.6	1291.5	1262.4	1238.5	1211.5	1184.5	1157.5
12.5°	1457.6	1419.2	1393.2	1365.2	1327.8	1289.4	1252.0	1218.8	1190.8	1154.4	1124.3
15°	1480.4	1437.8	1411.9	1384.9	1328.8	1286.3	1242.7	1200.1	1162.7	1124.3	1096.3
17.5°	1493.9	1446.2	1417.1	1392.2	1335.1	1276.9	1220.9	1175.2	1134.7	1089.0	1051.7
20°	1487.7	1441.0	1414.0	1390.1	1323.7	1265.5	1205.3	1152.4	1101.5	1054.8	1015.3
22.5°	1474.2	1425.4	1395.3	1373.5	1314.3	1245.8	1179.3	1122.2	1069.3	1022.6	977.9
25°	1445.1	1397.4	1371.4	1344.4	1286.3	1220.9	1153.4	1092.1	1036.1	986.3	936.4
27.5°	1419.2	1361.0	1334.0	1310.2	1248.9	1190.8	1124.3	1056.8	999.7	947.8	898.0
30°	1389.1	1323.7	1294.6	1262.4	1207.4	1152.4	1085.9	1023.6	964.4	909.4	861.7
32.5°	1356.9	1281.1	1247.9	1211.5	1155.5	1103.6	1047.5	986.3	927.1	873.1	823.3
35°	1315.3	1234.4	1196.0	1161.7	1103.6	1051.7	999.7	948.9	889.7	832.6	784.8
37.5°	1275.9	1186.6	1146.1	1106.7	1045.4	995.6	953.0	905.3	848.2	793.2	747.5
40°	1231.3	1128.5	1087.0	1050.6	987.3	932.3	893.9	856.5	806.6	753.7	703.9
42.5°	1190.8	1074.5	1030.9	993.5	927.1	875.2	838.8	807.7	764.1	715.3	664.4
45°	1134.7	1016.4	971.7	932.3	864.8	816.0	778.6	751.6	717.4	671.7	626.0
47.5°	1082.8	960.3	911.5	863.7	802.5	752.7	718.4	697.6	674.8	634.3	587.6
50°	1019.5	895.9	846.1	806.6	737.1	694.5	660.3	645.7	625.0	586.6	549.2
52.5°	951.0	833.6	786.9	739.2	674.8	633.3	603.2	586.6	569.9	541.9	506.6
55°	871.0	764.1	720.5	677.9	613.6	575.1	548.1	530.5	521.2	495.2	469.2
57.5°	794.2	693.5	653.0	613.6	557.5	513.9	496.2	480.7	467.2	448.5	426.7
60°	716.3	625.0	581.4	546.1	497.3	457.8	443.3	427.7	417.3	402.8	387.2
62.5°	627.0	549.2	516.0	482.7	441.2	410.1	393.5	381.0	367.5	358.2	344.7
65°	532.6	477.6	445.4	420.5	381.0	353.0	340.5	332.2	320.8	311.4	301.1
67.5°	444.3	400.7	387.2	360.2	330.1	305.2	295.9	285.5	276.2	271.0	261.6
70°	359.2	328.1	314.6	307.3	274.1	257.5	249.2	245.0	233.6	228.4	222.2
72.5°	278.2	266.8	257.5	248.1	226.3	215.9	206.6	202.4	194.1	190.0	187.9
75°	205.6	198.3	193.1	192.1	182.7	172.3	163.0	160.9	154.7	150.5	148.5
77.5°	144.3	142.2	141.2	142.2	136.0	129.8	127.7	125.6	118.4	117.3	117.3
80°	94.5	99.7	99.7	98.6	96.5	95.5	92.4	90.3	86.2	85.1	86.2
82.5°	58.1	61.3	62.3	64.4	63.3	62.3	60.2	59.2	60.2	58.1	59.2
85°	29.1	31.1	35.3	35.3	36.3	36.3	36.3	35.3	33.2	34.3	33.2
87.5°	11.4	12.5	12.5	12.5	11.4	14.5	15.6	15.6	15.6	13.5	13.5
90°	8.5	7.4	6.8	6.1	4.8	3.5	2.1	0.8	2.1	3.5	4.8
92.5°	28.5	27.0	26.3	25.9	25.0	24.2	23.3	22.5	23.3	24.2	25.0
95°	52.8	51.1	50.3	50.1	49.8	49.5	49.1	48.8	49.1	49.5	49.8
97.5°	79.3	77.0	75.8	75.7	75.6	75.4	75.3	75.1	75.3	75.4	75.6
100°	108.4	106.2	105.1	105.1	105.1	105.1	105.1	105.1	105.1	105.1	105.1
102.5°	142.4	141.5	141.1	140.7	139.9	139.0	138.2	137.4	138.2	139.0	139.9
105°	176.4	175.4	174.9	174.5	173.7	172.8	172.0	171.2	172.0	172.8	173.7
107.5°	213.0	212.1	211.7	211.3	210.5	209.6	208.8	208.0	208.8	209.6	210.5
110°	250.8	250.3	250.0	249.6	248.8	247.9	247.1	246.3	247.1	247.9	248.8

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	287.8	287.1	286.8	286.6	286.3	286.0	285.6	285.3	285.6	286.0	286.3
115°	327.1	326.8	326.6	326.3	325.6	324.9	324.3	323.6	324.3	324.9	325.6
117.5°	363.9	363.6	363.4	363.3	363.1	363.0	362.8	362.6	362.8	363.0	363.1
120°	402.7	402.5	402.4	402.0	401.2	400.3	399.5	398.7	399.5	400.3	401.2
122.5°	439.2	438.7	438.4	438.3	438.2	438.0	437.9	437.7	437.9	438.0	438.2
125°	477.0	476.8	476.7	476.2	475.2	474.2	473.2	472.2	473.2	474.2	475.2
127.5°	513.0	512.9	512.8	512.5	512.0	511.5	511.0	510.5	511.0	511.5	512.0
130°	548.6	548.3	548.1	547.7	546.8	546.0	545.1	544.3	545.1	546.0	546.8
132.5°	584.6	584.7	584.8	584.1	582.6	581.1	579.6	578.1	579.6	581.1	582.6
135°	618.9	618.7	618.6	618.1	617.1	616.1	615.1	614.1	615.1	616.1	617.1
137.5°	652.9	652.6	652.4	651.9	650.9	649.9	648.9	647.9	648.9	649.9	650.9
140°	684.7	684.2	683.9	683.5	682.7	681.8	681.0	680.2	681.0	681.8	682.7
142.5°	716.5	715.8	715.5	715.2	714.5	713.8	713.2	712.5	713.2	713.8	714.5
145°	747.8	747.3	747.0	746.7	746.0	745.3	744.7	744.0	744.7	745.3	746.0
147.5°	776.0	775.7	775.5	775.3	774.8	774.3	773.8	773.3	773.8	774.3	774.8
150°	802.8	802.1	801.8	801.9	802.1	802.2	802.4	802.6	802.4	802.2	802.1
152.5°	828.3	828.2	828.1	827.9	827.6	827.3	826.9	826.6	826.9	827.3	827.6
155°	851.6	851.5	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
157.5°	872.6	872.5	872.4	872.6	872.9	873.2	873.6	873.9	873.6	873.2	872.9
160°	891.4	891.3	891.2	891.4	891.9	892.4	892.9	893.4	892.9	892.4	891.9
162.5°	909.2	909.2	909.2	909.4	909.7	910.0	910.4	910.7	910.4	910.0	909.7
165°	924.4	924.3	924.2	924.4	924.7	925.0	925.4	925.7	925.4	925.0	924.7
167.5°	936.2	936.2	936.2	936.5	937.2	937.9	938.5	939.2	938.5	937.9	937.2
170°	946.7	946.7	946.7	947.0	947.7	948.4	949.0	949.7	949.0	948.4	947.7
172.5°	954.2	954.2	954.2	954.5	955.2	955.9	956.5	957.2	956.5	955.9	955.2
175°	959.5	959.5	959.5	959.8	960.5	961.2	961.8	962.5	961.8	961.2	960.5
177.5°	963.0	963.1	963.2	963.5	964.2	964.9	965.5	966.2	965.5	964.9	964.2
180°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1247.9	1243.7	1240.6	1237.5	1224.0	1209.5	1207.4	1204.3	1198.0	1205.3	1202.2
5°	1215.7	1206.3	1201.1	1187.7	1171.0	1158.6	1148.2	1135.7	1130.6	1126.4	1125.4
7.5°	1176.2	1167.9	1158.6	1145.1	1124.3	1103.6	1088.0	1075.5	1065.2	1060.0	1060.0
10°	1137.8	1127.4	1115.0	1092.1	1072.4	1046.5	1029.9	1017.4	1002.9	994.6	987.3
12.5°	1098.4	1087.0	1075.5	1046.5	1023.6	996.6	972.8	957.2	949.9	940.6	928.1
15°	1058.9	1041.3	1029.9	1000.8	971.7	944.7	929.2	912.5	895.9	886.6	882.4
17.5°	1017.4	1004.9	986.3	955.1	922.9	899.0	876.2	860.6	840.9	831.6	822.2
20°	980.0	961.3	942.6	911.5	880.4	848.2	825.3	806.6	794.2	786.9	778.6
22.5°	935.4	917.7	902.2	868.9	834.7	804.6	779.7	768.2	755.8	744.4	736.1
25°	897.0	879.3	863.7	827.4	790.0	762.0	743.3	728.8	715.3	710.1	701.8
27.5°	856.5	839.9	819.1	782.8	749.6	725.7	705.9	692.5	682.1	671.7	665.5
30°	818.1	799.4	780.7	741.2	714.3	690.4	671.7	655.1	646.8	641.6	631.2
32.5°	780.7	756.8	741.2	704.9	679.0	656.1	640.5	626.0	615.6	606.3	598.0
35°	740.2	714.3	698.7	668.6	641.6	618.7	605.2	594.9	582.4	574.1	569.9
37.5°	701.8	680.0	664.4	633.3	606.3	587.6	573.1	559.6	554.4	543.0	540.9
40°	660.3	641.6	627.0	596.9	572.0	557.5	541.9	529.5	520.1	514.9	507.7
42.5°	622.9	607.3	591.8	563.7	539.8	522.2	510.8	499.4	491.0	482.7	477.6
45°	588.6	572.0	557.5	530.5	506.6	491.0	479.6	466.1	464.1	452.6	447.4
47.5°	552.3	537.8	525.3	497.3	475.5	459.9	446.4	437.1	427.7	423.6	416.3
50°	517.0	502.5	487.9	463.0	443.3	427.7	414.2	403.8	398.7	392.4	386.2
52.5°	478.6	467.2	455.8	429.8	410.1	396.6	385.2	371.7	366.5	361.3	357.1
55°	446.4	429.8	417.3	395.5	377.9	363.4	350.9	340.5	335.3	331.2	326.0
57.5°	402.8	392.4	382.0	362.3	345.7	331.2	318.7	310.4	304.2	301.1	302.1
60°	365.4	354.0	347.8	327.0	310.4	299.0	287.6	279.3	273.0	269.9	268.9
62.5°	326.0	317.7	306.3	291.7	275.1	264.7	256.4	250.2	239.8	238.8	235.7
65°	287.6	281.3	271.0	257.5	244.0	234.6	225.3	217.0	212.8	207.6	204.5
67.5°	250.2	244.0	234.6	223.2	213.9	204.5	196.2	187.9	180.6	176.5	174.4
70°	213.9	208.7	202.4	188.9	177.5	170.3	164.0	158.8	151.6	149.5	148.5
72.5°	178.6	173.4	170.3	158.8	148.5	142.2	136.0	130.8	127.7	126.7	123.5
75°	146.4	141.2	137.0	126.7	120.4	116.3	110.0	108.0	104.9	103.8	102.8
77.5°	114.2	109.0	108.0	100.7	93.4	91.4	89.3	85.1	85.1	85.1	83.1
80°	82.0	81.0	79.9	72.7	69.6	67.5	66.4	63.3	61.3	59.2	58.1
82.5°	55.0	54.0	52.9	49.8	46.7	45.7	44.6	42.6	42.6	43.6	41.5
85°	33.2	31.1	30.1	29.1	27.0	27.0	28.0	27.0	27.0	27.0	26.0
87.5°	12.5	12.5	12.5	12.5	13.5	11.4	12.5	12.5	11.4	11.4	10.4
90°	6.1	6.8	7.4	8.5	9.7	10.8	12.0	12.8	13.7	14.5	15.4
92.5°	25.9	26.3	27.0	28.5	30.0	31.5	33.0	34.2	35.4	36.5	37.7
95°	50.1	50.3	51.1	52.8	54.5	56.1	57.8	59.0	60.2	61.3	62.5
97.5°	75.7	75.8	77.0	79.3	81.6	84.0	86.3	87.3	88.3	89.3	90.3
100°	105.1	105.1	106.2	108.4	110.5	112.7	114.9	116.4	117.9	119.4	120.9
102.5°	140.7	141.1	141.5	142.4	143.2	144.1	144.9	146.6	148.2	149.9	151.6
105°	174.5	174.9	175.4	176.4	177.4	178.4	179.4	180.4	181.4	182.4	183.4
107.5°	211.3	211.7	212.1	213.0	213.8	214.7	215.5	216.0	216.5	217.0	217.5
110°	249.6	250.0	250.3	250.8	251.3	251.8	252.3	252.8	253.3	253.8	254.3

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	286.6	286.8	287.1	287.8	288.5	289.1	289.8	290.0	290.1	290.3	290.4
115°	326.3	326.6	326.8	327.1	327.4	327.8	328.1	327.9	327.7	327.6	327.4
117.5°	363.3	363.4	363.6	363.9	364.2	364.6	364.9	365.1	365.2	365.4	365.5
120°	402.0	402.4	402.5	402.7	402.8	403.0	403.2	403.2	403.2	403.2	403.2
122.5°	438.3	438.4	438.7	439.2	439.7	440.2	440.7	440.5	440.3	440.2	440.0
125°	476.2	476.7	476.8	477.0	477.1	477.3	477.5	477.2	476.8	476.5	476.2
127.5°	512.5	512.8	512.9	513.0	513.2	513.3	513.5	513.3	513.2	513.0	512.9
130°	547.7	548.1	548.3	548.6	548.9	549.3	549.6	549.4	549.2	549.1	548.9
132.5°	584.1	584.8	584.7	584.6	584.4	584.3	584.1	583.9	583.7	583.6	583.4
135°	618.1	618.6	618.7	618.9	619.0	619.2	619.4	619.4	619.4	619.4	619.4
137.5°	651.9	652.4	652.6	652.9	653.2	653.6	653.9	654.1	654.3	654.4	654.6
140°	683.5	683.9	684.2	684.7	685.2	685.7	686.2	686.5	686.9	687.2	687.5
142.5°	715.2	715.5	715.8	716.5	717.2	717.8	718.5	718.7	718.8	719.0	719.1
145°	746.7	747.0	747.3	747.8	748.3	748.8	749.3	749.3	749.3	749.3	749.3
147.5°	775.3	775.5	775.7	776.0	776.3	776.7	777.0	777.5	778.0	778.5	779.0
150°	801.9	801.8	802.1	802.8	803.5	804.1	804.8	804.8	804.8	804.8	804.8
152.5°	827.9	828.1	828.2	828.3	828.5	828.6	828.8	829.3	829.8	830.3	830.8
155°	851.4	851.4	851.5	851.6	851.8	851.9	852.1	852.8	853.4	854.1	854.8
157.5°	872.6	872.4	872.5	872.6	872.8	872.9	873.1	873.8	874.4	875.1	875.8
160°	891.4	891.2	891.3	891.4	891.6	891.7	891.9	892.6	893.2	893.9	894.6
162.5°	909.4	909.2	909.2	909.2	909.2	909.2	909.2	910.0	910.8	911.7	912.5
165°	924.4	924.2	924.3	924.4	924.6	924.7	924.9	925.6	926.2	926.9	927.6
167.5°	936.5	936.2	936.2	936.2	936.2	936.2	936.2	937.2	938.2	939.2	940.2
170°	947.0	946.7	946.7	946.7	946.7	946.7	946.7	947.7	948.7	949.7	950.7
172.5°	954.5	954.2	954.2	954.2	954.2	954.2	954.2	955.2	956.2	957.2	958.2
175°	959.8	959.5	959.5	959.5	959.5	959.5	959.5	960.5	961.5	962.5	963.5
177.5°	963.5	963.2	963.1	963.0	962.8	962.7	962.5	963.5	964.5	965.5	966.5
180°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1197.0	1199.1	1193.9	1191.8	1187.7	1192.8	1193.9	1192.8	1202.2	1198.0	1200.1
5°	1127.4	1123.3	1120.2	1112.9	1112.9	1113.9	1117.1	1111.9	1115.0	1122.2	1121.2
7.5°	1050.6	1048.5	1049.6	1041.3	1035.0	1037.1	1035.0	1044.4	1049.6	1047.5	1051.7
10°	981.1	985.2	975.9	971.7	967.6	971.7	970.7	972.8	979.0	983.1	990.4
12.5°	925.0	924.0	918.8	914.6	907.4	909.4	915.7	913.6	914.6	924.0	922.9
15°	872.1	865.8	861.7	852.3	854.4	847.1	853.4	860.6	863.7	872.1	877.2
17.5°	819.1	818.1	812.9	811.8	800.4	797.3	803.5	805.6	808.7	812.9	820.1
20°	774.5	773.4	766.2	764.1	754.7	761.0	758.9	763.0	765.1	773.4	776.5
22.5°	734.0	728.8	726.7	723.6	720.5	719.4	723.6	722.6	729.8	732.9	734.0
25°	696.6	692.5	691.4	686.2	684.1	681.0	684.1	687.3	695.6	698.7	702.8
27.5°	662.3	659.2	657.2	653.0	649.9	649.9	652.0	656.1	659.2	661.3	663.4
30°	631.2	629.1	622.9	620.8	617.7	617.7	617.7	619.8	625.0	631.2	634.3
32.5°	599.0	594.9	590.7	590.7	587.6	587.6	588.6	590.7	595.9	596.9	602.1
35°	567.9	563.7	560.6	558.5	559.6	555.4	557.5	560.6	566.8	568.9	572.0
37.5°	537.8	536.7	530.5	527.4	529.5	529.5	528.4	530.5	534.7	538.8	540.9
40°	504.5	502.5	502.5	499.4	500.4	496.2	499.4	501.4	503.5	507.7	510.8
42.5°	475.5	473.4	469.2	470.3	467.2	467.2	469.2	470.3	473.4	478.6	480.7
45°	444.3	444.3	442.3	439.1	440.2	437.1	439.1	440.2	444.3	449.5	447.4
47.5°	414.2	413.2	413.2	409.0	411.1	408.0	411.1	412.1	414.2	417.3	416.3
50°	385.2	382.0	383.1	382.0	381.0	381.0	383.1	383.1	385.2	385.2	388.3
52.5°	355.1	355.1	353.0	354.0	356.1	354.0	357.1	354.0	356.1	357.1	359.2
55°	328.1	326.0	327.0	326.0	330.1	327.0	330.1	328.1	330.1	329.1	331.2
57.5°	299.0	295.9	296.9	295.9	299.0	298.0	301.1	298.0	299.0	300.0	303.1
60°	265.8	265.8	265.8	263.7	266.8	266.8	265.8	265.8	269.9	272.0	271.0
62.5°	234.6	233.6	230.5	229.4	230.5	228.4	232.5	231.5	233.6	235.7	237.7
65°	200.4	198.3	197.3	195.2	195.2	194.1	195.2	199.3	200.4	201.4	206.6
67.5°	172.3	171.3	170.3	167.1	167.1	169.2	169.2	169.2	175.4	172.3	176.5
70°	147.4	145.3	143.3	142.2	142.2	143.3	144.3	145.3	144.3	148.5	149.5
72.5°	123.5	124.6	122.5	122.5	122.5	121.5	121.5	123.5	124.6	123.5	124.6
75°	102.8	102.8	101.7	102.8	102.8	101.7	101.7	103.8	103.8	102.8	105.9
77.5°	83.1	82.0	79.9	77.9	78.9	77.9	78.9	77.9	81.0	84.1	82.0
80°	58.1	57.1	57.1	57.1	58.1	57.1	59.2	57.1	58.1	58.1	59.2
82.5°	41.5	42.6	42.6	41.5	42.6	41.5	42.6	42.6	42.6	41.5	42.6
85°	27.0	27.0	27.0	27.0	26.0	27.0	27.0	27.0	28.0	27.0	28.0
87.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	12.5	11.4	12.5
90°	15.8	16.0	16.5	17.0	17.5	18.0	17.5	17.0	16.5	16.0	15.8
92.5°	38.3	38.5	38.8	39.1	39.5	39.8	39.5	39.1	38.8	38.5	38.3
95°	63.1	63.3	63.6	63.9	64.3	64.6	64.3	63.9	63.6	63.3	63.1
97.5°	90.8	90.9	91.1	91.2	91.4	91.6	91.4	91.2	91.1	90.9	90.8
100°	121.6	121.8	122.1	122.4	122.8	123.1	122.8	122.4	122.1	121.8	121.6
102.5°	152.4	152.7	153.2	153.7	154.2	154.7	154.2	153.7	153.2	152.7	152.4
105°	183.9	184.2	184.7	185.2	185.7	186.2	185.7	185.2	184.7	184.2	183.9
107.5°	217.7	217.7	217.7	217.7	217.7	217.7	217.7	217.7	217.7	217.7	217.7
110°	254.5	254.4	254.3	254.1	254.0	253.8	254.0	254.1	254.3	254.4	254.5

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	290.5	290.3	290.0	289.7	289.3	289.0	289.3	289.7	290.0	290.3	290.5
115°	327.3	327.2	327.1	326.9	326.8	326.6	326.8	326.9	327.1	327.2	327.3
117.5°	365.6	365.3	364.6	363.9	363.3	362.6	363.3	363.9	364.6	365.3	365.6
120°	403.2	402.9	402.2	401.5	400.9	400.2	400.9	401.5	402.2	402.9	403.2
122.5°	439.9	439.7	439.2	438.7	438.2	437.7	438.2	438.7	439.2	439.7	439.9
125°	476.0	475.9	475.7	475.6	475.4	475.2	475.4	475.6	475.7	475.9	476.0
127.5°	512.8	512.6	512.3	512.0	511.6	511.3	511.6	512.0	512.3	512.6	512.8
130°	548.8	548.6	548.3	548.0	547.6	547.3	547.6	548.0	548.3	548.6	548.8
132.5°	583.3	583.1	582.6	582.1	581.6	581.1	581.6	582.1	582.6	583.1	583.3
135°	619.4	619.1	618.4	617.7	617.1	616.4	617.1	617.7	618.4	619.1	619.4
137.5°	654.7	654.3	653.4	652.6	651.7	650.9	651.7	652.6	653.4	654.3	654.7
140°	687.7	687.3	686.4	685.6	684.7	683.9	684.7	685.6	686.4	687.3	687.7
142.5°	719.2	718.8	718.0	717.1	716.3	715.5	716.3	717.1	718.0	718.8	719.2
145°	749.3	749.0	748.5	748.0	747.5	747.0	747.5	748.0	748.5	749.0	749.3
147.5°	779.3	778.6	777.3	776.0	774.6	773.3	774.6	776.0	777.3	778.6	779.3
150°	804.8	804.6	804.3	804.0	803.6	803.3	803.6	804.0	804.3	804.6	804.8
152.5°	831.1	830.8	830.1	829.4	828.8	828.1	828.8	829.4	830.1	830.8	831.1
155°	855.1	854.7	853.9	853.0	852.2	851.4	852.2	853.0	853.9	854.7	855.1
157.5°	876.1	875.5	874.4	873.2	872.1	870.9	872.1	873.2	874.4	875.5	876.1
160°	894.9	894.5	893.7	892.8	892.0	891.2	892.0	892.8	893.7	894.5	894.9
162.5°	912.9	912.4	911.4	910.4	909.4	908.4	909.4	910.4	911.4	912.4	912.9
165°	927.9	927.4	926.4	925.4	924.4	923.4	924.4	925.4	926.4	927.4	927.9
167.5°	940.7	940.2	939.2	938.2	937.2	936.2	937.2	938.2	939.2	940.2	940.7
170°	951.2	950.6	949.5	948.3	947.2	946.0	947.2	948.3	949.5	950.6	951.2
172.5°	958.7	958.2	957.2	956.2	955.2	954.2	955.2	956.2	957.2	958.2	958.7
175°	964.0	963.4	962.2	961.1	959.9	958.7	959.9	961.1	962.2	963.4	964.0
177.5°	967.0	966.4	965.2	964.1	962.9	961.7	962.9	964.1	965.2	966.4	967.0
180°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1196.0	1201.1	1197.0	1193.9	1202.2	1206.3	1206.3	1213.6	1220.9	1227.1	1228.1
5°	1122.2	1130.6	1132.6	1131.6	1144.1	1150.3	1163.8	1171.0	1181.4	1188.7	1197.0
7.5°	1054.8	1066.2	1067.2	1069.3	1088.0	1098.4	1109.8	1128.5	1143.0	1153.4	1162.7
10°	987.3	994.6	1001.8	1011.2	1029.9	1047.5	1064.1	1083.8	1102.5	1112.9	1126.4
12.5°	936.4	941.6	949.9	956.1	975.9	991.4	1013.2	1040.2	1067.2	1075.5	1092.1
15°	883.5	886.6	903.2	909.4	926.0	952.0	965.5	991.4	1020.5	1036.1	1054.8
17.5°	822.2	840.9	851.3	858.6	879.3	900.1	921.9	948.9	986.3	1000.8	1014.3
20°	778.6	792.1	803.5	812.9	831.6	862.7	882.4	904.2	939.5	956.1	975.9
22.5°	740.2	751.6	762.0	772.4	784.8	812.9	835.7	865.8	901.1	916.7	939.5
25°	703.9	715.3	721.5	734.0	750.6	770.3	797.3	824.3	859.6	877.2	899.0
27.5°	668.6	680.0	691.4	701.8	713.2	731.9	750.6	784.8	821.2	841.9	860.6
30°	638.5	643.7	654.0	665.5	676.9	694.5	716.3	740.2	781.7	800.4	823.3
32.5°	605.2	614.6	621.9	630.2	644.7	659.2	679.0	709.1	742.3	759.9	784.8
35°	574.1	582.4	587.6	602.1	611.5	627.0	646.8	673.8	701.8	721.5	743.3
37.5°	544.0	552.3	558.5	566.8	579.3	592.8	613.6	633.3	666.5	683.1	708.0
40°	512.9	520.1	527.4	536.7	548.1	564.8	577.2	602.1	629.1	647.8	666.5
42.5°	482.7	486.9	495.2	505.6	517.0	531.5	549.2	568.9	595.9	612.5	629.1
45°	450.6	457.8	467.2	474.4	484.8	499.4	514.9	532.6	559.6	576.2	593.8
47.5°	420.5	425.6	431.9	443.3	456.8	467.2	483.8	500.4	525.3	540.9	557.5
50°	389.3	394.5	403.8	411.1	421.5	435.0	450.6	468.2	492.1	502.5	519.1
52.5°	360.2	362.3	371.7	378.9	389.3	404.9	417.3	432.9	455.8	467.2	483.8
55°	331.2	333.2	338.4	345.7	357.1	369.6	383.1	400.7	420.5	430.8	446.4
57.5°	301.1	303.1	308.3	313.5	324.9	336.4	351.9	366.5	386.2	395.5	410.1
60°	271.0	271.0	276.2	283.4	291.7	302.1	315.6	333.2	347.8	359.2	369.6
62.5°	238.8	241.9	245.0	250.2	259.5	272.0	283.4	295.9	313.5	321.8	331.2
65°	206.6	209.7	215.9	221.1	228.4	236.7	251.2	261.6	275.1	284.5	292.8
67.5°	178.6	181.7	185.8	192.1	197.3	206.6	217.0	227.4	241.9	248.1	254.3
70°	149.5	152.6	155.7	164.0	169.2	176.5	183.8	194.1	206.6	210.7	215.9
72.5°	126.7	127.7	131.8	133.9	141.2	147.4	155.7	162.0	171.3	176.5	180.6
75°	106.9	106.9	108.0	110.0	114.2	118.4	124.6	130.8	139.1	142.2	147.4
77.5°	84.1	87.2	86.2	88.2	90.3	92.4	97.6	101.7	110.0	112.1	114.2
80°	60.2	61.3	64.4	67.5	67.5	70.6	73.7	74.7	79.9	83.1	83.1
82.5°	43.6	44.6	43.6	44.6	45.7	46.7	49.8	54.0	54.0	55.0	57.1
85°	27.0	27.0	28.0	29.1	29.1	28.0	30.1	29.1	30.1	32.2	32.2
87.5°	13.5	12.5	12.5	12.5	12.5	12.5	13.5	12.5	13.5	13.5	13.5
90°	15.4	14.5	13.7	12.8	12.0	10.8	9.7	8.5	7.4	6.8	6.1
92.5°	37.7	36.5	35.4	34.2	33.0	31.5	30.0	28.5	27.0	26.3	25.9
95°	62.5	61.3	60.2	59.0	57.8	56.1	54.5	52.8	51.1	50.3	50.1
97.5°	90.3	89.3	88.3	87.3	86.3	84.0	81.6	79.3	77.0	75.8	75.7
100°	120.9	119.4	117.9	116.4	114.9	112.7	110.5	108.4	106.2	105.1	105.1
102.5°	151.6	149.9	148.2	146.6	144.9	144.1	143.2	142.4	141.5	141.1	140.7
105°	183.4	182.4	181.4	180.4	179.4	178.4	177.4	176.4	175.4	174.9	174.5
107.5°	217.5	217.0	216.5	216.0	215.5	214.7	213.8	213.0	212.1	211.7	211.3
110°	254.3	253.8	253.3	252.8	252.3	251.8	251.3	250.8	250.3	250.0	249.6

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	290.4	290.3	290.1	290.0	289.8	289.1	288.5	287.8	287.1	286.8	286.6
115°	327.4	327.6	327.7	327.9	328.1	327.8	327.4	327.1	326.8	326.6	326.3
117.5°	365.5	365.4	365.2	365.1	364.9	364.6	364.2	363.9	363.6	363.4	363.3
120°	403.2	403.2	403.2	403.2	403.2	403.0	402.8	402.7	402.5	402.4	402.0
122.5°	440.0	440.2	440.3	440.5	440.7	440.2	439.7	439.2	438.7	438.4	438.3
125°	476.2	476.5	476.8	477.2	477.5	477.3	477.1	477.0	476.8	476.7	476.2
127.5°	512.9	513.0	513.2	513.3	513.5	513.3	513.2	513.0	512.9	512.8	512.5
130°	548.9	549.1	549.2	549.4	549.6	549.3	548.9	548.6	548.3	548.1	547.7
132.5°	583.4	583.6	583.7	583.9	584.1	584.3	584.4	584.6	584.7	584.8	584.1
135°	619.4	619.4	619.4	619.4	619.4	619.2	619.0	618.9	618.7	618.6	618.1
137.5°	654.6	654.4	654.3	654.1	653.9	653.6	653.2	652.9	652.6	652.4	651.9
140°	687.5	687.2	686.9	686.5	686.2	685.7	685.2	684.7	684.2	683.9	683.5
142.5°	719.1	719.0	718.8	718.7	718.5	717.8	717.2	716.5	715.8	715.5	715.2
145°	749.3	749.3	749.3	749.3	749.3	748.8	748.3	747.8	747.3	747.0	746.7
147.5°	779.0	778.5	778.0	777.5	777.0	776.7	776.3	776.0	775.7	775.5	775.3
150°	804.8	804.8	804.8	804.8	804.8	804.1	803.5	802.8	802.1	801.8	801.9
152.5°	830.8	830.3	829.8	829.3	828.8	828.6	828.5	828.3	828.2	828.1	827.9
155°	854.8	854.1	853.4	852.8	852.1	851.9	851.8	851.6	851.5	851.4	851.4
157.5°	875.8	875.1	874.4	873.8	873.1	872.9	872.8	872.6	872.5	872.4	872.6
160°	894.6	893.9	893.2	892.6	891.9	891.7	891.6	891.4	891.3	891.2	891.4
162.5°	912.5	911.7	910.8	910.0	909.2	909.2	909.2	909.2	909.2	909.2	909.4
165°	927.6	926.9	926.2	925.6	924.9	924.7	924.6	924.4	924.3	924.2	924.4
167.5°	940.2	939.2	938.2	937.2	936.2	936.2	936.2	936.2	936.2	936.2	936.5
170°	950.7	949.7	948.7	947.7	946.7	946.7	946.7	946.7	946.7	946.7	947.0
172.5°	958.2	957.2	956.2	955.2	954.2	954.2	954.2	954.2	954.2	954.2	954.5
175°	963.5	962.5	961.5	960.5	959.5	959.5	959.5	959.5	959.5	959.5	959.8
177.5°	966.5	965.5	964.5	963.5	962.5	962.7	962.8	963.0	963.1	963.2	963.5
180°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7

TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1264.5	1264.5	1264.5	1264.5
2.5°	1235.4	1244.8	1254.1	1265.5
5°	1210.5	1227.1	1244.8	1261.4
7.5°	1183.5	1207.4	1230.2	1254.1
10°	1153.4	1183.5	1209.5	1242.7
12.5°	1120.2	1152.4	1188.7	1226.1
15°	1087.0	1127.4	1165.9	1208.4
17.5°	1055.8	1094.2	1136.8	1187.7
20°	1018.4	1061.0	1108.8	1162.7
22.5°	979.0	1025.7	1077.6	1135.7
25°	945.8	993.5	1043.3	1104.6
27.5°	909.4	959.3	1008.1	1073.5
30°	867.9	921.9	971.7	1039.2
32.5°	828.5	882.4	937.5	1000.8
35°	790.0	843.0	898.0	962.4
37.5°	753.7	801.5	855.4	913.6
40°	719.4	763.0	810.8	863.7
42.5°	675.8	726.7	771.4	809.8
45°	638.5	680.0	721.5	752.7
47.5°	594.9	636.4	671.7	696.6
50°	558.5	591.8	620.8	642.6
52.5°	514.9	546.1	569.9	586.6
55°	472.4	499.4	520.1	531.5
57.5°	434.0	451.6	467.2	477.6
60°	391.4	404.9	418.4	429.8
62.5°	345.7	360.2	367.5	380.0
65°	305.2	314.6	326.0	330.1
67.5°	265.8	271.0	278.2	286.5
70°	224.2	227.4	234.6	246.0
72.5°	187.9	191.0	196.2	200.4
75°	149.5	152.6	156.8	160.9
77.5°	117.3	118.4	120.4	124.6
80°	85.1	88.2	90.3	91.4
82.5°	59.2	60.2	60.2	61.3
85°	37.4	35.3	35.3	36.3
87.5°	13.5	15.6	15.6	17.6
90°	4.8	3.5	2.1	0.8
92.5°	25.0	24.2	23.3	22.5
95°	49.8	49.5	49.1	48.8
97.5°	75.6	75.4	75.3	75.1
100°	105.1	105.1	105.1	105.1
102.5°	139.9	139.0	138.2	137.4
105°	173.7	172.8	172.0	171.2
107.5°	210.5	209.6	208.8	208.0
110°	248.8	247.9	247.1	246.3



TEST NUMBER: P1036157

CATALOG NUMBER: S125RDIW-B850D770UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	286.3	286.0	285.6	285.3
115°	325.6	324.9	324.3	323.6
117.5°	363.1	363.0	362.8	362.6
120°	401.2	400.3	399.5	398.7
122.5°	438.2	438.0	437.9	437.7
125°	475.2	474.2	473.2	472.2
127.5°	512.0	511.5	511.0	510.5
130°	546.8	546.0	545.1	544.3
132.5°	582.6	581.1	579.6	578.1
135°	617.1	616.1	615.1	614.1
137.5°	650.9	649.9	648.9	647.9
140°	682.7	681.8	681.0	680.2
142.5°	714.5	713.8	713.2	712.5
145°	746.0	745.3	744.7	744.0
147.5°	774.8	774.3	773.8	773.3
150°	802.1	802.2	802.4	802.6
152.5°	827.6	827.3	826.9	826.6
155°	851.4	851.4	851.4	851.4
157.5°	872.9	873.2	873.6	873.9
160°	891.9	892.4	892.9	893.4
162.5°	909.7	910.0	910.4	910.7
165°	924.7	925.0	925.4	925.7
167.5°	937.2	937.9	938.5	939.2
170°	947.7	948.4	949.0	949.7
172.5°	955.2	955.9	956.5	957.2
175°	960.5	961.2	961.8	962.5
177.5°	964.2	964.9	965.5	966.2
180°	964.7	964.7	964.7	964.7

(END OF REPORT)