

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007266

Luminaire Tested: S125RDW-B375DB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDW-B375DB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1395.0 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007266

CATALOG NUMBER: S125RDW-B375DB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007266

CATALOG NUMBER: S125RDW-B375DB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85		
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	72		
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	61		
4	84	73	64	58	82	71	64	57	69	62	57	67	61	56	64	59	55	53		
5	78	65	57	50	76	64	56	50	62	55	49	60	54	49	58	53	48	46		
6	72	59	50	44	70	58	50	44	56	49	44	55	48	43	53	47	43	41		
7	67	54	45	39	65	53	45	39	51	44	39	50	43	39	49	43	38	36		
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	33		
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	29		
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3783	3783	3783
5°	3791	3749	3771
10°	3763	3714	3714
15°	3719	3638	3609
20°	3661	3533	3491
25°	3594	3430	3354
30°	3510	3309	3203
35°	3425	3185	3035
40°	3346	3054	2868
45°	3248	2909	2687
50°	3152	2751	2498
55°	3038	2600	2297
60°	2925	2417	2080
65°	2793	2204	1833
70°	2639	1939	1579
75°	2428	1634	1314
80°	2140	1284	1103
85°	1801	1051	985

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3248 cd/sqm

TEST NUMBER: P1007266

CATALOG NUMBER: S125RDW-B375DB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	4.0
10°-20°	155.3	11.1
20°-30°	225.2	16.1
30°-40°	256.5	18.4
40°-50°	250.0	17.9
50°-60°	210.4	15.1
60°-70°	147.5	10.6
70°-80°	75.6	5.4
80°-90°	18.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	436.0	31.3
0°-40°	692.6	49.6
0°-60°	1153.1	82.7
0°-90°	1395.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1395.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	590	588	583	587	586	56
15°	561	558	548	548	544	158
25°	508	502	485	479	474	234
35°	438	427	407	394	388	274
45°	358	346	321	303	297	277
55°	272	258	233	213	206	243
65°	184	169	145	128	121	182
75°	98	85	66	56	53	104
85°	24	16	14	14	13	28
90°	0	0	0	0	0	

TEST NUMBER: P1007266

CATALOG NUMBER: S125RDW-B375DB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	590.4	590.4	590.4	590.4	590.4
2.5°	591.8	590.4	586.0	590.4	590.0
5°	589.5	587.8	582.9	587.3	586.4
7.5°	585.1	583.3	577.5	581.1	580.2
10°	578.4	577.1	570.8	572.2	570.8
12.5°	570.8	569.0	560.1	561.0	558.8
15°	560.6	557.9	548.5	548.1	544.1
17.5°	549.9	545.8	534.7	532.5	529.3
20°	536.9	532.5	518.2	516.0	512.0
22.5°	522.7	518.2	503.0	498.1	495.0
25°	508.4	501.7	485.2	479.4	474.5
27.5°	492.3	484.3	466.9	459.3	454.4
30°	474.5	466.0	447.3	437.0	433.0
32.5°	457.1	446.8	427.7	416.1	410.7
35°	437.9	427.2	407.2	394.2	388.0
37.5°	419.6	406.7	386.2	371.0	364.8
40°	400.0	386.6	365.2	348.3	342.9
42.5°	379.5	365.7	343.4	327.3	318.9
45°	358.5	345.6	321.1	303.2	296.6
47.5°	336.7	323.3	298.8	280.5	272.9
50°	316.2	301.5	276.0	257.3	250.6
52.5°	293.9	278.7	255.1	234.6	227.9
55°	272.0	257.8	232.8	212.7	205.6
57.5°	249.7	234.6	210.5	190.9	184.6
60°	228.3	212.7	188.6	169.0	162.3
62.5°	205.6	190.9	166.3	148.5	141.8
65°	184.2	169.0	145.4	127.5	120.9
67.5°	162.8	147.6	124.9	107.9	102.6
70°	140.9	125.8	103.5	89.6	84.3
72.5°	119.5	104.8	84.3	71.8	68.7
75°	98.1	84.7	66.0	56.2	53.1
77.5°	76.3	65.6	49.9	42.4	39.7
80°	58.0	47.3	34.8	30.8	29.9
82.5°	40.1	30.8	23.2	21.9	21.4
85°	24.5	16.5	14.3	13.8	13.4
87.5°	10.3	7.1	6.7	6.7	6.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)