

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007269

Luminaire Tested: S125RDW-B375DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDW-B375DB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1399.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007269

CATALOG NUMBER: S125RDW-B375DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007269

CATALOG NUMBER: S125RDW-B375DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	109	105	101	97	107	103	99	96	99	96	93		95	92	90		91	89	87		85
2	100	92	86	80	98	90	84	79	87	82	78		84	79	76		81	77	74		72
3	92	82	74	68	89	80	73	67	77	71	66		74	69	65		72	67	64		61
4	84	73	64	58	82	71	64	57	69	62	57		67	61	56		64	59	55		53
5	78	65	57	50	76	64	56	50	62	55	49		60	54	49		58	53	48		46
6	72	59	50	44	70	58	50	44	56	49	44		55	48	43		53	47	43		41
7	67	54	45	39	65	53	45	39	51	44	39		50	43	39		49	43	38		36
8	62	49	41	35	61	48	41	35	47	40	35		46	39	35		45	39	34		33
9	58	45	37	32	57	45	37	32	44	37	32		42	36	31		41	36	31		29
10	55	42	34	29	54	41	34	29	40	34	29		39	33	29		39	33	29		27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3794	3794	3794
5°	3802	3759	3782
10°	3774	3725	3725
15°	3729	3649	3619
20°	3672	3543	3501
25°	3604	3440	3364
30°	3521	3319	3213
35°	3435	3194	3043
40°	3356	3064	2876
45°	3258	2918	2695
50°	3161	2759	2505
55°	3047	2608	2303
60°	2934	2424	2086
65°	2800	2210	1837
70°	2647	1944	1583
75°	2436	1639	1317
80°	2144	1288	1107
85°	1808	1051	985

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3258 cd/sqm

TEST NUMBER: P1007269

CATALOG NUMBER: S125RDW-B375DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	4.0
10°-20°	155.7	11.1
20°-30°	225.8	16.1
30°-40°	257.3	18.4
40°-50°	250.8	17.9
50°-60°	211.0	15.1
60°-70°	147.9	10.6
70°-80°	75.8	5.4
80°-90°	18.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	437.3	31.3
0°-40°	694.6	49.6
0°-60°	1156.4	82.7
0°-90°	1399.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1399.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	592	592	592	592	592	
5°	591	589	584	589	588	56
15°	562	560	550	550	546	159
25°	510	503	487	481	476	235
35°	439	428	408	395	389	275
45°	360	347	322	304	297	277
55°	273	258	234	213	206	244
65°	185	170	146	128	121	183
75°	98	85	66	56	53	104
85°	25	16	14	14	13	28
90°	0	0	0	0	0	

TEST NUMBER: P1007269

CATALOG NUMBER: S125RDW-B375DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	592.1	592.1	592.1	592.1	592.1
2.5°	593.5	592.1	587.7	592.1	591.7
5°	591.2	589.4	584.5	589.0	588.1
7.5°	586.8	585.0	579.2	582.7	581.8
10°	580.1	578.7	572.5	573.8	572.5
12.5°	572.5	570.7	561.7	562.6	560.4
15°	562.2	559.5	550.1	549.6	545.6
17.5°	551.4	547.4	536.2	534.0	530.9
20°	538.5	534.0	519.7	517.4	513.4
22.5°	524.2	519.7	504.5	499.6	496.4
25°	509.8	503.1	486.6	480.8	475.9
27.5°	493.7	485.7	468.3	460.6	455.7
30°	475.9	467.4	448.6	438.3	434.3
32.5°	458.4	448.1	428.9	417.3	411.9
35°	439.2	428.4	408.3	395.4	389.1
37.5°	420.8	407.9	387.3	372.1	365.8
40°	401.2	387.7	366.3	349.3	343.9
42.5°	380.6	366.7	344.4	328.3	319.8
45°	359.6	346.6	322.0	304.1	297.4
47.5°	337.7	324.2	299.6	281.3	273.7
50°	317.1	302.3	276.8	258.1	251.3
52.5°	294.7	279.5	255.8	235.2	228.5
55°	272.8	258.5	233.5	213.3	206.2
57.5°	250.4	235.2	211.1	191.4	185.2
60°	229.0	213.3	189.2	169.5	162.8
62.5°	206.2	191.4	166.8	148.9	142.2
65°	184.7	169.5	145.8	127.9	121.2
67.5°	163.2	148.0	125.2	108.2	102.9
70°	141.3	126.1	103.8	89.9	84.5
72.5°	119.9	105.1	84.5	72.0	68.9
75°	98.4	85.0	66.2	56.4	53.2
77.5°	76.5	65.7	50.1	42.5	39.8
80°	58.1	47.4	34.9	30.9	30.0
82.5°	40.3	30.9	23.3	21.9	21.5
85°	24.6	16.5	14.3	13.9	13.4
87.5°	10.3	7.2	6.7	6.7	6.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)