

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983420

Luminaire Tested: S125IW-B1050UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1050UB2750-4F0-XX-W2A-1_2700K
Description: Define 5 Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3656.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983420

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P983420

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983420

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	87.1	2.4
100°-110°	258.6	7.1
110°-120°	438.6	12.0
120°-130°	577.5	15.8
130°-140°	647.1	17.7
140°-150°	634.3	17.3
150°-160°	532.8	14.6
160°-170°	354.1	9.7
170°-180°	123.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	784.3	21.5
90°-150°	2643.2	72.3
90°-180°	3654.0	99.9
0°-180°	3656.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	4
95°	66	68	78	86	88	69
105°	232	237	244	250	253	248
115°	439	443	445	444	443	434
125°	641	647	648	646	645	574
135°	833	840	841	841	836	642
145°	1010	1014	1017	1017	1014	631
155°	1155	1155	1156	1160	1155	532
165°	1256	1254	1255	1259	1253	354
175°	1306	1302	1302	1308	1301	124
180°	1309	1309	1309	1309	1309	

TEST NUMBER: P983420

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	9.2	16.3	21.4	24.5
92.5°	30.6	35.7	44.8	52.0	54.0
95°	66.2	68.3	78.5	85.6	87.6
97.5°	101.9	102.9	117.2	123.3	124.3
100°	142.6	142.6	155.9	165.1	167.1
102.5°	186.5	191.5	196.6	206.8	209.9
105°	232.3	237.4	243.5	249.6	252.7
107.5°	282.2	287.3	292.4	295.5	295.5
110°	334.2	339.3	342.3	345.4	344.4

TEST NUMBER: P983420

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	387.2	389.2	393.3	394.3	392.3
115°	439.1	443.2	445.2	444.2	443.2
117.5°	492.1	493.1	495.2	496.2	492.1
120°	541.0	546.1	547.1	547.1	543.1
122.5°	594.0	595.0	598.1	597.1	594.0
125°	640.9	647.0	648.0	646.0	644.9
127.5°	692.8	695.9	696.9	695.9	693.8
130°	738.7	743.8	745.8	744.8	742.7
132.5°	784.5	793.7	792.7	791.7	788.6
135°	833.4	839.5	840.6	840.6	836.5
137.5°	879.3	885.4	887.4	888.4	883.3
140°	923.1	928.2	931.2	933.3	928.2
142.5°	966.9	971.0	975.0	976.1	971.0
145°	1009.7	1013.8	1016.8	1016.8	1013.8
147.5°	1049.4	1052.5	1054.5	1057.6	1049.4
150°	1089.2	1088.1	1092.2	1092.2	1090.2
152.5°	1121.8	1123.8	1124.8	1127.9	1123.8
155°	1155.4	1155.4	1156.4	1160.5	1155.4
157.5°	1186.0	1183.9	1184.9	1189.0	1181.9
160°	1212.4	1209.4	1210.4	1214.5	1209.4
162.5°	1235.9	1233.8	1233.8	1238.9	1232.8
165°	1256.3	1254.2	1255.2	1259.3	1253.2
167.5°	1274.6	1270.5	1270.5	1276.6	1270.5
170°	1288.9	1284.8	1284.8	1290.9	1283.8
172.5°	1299.0	1295.0	1295.0	1301.1	1295.0
175°	1306.2	1302.1	1302.1	1308.2	1301.1
177.5°	1311.3	1307.2	1306.2	1312.3	1305.2
180°	1309.2	1309.2	1309.2	1309.2	1309.2

(END OF REPORT)