

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983429

Luminaire Tested: S125IW-B1050UB2750-4F0-XX-W2A_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983429
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1050UB2750-4F0-XX-W2A_5000K
Description: Define 5 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4089.0 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983429

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P983429

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983429

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.0
90°-100°	45.2	1.1
100°-110°	300.3	7.3
110°-120°	540.7	13.2
120°-130°	694.1	17.0
130°-140°	746.5	18.3
140°-150°	700.6	17.1
150°-160°	566.7	13.9
160°-170°	366.5	9.0
170°-180°	126.4	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.0
90°-120°	886.2	21.7
90°-150°	3027.4	74.0
90°-180°	4087.0	100.0
0°-180°	4089.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	3
95°	56	53	16	21	21	69
105°	290	294	294	294	293	307
115°	544	549	550	546	540	540
125°	774	781	781	777	774	692
135°	966	972	970	968	962	744
145°	1119	1121	1121	1122	1116	700
155°	1233	1227	1229	1232	1224	568
165°	1301	1295	1296	1302	1294	367
175°	1330	1325	1326	1334	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P983429

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	8.9	15.8	20.7	23.7
92.5°	18.7	9.9	15.8	20.7	21.7
95°	56.2	53.3	15.8	20.7	20.7
97.5°	105.5	111.5	17.8	19.7	20.7
100°	164.7	167.7	171.6	24.7	20.7
102.5°	224.9	228.8	230.8	232.8	149.9
105°	290.0	293.9	293.9	293.9	292.9
107.5°	357.0	357.0	359.0	360.0	356.1
110°	422.1	422.1	424.1	421.1	422.1

TEST NUMBER: P983429

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	483.3	486.2	487.2	483.3	481.3
115°	544.4	549.4	550.3	546.4	540.5
117.5°	608.5	608.5	612.5	606.6	604.6
120°	667.7	666.7	669.7	667.7	662.8
122.5°	720.0	724.9	725.9	723.9	718.0
125°	774.2	781.1	781.1	777.2	774.2
127.5°	826.5	831.4	830.5	828.5	820.6
130°	873.9	878.8	879.8	876.8	871.9
132.5°	921.2	927.1	924.2	924.2	919.2
135°	965.6	971.5	969.5	967.5	961.6
137.5°	1007.0	1012.9	1010.9	1010.9	1006.0
140°	1047.4	1049.4	1048.4	1050.4	1044.5
142.5°	1083.9	1084.9	1086.9	1086.9	1081.0
145°	1119.4	1121.4	1121.4	1122.4	1116.5
147.5°	1151.0	1151.0	1152.0	1153.0	1146.1
150°	1180.6	1178.6	1180.6	1182.6	1174.7
152.5°	1209.2	1204.3	1206.2	1208.2	1201.3
155°	1232.9	1226.9	1228.9	1231.9	1224.0
157.5°	1251.6	1248.6	1248.6	1251.6	1243.7
160°	1271.3	1265.4	1266.4	1270.3	1262.4
162.5°	1287.1	1281.2	1282.2	1288.1	1279.2
165°	1300.9	1295.0	1296.0	1301.9	1294.0
167.5°	1311.8	1305.8	1306.8	1313.7	1304.9
170°	1320.6	1313.7	1314.7	1322.6	1313.7
172.5°	1326.6	1319.7	1321.6	1328.5	1319.7
175°	1330.5	1324.6	1325.6	1333.5	1324.6
177.5°	1333.5	1327.5	1328.5	1335.4	1327.5
180°	1330.5	1330.5	1330.5	1330.5	1330.5

(END OF REPORT)