

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983444

Luminaire Tested: S125IW-B1340UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983444
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1340UB2750-4F0-XX-W2A-1_5000K
Description: Define 5 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4478.0 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983444

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P983444

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983444

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.5	0.1
90°-100°	106.6	2.4
100°-110°	316.8	7.1
110°-120°	537.3	12.0
120°-130°	707.3	15.8
130°-140°	792.6	17.7
140°-150°	776.9	17.3
150°-160°	652.5	14.6
160°-170°	433.8	9.7
170°-180°	151.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.5	0.1
90°-120°	960.7	21.5
90°-150°	3237.4	72.3
90°-180°	4475.0	99.9
0°-180°	4478.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	20	26	30	5
95°	81	84	96	105	107	85
105°	284	291	298	306	310	303
115°	538	543	545	544	543	532
125°	785	792	794	791	790	703
135°	1021	1028	1030	1030	1025	787
145°	1237	1242	1245	1245	1242	773
155°	1415	1415	1416	1421	1415	652
165°	1539	1536	1538	1542	1535	434
175°	1600	1595	1595	1602	1594	152
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P983444

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	11.2	20.0	26.2	30.0
92.5°	37.4	43.7	54.9	63.6	66.1
95°	81.1	83.6	96.1	104.8	107.3
97.5°	124.8	126.0	143.5	151.0	152.2
100°	174.7	174.7	190.9	202.2	204.7
102.5°	228.4	234.6	240.9	253.3	257.1
105°	284.5	290.8	298.3	305.7	309.5
107.5°	345.7	351.9	358.2	361.9	361.9
110°	409.3	415.6	419.3	423.0	421.8

TEST NUMBER: P983444

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	474.2	476.7	481.7	483.0	480.5
115°	537.9	542.9	545.3	544.1	542.9
117.5°	602.8	604.0	606.5	607.7	602.8
120°	662.7	668.9	670.1	670.1	665.1
122.5°	727.5	728.8	732.5	731.3	727.5
125°	785.0	792.4	793.7	791.2	789.9
127.5°	848.6	852.3	853.6	852.3	849.8
130°	904.8	911.0	913.5	912.2	909.7
132.5°	960.9	972.1	970.9	969.6	965.9
135°	1020.8	1028.3	1029.5	1029.5	1024.6
137.5°	1077.0	1084.5	1087.0	1088.2	1082.0
140°	1130.6	1136.9	1140.6	1143.1	1136.9
142.5°	1184.3	1189.3	1194.3	1195.5	1189.3
145°	1236.7	1241.7	1245.4	1245.4	1241.7
147.5°	1285.4	1289.1	1291.6	1295.4	1285.4
150°	1334.0	1332.8	1337.8	1337.8	1335.3
152.5°	1374.0	1376.5	1377.7	1381.5	1376.5
155°	1415.2	1415.2	1416.4	1421.4	1415.2
157.5°	1452.6	1450.1	1451.3	1456.3	1447.6
160°	1485.0	1481.3	1482.5	1487.5	1481.3
162.5°	1513.7	1511.2	1511.2	1517.5	1510.0
165°	1538.7	1536.2	1537.5	1542.4	1535.0
167.5°	1561.2	1556.2	1556.2	1563.7	1556.2
170°	1578.6	1573.6	1573.6	1581.1	1572.4
172.5°	1591.1	1586.1	1586.1	1593.6	1586.1
175°	1599.9	1594.9	1594.9	1602.3	1593.6
177.5°	1606.1	1601.1	1599.9	1607.3	1598.6
180°	1603.6	1603.6	1603.6	1603.6	1603.6

(END OF REPORT)