

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983446

Luminaire Tested: S125IW-B1340UB2750-4F0-XX-W2A_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1340UB2750-4F0-XX-W2A_3000K
Description: Define 5 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5370.0 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983446

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P983446

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983446

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.0
90°-100°	59.3	1.1
100°-110°	394.4	7.3
110°-120°	710.2	13.2
120°-130°	911.5	17.0
130°-140°	980.4	18.3
140°-150°	920.1	17.1
150°-160°	744.3	13.9
160°-170°	481.3	9.0
170°-180°	166.0	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.0
90°-120°	1163.8	21.7
90°-150°	3975.8	74.0
90°-180°	5367.0	99.9
0°-180°	5370.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	12	21	27	31	4
95°	74	70	21	27	27	90
105°	381	386	386	386	385	403
115°	715	722	723	718	710	709
125°	1017	1026	1026	1021	1017	908
135°	1268	1276	1273	1271	1263	978
145°	1470	1473	1473	1474	1466	919
155°	1619	1611	1614	1618	1607	746
165°	1708	1701	1702	1710	1699	483
175°	1747	1740	1741	1751	1740	166
180°	1747	1747	1747	1747	1747	

TEST NUMBER: P983446

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.3	11.7	20.7	27.2	31.1
92.5°	24.6	13.0	20.7	27.2	28.5
95°	73.8	69.9	20.7	27.2	27.2
97.5°	138.6	146.4	23.3	25.9	27.2
100°	216.3	220.2	225.4	32.4	27.2
102.5°	295.3	300.5	303.1	305.7	196.9
105°	380.8	386.0	386.0	386.0	384.7
107.5°	468.9	468.9	471.5	472.8	467.6
110°	554.4	554.4	557.0	553.1	554.4

TEST NUMBER: P983446

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	634.7	638.6	639.9	634.7	632.1
115°	715.0	721.5	722.8	717.6	709.8
117.5°	799.2	799.2	804.4	796.6	794.0
120°	876.9	875.6	879.5	876.9	870.4
122.5°	945.5	952.0	953.3	950.7	943.0
125°	1016.8	1025.9	1025.9	1020.7	1016.8
127.5°	1085.4	1091.9	1090.6	1088.0	1077.7
130°	1147.6	1154.1	1155.4	1151.5	1145.0
132.5°	1209.8	1217.6	1213.7	1213.7	1207.2
135°	1268.1	1275.8	1273.3	1270.7	1262.9
137.5°	1322.5	1330.2	1327.7	1327.7	1321.2
140°	1375.6	1378.2	1376.9	1379.5	1371.7
142.5°	1423.5	1424.8	1427.4	1427.4	1419.6
145°	1470.1	1472.7	1472.7	1474.0	1466.2
147.5°	1511.6	1511.6	1512.9	1514.2	1505.1
150°	1550.4	1547.9	1550.4	1553.0	1542.7
152.5°	1588.0	1581.5	1584.1	1586.7	1577.6
155°	1619.1	1611.3	1613.9	1617.8	1607.4
157.5°	1643.7	1639.8	1639.8	1643.7	1633.3
160°	1669.6	1661.8	1663.1	1668.3	1657.9
162.5°	1690.3	1682.6	1683.9	1691.6	1680.0
165°	1708.5	1700.7	1702.0	1709.8	1699.4
167.5°	1722.7	1714.9	1716.2	1725.3	1713.6
170°	1734.4	1725.3	1726.6	1737.0	1725.3
172.5°	1742.1	1733.1	1735.7	1744.7	1733.1
175°	1747.3	1739.6	1740.8	1751.2	1739.6
177.5°	1751.2	1743.4	1744.7	1753.8	1743.4
180°	1747.3	1747.3	1747.3	1747.3	1747.3

(END OF REPORT)