

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983448

Luminaire Tested: S125IW-B1340UB2750-4F0-XX-W2A_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1340UB2750-4F0-XX-W2A_4000K
Description: Define 5 Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5340.0 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983448

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P983448

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983448

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.0
90°-100°	59.0	1.1
100°-110°	392.1	7.3
110°-120°	706.2	13.2
120°-130°	906.4	17.0
130°-140°	974.9	18.3
140°-150°	915.0	17.1
150°-160°	740.1	13.9
160°-170°	478.7	9.0
170°-180°	165.1	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.0
90°-120°	1157.3	21.7
90°-150°	3953.6	74.0
90°-180°	5337.0	99.9
0°-180°	5340.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	12	21	27	31	4
95°	73	70	21	27	27	90
105°	379	384	384	384	382	401
115°	711	717	719	714	706	705
125°	1011	1020	1020	1015	1011	903
135°	1261	1269	1266	1264	1256	972
145°	1462	1464	1464	1466	1458	914
155°	1610	1602	1605	1609	1598	742
165°	1699	1691	1692	1700	1690	480
175°	1738	1730	1731	1741	1730	165
180°	1738	1738	1738	1738	1738	

TEST NUMBER: P983448

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.3	11.6	20.6	27.0	30.9
92.5°	24.5	12.9	20.6	27.0	28.3
95°	73.4	69.6	20.6	27.0	27.0
97.5°	137.8	145.5	23.2	25.8	27.0
100°	215.1	219.0	224.1	32.2	27.0
102.5°	293.7	298.8	301.4	304.0	195.8
105°	378.7	383.8	383.8	383.8	382.5
107.5°	466.3	466.3	468.8	470.1	465.0
110°	551.3	551.3	553.9	550.0	551.3

TEST NUMBER: P983448

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	631.1	635.0	636.3	631.1	628.6
115°	711.0	717.4	718.7	713.6	705.8
117.5°	794.7	794.7	799.9	792.1	789.6
120°	872.0	870.7	874.6	872.0	865.6
122.5°	940.3	946.7	948.0	945.4	937.7
125°	1011.1	1020.1	1020.1	1015.0	1011.1
127.5°	1079.4	1085.8	1084.5	1082.0	1071.6
130°	1141.2	1147.6	1148.9	1145.1	1138.6
132.5°	1203.0	1210.8	1206.9	1206.9	1200.5
135°	1261.0	1268.7	1266.1	1263.6	1255.8
137.5°	1315.1	1322.8	1320.2	1320.2	1313.8
140°	1367.9	1370.5	1369.2	1371.8	1364.0
142.5°	1415.6	1416.8	1419.4	1419.4	1411.7
145°	1461.9	1464.5	1464.5	1465.8	1458.1
147.5°	1503.1	1503.1	1504.4	1505.7	1496.7
150°	1541.8	1539.2	1541.8	1544.4	1534.1
152.5°	1579.1	1572.7	1575.3	1577.8	1568.8
155°	1610.0	1602.3	1604.9	1608.8	1598.5
157.5°	1634.5	1630.7	1630.7	1634.5	1624.2
160°	1660.3	1652.6	1653.8	1659.0	1648.7
162.5°	1680.9	1673.2	1674.4	1682.2	1670.6
165°	1698.9	1691.2	1692.5	1700.2	1689.9
167.5°	1713.1	1705.4	1706.6	1715.7	1704.1
170°	1724.7	1715.7	1717.0	1727.3	1715.7
172.5°	1732.4	1723.4	1726.0	1735.0	1723.4
175°	1737.6	1729.8	1731.1	1741.4	1729.8
177.5°	1741.4	1733.7	1735.0	1744.0	1733.7
180°	1737.6	1737.6	1737.6	1737.6	1737.6

(END OF REPORT)