

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983463

Luminaire Tested: S125IW-B1560UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1560UB2750-4F0-XX-W2A-1_4000K
Description: Define 5 Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5460.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983463

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P983463

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983463

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.0	0.1
90°-100°	130.0	2.4
100°-110°	386.3	7.1
110°-120°	655.1	12.0
120°-130°	862.4	15.8
130°-140°	966.4	17.7
140°-150°	947.2	17.3
150°-160°	795.6	14.6
160°-170°	528.9	9.7
170°-180°	185.1	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.0	0.1
90°-120°	1171.4	21.5
90°-150°	3947.4	72.3
90°-180°	5457.0	99.9
0°-180°	5460.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	14	24	32	36	7
95°	99	102	117	128	131	103
105°	347	354	364	373	377	370
115°	656	662	665	663	662	649
125°	957	966	968	965	963	858
135°	1245	1254	1255	1255	1249	959
145°	1508	1514	1519	1519	1514	943
155°	1726	1726	1727	1733	1726	795
165°	1876	1873	1875	1881	1872	529
175°	1951	1945	1945	1954	1943	185
180°	1955	1955	1955	1955	1955	

TEST NUMBER: P983463

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.5	13.7	24.3	32.0	36.5
92.5°	45.6	53.3	67.0	77.6	80.6
95°	98.9	101.9	117.2	127.8	130.9
97.5°	152.2	153.7	175.0	184.1	185.6
100°	213.0	213.0	232.8	246.5	249.5
102.5°	278.5	286.1	293.7	308.9	313.4
105°	346.9	354.5	363.7	372.8	377.4
107.5°	421.5	429.1	436.7	441.3	441.3
110°	499.1	506.7	511.3	515.8	514.3

TEST NUMBER: P983463

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.2	581.3	587.3	588.9	585.8
115°	655.8	661.9	664.9	663.4	661.9
117.5°	734.9	736.5	739.5	741.0	734.9
120°	808.0	815.6	817.1	817.1	811.0
122.5°	887.1	888.6	893.2	891.7	887.1
125°	957.1	966.2	967.7	964.7	963.2
127.5°	1034.7	1039.3	1040.8	1039.3	1036.2
130°	1103.2	1110.8	1113.8	1112.3	1109.2
132.5°	1171.6	1185.3	1183.8	1182.3	1177.7
135°	1244.7	1253.8	1255.3	1255.3	1249.2
137.5°	1313.1	1322.3	1325.3	1326.8	1319.2
140°	1378.6	1386.2	1390.7	1393.8	1386.2
142.5°	1444.0	1450.1	1456.2	1457.7	1450.1
145°	1507.9	1514.0	1518.6	1518.6	1514.0
147.5°	1567.2	1571.8	1574.9	1579.4	1567.2
150°	1626.6	1625.1	1631.2	1631.2	1628.1
152.5°	1675.3	1678.3	1679.8	1684.4	1678.3
155°	1725.5	1725.5	1727.0	1733.1	1725.5
157.5°	1771.1	1768.1	1769.6	1775.7	1765.1
160°	1810.7	1806.1	1807.7	1813.7	1806.1
162.5°	1845.7	1842.7	1842.7	1850.3	1841.1
165°	1876.1	1873.1	1874.6	1880.7	1871.6
167.5°	1903.5	1897.4	1897.4	1906.6	1897.4
170°	1924.8	1918.7	1918.7	1927.9	1917.2
172.5°	1940.0	1934.0	1934.0	1943.1	1934.0
175°	1950.7	1944.6	1944.6	1953.7	1943.1
177.5°	1958.3	1952.2	1950.7	1959.8	1949.2
180°	1955.3	1955.3	1955.3	1955.3	1955.3

(END OF REPORT)