

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983466

Luminaire Tested: S125IW-B1560UB2750-4F0-XX-W2A_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1560UB2750-4F0-XX-W2A_3000K
Description: Define 5 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6332.0 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983466

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P983466

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983466

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.1	0.0
90°-100°	69.9	1.1
100°-110°	465.0	7.3
110°-120°	837.4	13.2
120°-130°	1074.8	17.0
130°-140°	1156.0	18.3
140°-150°	1084.9	17.1
150°-160°	877.6	13.9
160°-170°	567.6	9.0
170°-180°	195.7	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.1	0.0
90°-120°	1372.3	21.7
90°-150°	4688.0	74.0
90°-180°	6329.0	100.0
0°-180°	6332.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	14	24	32	37	4
95°	87	82	24	32	32	107
105°	449	455	455	455	454	476
115°	843	851	852	846	837	836
125°	1199	1210	1210	1204	1199	1071
135°	1495	1504	1501	1498	1489	1153
145°	1734	1737	1737	1738	1729	1084
155°	1909	1900	1903	1908	1895	880
165°	2014	2005	2007	2016	2004	569
175°	2060	2051	2053	2065	2051	196
180°	2060	2060	2060	2060	2060	

TEST NUMBER: P983466

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.5	13.7	24.4	32.1	36.7
92.5°	29.0	15.3	24.4	32.1	33.6
95°	87.1	82.5	24.4	32.1	32.1
97.5°	163.4	172.6	27.5	30.5	32.1
100°	255.1	259.6	265.8	38.2	32.1
102.5°	348.2	354.3	357.4	360.4	232.2
105°	449.0	455.1	455.1	455.1	453.6
107.5°	552.9	552.9	555.9	557.5	551.4
110°	653.7	653.7	656.7	652.2	653.7

TEST NUMBER: P983466

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	748.4	753.0	754.5	748.4	745.3
115°	843.1	850.7	852.2	846.1	837.0
117.5°	942.4	942.4	948.5	939.3	936.2
120°	1034.0	1032.5	1037.0	1034.0	1026.4
122.5°	1114.9	1122.6	1124.1	1121.0	1111.9
125°	1198.9	1209.6	1209.6	1203.5	1198.9
127.5°	1279.9	1287.5	1286.0	1282.9	1270.7
130°	1353.2	1360.8	1362.4	1357.8	1350.1
132.5°	1426.5	1435.7	1431.1	1431.1	1423.5
135°	1495.2	1504.4	1501.3	1498.3	1489.1
137.5°	1559.4	1568.6	1565.5	1565.5	1557.9
140°	1622.0	1625.1	1623.5	1626.6	1617.4
142.5°	1678.5	1680.0	1683.1	1683.1	1673.9
145°	1733.5	1736.6	1736.6	1738.1	1728.9
147.5°	1782.4	1782.4	1783.9	1785.4	1774.7
150°	1828.2	1825.1	1828.2	1831.2	1819.0
152.5°	1872.5	1864.8	1867.9	1871.0	1860.3
155°	1909.1	1900.0	1903.0	1907.6	1895.4
157.5°	1938.2	1933.6	1933.6	1938.2	1925.9
160°	1968.7	1959.5	1961.1	1967.2	1955.0
162.5°	1993.1	1984.0	1985.5	1994.7	1980.9
165°	2014.5	2005.4	2006.9	2016.1	2003.8
167.5°	2031.3	2022.2	2023.7	2034.4	2020.6
170°	2045.1	2034.4	2035.9	2048.1	2034.4
172.5°	2054.2	2043.5	2046.6	2057.3	2043.5
175°	2060.3	2051.2	2052.7	2064.9	2051.2
177.5°	2064.9	2055.8	2057.3	2068.0	2055.8
180°	2060.3	2060.3	2060.3	2060.3	2060.3

(END OF REPORT)