

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035677

Luminaire Tested: S125RDIW-B1090D1050UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035677
REPORT IS A COMBINATION OF REPORTS P1005923 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1050UB27-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7818.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035677

CATALOG NUMBER: S125RDIW-B1090D1050UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035677

CATALOG NUMBER: S125RDIW-B1090D1050UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	53	51	50
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	56	58	54	50	50	46	43	41	39	37
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11287	11287	11287
5°	11288	11005	11023
10°	11178	10728	10633
15°	11019	10340	10121
20°	10824	9873	9584
25°	10599	9417	9008
30°	10325	8915	8403
35°	10044	8406	7760
40°	9777	7883	7133
45°	9456	7319	6475
50°	9130	6720	5806
55°	8753	6129	5113
60°	8367	5454	4394
65°	7907	4700	3619
70°	7369	3827	2848
75°	6627	2877	2075
80°	5591	1864	1399
85°	4185	1002	788

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9456 cd/sqm

TEST NUMBER: P1035677

CATALOG NUMBER: S125RDIW-B1090D1050UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.8	2.1
10°-20°	463.3	5.9
20°-30°	671.8	8.6
30°-40°	765.4	9.8
40°-50°	746.0	9.5
50°-60°	627.8	8.0
60°-70°	440.0	5.6
70°-80°	225.6	2.9
80°-90°	58.3	0.7
90°-100°	87.1	1.1
100°-110°	258.6	3.3
110°-120°	438.6	5.6
120°-130°	577.5	7.4
130°-140°	647.1	8.3
140°-150°	634.3	8.1
150°-160°	532.8	6.8
160°-170°	354.1	4.5
170°-180°	123.9	1.6
0°-30°	1300.9	16.6
0°-40°	2066.3	26.4
0°-60°	3440.2	44.0
0°-90°	4164.0	53.3
90°-120°	784.3	10.0
90°-150°	2643.2	33.8
90°-180°	3654.0	46.7
0°-180°	7818.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1762	1762	1762	1762	1762	
5°	1759	1754	1739	1752	1750	167
15°	1672	1664	1636	1635	1623	472
25°	1517	1497	1448	1430	1416	698
35°	1307	1275	1215	1176	1158	818
45°	1070	1031	958	905	885	825
55°	812	769	694	635	613	726
65°	550	504	434	380	361	544
75°	293	253	197	168	158	309
85°	73	49	43	41	40	80
90°	1	9	16	21	24	9
95°	66	68	78	86	88	69
105°	232	237	244	250	253	248
115°	439	443	445	444	443	434
125°	641	647	648	646	645	574
135°	833	840	841	841	836	642
145°	1010	1014	1017	1017	1014	631
155°	1155	1155	1156	1160	1155	532
165°	1256	1254	1255	1259	1253	354
175°	1306	1302	1302	1308	1301	124
180°	1309	1309	1309	1309	1309	

TEST NUMBER: P1035677

CATALOG NUMBER: S125RDIW-B1090D1050UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1761.6	1761.6	1761.6	1761.6	1761.6
2.5°	1765.6	1761.6	1748.3	1761.6	1760.3
5°	1758.9	1753.6	1739.0	1752.3	1749.6
7.5°	1745.6	1740.3	1723.0	1733.6	1731.0
10°	1725.7	1721.7	1703.0	1707.0	1703.0
12.5°	1703.0	1697.7	1671.1	1673.8	1667.1
15°	1672.4	1664.5	1636.5	1635.2	1623.2
17.5°	1640.5	1628.5	1595.3	1588.6	1579.3
20°	1601.9	1588.6	1546.0	1539.4	1527.4
22.5°	1559.3	1546.0	1500.8	1486.2	1476.9
25°	1516.8	1496.8	1447.6	1430.3	1415.7
27.5°	1468.9	1444.9	1393.0	1370.4	1355.8
30°	1415.7	1390.4	1334.5	1303.9	1291.9
32.5°	1363.8	1333.2	1276.0	1241.4	1225.4
35°	1306.6	1274.6	1214.7	1176.2	1157.5
37.5°	1252.0	1213.4	1152.2	1107.0	1088.4
40°	1193.5	1153.5	1089.7	1039.1	1023.2
42.5°	1132.3	1091.0	1024.5	976.6	951.3
45°	1069.7	1031.1	958.0	904.7	884.8
47.5°	1004.5	964.6	891.4	836.9	814.3
50°	943.3	899.4	823.6	767.7	747.7
52.5°	876.8	831.6	761.0	699.8	679.9
55°	811.6	769.0	694.5	634.6	613.4
57.5°	745.1	699.8	628.0	569.5	550.8
60°	681.2	634.6	562.8	504.3	484.3
62.5°	613.4	569.5	496.3	443.1	423.1
65°	549.5	504.3	433.7	380.5	360.6
67.5°	485.6	440.4	372.5	322.0	306.0
70°	420.4	375.2	308.7	267.4	251.5
72.5°	356.6	312.7	251.5	214.2	204.9
75°	292.7	252.8	196.9	167.6	158.3
77.5°	227.5	195.6	149.0	126.4	118.4
80°	173.0	141.0	103.8	91.8	89.1
82.5°	119.7	91.8	69.2	65.2	63.9
85°	73.2	49.2	42.6	41.2	39.9
87.5°	30.6	21.3	20.0	20.0	18.6
90°	1.0	9.2	16.3	21.4	24.5
92.5°	30.6	35.7	44.8	52.0	54.0
95°	66.2	68.3	78.5	85.6	87.6
97.5°	101.9	102.9	117.2	123.3	124.3
100°	142.6	142.6	155.9	165.1	167.1
102.5°	186.5	191.5	196.6	206.8	209.9
105°	232.3	237.4	243.5	249.6	252.7
107.5°	282.2	287.3	292.4	295.5	295.5
110°	334.2	339.3	342.3	345.4	344.4

TEST NUMBER: P1035677

CATALOG NUMBER: S125RDIW-B1090D1050UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	387.2	389.2	393.3	394.3	392.3
115°	439.1	443.2	445.2	444.2	443.2
117.5°	492.1	493.1	495.2	496.2	492.1
120°	541.0	546.1	547.1	547.1	543.1
122.5°	594.0	595.0	598.1	597.1	594.0
125°	640.9	647.0	648.0	646.0	644.9
127.5°	692.8	695.9	696.9	695.9	693.8
130°	738.7	743.8	745.8	744.8	742.7
132.5°	784.5	793.7	792.7	791.7	788.6
135°	833.4	839.5	840.6	840.6	836.5
137.5°	879.3	885.4	887.4	888.4	883.3
140°	923.1	928.2	931.2	933.3	928.2
142.5°	966.9	971.0	975.0	976.1	971.0
145°	1009.7	1013.8	1016.8	1016.8	1013.8
147.5°	1049.4	1052.5	1054.5	1057.6	1049.4
150°	1089.2	1088.1	1092.2	1092.2	1090.2
152.5°	1121.8	1123.8	1124.8	1127.9	1123.8
155°	1155.4	1155.4	1156.4	1160.5	1155.4
157.5°	1186.0	1183.9	1184.9	1189.0	1181.9
160°	1212.4	1209.4	1210.4	1214.5	1209.4
162.5°	1235.9	1233.8	1233.8	1238.9	1232.8
165°	1256.3	1254.2	1255.2	1259.3	1253.2
167.5°	1274.6	1270.5	1270.5	1276.6	1270.5
170°	1288.9	1284.8	1284.8	1290.9	1283.8
172.5°	1299.0	1295.0	1295.0	1301.1	1295.0
175°	1306.2	1302.1	1302.1	1308.2	1301.1
177.5°	1311.3	1307.2	1306.2	1312.3	1305.2
180°	1309.2	1309.2	1309.2	1309.2	1309.2

(END OF REPORT)