

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983468

Luminaire Tested: S125IW-B1560UB2750-4F0-XX-W2A_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1560UB2750-4F0-XX-W2A_4000K
Description: Define 5 Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6296.0 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983468

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P983468

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983468

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.0	0.0
90°-100°	69.5	1.1
100°-110°	462.4	7.3
110°-120°	832.6	13.2
120°-130°	1068.7	17.0
130°-140°	1149.4	18.3
140°-150°	1078.8	17.1
150°-160°	872.6	13.9
160°-170°	564.3	9.0
170°-180°	194.6	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.0	0.0
90°-120°	1364.5	21.7
90°-150°	4661.4	74.0
90°-180°	6293.0	100.0
0°-180°	6296.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	14	24	32	36	4
95°	87	82	24	32	32	106
105°	446	453	453	453	451	473
115°	838	846	847	841	832	831
125°	1192	1203	1203	1197	1192	1065
135°	1487	1496	1493	1490	1481	1146
145°	1724	1727	1727	1728	1719	1078
155°	1898	1889	1892	1897	1885	875
165°	2003	1994	1996	2005	1992	566
175°	2049	2040	2041	2053	2040	195
180°	2049	2049	2049	2049	2049	

TEST NUMBER: P983468

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.5	13.7	24.3	31.9	36.4
92.5°	28.9	15.2	24.3	31.9	33.4
95°	86.6	82.0	24.3	31.9	31.9
97.5°	162.5	171.6	27.3	30.4	31.9
100°	253.6	258.2	264.2	38.0	31.9
102.5°	346.2	352.3	355.4	358.4	230.8
105°	446.5	452.6	452.6	452.6	451.0
107.5°	549.7	549.7	552.8	554.3	548.2
110°	650.0	650.0	653.0	648.5	650.0

TEST NUMBER: P983468

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	744.1	748.7	750.2	744.1	741.1
115°	838.3	845.9	847.4	841.3	832.2
117.5°	937.0	937.0	943.1	934.0	930.9
120°	1028.1	1026.6	1031.1	1028.1	1020.5
122.5°	1108.6	1116.2	1117.7	1114.7	1105.6
125°	1192.1	1202.8	1202.8	1196.7	1192.1
127.5°	1272.6	1280.2	1278.7	1275.6	1263.5
130°	1345.5	1353.1	1354.6	1350.1	1342.5
132.5°	1418.4	1427.5	1423.0	1423.0	1415.4
135°	1486.7	1495.8	1492.8	1489.8	1480.7
137.5°	1550.5	1559.6	1556.6	1556.6	1549.0
140°	1612.8	1615.8	1614.3	1617.3	1608.2
142.5°	1669.0	1670.5	1673.5	1673.5	1664.4
145°	1723.6	1726.7	1726.7	1728.2	1719.1
147.5°	1772.2	1772.2	1773.8	1775.3	1764.6
150°	1817.8	1814.8	1817.8	1820.8	1808.7
152.5°	1861.8	1854.2	1857.3	1860.3	1849.7
155°	1898.3	1889.2	1892.2	1896.8	1884.6
157.5°	1927.1	1922.6	1922.6	1927.1	1915.0
160°	1957.5	1948.4	1949.9	1956.0	1943.8
162.5°	1981.8	1972.7	1974.2	1983.3	1969.7
165°	2003.1	1994.0	1995.5	2004.6	1992.4
167.5°	2019.8	2010.7	2012.2	2022.8	2009.1
170°	2033.4	2022.8	2024.3	2036.5	2022.8
172.5°	2042.6	2031.9	2035.0	2045.6	2031.9
175°	2048.6	2039.5	2041.0	2053.2	2039.5
177.5°	2053.2	2044.1	2045.6	2056.2	2044.1
180°	2048.6	2048.6	2048.6	2048.6	2048.6

(END OF REPORT)