

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983469

Luminaire Tested: S125IW-B1560UB2750-4F0-XX-W2A_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1560UB2750-4F0-XX-W2A_5000K
Description: Define 5 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6089.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983469

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P983469

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983469

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.9	0.0
90°-100°	67.2	1.1
100°-110°	447.2	7.3
110°-120°	805.2	13.2
120°-130°	1033.6	17.0
130°-140°	1111.6	18.3
140°-150°	1043.3	17.1
150°-160°	843.9	13.9
160°-170°	545.8	9.0
170°-180°	188.2	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.9	0.0
90°-120°	1319.6	21.7
90°-150°	4508.1	74.0
90°-180°	6086.0	100.0
0°-180°	6089.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	13	24	31	35	4
95°	84	79	24	31	31	103
105°	432	438	438	438	436	457
115°	811	818	820	814	805	804
125°	1153	1163	1163	1157	1153	1030
135°	1438	1447	1444	1441	1432	1109
145°	1667	1670	1670	1671	1663	1043
155°	1836	1827	1830	1834	1823	846
165°	1937	1928	1930	1939	1927	547
175°	1981	1972	1974	1986	1972	189
180°	1981	1981	1981	1981	1981	

TEST NUMBER: P983469

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.5	13.2	23.5	30.8	35.2
92.5°	27.9	14.7	23.5	30.8	32.3
95°	83.7	79.3	23.5	30.8	30.8
97.5°	157.2	166.0	26.4	29.4	30.8
100°	245.3	249.7	255.6	36.7	30.8
102.5°	334.9	340.7	343.7	346.6	223.2
105°	431.8	437.7	437.7	437.7	436.2
107.5°	531.7	531.7	534.6	536.1	530.2
110°	628.6	628.6	631.5	627.1	628.6

TEST NUMBER: P983469

CATALOG NUMBER: S125IW-B1560UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.7	724.1	725.5	719.7	716.7
115°	810.7	818.1	819.5	813.7	804.8
117.5°	906.2	906.2	912.1	903.3	900.3
120°	994.3	992.8	997.2	994.3	987.0
122.5°	1072.2	1079.5	1081.0	1078.0	1069.2
125°	1152.9	1163.2	1163.2	1157.3	1152.9
127.5°	1230.8	1238.1	1236.6	1233.7	1222.0
130°	1301.3	1308.6	1310.1	1305.7	1298.3
132.5°	1371.8	1380.6	1376.2	1376.2	1368.8
135°	1437.9	1446.7	1443.7	1440.8	1432.0
137.5°	1499.5	1508.4	1505.4	1505.4	1498.1
140°	1559.8	1562.7	1561.2	1564.2	1555.4
142.5°	1614.1	1615.6	1618.5	1618.5	1609.7
145°	1667.0	1669.9	1669.9	1671.4	1662.6
147.5°	1714.0	1714.0	1715.4	1716.9	1706.6
150°	1758.0	1755.1	1758.0	1761.0	1749.2
152.5°	1800.6	1793.3	1796.2	1799.2	1788.9
155°	1835.9	1827.1	1830.0	1834.4	1822.7
157.5°	1863.8	1859.4	1859.4	1863.8	1852.0
160°	1893.2	1884.3	1885.8	1891.7	1879.9
162.5°	1916.7	1907.8	1909.3	1918.1	1904.9
165°	1937.2	1928.4	1929.9	1938.7	1926.9
167.5°	1953.4	1944.6	1946.0	1956.3	1943.1
170°	1966.6	1956.3	1957.8	1969.5	1956.3
172.5°	1975.4	1965.1	1968.1	1978.3	1965.1
175°	1981.3	1972.5	1973.9	1985.7	1972.5
177.5°	1985.7	1976.9	1978.3	1988.6	1976.9
180°	1981.3	1981.3	1981.3	1981.3	1981.3

(END OF REPORT)