

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983484

Luminaire Tested: S125IW-B470UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983484
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B470UB2750-4F0-XX-W2A-1_5000K
Description: Define 5 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1581.0 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983484

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P983484

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983484

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.9	0.1
90°-100°	37.7	2.4
100°-110°	111.8	7.1
110°-120°	189.7	12.0
120°-130°	249.7	15.8
130°-140°	279.8	17.7
140°-150°	274.3	17.3
150°-160°	230.4	14.6
160°-170°	153.1	9.7
170°-180°	53.6	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.9	0.1
90°-120°	339.2	21.5
90°-150°	1143.0	72.3
90°-180°	1580.0	99.9
0°-180°	1581.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	7	9	11	2
95°	29	30	34	37	38	30
105°	100	103	105	108	109	107
115°	190	192	192	192	192	188
125°	277	280	280	279	279	248
135°	360	363	364	364	362	278
145°	437	438	440	440	438	273
155°	500	500	500	502	500	230
165°	543	542	543	545	542	153
175°	565	563	563	566	563	54
180°	566	566	566	566	566	

TEST NUMBER: P983484

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.4	4.0	7.0	9.3	10.6
92.5°	13.2	15.4	19.4	22.5	23.4
95°	28.6	29.5	33.9	37.0	37.9
97.5°	44.1	44.5	50.7	53.3	53.8
100°	61.7	61.7	67.4	71.4	72.3
102.5°	80.6	82.8	85.0	89.4	90.8
105°	100.5	102.7	105.3	107.9	109.3
107.5°	122.0	124.2	126.5	127.8	127.8
110°	144.5	146.7	148.0	149.4	148.9

TEST NUMBER: P983484

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	167.4	168.3	170.1	170.5	169.6
115°	189.9	191.7	192.5	192.1	191.7
117.5°	212.8	213.2	214.1	214.6	212.8
120°	234.0	236.2	236.6	236.6	234.8
122.5°	256.9	257.3	258.6	258.2	256.9
125°	277.1	279.8	280.2	279.3	278.9
127.5°	299.6	300.9	301.4	300.9	300.0
130°	319.4	321.6	322.5	322.1	321.2
132.5°	339.3	343.2	342.8	342.3	341.0
135°	360.4	363.1	363.5	363.5	361.7
137.5°	380.2	382.9	383.8	384.2	382.0
140°	399.2	401.4	402.7	403.6	401.4
142.5°	418.1	419.9	421.6	422.1	419.9
145°	436.6	438.4	439.7	439.7	438.4
147.5°	453.8	455.1	456.0	457.3	453.8
150°	471.0	470.6	472.3	472.3	471.4
152.5°	485.1	486.0	486.4	487.7	486.0
155°	499.6	499.6	500.1	501.8	499.6
157.5°	512.9	512.0	512.4	514.2	511.1
160°	524.3	523.0	523.4	525.2	523.0
162.5°	534.4	533.6	533.6	535.8	533.1
165°	543.3	542.4	542.8	544.6	541.9
167.5°	551.2	549.4	549.4	552.1	549.4
170°	557.4	555.6	555.6	558.2	555.1
172.5°	561.8	560.0	560.0	562.6	560.0
175°	564.8	563.1	563.1	565.7	562.6
177.5°	567.0	565.3	564.8	567.5	564.4
180°	566.2	566.2	566.2	566.2	566.2

(END OF REPORT)