

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035690

Luminaire Tested: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035690
REPORT IS A COMBINATION OF REPORTS P1005957 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8161.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	94	90	87	91	87	84	81	74	71	69	61	60	58	50	49	48	48	48	48	43
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	45	43	41	41	41	41	37
3	82	73	66	60	76	68	61	56	58	53	49	48	45	42	40	38	35	35	35	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	40	36	36	33	31	31	31	31	27
5	69	58	50	44	64	54	47	41	46	41	37	39	35	32	32	29	27	27	27	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24	24	24	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	21	21	21	19
8	55	43	35	30	51	40	33	28	34	29	25	29	25	22	25	22	19	19	19	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	17	17	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10070	10070	10070	10070
5°	10061	11349	10061	8723
10°	10005	12754	9972	7541
15°	9897	13493	9829	6566
20°	9766	14566	9678	5935
25°	9594	16487	9486	5386
30°	9420	17525	9279	4994
35°	9195	14412	9066	4628
40°	8795	9787	8721	4300
45°	8270	7036	8259	3976
50°	7732	5410	7769	3677
55°	7126	4400	7112	3389
60°	6561	3605	6529	3008
65°	5905	3005	5941	2422
70°	5360	2411	5338	2017
75°	4529	1827	4529	1658
80°	3671	1115	3629	1115
85°	2584	587	2510	664

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14334 cd/sqm

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	1.8
10°-20°	441.9	5.4
20°-30°	700.6	8.6
30°-40°	846.6	10.4
40°-50°	753.8	9.2
50°-60°	578.0	7.1
60°-70°	375.4	4.6
70°-80°	182.2	2.2
80°-90°	44.8	0.5
90°-100°	45.2	0.6
100°-110°	300.3	3.7
110°-120°	540.7	6.6
120°-130°	694.1	8.5
130°-140°	746.5	9.1
140°-150°	700.6	8.6
150°-160°	566.7	6.9
160°-170°	366.5	4.5
170°-180°	126.4	1.5
0°-30°	1293.2	15.8
0°-40°	2139.8	26.2
0°-60°	3471.6	42.5
0°-90°	4074.0	49.9
90°-120°	886.2	10.9
90°-150°	3027.4	37.1
90°-180°	4087.0	50.1
0°-180°	8161.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1572	1572	1572	1572	1572	
5°	1568	1801	1568	1385	1568	149
15°	1502	2164	1492	1053	1502	424
25°	1373	2591	1358	846	1373	633
35°	1196	2150	1179	690	1196	745
45°	936	961	934	543	936	722
55°	661	528	659	406	661	592
65°	410	299	413	241	410	410
75°	200	139	200	126	200	214
85°	45	30	44	34	45	51
90°	1	24	1	24	1	6
95°	56	21	56	21	56	69
105°	290	293	290	293	290	307
115°	544	540	544	540	544	540
125°	774	774	774	774	774	692
135°	966	962	966	962	966	744
145°	1119	1116	1119	1116	1119	700
155°	1233	1224	1233	1224	1233	568
165°	1301	1294	1301	1294	1301	367
175°	1330	1325	1330	1325	1330	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1573.0	1585.9	1589.8	1600.1	1611.7	1614.3	1620.8	1629.8	1634.9	1633.7	1633.7
5°	1567.8	1589.8	1605.3	1623.3	1645.3	1654.3	1662.0	1681.4	1696.9	1705.9	1721.4
7.5°	1558.8	1591.1	1616.9	1644.0	1677.5	1693.0	1709.8	1736.9	1765.3	1783.3	1800.1
10°	1544.6	1585.9	1622.0	1662.0	1707.2	1730.4	1751.1	1792.4	1827.2	1850.4	1889.2
12.5°	1524.0	1575.6	1625.9	1678.8	1735.6	1760.1	1788.5	1833.7	1882.7	1916.3	1948.5
15°	1502.0	1564.0	1618.2	1681.4	1749.8	1787.2	1823.3	1871.1	1915.0	1952.4	1989.8
17.5°	1476.2	1542.0	1609.1	1681.4	1758.8	1796.3	1827.2	1884.0	1930.5	1967.9	2001.4
20°	1445.3	1518.8	1594.9	1675.0	1753.7	1788.5	1818.2	1880.1	1921.4	1961.4	2009.2
22.5°	1411.7	1491.7	1573.0	1651.7	1729.1	1766.6	1801.4	1855.6	1900.8	1955.0	2016.9
25°	1373.0	1460.7	1543.3	1622.0	1695.6	1730.4	1761.4	1820.8	1884.0	1952.4	2022.1
27.5°	1334.3	1419.5	1499.5	1571.7	1651.7	1684.0	1715.0	1789.8	1864.6	1936.9	2032.4
30°	1291.7	1378.2	1447.8	1514.9	1592.4	1625.9	1664.6	1749.8	1835.0	1933.0	2049.2
32.5°	1244.0	1322.7	1387.2	1456.9	1526.6	1567.8	1616.9	1709.8	1807.9	1925.3	2073.7
35°	1196.2	1259.4	1318.8	1384.6	1468.5	1512.4	1560.1	1658.2	1780.8	1921.4	2094.3
37.5°	1135.6	1196.2	1242.7	1309.8	1396.2	1447.8	1495.6	1609.1	1748.5	1912.4	2093.0
40°	1073.6	1125.2	1169.1	1238.8	1333.0	1380.7	1432.4	1556.2	1715.0	1886.6	2062.1
42.5°	1006.5	1050.4	1098.1	1165.2	1256.9	1303.3	1362.7	1507.2	1668.5	1850.4	1982.1
45°	935.5	978.1	1018.1	1087.8	1179.4	1229.8	1294.3	1442.7	1611.7	1774.3	1853.0
47.5°	865.9	903.3	945.9	1006.5	1099.4	1154.9	1220.7	1379.4	1535.6	1672.4	1678.8
50°	798.8	828.4	864.6	926.5	1023.3	1076.2	1144.6	1293.0	1445.3	1539.5	1476.2
52.5°	729.1	756.2	793.6	847.8	938.1	1000.1	1059.4	1207.8	1335.6	1398.8	1282.7
55°	660.7	683.9	722.6	783.3	862.0	909.7	970.4	1108.5	1220.7	1222.0	1095.6
57.5°	593.6	614.2	646.5	700.7	774.2	829.7	885.2	1005.2	1081.4	1059.4	918.8
60°	534.2	547.1	576.8	629.7	698.1	738.1	797.5	898.1	948.5	908.4	757.5
62.5°	472.3	485.2	508.4	551.0	615.5	658.1	695.5	778.1	813.0	752.3	628.4
65°	410.4	425.8	442.6	476.2	536.8	565.2	598.8	659.4	692.9	622.0	514.9
67.5°	356.2	363.9	380.7	415.5	458.1	483.9	507.1	548.4	554.9	498.1	410.4
70°	305.8	308.4	323.9	344.5	376.8	392.3	411.6	436.2	436.2	389.7	320.0
72.5°	249.0	252.9	264.5	286.5	305.8	313.6	320.0	335.5	332.9	290.3	242.6
75°	200.0	202.6	211.6	222.0	229.7	243.9	249.0	246.5	245.2	209.0	181.9
77.5°	154.8	156.1	162.6	171.6	172.9	178.1	174.2	174.2	162.6	141.9	127.8
80°	113.6	114.8	117.4	120.0	120.0	120.0	120.0	113.6	105.8	92.9	89.0
82.5°	76.1	76.1	77.4	80.0	78.7	76.1	73.6	67.1	61.9	58.1	55.5
85°	45.2	45.2	46.5	45.2	40.0	38.7	36.1	34.8	33.6	32.3	32.3
87.5°	21.9	20.6	18.1	15.5	15.5	15.5	15.5	15.5	15.5	14.2	14.2
90°	1.0	2.8	4.5	6.3	8.0	8.9	9.7	11.2	12.7	14.3	15.8
92.5°	18.7	16.7	14.8	12.8	10.9	9.9	10.6	11.9	13.2	14.5	15.8
95°	56.2	55.6	54.9	54.3	53.6	53.3	49.1	40.8	32.5	24.1	15.8
97.5°	105.5	106.8	108.2	109.5	110.8	111.5	101.1	80.3	59.4	38.6	17.8
100°	164.7	165.4	166.0	166.7	167.4	167.7	168.1	169.0	169.9	170.7	171.6
102.5°	224.9	225.8	226.6	227.5	228.4	228.8	229.0	229.5	229.9	230.4	230.8
105°	290.0	290.9	291.7	292.6	293.5	293.9	293.9	293.9	293.9	293.9	293.9
107.5°	357.0	357.0	357.0	357.0	357.0	357.0	357.2	357.7	358.1	358.6	359.0
110°	422.1	422.1	422.1	422.1	422.1	422.1	422.3	422.8	423.2	423.7	424.1

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	483.3	483.9	484.6	485.2	485.9	486.2	486.3	486.5	486.8	487.0	487.2
115°	544.4	545.5	546.6	547.7	548.8	549.4	549.5	549.7	549.9	550.1	550.3
117.5°	608.5	608.5	608.5	608.5	608.5	608.5	608.9	609.8	610.7	611.6	612.5
120°	667.7	667.5	667.3	667.0	666.8	666.7	667.0	667.7	668.4	669.0	669.7
122.5°	720.0	721.1	722.2	723.3	724.4	724.9	725.0	725.2	725.5	725.7	725.9
125°	774.2	775.7	777.3	778.8	780.3	781.1	781.1	781.1	781.1	781.1	781.1
127.5°	826.5	827.6	828.7	829.8	830.9	831.4	831.3	831.1	830.9	830.7	830.5
130°	873.9	875.0	876.1	877.2	878.3	878.8	878.9	879.1	879.4	879.6	879.8
132.5°	921.2	922.5	923.8	925.1	926.4	927.1	926.8	926.1	925.5	924.8	924.2
135°	965.6	966.9	968.2	969.5	970.8	971.5	971.3	970.8	970.4	969.9	969.5
137.5°	1007.0	1008.3	1009.6	1010.9	1012.2	1012.9	1012.7	1012.2	1011.8	1011.3	1010.9
140°	1047.4	1047.8	1048.3	1048.7	1049.2	1049.4	1049.3	1049.1	1048.8	1048.6	1048.4
142.5°	1083.9	1084.1	1084.3	1084.6	1084.8	1084.9	1085.1	1085.6	1086.0	1086.5	1086.9
145°	1119.4	1119.8	1120.3	1120.7	1121.2	1121.4	1121.4	1121.4	1121.4	1121.4	1121.4
147.5°	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0	1151.1	1151.3	1151.6	1151.8	1152.0
150°	1180.6	1180.2	1179.7	1179.3	1178.8	1178.6	1178.8	1179.3	1179.7	1180.2	1180.6
152.5°	1209.2	1208.1	1207.0	1205.9	1204.8	1204.3	1204.5	1204.9	1205.4	1205.8	1206.2
155°	1232.9	1231.6	1230.2	1228.9	1227.6	1226.9	1227.1	1227.6	1228.0	1228.5	1228.9
157.5°	1251.6	1250.9	1250.3	1249.6	1248.9	1248.6	1248.6	1248.6	1248.6	1248.6	1248.6
160°	1271.3	1270.0	1268.7	1267.4	1266.1	1265.4	1265.5	1265.7	1266.0	1266.2	1266.4
162.5°	1287.1	1285.8	1284.5	1283.2	1281.9	1281.2	1281.3	1281.5	1281.8	1282.0	1282.2
165°	1300.9	1299.6	1298.3	1297.0	1295.7	1295.0	1295.1	1295.3	1295.6	1295.8	1296.0
167.5°	1311.8	1310.5	1309.1	1307.8	1306.5	1305.8	1305.9	1306.1	1306.4	1306.6	1306.8
170°	1320.6	1319.1	1317.5	1316.0	1314.5	1313.7	1313.8	1314.0	1314.3	1314.5	1314.7
172.5°	1326.6	1325.1	1323.5	1322.0	1320.5	1319.7	1319.9	1320.3	1320.8	1321.2	1321.6
175°	1330.5	1329.2	1327.9	1326.6	1325.3	1324.6	1324.7	1324.9	1325.2	1325.4	1325.6
177.5°	1333.5	1332.2	1330.8	1329.5	1328.2	1327.5	1327.6	1327.8	1328.1	1328.3	1328.5
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1640.1	1649.1	1656.9	1653.0	1668.5	1667.2	1669.8	1675.0	1676.2	1673.7	1668.5
5°	1729.1	1742.1	1764.0	1775.6	1773.0	1783.3	1788.5	1796.3	1804.0	1801.4	1801.4
7.5°	1828.5	1846.6	1868.5	1898.2	1902.1	1911.1	1926.6	1926.6	1935.6	1931.7	1930.5
10°	1915.0	1936.9	1971.7	1995.0	2005.3	2010.5	2025.9	2031.1	2041.4	2042.7	2042.7
12.5°	1985.9	2024.7	2047.9	2071.1	2076.3	2084.0	2095.6	2103.4	2107.2	2107.2	2103.4
15°	2023.4	2054.3	2081.4	2105.9	2120.1	2126.6	2138.2	2147.2	2152.4	2164.0	2166.6
17.5°	2038.8	2076.3	2120.1	2155.0	2179.5	2186.0	2209.2	2216.9	2227.2	2232.4	2238.9
20°	2060.8	2115.0	2167.9	2210.5	2233.7	2250.5	2275.0	2311.1	2321.4	2321.4	2317.6
22.5°	2080.1	2149.8	2222.1	2290.5	2309.8	2343.4	2388.5	2427.3	2442.7	2449.2	2444.0
25°	2103.4	2198.9	2293.1	2378.2	2431.1	2455.6	2516.3	2562.8	2580.8	2591.1	2593.7
27.5°	2143.4	2263.4	2383.4	2491.8	2546.0	2574.4	2637.6	2677.6	2699.5	2708.6	2702.1
30°	2188.5	2335.6	2475.0	2571.8	2607.9	2642.8	2684.1	2699.5	2694.4	2694.4	2713.7
32.5°	2235.0	2387.3	2511.1	2574.4	2587.3	2582.1	2565.3	2518.9	2491.8	2491.8	2508.6
35°	2260.8	2392.4	2455.6	2435.0	2384.7	2355.0	2263.4	2211.8	2153.7	2149.8	2169.2
37.5°	2246.6	2303.4	2277.6	2142.1	2073.7	2016.9	1873.7	1816.9	1774.3	1715.0	1806.6
40°	2147.2	2127.9	1993.7	1798.8	1722.7	1642.7	1529.1	1472.4	1413.0	1404.0	1425.9
42.5°	1979.5	1864.6	1668.5	1480.1	1402.7	1345.9	1259.4	1204.0	1166.5	1151.0	1176.9
45°	1770.4	1589.8	1393.6	1244.0	1158.8	1129.1	1050.4	1001.4	973.0	961.4	979.4
47.5°	1514.9	1333.0	1147.2	1020.7	970.4	940.7	887.8	845.2	820.7	813.0	820.7
50°	1286.5	1099.4	943.3	862.0	816.8	792.3	748.4	721.3	702.0	696.8	709.7
52.5°	1089.1	918.8	800.1	727.8	698.1	677.5	646.5	623.3	611.7	606.5	615.5
55°	912.3	774.2	678.8	616.8	594.9	582.0	554.9	542.0	529.1	527.8	536.8
57.5°	756.2	660.7	572.9	529.1	522.6	503.3	480.0	468.4	462.0	460.7	464.5
60°	629.7	544.6	491.6	452.9	443.9	428.4	415.5	407.8	400.0	397.4	400.0
62.5°	523.9	456.8	414.2	388.4	375.5	371.6	357.4	348.4	347.1	347.1	349.7
65°	432.3	375.5	348.4	327.8	318.7	314.9	304.5	298.1	299.4	299.4	300.7
67.5°	352.3	311.0	286.5	276.1	268.4	267.1	256.8	254.2	251.6	251.6	254.2
70°	280.0	254.2	236.1	231.0	229.7	220.7	216.8	215.5	211.6	212.9	212.9
72.5°	219.4	202.6	192.3	184.5	185.8	180.7	175.5	175.5	172.9	176.8	176.8
75°	162.6	154.8	147.1	144.5	147.1	144.5	140.7	139.4	140.7	139.4	139.4
77.5°	120.0	116.1	113.6	112.3	112.3	107.1	104.5	107.1	101.9	104.5	104.5
80°	83.9	78.7	77.4	74.8	76.1	72.3	73.6	71.0	71.0	71.0	71.0
82.5°	52.9	51.6	51.6	51.6	50.3	50.3	50.3	50.3	50.3	50.3	49.0
85°	32.3	31.0	31.0	31.0	29.7	29.7	29.7	29.7	29.7	29.7	29.7
87.5°	12.9	14.2	14.2	15.5	14.2	12.9	12.9	12.9	14.2	14.2	12.9
90°	16.9	18.0	19.1	20.2	20.7	21.0	21.7	22.4	23.0	23.7	23.0
92.5°	16.9	18.0	19.1	20.2	20.7	20.8	21.0	21.3	21.5	21.7	21.5
95°	16.9	18.0	19.1	20.2	20.7	20.7	20.7	20.7	20.7	20.7	20.7
97.5°	18.2	18.6	19.1	19.5	19.7	19.8	20.0	20.3	20.5	20.7	20.5
100°	139.0	106.3	73.7	41.0	24.7	24.3	23.4	22.5	21.6	20.7	21.6
102.5°	231.2	231.7	232.1	232.6	232.8	223.6	205.2	186.7	168.3	149.9	168.3
105°	293.9	293.9	293.9	293.9	293.9	293.8	293.6	293.3	293.1	292.9	293.1
107.5°	359.2	359.4	359.7	359.9	360.0	359.6	358.7	357.8	357.0	356.1	357.0
110°	423.4	422.8	422.1	421.4	421.1	421.2	421.4	421.7	421.9	422.1	421.9

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	486.3	485.5	484.6	483.7	483.3	483.1	482.6	482.2	481.7	481.3	481.7
115°	549.4	548.6	547.7	546.8	546.4	545.7	544.4	543.1	541.8	540.5	541.8
117.5°	611.2	609.9	608.6	607.3	606.6	606.4	605.9	605.5	605.0	604.6	605.0
120°	669.3	668.8	668.4	667.9	667.7	667.2	666.1	665.0	663.9	662.8	663.9
122.5°	725.5	725.0	724.6	724.1	723.9	723.2	721.9	720.6	719.3	718.0	719.3
125°	780.2	779.4	778.5	777.6	777.2	776.9	776.2	775.5	774.9	774.2	774.9
127.5°	830.1	829.6	829.2	828.7	828.5	827.6	825.9	824.1	822.4	820.6	822.4
130°	879.1	878.5	877.8	877.1	876.8	876.3	875.2	874.1	873.0	871.9	873.0
132.5°	924.2	924.2	924.2	924.2	924.2	923.6	922.5	921.4	920.3	919.2	920.3
135°	969.1	968.6	968.2	967.7	967.5	966.8	965.5	964.2	962.9	961.6	962.9
137.5°	1010.9	1010.9	1010.9	1010.9	1010.9	1010.4	1009.3	1008.2	1007.1	1006.0	1007.1
140°	1048.8	1049.3	1049.7	1050.2	1050.4	1049.7	1048.4	1047.1	1045.8	1044.5	1045.8
142.5°	1086.9	1086.9	1086.9	1086.9	1086.9	1086.2	1084.9	1083.6	1082.3	1081.0	1082.3
145°	1121.6	1121.8	1122.1	1122.3	1122.4	1121.7	1120.4	1119.1	1117.8	1116.5	1117.8
147.5°	1152.2	1152.4	1152.7	1152.9	1153.0	1152.2	1150.7	1149.2	1147.6	1146.1	1147.6
150°	1181.0	1181.5	1181.9	1182.4	1182.6	1181.7	1180.0	1178.2	1176.5	1174.7	1176.5
152.5°	1206.6	1207.1	1207.5	1208.0	1208.2	1207.4	1205.9	1204.4	1202.8	1201.3	1202.8
155°	1229.6	1230.2	1230.9	1231.6	1231.9	1231.0	1229.3	1227.5	1225.8	1224.0	1225.8
157.5°	1249.3	1249.9	1250.6	1251.3	1251.6	1250.7	1249.0	1247.2	1245.5	1243.7	1245.5
160°	1267.3	1268.1	1269.0	1269.9	1270.3	1269.4	1267.7	1265.9	1264.2	1262.4	1264.2
162.5°	1283.5	1284.8	1286.1	1287.4	1288.1	1287.1	1285.1	1283.2	1281.2	1279.2	1281.2
165°	1297.3	1298.6	1299.9	1301.2	1301.9	1301.0	1299.3	1297.5	1295.8	1294.0	1295.8
167.5°	1308.3	1309.9	1311.4	1312.9	1313.7	1312.7	1310.8	1308.8	1306.9	1304.9	1306.9
170°	1316.5	1318.2	1320.0	1321.7	1322.6	1321.6	1319.6	1317.7	1315.7	1313.7	1315.7
172.5°	1323.1	1324.7	1326.2	1327.7	1328.5	1327.5	1325.6	1323.6	1321.7	1319.7	1321.7
175°	1327.4	1329.1	1330.9	1332.6	1333.5	1332.5	1330.5	1328.6	1326.6	1324.6	1326.6
177.5°	1330.0	1331.6	1333.1	1334.6	1335.4	1334.5	1332.8	1331.0	1329.3	1327.5	1329.3
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1675.0	1665.9	1669.8	1665.9	1662.0	1658.2	1649.1	1636.2	1625.9	1618.2	1616.9
5°	1804.0	1792.4	1784.6	1780.8	1773.0	1762.7	1745.9	1726.6	1703.3	1694.3	1676.2
7.5°	1922.7	1918.8	1900.8	1898.2	1893.0	1873.7	1845.3	1819.5	1789.8	1765.3	1742.1
10°	2035.0	2025.9	2013.0	1995.0	1992.4	1967.9	1940.8	1904.6	1865.9	1842.7	1801.4
12.5°	2104.7	2094.3	2080.1	2068.5	2062.1	2046.6	2009.2	1973.0	1938.2	1895.6	1859.5
15°	2155.0	2142.1	2116.3	2107.2	2099.5	2078.8	2051.8	2014.3	1967.9	1938.2	1886.6
17.5°	2223.4	2207.9	2182.1	2165.3	2151.1	2118.9	2080.1	2029.8	1985.9	1952.4	1905.9
20°	2302.1	2278.9	2245.3	2223.4	2202.7	2165.3	2111.1	2051.8	1988.5	1947.2	1899.5
22.5°	2432.4	2388.5	2335.6	2304.7	2276.3	2211.8	2147.2	2073.7	2002.7	1940.8	1882.7
25°	2558.9	2515.0	2449.2	2406.6	2362.7	2287.9	2202.7	2100.8	2010.5	1938.2	1862.1
27.5°	2676.3	2631.1	2570.5	2518.9	2476.3	2364.0	2251.8	2136.9	2022.1	1922.7	1845.3
30°	2703.4	2684.1	2637.6	2592.4	2553.7	2450.5	2320.2	2174.3	2036.3	1908.5	1822.1
32.5°	2539.5	2587.3	2598.9	2592.4	2567.9	2494.4	2374.4	2220.8	2056.9	1902.1	1783.3
35°	2198.9	2285.3	2374.4	2422.1	2445.3	2455.6	2384.7	2244.0	2071.1	1891.7	1757.5
37.5°	1823.3	1907.2	2047.9	2118.9	2197.6	2300.8	2329.2	2238.9	2064.7	1884.0	1716.2
40°	1498.2	1605.3	1721.4	1785.9	1854.3	2040.1	2180.8	2170.5	2044.0	1855.6	1684.0
42.5°	1219.4	1286.5	1388.5	1459.5	1543.3	1751.1	1939.5	2032.4	1982.1	1820.8	1642.7
45°	1016.8	1068.5	1140.7	1213.0	1264.6	1453.0	1676.2	1828.5	1876.3	1758.8	1579.5
47.5°	856.8	895.5	958.8	1003.9	1059.4	1207.8	1401.4	1615.6	1716.2	1671.1	1512.4
50°	734.2	765.2	815.5	843.9	893.0	1020.7	1167.8	1392.4	1544.6	1549.8	1423.3
52.5°	627.1	658.1	700.7	725.2	754.9	841.3	989.7	1179.4	1354.9	1419.5	1321.4
55°	545.8	563.9	598.8	618.1	645.2	729.1	823.3	984.6	1167.8	1273.6	1211.7
57.5°	471.0	490.4	512.3	527.8	547.1	614.2	699.4	820.7	1002.6	1117.5	1096.8
60°	410.4	422.0	442.6	454.2	472.3	516.2	575.5	696.8	841.3	949.7	961.4
62.5°	353.6	363.9	378.1	388.4	400.0	434.9	478.7	565.2	691.7	809.1	824.6
65°	304.5	313.6	321.3	330.3	339.4	361.3	398.7	465.8	563.9	673.6	707.1
67.5°	260.7	263.2	274.9	276.1	281.3	298.1	325.2	379.4	450.4	538.1	582.0
70°	218.1	223.2	225.8	229.7	234.9	246.5	268.4	296.8	349.7	420.7	462.0
72.5°	176.8	178.1	181.9	184.5	189.7	198.7	209.0	231.0	264.5	316.2	353.6
75°	140.7	141.9	144.5	145.8	149.7	152.3	157.4	172.9	196.1	227.1	254.2
77.5°	105.8	108.4	111.0	111.0	112.3	114.8	117.4	122.6	134.2	154.8	178.1
80°	72.3	73.6	73.6	74.8	73.6	77.4	81.3	87.7	92.9	99.4	111.0
82.5°	50.3	50.3	50.3	51.6	51.6	52.9	52.9	54.2	55.5	59.4	64.5
85°	31.0	31.0	32.3	29.7	31.0	32.3	32.3	31.0	32.3	33.6	34.8
87.5°	12.9	12.9	14.2	14.2	14.2	14.2	12.9	14.2	12.9	14.2	14.2
90°	22.4	21.7	21.0	20.7	20.2	19.1	18.0	16.9	15.8	14.3	12.7
92.5°	21.3	21.0	20.8	20.7	20.2	19.1	18.0	16.9	15.8	14.5	13.2
95°	20.7	20.7	20.7	20.7	20.2	19.1	18.0	16.9	15.8	24.1	32.5
97.5°	20.3	20.0	19.8	19.7	19.5	19.1	18.6	18.2	17.8	38.6	59.4
100°	22.5	23.4	24.3	24.7	41.0	73.7	106.3	139.0	171.6	170.7	169.9
102.5°	186.7	205.2	223.6	232.8	232.6	232.1	231.7	231.2	230.8	230.4	229.9
105°	293.3	293.6	293.8	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9
107.5°	357.8	358.7	359.6	360.0	359.9	359.7	359.4	359.2	359.0	358.6	358.1
110°	421.7	421.4	421.2	421.1	421.4	422.1	422.8	423.4	424.1	423.7	423.2

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	482.2	482.6	483.1	483.3	483.7	484.6	485.5	486.3	487.2	487.0	486.8
115°	543.1	544.4	545.7	546.4	546.8	547.7	548.6	549.4	550.3	550.1	549.9
117.5°	605.5	605.9	606.4	606.6	607.3	608.6	609.9	611.2	612.5	611.6	610.7
120°	665.0	666.1	667.2	667.7	667.9	668.4	668.8	669.3	669.7	669.0	668.4
122.5°	720.6	721.9	723.2	723.9	724.1	724.6	725.0	725.5	725.9	725.7	725.5
125°	775.5	776.2	776.9	777.2	777.6	778.5	779.4	780.2	781.1	781.1	781.1
127.5°	824.1	825.9	827.6	828.5	828.7	829.2	829.6	830.1	830.5	830.7	830.9
130°	874.1	875.2	876.3	876.8	877.1	877.8	878.5	879.1	879.8	879.6	879.4
132.5°	921.4	922.5	923.6	924.2	924.2	924.2	924.2	924.2	924.2	924.8	925.5
135°	964.2	965.5	966.8	967.5	967.7	968.2	968.6	969.1	969.5	969.9	970.4
137.5°	1008.2	1009.3	1010.4	1010.9	1010.9	1010.9	1010.9	1010.9	1010.9	1011.3	1011.8
140°	1047.1	1048.4	1049.7	1050.4	1050.2	1049.7	1049.3	1048.8	1048.4	1048.6	1048.8
142.5°	1083.6	1084.9	1086.2	1086.9	1086.9	1086.9	1086.9	1086.9	1086.9	1086.5	1086.0
145°	1119.1	1120.4	1121.7	1122.4	1122.3	1122.1	1121.8	1121.6	1121.4	1121.4	1121.4
147.5°	1149.2	1150.7	1152.2	1153.0	1152.9	1152.7	1152.4	1152.2	1152.0	1151.8	1151.6
150°	1178.2	1180.0	1181.7	1182.6	1182.4	1181.9	1181.5	1181.0	1180.6	1180.2	1179.7
152.5°	1204.4	1205.9	1207.4	1208.2	1208.0	1207.5	1207.1	1206.6	1206.2	1205.8	1205.4
155°	1227.5	1229.3	1231.0	1231.9	1231.6	1230.9	1230.2	1229.6	1228.9	1228.5	1228.0
157.5°	1247.2	1249.0	1250.7	1251.6	1251.3	1250.6	1249.9	1249.3	1248.6	1248.6	1248.6
160°	1265.9	1267.7	1269.4	1270.3	1269.9	1269.0	1268.1	1267.3	1266.4	1266.2	1266.0
162.5°	1283.2	1285.1	1287.1	1288.1	1287.4	1286.1	1284.8	1283.5	1282.2	1282.0	1281.8
165°	1297.5	1299.3	1301.0	1301.9	1301.2	1299.9	1298.6	1297.3	1296.0	1295.8	1295.6
167.5°	1308.8	1310.8	1312.7	1313.7	1312.9	1311.4	1309.9	1308.3	1306.8	1306.6	1306.4
170°	1317.7	1319.6	1321.6	1322.6	1321.7	1320.0	1318.2	1316.5	1314.7	1314.5	1314.3
172.5°	1323.6	1325.6	1327.5	1328.5	1327.7	1326.2	1324.7	1323.1	1321.6	1321.2	1320.8
175°	1328.6	1330.5	1332.5	1333.5	1332.6	1330.9	1329.1	1327.4	1325.6	1325.4	1325.2
177.5°	1331.0	1332.8	1334.5	1335.4	1334.6	1333.1	1331.6	1330.0	1328.5	1328.3	1328.1
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1613.0	1605.3	1600.1	1598.8	1591.1	1584.6	1576.9	1575.6	1571.7	1561.4	1554.9
5°	1663.3	1645.3	1641.4	1629.8	1610.4	1596.2	1578.2	1567.8	1556.2	1536.9	1521.4
7.5°	1715.0	1690.4	1672.4	1655.6	1628.5	1602.7	1576.9	1556.2	1535.6	1507.2	1484.0
10°	1765.3	1727.9	1705.9	1681.4	1644.0	1605.3	1569.1	1539.5	1505.9	1472.4	1438.8
12.5°	1811.7	1764.0	1731.7	1696.9	1650.4	1602.7	1556.2	1514.9	1480.1	1434.9	1397.5
15°	1840.1	1787.2	1755.0	1721.4	1651.7	1598.8	1544.6	1491.7	1445.3	1397.5	1362.7
17.5°	1856.9	1797.5	1761.4	1730.4	1659.5	1587.2	1517.5	1460.7	1410.4	1353.6	1307.2
20°	1849.2	1791.1	1757.5	1727.9	1645.3	1573.0	1498.2	1432.4	1369.1	1311.1	1262.0
22.5°	1832.4	1771.7	1734.3	1707.2	1633.7	1548.5	1465.9	1394.9	1329.1	1271.1	1215.6
25°	1796.3	1736.9	1704.6	1671.1	1598.8	1517.5	1433.6	1357.5	1287.8	1225.9	1163.9
27.5°	1764.0	1691.7	1658.2	1628.5	1552.4	1480.1	1397.5	1313.6	1242.7	1178.1	1116.2
30°	1726.6	1645.3	1609.1	1569.1	1500.7	1432.4	1349.8	1272.3	1198.8	1130.4	1071.0
32.5°	1686.6	1592.4	1551.1	1505.9	1436.2	1371.7	1302.0	1225.9	1152.3	1085.2	1023.3
35°	1634.9	1534.3	1486.6	1444.0	1371.7	1307.2	1242.7	1179.4	1105.9	1034.9	975.5
37.5°	1585.9	1474.9	1424.6	1375.6	1299.4	1237.5	1184.6	1125.2	1054.3	985.9	929.1
40°	1530.4	1402.7	1351.1	1305.9	1227.2	1158.8	1111.0	1064.6	1002.6	936.8	874.9
42.5°	1480.1	1335.6	1281.4	1234.9	1152.3	1087.8	1042.7	1003.9	949.7	889.1	825.9
45°	1410.4	1263.3	1207.8	1158.8	1074.9	1014.3	967.8	934.3	891.7	834.9	778.1
47.5°	1345.9	1193.6	1133.0	1073.6	997.5	935.5	893.0	867.2	838.8	788.4	730.4
50°	1267.2	1113.6	1051.7	1002.6	916.2	863.3	820.7	802.6	776.8	729.1	682.6
52.5°	1182.0	1036.2	978.1	918.8	838.8	787.1	749.7	729.1	708.4	673.6	629.7
55°	1082.7	949.7	895.5	842.6	762.6	714.9	681.3	659.4	647.8	615.5	583.3
57.5°	987.2	862.0	811.7	762.6	692.9	638.8	616.8	597.5	580.7	557.5	530.4
60°	890.4	776.8	722.6	678.8	618.1	569.1	551.0	531.6	518.7	500.7	481.3
62.5°	779.4	682.6	641.3	600.0	548.4	509.7	489.1	473.6	456.8	445.2	428.4
65°	662.0	593.6	553.6	522.6	473.6	438.7	423.3	412.9	398.7	387.1	374.2
67.5°	552.3	498.1	481.3	447.8	410.4	379.4	367.8	354.9	343.2	336.8	325.2
70°	446.5	407.8	391.0	382.0	340.7	320.0	309.7	304.5	290.3	283.9	276.1
72.5°	345.8	331.6	320.0	308.4	281.3	268.4	256.8	251.6	241.3	236.1	233.6
75°	255.5	246.5	240.0	238.7	227.1	214.2	202.6	200.0	192.3	187.1	184.5
77.5°	179.4	176.8	175.5	176.8	169.0	161.3	158.7	156.1	147.1	145.8	145.8
80°	117.4	123.9	123.9	122.6	120.0	118.7	114.8	112.3	107.1	105.8	107.1
82.5°	72.3	76.1	77.4	80.0	78.7	77.4	74.8	73.6	74.8	72.3	73.6
85°	36.1	38.7	43.9	43.9	45.2	45.2	45.2	43.9	41.3	42.6	41.3
87.5°	14.2	15.5	15.5	15.5	14.2	18.1	19.4	19.4	19.4	16.8	16.8
90°	11.2	9.7	8.9	8.0	6.3	4.5	2.8	1.0	2.8	4.5	6.3
92.5°	11.9	10.6	9.9	10.9	12.8	14.8	16.7	18.7	16.7	14.8	12.8
95°	40.8	49.1	53.3	53.6	54.3	54.9	55.6	56.2	55.6	54.9	54.3
97.5°	80.3	101.1	111.5	110.8	109.5	108.2	106.8	105.5	106.8	108.2	109.5
100°	169.0	168.1	167.7	167.4	166.7	166.0	165.4	164.7	165.4	166.0	166.7
102.5°	229.5	229.0	228.8	228.4	227.5	226.6	225.8	224.9	225.8	226.6	227.5
105°	293.9	293.9	293.9	293.5	292.6	291.7	290.9	290.0	290.9	291.7	292.6
107.5°	357.7	357.2	357.0	357.0	357.0	357.0	357.0	357.0	357.0	357.0	357.0
110°	422.8	422.3	422.1	422.1	422.1	422.1	422.1	422.1	422.1	422.1	422.1

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	486.5	486.3	486.2	485.9	485.2	484.6	483.9	483.3	483.9	484.6	485.2
115°	549.7	549.5	549.4	548.8	547.7	546.6	545.5	544.4	545.5	546.6	547.7
117.5°	609.8	608.9	608.5	608.5	608.5	608.5	608.5	608.5	608.5	608.5	608.5
120°	667.7	667.0	666.7	666.8	667.0	667.3	667.5	667.7	667.5	667.3	667.0
122.5°	725.2	725.0	724.9	724.4	723.3	722.2	721.1	720.0	721.1	722.2	723.3
125°	781.1	781.1	781.1	780.3	778.8	777.3	775.7	774.2	775.7	777.3	778.8
127.5°	831.1	831.3	831.4	830.9	829.8	828.7	827.6	826.5	827.6	828.7	829.8
130°	879.1	878.9	878.8	878.3	877.2	876.1	875.0	873.9	875.0	876.1	877.2
132.5°	926.1	926.8	927.1	926.4	925.1	923.8	922.5	921.2	922.5	923.8	925.1
135°	970.8	971.3	971.5	970.8	969.5	968.2	966.9	965.6	966.9	968.2	969.5
137.5°	1012.2	1012.7	1012.9	1012.2	1010.9	1009.6	1008.3	1007.0	1008.3	1009.6	1010.9
140°	1049.1	1049.3	1049.4	1049.2	1048.7	1048.3	1047.8	1047.4	1047.8	1048.3	1048.7
142.5°	1085.6	1085.1	1084.9	1084.8	1084.6	1084.3	1084.1	1083.9	1084.1	1084.3	1084.6
145°	1121.4	1121.4	1121.4	1121.2	1120.7	1120.3	1119.8	1119.4	1119.8	1120.3	1120.7
147.5°	1151.3	1151.1	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0	1151.0
150°	1179.3	1178.8	1178.6	1178.8	1179.3	1179.7	1180.2	1180.6	1180.2	1179.7	1179.3
152.5°	1204.9	1204.5	1204.3	1204.8	1205.9	1207.0	1208.1	1209.2	1208.1	1207.0	1205.9
155°	1227.6	1227.1	1226.9	1227.6	1228.9	1230.2	1231.6	1232.9	1231.6	1230.2	1228.9
157.5°	1248.6	1248.6	1248.6	1248.9	1249.6	1250.3	1250.9	1251.6	1250.9	1250.3	1249.6
160°	1265.7	1265.5	1265.4	1266.1	1267.4	1268.7	1270.0	1271.3	1270.0	1268.7	1267.4
162.5°	1281.5	1281.3	1281.2	1281.9	1283.2	1284.5	1285.8	1287.1	1285.8	1284.5	1283.2
165°	1295.3	1295.1	1295.0	1295.7	1297.0	1298.3	1299.6	1300.9	1299.6	1298.3	1297.0
167.5°	1306.1	1305.9	1305.8	1306.5	1307.8	1309.1	1310.5	1311.8	1310.5	1309.1	1307.8
170°	1314.0	1313.8	1313.7	1314.5	1316.0	1317.5	1319.1	1320.6	1319.1	1317.5	1316.0
172.5°	1320.3	1319.9	1319.7	1320.5	1322.0	1323.5	1325.1	1326.6	1325.1	1323.5	1322.0
175°	1324.9	1324.7	1324.6	1325.3	1326.6	1327.9	1329.2	1330.5	1329.2	1327.9	1326.6
177.5°	1327.8	1327.6	1327.5	1328.2	1329.5	1330.8	1332.2	1333.5	1332.2	1330.8	1329.5
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1551.1	1545.9	1542.0	1538.2	1521.4	1503.3	1500.7	1496.9	1489.1	1498.2	1494.3
5°	1511.1	1499.5	1493.0	1476.2	1455.6	1440.1	1427.2	1411.7	1405.3	1400.1	1398.8
7.5°	1462.0	1451.7	1440.1	1423.3	1397.5	1371.7	1352.3	1336.9	1324.0	1317.5	1317.5
10°	1414.3	1401.4	1385.9	1357.5	1333.0	1300.7	1280.1	1264.6	1246.5	1236.2	1227.2
12.5°	1365.3	1351.1	1336.9	1300.7	1272.3	1238.8	1209.1	1189.8	1180.7	1169.1	1153.6
15°	1316.2	1294.3	1280.1	1244.0	1207.8	1174.3	1154.9	1134.3	1113.6	1102.0	1096.8
17.5°	1264.6	1249.1	1225.9	1187.2	1147.2	1117.5	1089.1	1069.7	1045.2	1033.6	1022.0
20°	1218.1	1194.9	1171.7	1133.0	1094.3	1054.3	1025.9	1002.6	987.2	978.1	967.8
22.5°	1162.7	1140.7	1121.4	1080.1	1037.5	1000.1	969.1	954.9	939.4	925.2	914.9
25°	1114.9	1093.0	1073.6	1028.5	982.0	947.2	923.9	905.9	889.1	882.6	872.3
27.5°	1064.6	1043.9	1018.1	973.0	931.7	902.0	877.5	860.7	847.8	834.9	827.2
30°	1016.8	993.6	970.4	921.4	887.8	858.1	834.9	814.2	803.9	797.5	784.6
32.5°	970.4	940.7	921.4	876.2	843.9	815.5	796.2	778.1	765.2	753.6	743.3
35°	920.1	887.8	868.4	831.0	797.5	769.1	752.3	739.4	723.9	713.6	708.4
37.5°	872.3	845.2	825.9	787.1	753.6	730.4	712.3	695.5	689.1	674.9	672.3
40°	820.7	797.5	779.4	742.0	711.0	692.9	673.6	658.1	646.5	640.0	631.0
42.5°	774.2	754.9	735.5	700.7	671.0	649.1	634.9	620.7	610.4	600.0	593.6
45°	731.7	711.0	692.9	659.4	629.7	610.4	596.2	579.4	576.8	562.6	556.2
47.5°	686.5	668.4	652.9	618.1	591.0	571.7	554.9	543.3	531.6	526.5	517.5
50°	642.6	624.6	606.5	575.5	551.0	531.6	514.9	502.0	495.5	487.8	480.0
52.5°	594.9	580.7	566.5	534.2	509.7	492.9	478.7	462.0	455.5	449.1	443.9
55°	554.9	534.2	518.7	491.6	469.7	451.6	436.2	423.3	416.8	411.6	405.2
57.5°	500.7	487.8	474.9	450.4	429.7	411.6	396.2	385.8	378.1	374.2	375.5
60°	454.2	440.0	432.3	406.5	385.8	371.6	357.4	347.1	339.4	335.5	334.2
62.5°	405.2	394.9	380.7	362.6	342.0	329.1	318.7	311.0	298.1	296.8	292.9
65°	357.4	349.7	336.8	320.0	303.2	291.6	280.0	269.7	264.5	258.1	254.2
67.5°	311.0	303.2	291.6	277.4	265.8	254.2	243.9	233.6	224.5	219.4	216.8
70°	265.8	259.4	251.6	234.9	220.7	211.6	203.9	197.4	188.4	185.8	184.5
72.5°	222.0	215.5	211.6	197.4	184.5	176.8	169.0	162.6	158.7	157.4	153.6
75°	181.9	175.5	170.3	157.4	149.7	144.5	136.8	134.2	130.3	129.0	127.8
77.5°	141.9	135.5	134.2	125.2	116.1	113.6	111.0	105.8	105.8	105.8	103.2
80°	101.9	100.7	99.4	90.3	86.5	83.9	82.6	78.7	76.1	73.6	72.3
82.5°	68.4	67.1	65.8	61.9	58.1	56.8	55.5	52.9	52.9	54.2	51.6
85°	41.3	38.7	37.4	36.1	33.6	33.6	34.8	33.6	33.6	33.6	32.3
87.5°	15.5	15.5	15.5	15.5	16.8	14.2	15.5	15.5	14.2	14.2	12.9
90°	8.0	8.9	9.7	11.2	12.7	14.3	15.8	16.9	18.0	19.1	20.2
92.5°	10.9	9.9	10.6	11.9	13.2	14.5	15.8	16.9	18.0	19.1	20.2
95°	53.6	53.3	49.1	40.8	32.5	24.1	15.8	16.9	18.0	19.1	20.2
97.5°	110.8	111.5	101.1	80.3	59.4	38.6	17.8	18.2	18.6	19.1	19.5
100°	167.4	167.7	168.1	169.0	169.9	170.7	171.6	139.0	106.3	73.7	41.0
102.5°	228.4	228.8	229.0	229.5	229.9	230.4	230.8	231.2	231.7	232.1	232.6
105°	293.5	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9
107.5°	357.0	357.0	357.2	357.7	358.1	358.6	359.0	359.2	359.4	359.7	359.9
110°	422.1	422.1	422.3	422.8	423.2	423.7	424.1	423.4	422.8	422.1	421.4

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	485.9	486.2	486.3	486.5	486.8	487.0	487.2	486.3	485.5	484.6	483.7
115°	548.8	549.4	549.5	549.7	549.9	550.1	550.3	549.4	548.6	547.7	546.8
117.5°	608.5	608.5	608.9	609.8	610.7	611.6	612.5	611.2	609.9	608.6	607.3
120°	666.8	666.7	667.0	667.7	668.4	669.0	669.7	669.3	668.8	668.4	667.9
122.5°	724.4	724.9	725.0	725.2	725.5	725.7	725.9	725.5	725.0	724.6	724.1
125°	780.3	781.1	781.1	781.1	781.1	781.1	781.1	780.2	779.4	778.5	777.6
127.5°	830.9	831.4	831.3	831.1	830.9	830.7	830.5	830.1	829.6	829.2	828.7
130°	878.3	878.8	878.9	879.1	879.4	879.6	879.8	879.1	878.5	877.8	877.1
132.5°	926.4	927.1	926.8	926.1	925.5	924.8	924.2	924.2	924.2	924.2	924.2
135°	970.8	971.5	971.3	970.8	970.4	969.9	969.5	969.1	968.6	968.2	967.7
137.5°	1012.2	1012.9	1012.7	1012.2	1011.8	1011.3	1010.9	1010.9	1010.9	1010.9	1010.9
140°	1049.2	1049.4	1049.3	1049.1	1048.8	1048.6	1048.4	1048.8	1049.3	1049.7	1050.2
142.5°	1084.8	1084.9	1085.1	1085.6	1086.0	1086.5	1086.9	1086.9	1086.9	1086.9	1086.9
145°	1121.2	1121.4	1121.4	1121.4	1121.4	1121.4	1121.4	1121.6	1121.8	1122.1	1122.3
147.5°	1151.0	1151.0	1151.1	1151.3	1151.6	1151.8	1152.0	1152.2	1152.4	1152.7	1152.9
150°	1178.8	1178.6	1178.8	1179.3	1179.7	1180.2	1180.6	1181.0	1181.5	1181.9	1182.4
152.5°	1204.8	1204.3	1204.5	1204.9	1205.4	1205.8	1206.2	1206.6	1207.1	1207.5	1208.0
155°	1227.6	1226.9	1227.1	1227.6	1228.0	1228.5	1228.9	1229.6	1230.2	1230.9	1231.6
157.5°	1248.9	1248.6	1248.6	1248.6	1248.6	1248.6	1248.6	1249.3	1249.9	1250.6	1251.3
160°	1266.1	1265.4	1265.5	1265.7	1266.0	1266.2	1266.4	1267.3	1268.1	1269.0	1269.9
162.5°	1281.9	1281.2	1281.3	1281.5	1281.8	1282.0	1282.2	1283.5	1284.8	1286.1	1287.4
165°	1295.7	1295.0	1295.1	1295.3	1295.6	1295.8	1296.0	1297.3	1298.6	1299.9	1301.2
167.5°	1306.5	1305.8	1305.9	1306.1	1306.4	1306.6	1306.8	1308.3	1309.9	1311.4	1312.9
170°	1314.5	1313.7	1313.8	1314.0	1314.3	1314.5	1314.7	1316.5	1318.2	1320.0	1321.7
172.5°	1320.5	1319.7	1319.9	1320.3	1320.8	1321.2	1321.6	1323.1	1324.7	1326.2	1327.7
175°	1325.3	1324.6	1324.7	1324.9	1325.2	1325.4	1325.6	1327.4	1329.1	1330.9	1332.6
177.5°	1328.2	1327.5	1327.6	1327.8	1328.1	1328.3	1328.5	1330.0	1331.6	1333.1	1334.6
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1487.8	1490.4	1484.0	1481.4	1476.2	1482.7	1484.0	1482.7	1494.3	1489.1	1491.7
5°	1401.4	1396.2	1392.4	1383.3	1383.3	1384.6	1388.5	1382.0	1385.9	1394.9	1393.6
7.5°	1305.9	1303.3	1304.6	1294.3	1286.5	1289.1	1286.5	1298.2	1304.6	1302.0	1307.2
10°	1219.4	1224.6	1213.0	1207.8	1202.7	1207.8	1206.5	1209.1	1216.9	1222.0	1231.1
12.5°	1149.8	1148.5	1142.0	1136.9	1127.8	1130.4	1138.1	1135.6	1136.9	1148.5	1147.2
15°	1083.9	1076.2	1071.0	1059.4	1062.0	1053.0	1060.7	1069.7	1073.6	1083.9	1090.4
17.5°	1018.1	1016.8	1010.4	1009.1	994.9	991.0	998.8	1001.4	1005.2	1010.4	1019.4
20°	962.6	961.4	952.3	949.7	938.1	945.9	943.3	948.5	951.0	961.4	965.2
22.5°	912.3	905.9	903.3	899.4	895.5	894.3	899.4	898.1	907.2	911.0	912.3
25°	865.9	860.7	859.4	853.0	850.4	846.5	850.4	854.3	864.6	868.4	873.6
27.5°	823.3	819.4	816.8	811.7	807.8	807.8	810.4	815.5	819.4	822.0	824.6
30°	784.6	782.0	774.2	771.7	767.8	767.8	767.8	770.4	776.8	784.6	788.4
32.5°	744.6	739.4	734.2	734.2	730.4	730.4	731.7	734.2	740.7	742.0	748.4
35°	705.9	700.7	696.8	694.2	695.5	690.4	692.9	696.8	704.6	707.1	711.0
37.5°	668.4	667.1	659.4	655.5	658.1	658.1	656.8	659.4	664.6	669.7	672.3
40°	627.1	624.6	624.6	620.7	622.0	616.8	620.7	623.3	625.8	631.0	634.9
42.5°	591.0	588.4	583.3	584.6	580.7	580.7	583.3	584.6	588.4	594.9	597.5
45°	552.3	552.3	549.7	545.8	547.1	543.3	545.8	547.1	552.3	558.7	556.2
47.5°	514.9	513.6	513.6	508.4	511.0	507.1	511.0	512.3	514.9	518.7	517.5
50°	478.7	474.9	476.2	474.9	473.6	473.6	476.2	476.2	478.7	478.7	482.6
52.5°	441.3	441.3	438.7	440.0	442.6	440.0	443.9	440.0	442.6	443.9	446.5
55°	407.8	405.2	406.5	405.2	410.4	406.5	410.4	407.8	410.4	409.1	411.6
57.5°	371.6	367.8	369.1	367.8	371.6	370.3	374.2	370.3	371.6	372.9	376.8
60°	330.3	330.3	330.3	327.8	331.6	331.6	330.3	330.3	335.5	338.1	336.8
62.5°	291.6	290.3	286.5	285.2	286.5	283.9	289.1	287.8	290.3	292.9	295.5
65°	249.0	246.5	245.2	242.6	242.6	241.3	242.6	247.8	249.0	250.3	256.8
67.5°	214.2	212.9	211.6	207.8	207.8	210.3	210.3	210.3	218.1	214.2	219.4
70°	183.2	180.7	178.1	176.8	176.8	178.1	179.4	180.7	179.4	184.5	185.8
72.5°	153.6	154.8	152.3	152.3	152.3	151.0	151.0	153.6	154.8	153.6	154.8
75°	127.8	127.8	126.5	127.8	127.8	126.5	126.5	129.0	129.0	127.8	131.6
77.5°	103.2	101.9	99.4	96.8	98.1	96.8	98.1	96.8	100.7	104.5	101.9
80°	72.3	71.0	71.0	71.0	72.3	71.0	73.6	71.0	72.3	72.3	73.6
82.5°	51.6	52.9	52.9	51.6	52.9	51.6	52.9	52.9	52.9	51.6	52.9
85°	33.6	33.6	33.6	33.6	32.3	33.6	33.6	33.6	34.8	33.6	34.8
87.5°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	15.5	14.2	15.5
90°	20.7	21.0	21.7	22.4	23.0	23.7	23.0	22.4	21.7	21.0	20.7
92.5°	20.7	20.8	21.0	21.3	21.5	21.7	21.5	21.3	21.0	20.8	20.7
95°	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
97.5°	19.7	19.8	20.0	20.3	20.5	20.7	20.5	20.3	20.0	19.8	19.7
100°	24.7	24.3	23.4	22.5	21.6	20.7	21.6	22.5	23.4	24.3	24.7
102.5°	232.8	223.6	205.2	186.7	168.3	149.9	168.3	186.7	205.2	223.6	232.8
105°	293.9	293.8	293.6	293.3	293.1	292.9	293.1	293.3	293.6	293.8	293.9
107.5°	360.0	359.6	358.7	357.8	357.0	356.1	357.0	357.8	358.7	359.6	360.0
110°	421.1	421.2	421.4	421.7	421.9	422.1	421.9	421.7	421.4	421.2	421.1

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	483.3	483.1	482.6	482.2	481.7	481.3	481.7	482.2	482.6	483.1	483.3
115°	546.4	545.7	544.4	543.1	541.8	540.5	541.8	543.1	544.4	545.7	546.4
117.5°	606.6	606.4	605.9	605.5	605.0	604.6	605.0	605.5	605.9	606.4	606.6
120°	667.7	667.2	666.1	665.0	663.9	662.8	663.9	665.0	666.1	667.2	667.7
122.5°	723.9	723.2	721.9	720.6	719.3	718.0	719.3	720.6	721.9	723.2	723.9
125°	777.2	776.9	776.2	775.5	774.9	774.2	774.9	775.5	776.2	776.9	777.2
127.5°	828.5	827.6	825.9	824.1	822.4	820.6	822.4	824.1	825.9	827.6	828.5
130°	876.8	876.3	875.2	874.1	873.0	871.9	873.0	874.1	875.2	876.3	876.8
132.5°	924.2	923.6	922.5	921.4	920.3	919.2	920.3	921.4	922.5	923.6	924.2
135°	967.5	966.8	965.5	964.2	962.9	961.6	962.9	964.2	965.5	966.8	967.5
137.5°	1010.9	1010.4	1009.3	1008.2	1007.1	1006.0	1007.1	1008.2	1009.3	1010.4	1010.9
140°	1050.4	1049.7	1048.4	1047.1	1045.8	1044.5	1045.8	1047.1	1048.4	1049.7	1050.4
142.5°	1086.9	1086.2	1084.9	1083.6	1082.3	1081.0	1082.3	1083.6	1084.9	1086.2	1086.9
145°	1122.4	1121.7	1120.4	1119.1	1117.8	1116.5	1117.8	1119.1	1120.4	1121.7	1122.4
147.5°	1153.0	1152.2	1150.7	1149.2	1147.6	1146.1	1147.6	1149.2	1150.7	1152.2	1153.0
150°	1182.6	1181.7	1180.0	1178.2	1176.5	1174.7	1176.5	1178.2	1180.0	1181.7	1182.6
152.5°	1208.2	1207.4	1205.9	1204.4	1202.8	1201.3	1202.8	1204.4	1205.9	1207.4	1208.2
155°	1231.9	1231.0	1229.3	1227.5	1225.8	1224.0	1225.8	1227.5	1229.3	1231.0	1231.9
157.5°	1251.6	1250.7	1249.0	1247.2	1245.5	1243.7	1245.5	1247.2	1249.0	1250.7	1251.6
160°	1270.3	1269.4	1267.7	1265.9	1264.2	1262.4	1264.2	1265.9	1267.7	1269.4	1270.3
162.5°	1288.1	1287.1	1285.1	1283.2	1281.2	1279.2	1281.2	1283.2	1285.1	1287.1	1288.1
165°	1301.9	1301.0	1299.3	1297.5	1295.8	1294.0	1295.8	1297.5	1299.3	1301.0	1301.9
167.5°	1313.7	1312.7	1310.8	1308.8	1306.9	1304.9	1306.9	1308.8	1310.8	1312.7	1313.7
170°	1322.6	1321.6	1319.6	1317.7	1315.7	1313.7	1315.7	1317.7	1319.6	1321.6	1322.6
172.5°	1328.5	1327.5	1325.6	1323.6	1321.7	1319.7	1321.7	1323.6	1325.6	1327.5	1328.5
175°	1333.5	1332.5	1330.5	1328.6	1326.6	1324.6	1326.6	1328.6	1330.5	1332.5	1333.5
177.5°	1335.4	1334.5	1332.8	1331.0	1329.3	1327.5	1329.3	1331.0	1332.8	1334.5	1335.4
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1486.6	1493.0	1487.8	1484.0	1494.3	1499.5	1499.5	1508.5	1517.5	1525.3	1526.6
5°	1394.9	1405.3	1407.8	1406.5	1422.0	1429.8	1446.5	1455.6	1468.5	1477.5	1487.8
7.5°	1311.1	1325.3	1326.5	1329.1	1352.3	1365.3	1379.4	1402.7	1420.7	1433.6	1445.3
10°	1227.2	1236.2	1245.2	1256.9	1280.1	1302.0	1322.7	1347.2	1370.4	1383.3	1400.1
12.5°	1163.9	1170.4	1180.7	1188.5	1213.0	1232.3	1259.4	1293.0	1326.5	1336.9	1357.5
15°	1098.1	1102.0	1122.7	1130.4	1151.0	1183.3	1200.1	1232.3	1268.5	1287.8	1311.1
17.5°	1022.0	1045.2	1058.1	1067.2	1093.0	1118.8	1145.9	1179.4	1225.9	1244.0	1260.7
20°	967.8	984.6	998.8	1010.4	1033.6	1072.3	1096.8	1123.9	1167.8	1188.5	1213.0
22.5°	920.1	934.3	947.2	960.1	975.5	1010.4	1038.8	1076.2	1120.1	1139.4	1167.8
25°	874.9	889.1	896.8	912.3	933.0	957.5	991.0	1024.6	1068.5	1090.4	1117.5
27.5°	831.0	845.2	859.4	872.3	886.5	909.7	933.0	975.5	1020.7	1046.5	1069.7
30°	793.6	800.1	813.0	827.2	841.3	863.3	890.4	920.1	971.7	994.9	1023.3
32.5°	752.3	763.9	773.0	783.3	801.3	819.4	843.9	881.3	922.6	944.6	975.5
35°	713.6	723.9	730.4	748.4	760.1	779.4	803.9	837.5	872.3	896.8	923.9
37.5°	676.2	686.5	694.2	704.6	720.0	736.8	762.6	787.1	828.4	849.1	880.1
40°	637.5	646.5	655.5	667.1	681.3	702.0	717.5	748.4	782.0	805.2	828.4
42.5°	600.0	605.2	615.5	628.4	642.6	660.7	682.6	707.1	740.7	761.3	782.0
45°	560.0	569.1	580.7	589.7	602.6	620.7	640.0	662.0	695.5	716.2	738.1
47.5°	522.6	529.1	536.8	551.0	567.8	580.7	601.3	622.0	652.9	672.3	692.9
50°	483.9	490.4	502.0	511.0	523.9	540.7	560.0	582.0	611.7	624.6	645.2
52.5°	447.8	450.4	462.0	471.0	483.9	503.3	518.7	538.1	566.5	580.7	601.3
55°	411.6	414.2	420.7	429.7	443.9	459.4	476.2	498.1	522.6	535.5	554.9
57.5°	374.2	376.8	383.3	389.7	403.9	418.1	437.4	455.5	480.0	491.6	509.7
60°	336.8	336.8	343.2	352.3	362.6	375.5	392.3	414.2	432.3	446.5	459.4
62.5°	296.8	300.7	304.5	311.0	322.6	338.1	352.3	367.8	389.7	400.0	411.6
65°	256.8	260.7	268.4	274.9	283.9	294.2	312.3	325.2	342.0	353.6	363.9
67.5°	222.0	225.8	231.0	238.7	245.2	256.8	269.7	282.6	300.7	308.4	316.2
70°	185.8	189.7	193.6	203.9	210.3	219.4	228.4	241.3	256.8	262.0	268.4
72.5°	157.4	158.7	163.9	166.5	175.5	183.2	193.6	201.3	212.9	219.4	224.5
75°	132.9	132.9	134.2	136.8	141.9	147.1	154.8	162.6	172.9	176.8	183.2
77.5°	104.5	108.4	107.1	109.7	112.3	114.8	121.3	126.5	136.8	139.4	141.9
80°	74.8	76.1	80.0	83.9	83.9	87.7	91.6	92.9	99.4	103.2	103.2
82.5°	54.2	55.5	54.2	55.5	56.8	58.1	61.9	67.1	67.1	68.4	71.0
85°	33.6	33.6	34.8	36.1	36.1	34.8	37.4	36.1	37.4	40.0	40.0
87.5°	16.8	15.5	15.5	15.5	15.5	15.5	16.8	15.5	16.8	16.8	16.8
90°	20.2	19.1	18.0	16.9	15.8	14.3	12.7	11.2	9.7	8.9	8.0
92.5°	20.2	19.1	18.0	16.9	15.8	14.5	13.2	11.9	10.6	9.9	10.9
95°	20.2	19.1	18.0	16.9	15.8	24.1	32.5	40.8	49.1	53.3	53.6
97.5°	19.5	19.1	18.6	18.2	17.8	38.6	59.4	80.3	101.1	111.5	110.8
100°	41.0	73.7	106.3	139.0	171.6	170.7	169.9	169.0	168.1	167.7	167.4
102.5°	232.6	232.1	231.7	231.2	230.8	230.4	229.9	229.5	229.0	228.8	228.4
105°	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.9	293.5
107.5°	359.9	359.7	359.4	359.2	359.0	358.6	358.1	357.7	357.2	357.0	357.0
110°	421.4	422.1	422.8	423.4	424.1	423.7	423.2	422.8	422.3	422.1	422.1

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	483.7	484.6	485.5	486.3	487.2	487.0	486.8	486.5	486.3	486.2	485.9
115°	546.8	547.7	548.6	549.4	550.3	550.1	549.9	549.7	549.5	549.4	548.8
117.5°	607.3	608.6	609.9	611.2	612.5	611.6	610.7	609.8	608.9	608.5	608.5
120°	667.9	668.4	668.8	669.3	669.7	669.0	668.4	667.7	667.0	666.7	666.8
122.5°	724.1	724.6	725.0	725.5	725.9	725.7	725.5	725.2	725.0	724.9	724.4
125°	777.6	778.5	779.4	780.2	781.1	781.1	781.1	781.1	781.1	781.1	780.3
127.5°	828.7	829.2	829.6	830.1	830.5	830.7	830.9	831.1	831.3	831.4	830.9
130°	877.1	877.8	878.5	879.1	879.8	879.6	879.4	879.1	878.9	878.8	878.3
132.5°	924.2	924.2	924.2	924.2	924.2	924.8	925.5	926.1	926.8	927.1	926.4
135°	967.7	968.2	968.6	969.1	969.5	969.9	970.4	970.8	971.3	971.5	970.8
137.5°	1010.9	1010.9	1010.9	1010.9	1010.9	1011.3	1011.8	1012.2	1012.7	1012.9	1012.2
140°	1050.2	1049.7	1049.3	1048.8	1048.4	1048.6	1048.8	1049.1	1049.3	1049.4	1049.2
142.5°	1086.9	1086.9	1086.9	1086.9	1086.9	1086.5	1086.0	1085.6	1085.1	1084.9	1084.8
145°	1122.3	1122.1	1121.8	1121.6	1121.4	1121.4	1121.4	1121.4	1121.4	1121.4	1121.2
147.5°	1152.9	1152.7	1152.4	1152.2	1152.0	1151.8	1151.6	1151.3	1151.1	1151.0	1151.0
150°	1182.4	1181.9	1181.5	1181.0	1180.6	1180.2	1179.7	1179.3	1178.8	1178.6	1178.8
152.5°	1208.0	1207.5	1207.1	1206.6	1206.2	1205.8	1205.4	1204.9	1204.5	1204.3	1204.8
155°	1231.6	1230.9	1230.2	1229.6	1228.9	1228.5	1228.0	1227.6	1227.1	1226.9	1227.6
157.5°	1251.3	1250.6	1249.9	1249.3	1248.6	1248.6	1248.6	1248.6	1248.6	1248.6	1248.9
160°	1269.9	1269.0	1268.1	1267.3	1266.4	1266.2	1266.0	1265.7	1265.5	1265.4	1266.1
162.5°	1287.4	1286.1	1284.8	1283.5	1282.2	1282.0	1281.8	1281.5	1281.3	1281.2	1281.9
165°	1301.2	1299.9	1298.6	1297.3	1296.0	1295.8	1295.6	1295.3	1295.1	1295.0	1295.7
167.5°	1312.9	1311.4	1309.9	1308.3	1306.8	1306.6	1306.4	1306.1	1305.9	1305.8	1306.5
170°	1321.7	1320.0	1318.2	1316.5	1314.7	1314.5	1314.3	1314.0	1313.8	1313.7	1314.5
172.5°	1327.7	1326.2	1324.7	1323.1	1321.6	1321.2	1320.8	1320.3	1319.9	1319.7	1320.5
175°	1332.6	1330.9	1329.1	1327.4	1325.6	1325.4	1325.2	1324.9	1324.7	1324.6	1325.3
177.5°	1334.6	1333.1	1331.6	1330.0	1328.5	1328.3	1328.1	1327.8	1327.6	1327.5	1328.2
180°	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5	1330.5

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1571.7	1571.7	1571.7	1571.7
2.5°	1535.6	1547.2	1558.8	1573.0
5°	1504.6	1525.3	1547.2	1567.8
7.5°	1471.1	1500.7	1529.1	1558.8
10°	1433.6	1471.1	1503.3	1544.6
12.5°	1392.4	1432.4	1477.5	1524.0
15°	1351.1	1401.4	1449.1	1502.0
17.5°	1312.3	1360.1	1413.0	1476.2
20°	1265.9	1318.8	1378.2	1445.3
22.5°	1216.9	1274.9	1339.4	1411.7
25°	1175.6	1234.9	1296.9	1373.0
27.5°	1130.4	1192.3	1253.0	1334.3
30°	1078.8	1145.9	1207.8	1291.7
32.5°	1029.7	1096.8	1165.2	1244.0
35°	982.0	1047.8	1116.2	1196.2
37.5°	936.8	996.2	1063.3	1135.6
40°	894.3	948.5	1007.8	1073.6
42.5°	840.1	903.3	958.8	1006.5
45°	793.6	845.2	896.8	935.5
47.5°	739.4	791.0	834.9	865.9
50°	694.2	735.5	771.7	798.8
52.5°	640.0	678.8	708.4	729.1
55°	587.1	620.7	646.5	660.7
57.5°	539.4	561.3	580.7	593.6
60°	486.5	503.3	520.0	534.2
62.5°	429.7	447.8	456.8	472.3
65°	379.4	391.0	405.2	410.4
67.5°	330.3	336.8	345.8	356.2
70°	278.7	282.6	291.6	305.8
72.5°	233.6	237.4	243.9	249.0
75°	185.8	189.7	194.9	200.0
77.5°	145.8	147.1	149.7	154.8
80°	105.8	109.7	112.3	113.6
82.5°	73.6	74.8	74.8	76.1
85°	46.5	43.9	43.9	45.2
87.5°	16.8	19.4	19.4	21.9
90°	6.3	4.5	2.8	1.0
92.5°	12.8	14.8	16.7	18.7
95°	54.3	54.9	55.6	56.2
97.5°	109.5	108.2	106.8	105.5
100°	166.7	166.0	165.4	164.7
102.5°	227.5	226.6	225.8	224.9
105°	292.6	291.7	290.9	290.0
107.5°	357.0	357.0	357.0	357.0
110°	422.1	422.1	422.1	422.1

TEST NUMBER: P1035690

CATALOG NUMBER: S125RDIW-B1090D1050UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	485.2	484.6	483.9	483.3
115°	547.7	546.6	545.5	544.4
117.5°	608.5	608.5	608.5	608.5
120°	667.0	667.3	667.5	667.7
122.5°	723.3	722.2	721.1	720.0
125°	778.8	777.3	775.7	774.2
127.5°	829.8	828.7	827.6	826.5
130°	877.2	876.1	875.0	873.9
132.5°	925.1	923.8	922.5	921.2
135°	969.5	968.2	966.9	965.6
137.5°	1010.9	1009.6	1008.3	1007.0
140°	1048.7	1048.3	1047.8	1047.4
142.5°	1084.6	1084.3	1084.1	1083.9
145°	1120.7	1120.3	1119.8	1119.4
147.5°	1151.0	1151.0	1151.0	1151.0
150°	1179.3	1179.7	1180.2	1180.6
152.5°	1205.9	1207.0	1208.1	1209.2
155°	1228.9	1230.2	1231.6	1232.9
157.5°	1249.6	1250.3	1250.9	1251.6
160°	1267.4	1268.7	1270.0	1271.3
162.5°	1283.2	1284.5	1285.8	1287.1
165°	1297.0	1298.3	1299.6	1300.9
167.5°	1307.8	1309.1	1310.5	1311.8
170°	1316.0	1317.5	1319.1	1320.6
172.5°	1322.0	1323.5	1325.1	1326.6
175°	1326.6	1327.9	1329.2	1330.5
177.5°	1329.5	1330.8	1332.2	1333.5
180°	1330.5	1330.5	1330.5	1330.5

(END OF REPORT)