

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983485

Luminaire Tested: S125IW-B470UB2750-4F0-XX-W2A_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B470UB2750-4F0-XX-W2A_2700K
Description: Define 5 Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1880.0 lumens
Efficiency: N/A
Efficacy: 142.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983485

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P983485

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6				
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 0°

Luminance: 0 cd/sqm

TEST NUMBER: P983485

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.9	0.0
90°-100°	20.8	1.1
100°-110°	138.1	7.3
110°-120°	248.6	13.2
120°-130°	319.1	17.0
130°-140°	343.2	18.3
140°-150°	322.1	17.1
150°-160°	260.6	13.9
160°-170°	168.5	9.0
170°-180°	58.1	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.9	0.0
90°-120°	407.4	21.7
90°-150°	1391.9	74.0
90°-180°	1879.0	99.9
0°-180°	1880.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	7	10	11	1
95°	26	24	7	10	10	32
105°	133	135	135	135	135	141
115°	250	253	253	251	248	248
125°	356	359	359	357	356	318
135°	444	447	446	445	442	342
145°	515	516	516	516	513	322
155°	567	564	565	566	563	261
165°	598	595	596	599	595	169
175°	612	609	610	613	609	58
180°	612	612	612	612	612	

TEST NUMBER: P983485

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.5	4.1	7.3	9.5	10.9
92.5°	8.6	4.5	7.3	9.5	10.0
95°	25.8	24.5	7.3	9.5	9.5
97.5°	48.5	51.2	8.2	9.1	9.5
100°	75.7	77.1	78.9	11.3	9.5
102.5°	103.4	105.2	106.1	107.0	68.9
105°	133.3	135.1	135.1	135.1	134.7
107.5°	164.2	164.2	165.1	165.5	163.7
110°	194.1	194.1	195.0	193.6	194.1

TEST NUMBER: P983485

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	222.2	223.6	224.0	222.2	221.3
115°	250.3	252.6	253.0	251.2	248.5
117.5°	279.8	279.8	281.6	278.9	278.0
120°	307.0	306.5	307.9	307.0	304.7
122.5°	331.0	333.3	333.8	332.8	330.1
125°	356.0	359.1	359.1	357.3	356.0
127.5°	380.0	382.3	381.8	380.9	377.3
130°	401.8	404.0	404.5	403.1	400.9
132.5°	423.5	426.3	424.9	424.9	422.6
135°	443.9	446.7	445.8	444.9	442.1
137.5°	463.0	465.7	464.8	464.8	462.5
140°	481.6	482.5	482.0	482.9	480.2
142.5°	498.4	498.8	499.7	499.7	497.0
145°	514.7	515.6	515.6	516.0	513.3
147.5°	529.2	529.2	529.6	530.1	526.9
150°	542.8	541.9	542.8	543.7	540.1
152.5°	555.9	553.7	554.6	555.5	552.3
155°	566.8	564.1	565.0	566.4	562.8
157.5°	575.4	574.1	574.1	575.4	571.8
160°	584.5	581.8	582.3	584.1	580.4
162.5°	591.8	589.1	589.5	592.2	588.1
165°	598.1	595.4	595.9	598.6	594.9
167.5°	603.1	600.4	600.8	604.0	599.9
170°	607.2	604.0	604.5	608.1	604.0
172.5°	609.9	606.7	607.6	610.8	606.7
175°	611.7	609.0	609.5	613.1	609.0
177.5°	613.1	610.4	610.8	614.0	610.4
180°	611.7	611.7	611.7	611.7	611.7

(END OF REPORT)