

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983487

Luminaire Tested: S125IW-B470UB2750-4F0-XX-W2A_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983487
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B470UB2750-4F0-XX-W2A_3500K
Description: Define 5 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1904.0 lumens
Efficiency: N/A
Efficacy: 144.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983487

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P983487

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983487

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.9	0.0
90°-100°	21.0	1.1
100°-110°	139.8	7.3
110°-120°	251.8	13.2
120°-130°	323.2	17.0
130°-140°	347.6	18.3
140°-150°	326.2	17.1
150°-160°	263.9	13.9
160°-170°	170.7	9.0
170°-180°	58.9	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.9	0.0
90°-120°	412.6	21.7
90°-150°	1409.7	74.0
90°-180°	1903.0	99.9
0°-180°	1904.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	7	10	11	1
95°	26	25	7	10	10	32
105°	135	137	137	137	136	143
115°	254	256	256	254	252	251
125°	360	364	364	362	360	322
135°	450	452	451	450	448	347
145°	521	522	522	523	520	326
155°	574	571	572	574	570	265
165°	606	603	604	606	602	171
175°	620	617	617	621	617	59
180°	620	620	620	620	620	

TEST NUMBER: P983487

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.5	4.1	7.3	9.6	11.0
92.5°	8.7	4.6	7.3	9.6	10.1
95°	26.2	24.8	7.3	9.6	9.6
97.5°	49.1	51.9	8.3	9.2	9.6
100°	76.7	78.1	79.9	11.5	9.6
102.5°	104.7	106.5	107.5	108.4	69.8
105°	135.0	136.9	136.9	136.9	136.4
107.5°	166.3	166.3	167.2	167.6	165.8
110°	196.6	196.6	197.5	196.1	196.6

TEST NUMBER: P983487

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.0	226.4	226.9	225.0	224.1
115°	253.5	255.8	256.3	254.4	251.7
117.5°	283.4	283.4	285.2	282.4	281.5
120°	310.9	310.5	311.8	310.9	308.6
122.5°	335.3	337.6	338.0	337.1	334.3
125°	360.5	363.7	363.7	361.9	360.5
127.5°	384.9	387.2	386.7	385.8	382.1
130°	406.9	409.2	409.7	408.3	406.0
132.5°	428.9	431.7	430.3	430.3	428.0
135°	449.6	452.4	451.4	450.5	447.8
137.5°	468.9	471.7	470.7	470.7	468.4
140°	487.7	488.6	488.2	489.1	486.4
142.5°	504.7	505.2	506.1	506.1	503.3
145°	521.3	522.2	522.2	522.6	519.9
147.5°	536.0	536.0	536.4	536.9	533.7
150°	549.7	548.8	549.7	550.6	547.0
152.5°	563.0	560.8	561.7	562.6	559.4
155°	574.1	571.3	572.2	573.6	569.9
157.5°	582.8	581.4	581.4	582.8	579.1
160°	592.0	589.2	589.7	591.5	587.8
162.5°	599.3	596.6	597.0	599.8	595.7
165°	605.8	603.0	603.5	606.2	602.5
167.5°	610.8	608.1	608.5	611.7	607.6
170°	614.9	611.7	612.2	615.9	611.7
172.5°	617.7	614.5	615.4	618.6	614.5
175°	619.5	616.8	617.2	620.9	616.8
177.5°	620.9	618.2	618.6	621.8	618.2
180°	619.5	619.5	619.5	619.5	619.5

(END OF REPORT)