

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035704

Luminaire Tested: S125RDIW-B1090D1340UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035704
REPORT IS A COMBINATION OF REPORTS P1005992 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1340UB35-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9609.0 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 88.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035704

CATALOG NUMBER: S125RDIW-B1090D1340UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035704

CATALOG NUMBER: S125RDIW-B1090D1340UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11433	11433	11433
5°	11434	11148	11166
10°	11323	10867	10771
15°	11162	10474	10253
20°	10964	10001	9708
25°	10737	9539	9125
30°	10458	9031	8512
35°	10174	8515	7861
40°	9903	7985	7225
45°	9579	7414	6560
50°	9250	6807	5881
55°	8867	6209	5179
60°	8476	5525	4451
65°	8009	4762	3665
70°	7466	3876	2884
75°	6714	2915	2102
80°	5662	1887	1418
85°	4237	1013	798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9579 cd/sqm

TEST NUMBER: P1035704

CATALOG NUMBER: S125RDIW-B1090D1340UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.9	1.7
10°-20°	469.3	4.9
20°-30°	680.5	7.1
30°-40°	775.3	8.1
40°-50°	755.7	7.9
50°-60°	636.0	6.6
60°-70°	445.7	4.6
70°-80°	228.5	2.4
80°-90°	59.6	0.6
90°-100°	59.5	0.6
100°-110°	396.0	4.1
110°-120°	713.2	7.4
120°-130°	915.4	9.5
130°-140°	984.6	10.2
140°-150°	924.1	9.6
150°-160°	747.5	7.8
160°-170°	483.4	5.0
170°-180°	166.7	1.7
0°-30°	1317.8	13.7
0°-40°	2093.2	21.8
0°-60°	3484.9	36.3
0°-90°	4218.6	43.9
90°-120°	1168.8	12.2
90°-150°	3992.8	41.6
90°-180°	5390.0	56.1
0°-180°	9609.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1784	1784	1784	1784	1784	
5°	1782	1776	1762	1775	1772	169
15°	1694	1686	1658	1656	1644	478
25°	1536	1516	1466	1449	1434	707
35°	1324	1291	1230	1191	1173	829
45°	1084	1044	970	916	896	836
55°	822	779	704	643	621	735
65°	557	511	439	386	365	551
75°	296	256	200	170	160	313
85°	74	50	43	42	40	81
90°	1	12	21	27	31	8
95°	74	70	21	27	27	91
105°	382	388	388	388	386	405
115°	718	725	726	721	713	712
125°	1021	1030	1030	1025	1021	912
135°	1274	1281	1279	1276	1268	982
145°	1476	1479	1479	1480	1472	923
155°	1626	1618	1621	1625	1614	749
165°	1716	1708	1709	1717	1707	485
175°	1755	1747	1748	1759	1747	167
180°	1755	1755	1755	1755	1755	

TEST NUMBER: P1035704

CATALOG NUMBER: S125RDIW-B1090D1340UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.4	1784.4	1784.4	1784.4	1784.4
2.5°	1788.5	1784.4	1771.0	1784.4	1783.1
5°	1781.7	1776.4	1761.5	1775.0	1772.3
7.5°	1768.3	1762.9	1745.4	1756.1	1753.4
10°	1748.1	1744.0	1725.1	1729.2	1725.1
12.5°	1725.1	1719.7	1692.8	1695.5	1688.8
15°	1694.1	1686.1	1657.8	1656.4	1644.3
17.5°	1661.8	1649.7	1616.0	1609.2	1599.8
20°	1622.7	1609.2	1566.1	1559.4	1547.2
22.5°	1579.6	1566.1	1520.3	1505.5	1496.0
25°	1536.5	1516.2	1466.4	1448.8	1434.0
27.5°	1487.9	1463.7	1411.1	1388.2	1373.4
30°	1434.0	1408.4	1351.8	1320.8	1308.7
32.5°	1381.5	1350.5	1292.5	1257.5	1241.3
35°	1323.5	1291.2	1230.5	1191.4	1172.6
37.5°	1268.2	1229.2	1167.2	1121.3	1102.5
40°	1208.9	1168.5	1103.8	1052.6	1036.4
42.5°	1146.9	1105.2	1037.8	989.3	963.7
45°	1083.6	1044.5	970.4	916.5	896.3
47.5°	1017.6	977.1	903.0	847.7	824.8
50°	955.6	911.1	834.3	777.7	757.4
52.5°	888.2	842.4	770.9	708.9	688.7
55°	822.1	779.0	703.5	642.9	621.3
57.5°	754.7	708.9	636.1	576.8	558.0
60°	690.1	642.9	570.1	510.8	490.6
62.5°	621.3	576.8	502.7	448.8	428.6
65°	556.6	510.8	439.4	385.5	365.2
67.5°	491.9	446.1	377.4	326.2	310.0
70°	425.9	380.1	312.7	270.9	254.7
72.5°	361.2	316.7	254.7	217.0	207.6
75°	296.5	256.1	199.5	169.8	160.4
77.5°	230.5	198.1	150.9	128.0	120.0
80°	175.2	142.9	105.1	93.0	90.3
82.5°	121.3	93.0	70.1	66.0	64.7
85°	74.1	49.9	43.1	41.8	40.4
87.5°	31.0	21.6	20.2	20.2	18.9
90°	1.3	11.7	20.8	27.3	31.2
92.5°	24.7	13.0	20.8	27.3	28.6
95°	74.1	70.2	20.8	27.3	27.3
97.5°	139.2	147.0	23.4	26.0	27.3
100°	217.2	221.1	226.3	32.5	27.3
102.5°	296.6	301.8	304.4	307.0	197.7
105°	382.4	387.6	387.6	387.6	386.3
107.5°	470.9	470.9	473.5	474.8	469.6
110°	556.8	556.8	559.4	555.5	556.8

TEST NUMBER: P1035704

CATALOG NUMBER: S125RDIW-B1090D1340UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	637.4	641.3	642.6	637.4	634.8
115°	718.1	724.6	725.9	720.7	712.8
117.5°	802.6	802.6	807.8	800.0	797.4
120°	880.7	879.4	883.3	880.7	874.2
122.5°	949.6	956.1	957.4	954.8	947.0
125°	1021.1	1030.3	1030.3	1025.0	1021.1
127.5°	1090.1	1096.6	1095.3	1092.7	1082.3
130°	1152.5	1159.0	1160.3	1156.4	1149.9
132.5°	1215.0	1222.8	1218.9	1218.9	1212.4
135°	1273.5	1281.3	1278.7	1276.1	1268.3
137.5°	1328.1	1335.9	1333.3	1333.3	1326.8
140°	1381.5	1384.1	1382.8	1385.4	1377.6
142.5°	1429.6	1430.9	1433.5	1433.5	1425.7
145°	1476.4	1479.0	1479.0	1480.3	1472.5
147.5°	1518.1	1518.1	1519.4	1520.7	1511.6
150°	1557.1	1554.5	1557.1	1559.7	1549.3
152.5°	1594.8	1588.3	1590.9	1593.5	1584.4
155°	1626.0	1618.2	1620.8	1624.7	1614.3
157.5°	1650.7	1646.8	1646.8	1650.7	1640.3
160°	1676.8	1669.0	1670.3	1675.5	1665.1
162.5°	1697.6	1689.8	1691.1	1698.9	1687.2
165°	1715.8	1708.0	1709.3	1717.1	1706.7
167.5°	1730.1	1722.3	1723.6	1732.7	1721.0
170°	1741.8	1732.7	1734.0	1744.4	1732.7
172.5°	1749.6	1740.5	1743.1	1752.2	1740.5
175°	1754.8	1747.0	1748.3	1758.7	1747.0
177.5°	1758.7	1750.9	1752.2	1761.3	1750.9
180°	1754.8	1754.8	1754.8	1754.8	1754.8

(END OF REPORT)