

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035730

Luminaire Tested: S125RDIW-B1090D1560UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035730
REPORT IS A COMBINATION OF REPORTS P1006048 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1560UB50-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10125.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035730

CATALOG NUMBER: S125RDIW-B1090D1560UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035730

CATALOG NUMBER: S125RDIW-B1090D1560UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	84	87	83	80	77	68	66	64	54	53	52	42	41	40
2	87	80	74	69	79	73	68	64	60	56	53	48	46	43	37	35	34
3	80	70	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29
4	73	62	55	49	66	57	50	45	47	42	38	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	37	32	52	41	35	30	35	29	25	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10945	10945	10945
5°	10946	10672	10689
10°	10839	10403	10312
15°	10686	10027	9815
20°	10496	9574	9294
25°	10279	9132	8735
30°	10012	8646	8148
35°	9739	8152	7525
40°	9481	7645	6917
45°	9170	7097	6279
50°	8855	6516	5630
55°	8488	5944	4958
60°	8114	5290	4261
65°	7668	4558	3510
70°	7147	3710	2762
75°	6426	2791	2012
80°	5419	1806	1356
85°	4059	971	764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9170 cd/sqm

TEST NUMBER: P1035730

CATALOG NUMBER: S125RDIW-B1090D1560UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	1.6
10°-20°	449.3	4.4
20°-30°	651.5	6.4
30°-40°	742.2	7.3
40°-50°	723.5	7.1
50°-60°	608.8	6.0
60°-70°	426.7	4.2
70°-80°	218.7	2.2
80°-90°	57.5	0.6
90°-100°	67.2	0.7
100°-110°	447.2	4.4
110°-120°	805.2	8.0
120°-130°	1033.6	10.2
130°-140°	1111.6	11.0
140°-150°	1043.3	10.3
150°-160°	843.9	8.3
160°-170°	545.8	5.4
170°-180°	188.2	1.9
0°-30°	1261.6	12.5
0°-40°	2003.8	19.8
0°-60°	3336.1	32.9
0°-90°	4038.9	39.9
90°-120°	1319.6	13.0
90°-150°	4508.1	44.5
90°-180°	6086.0	60.1
0°-180°	10125.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1708	1708	1708	1708	1708	
5°	1706	1700	1686	1699	1697	162
15°	1622	1614	1587	1586	1574	457
25°	1471	1452	1404	1387	1373	677
35°	1267	1236	1178	1141	1122	793
45°	1037	1000	929	877	858	800
55°	787	746	674	615	595	704
65°	533	489	421	369	350	528
75°	284	245	191	163	154	300
85°	71	48	41	40	39	78
90°	2	13	24	31	35	8
95°	84	79	24	31	31	103
105°	432	438	438	438	436	457
115°	811	818	820	814	805	804
125°	1153	1163	1163	1157	1153	1030
135°	1438	1447	1444	1441	1432	1109
145°	1667	1670	1670	1671	1663	1043
155°	1836	1827	1830	1834	1823	846
165°	1937	1928	1930	1939	1927	547
175°	1981	1972	1974	1986	1972	189
180°	1981	1981	1981	1981	1981	

TEST NUMBER: P1035730

CATALOG NUMBER: S125RDIW-B1090D1560UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1708.3	1708.3	1708.3	1708.3	1708.3
2.5°	1712.1	1708.3	1695.4	1708.3	1707.0
5°	1705.7	1700.5	1686.3	1699.2	1696.6
7.5°	1692.8	1687.6	1670.8	1681.2	1678.6
10°	1673.4	1669.5	1651.5	1655.4	1651.5
12.5°	1651.5	1646.3	1620.5	1623.1	1616.6
15°	1621.8	1614.1	1587.0	1585.7	1574.1
17.5°	1590.8	1579.2	1547.0	1540.5	1531.5
20°	1553.4	1540.5	1499.2	1492.8	1481.2
22.5°	1512.1	1499.2	1455.4	1441.2	1432.1
25°	1470.9	1451.5	1403.8	1387.0	1372.8
27.5°	1424.4	1401.2	1350.9	1328.9	1314.7
30°	1372.8	1348.3	1294.1	1264.4	1252.8
32.5°	1322.5	1292.8	1237.3	1203.8	1188.3
35°	1267.0	1236.0	1178.0	1140.6	1122.5
37.5°	1214.1	1176.7	1117.3	1073.5	1055.4
40°	1157.3	1118.6	1056.7	1007.7	992.2
42.5°	1098.0	1058.0	993.5	947.0	922.5
45°	1037.3	999.9	929.0	877.4	858.0
47.5°	974.1	935.4	864.4	811.6	789.6
50°	914.8	872.2	798.6	744.5	725.1
52.5°	850.3	806.4	738.0	678.7	659.3
55°	787.0	745.7	673.5	615.4	594.8
57.5°	722.5	678.7	609.0	552.2	534.2
60°	660.6	615.4	545.8	489.0	469.6
62.5°	594.8	552.2	481.3	429.6	410.3
65°	532.9	489.0	420.6	369.0	349.7
67.5°	470.9	427.1	361.3	312.2	296.8
70°	407.7	363.8	299.3	259.3	243.9
72.5°	345.8	303.2	243.9	207.7	198.7
75°	283.8	245.1	191.0	162.6	153.5
77.5°	220.6	189.7	144.5	122.6	114.8
80°	167.7	136.8	100.6	89.0	86.4
82.5°	116.1	89.0	67.1	63.2	61.9
85°	71.0	47.7	41.3	40.0	38.7
87.5°	29.7	20.6	19.4	19.4	18.1
90°	1.5	13.2	23.5	30.8	35.2
92.5°	27.9	14.7	23.5	30.8	32.3
95°	83.7	79.3	23.5	30.8	30.8
97.5°	157.2	166.0	26.4	29.4	30.8
100°	245.3	249.7	255.6	36.7	30.8
102.5°	334.9	340.7	343.7	346.6	223.2
105°	431.8	437.7	437.7	437.7	436.2
107.5°	531.7	531.7	534.6	536.1	530.2
110°	628.6	628.6	631.5	627.1	628.6

TEST NUMBER: P1035730

CATALOG NUMBER: S125RDIW-B1090D1560UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.7	724.1	725.5	719.7	716.7
115°	810.7	818.1	819.5	813.7	804.8
117.5°	906.2	906.2	912.1	903.3	900.3
120°	994.3	992.8	997.2	994.3	987.0
122.5°	1072.2	1079.5	1081.0	1078.0	1069.2
125°	1152.9	1163.2	1163.2	1157.3	1152.9
127.5°	1230.8	1238.1	1236.6	1233.7	1222.0
130°	1301.3	1308.6	1310.1	1305.7	1298.3
132.5°	1371.8	1380.6	1376.2	1376.2	1368.8
135°	1437.9	1446.7	1443.7	1440.8	1432.0
137.5°	1499.5	1508.4	1505.4	1505.4	1498.1
140°	1559.8	1562.7	1561.2	1564.2	1555.4
142.5°	1614.1	1615.6	1618.5	1618.5	1609.7
145°	1667.0	1669.9	1669.9	1671.4	1662.6
147.5°	1714.0	1714.0	1715.4	1716.9	1706.6
150°	1758.0	1755.1	1758.0	1761.0	1749.2
152.5°	1800.6	1793.3	1796.2	1799.2	1788.9
155°	1835.9	1827.1	1830.0	1834.4	1822.7
157.5°	1863.8	1859.4	1859.4	1863.8	1852.0
160°	1893.2	1884.3	1885.8	1891.7	1879.9
162.5°	1916.7	1907.8	1909.3	1918.1	1904.9
165°	1937.2	1928.4	1929.9	1938.7	1926.9
167.5°	1953.4	1944.6	1946.0	1956.3	1943.1
170°	1966.6	1956.3	1957.8	1969.5	1956.3
172.5°	1975.4	1965.1	1968.1	1978.3	1965.1
175°	1981.3	1972.5	1973.9	1985.7	1972.5
177.5°	1985.7	1976.9	1978.3	1988.6	1976.9
180°	1981.3	1981.3	1981.3	1981.3	1981.3

(END OF REPORT)