

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983491

Luminaire Tested: S125IW-B470UB30-4F0-XX-W2A

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983491
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B470UB30-4F0-XX-W2A
Description: Define 5 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1896.0 lumens
Efficiency: N/A
Efficacy: 143.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983491

CATALOG NUMBER: S125IW-B470UB30-4F0-XX-W2A

Luminous Intensity Polar Plot



TEST NUMBER: P983491

CATALOG NUMBER: S125IW-B470UB30-4F0-XX-W2A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983491

CATALOG NUMBER: S125IW-B470UB30-4F0-XX-W2A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.9	0.0
90°-100°	20.9	1.1
100°-110°	139.2	7.3
110°-120°	250.7	13.2
120°-130°	321.8	17.0
130°-140°	346.1	18.3
140°-150°	324.9	17.1
150°-160°	262.8	13.9
160°-170°	170.0	9.0
170°-180°	58.6	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.9	0.0
90°-120°	410.9	21.7
90°-150°	1403.8	74.0
90°-180°	1895.0	99.9
0°-180°	1896.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	7	10	11	1
95°	26	25	7	10	10	32
105°	134	136	136	136	136	142
115°	252	255	255	253	251	250
125°	359	362	362	360	359	321
135°	448	450	450	449	446	345
145°	519	520	520	520	518	325
155°	572	569	570	571	568	263
165°	603	600	601	604	600	170
175°	617	614	615	618	614	59
180°	617	617	617	617	617	

TEST NUMBER: P983491

CATALOG NUMBER: S125IW-B470UB30-4F0-XX-W2A

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.5	4.1	7.3	9.6	11.0
92.5°	8.7	4.6	7.3	9.6	10.1
95°	26.1	24.7	7.3	9.6	9.6
97.5°	48.9	51.7	8.2	9.1	9.6
100°	76.4	77.7	79.6	11.4	9.6
102.5°	104.3	106.1	107.0	107.9	69.5
105°	134.5	136.3	136.3	136.3	135.8
107.5°	165.6	165.6	166.5	166.9	165.1
110°	195.7	195.7	196.6	195.3	195.7

TEST NUMBER: P983491

CATALOG NUMBER: S125IW-B470UB30-4F0-XX-W2A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	224.1	225.5	225.9	224.1	223.2
115°	252.4	254.7	255.2	253.4	250.6
117.5°	282.2	282.2	284.0	281.3	280.3
120°	309.6	309.2	310.5	309.6	307.3
122.5°	333.8	336.1	336.6	335.7	332.9
125°	359.0	362.2	362.2	360.4	359.0
127.5°	383.2	385.5	385.1	384.2	380.5
130°	405.2	407.5	407.9	406.6	404.3
132.5°	427.1	429.9	428.5	428.5	426.2
135°	447.7	450.5	449.6	448.6	445.9
137.5°	466.9	469.7	468.8	468.8	466.5
140°	485.7	486.6	486.1	487.1	484.3
142.5°	502.6	503.1	504.0	504.0	501.2
145°	519.1	520.0	520.0	520.4	517.7
147.5°	533.7	533.7	534.2	534.6	531.4
150°	547.4	546.5	547.4	548.3	544.7
152.5°	560.7	558.4	559.3	560.2	557.0
155°	571.7	568.9	569.8	571.2	567.5
157.5°	580.3	579.0	579.0	580.3	576.7
160°	589.5	586.7	587.2	589.0	585.4
162.5°	596.8	594.1	594.5	597.3	593.2
165°	603.2	600.5	600.9	603.7	600.0
167.5°	608.2	605.5	606.0	609.2	605.0
170°	612.4	609.2	609.6	613.3	609.2
172.5°	615.1	611.9	612.8	616.0	611.9
175°	616.9	614.2	614.6	618.3	614.2
177.5°	618.3	615.6	616.0	619.2	615.6
180°	616.9	616.9	616.9	616.9	616.9

(END OF REPORT)